

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925663

Luminaire Tested: DFN2DIP-SQ3F0-100D060US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925663
REPORT IS A COMBINATION OF REPORTS P901430 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D060US950-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13775.7 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 143.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925663
CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P925663

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	55	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	48	43			43
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37			37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	23	21	19			19
10	50	38	31	26	46	36	29	25	32	27	23	29	24	21	25	22	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4518	4518	4518
5°	4522	4443	4473
10°	4474	4353	4326
15°	4410	4206	4100
20°	4326	4005	3822
25°	4239	3780	3555
30°	4124	3550	3216
35°	4011	3303	2918
40°	3896	3047	2577
45°	3763	2764	2268
50°	3625	2478	1966
55°	3480	2173	1676
60°	3313	1855	1378
65°	3119	1532	1238
70°	2885	1230	1119
75°	2590	1078	1014
80°	2165	895	875
85°	1468	583	648

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3763 cd/sqm



TEST NUMBER: P925663

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.5	2.7
10°-20°	1014.4	7.4
20°-30°	1424.2	10.3
30°-40°	1552.5	11.3
40°-50°	1426.9	10.4
50°-60°	1120.6	8.1
60°-70°	729.4	5.3
70°-80°	375.5	2.7
80°-90°	99.2	0.7
90°-100°	63.7	0.5
100°-110°	237.5	1.7
110°-120°	629.8	4.6
120°-130°	1044.5	7.6
130°-140°	1109.5	8.1
140°-150°	1031.2	7.5
150°-160°	829.1	6.0
160°-170°	534.2	3.9
170°-180°	183.9	1.3
0°-30°	2808.2	20.4
0°-40°	4360.7	31.7
0°-60°	6908.2	50.1
0°-90°	8112.4	58.9
90°-120°	930.9	6.8
90°-150°	4116.2	29.9
90°-180°	5663.0	41.1
0°-180°	13775.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3943	3943	3943	3943	3943	
5°	3943	3925	3878	3911	3900	374
15°	3750	3711	3590	3522	3486	1057
25°	3404	3290	3054	2908	2854	1566
35°	2933	2751	2437	2212	2134	1836
45°	2398	2159	1784	1531	1445	1852
55°	1823	1545	1160	946	878	1629
65°	1231	942	621	500	489	1221
75°	656	407	285	260	257	694
85°	153	78	68	68	68	176
90°	1	17	28	35	38	13
95°	91	45	54	62	60	108
105°	425	467	85	101	106	454
115°	804	828	862	215	115	791
125°	1136	1155	1181	1191	1195	1014
135°	1406	1429	1441	1455	1452	1086
145°	1631	1630	1654	1663	1656	1020
155°	1796	1784	1800	1809	1798	828
165°	1893	1884	1888	1898	1888	535
175°	1936	1926	1929	1939	1925	184
180°	1932	1932	1932	1932	1932	



TEST NUMBER: P925663

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3942.9	3942.9	3942.9	3942.9	3942.9
2.5°	3960.6	3942.9	3903.5	3939.4	3932.3
5°	3942.9	3925.0	3878.5	3910.7	3900.0
7.5°	3910.7	3889.5	3839.5	3853.5	3835.7
10°	3867.9	3842.9	3771.7	3760.8	3739.6
12.5°	3814.6	3782.3	3685.8	3664.6	3625.2
15°	3750.2	3710.8	3589.6	3521.9	3486.3
17.5°	3675.2	3618.0	3468.2	3389.8	3332.6
20°	3589.6	3518.1	3339.8	3250.9	3172.0
22.5°	3496.9	3414.7	3207.6	3086.6	3033.1
25°	3404.2	3289.9	3054.3	2908.2	2854.5
27.5°	3293.6	3172.0	2911.6	2743.9	2661.8
30°	3175.9	3039.9	2754.5	2572.8	2476.3
32.5°	3061.6	2897.2	2605.0	2390.7	2301.3
35°	2933.2	2751.1	2437.3	2212.4	2133.6
37.5°	2808.3	2611.8	2280.2	2033.7	1944.7
40°	2676.2	2462.3	2115.9	1862.6	1769.9
42.5°	2540.6	2312.3	1952.0	1687.7	1598.7
45°	2397.9	2158.6	1784.3	1530.6	1445.0
47.5°	2262.4	2009.1	1623.7	1370.0	1291.7
50°	2112.4	1859.2	1466.6	1220.2	1145.6
52.5°	1965.9	1698.3	1316.7	1081.2	1013.4
55°	1823.2	1545.0	1159.6	945.7	877.9
57.5°	1677.1	1391.6	1020.7	820.7	763.6
60°	1527.2	1241.7	874.2	692.4	635.3
62.5°	1381.0	1095.6	749.2	578.1	549.7
65°	1231.1	941.9	620.9	499.7	488.7
67.5°	1088.4	799.2	499.7	438.7	428.2
70°	938.4	660.3	413.7	378.2	363.9
72.5°	795.7	531.5	346.0	317.6	310.4
75°	656.4	406.6	285.4	260.4	257.0
77.5°	517.5	288.9	224.9	210.5	203.3
80°	388.8	207.1	171.1	157.1	157.1
82.5°	271.0	139.3	117.7	110.6	110.6
85°	153.3	78.3	67.7	67.7	67.7
87.5°	57.1	28.4	28.4	25.0	25.0
90°	1.3	16.8	27.9	35.0	37.7
92.5°	35.0	29.4	33.5	36.3	37.7
95°	90.8	44.6	54.5	61.6	60.1
97.5°	163.5	48.9	71.2	75.6	76.9
100°	247.5	55.9	79.7	90.8	93.6
102.5°	339.6	337.0	82.5	97.8	102.1
105°	424.9	466.9	85.3	100.6	106.3
107.5°	524.2	559.0	88.1	103.4	109.0
110°	619.3	648.5	244.7	104.9	110.4



TEST NUMBER: P925663

CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	708.7	733.8	710.1	107.5	111.9
115°	803.7	827.5	862.5	215.3	114.7
117.5°	886.2	914.1	938.0	738.0	371.8
120°	978.5	999.4	1024.7	1041.4	852.7
122.5°	1056.7	1079.1	1107.1	1115.4	1116.9
125°	1136.4	1154.6	1181.1	1191.0	1195.1
127.5°	1209.1	1228.7	1249.7	1263.7	1265.0
130°	1277.6	1300.0	1315.3	1330.7	1329.4
132.5°	1347.5	1365.7	1381.0	1393.6	1392.3
135°	1406.3	1428.7	1441.1	1455.2	1452.4
137.5°	1467.6	1484.4	1498.5	1512.5	1508.4
140°	1527.7	1539.1	1554.4	1566.9	1560.0
142.5°	1578.2	1588.0	1606.2	1617.2	1610.3
145°	1631.3	1629.8	1653.6	1663.4	1656.4
147.5°	1677.3	1673.1	1696.9	1703.8	1698.4
150°	1722.2	1712.3	1734.8	1743.1	1736.1
152.5°	1759.8	1748.7	1769.6	1778.1	1768.2
155°	1796.2	1783.7	1800.5	1808.8	1797.6
157.5°	1825.6	1814.4	1827.0	1836.8	1825.6
160°	1850.8	1842.3	1850.8	1859.1	1849.3
162.5°	1873.0	1864.7	1871.7	1881.5	1868.9
165°	1892.6	1884.3	1888.4	1898.3	1888.4
167.5°	1908.0	1899.6	1903.9	1913.7	1901.0
170°	1920.7	1912.2	1915.1	1924.8	1912.2
172.5°	1929.0	1920.7	1923.5	1933.3	1920.7
175°	1936.0	1926.1	1929.0	1938.7	1924.8
177.5°	1938.7	1929.0	1930.4	1940.2	1927.7
180°	1931.8	1931.8	1931.8	1931.8	1931.8



TEST NUMBER: P925663
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D060US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.14	14.05	14.03	14.95	16.09	9.10	10.01	9.99	10.91	12.05
	3H	14.82	15.64	15.72	16.54	17.71	10.29	11.11	11.19	12.01	13.18
	4H	15.43	16.20	16.34	17.11	18.29	10.74	11.51	11.65	12.42	13.60
	6H	15.85	16.56	16.78	17.48	18.67	11.06	11.77	11.98	12.69	13.88
	8H	15.98	16.65	16.91	17.59	18.78	11.15	11.82	12.08	12.76	13.95
	12H	16.04	16.68	16.98	17.61	18.83	11.19	11.83	12.13	12.76	13.98
4H	2H	13.17	13.94	14.09	14.85	16.03	9.71	10.47	10.62	11.39	12.57
	3H	15.00	15.64	15.93	16.58	17.78	11.06	11.69	11.98	12.64	13.83
	4H	15.69	16.27	16.63	17.21	18.43	11.60	12.18	12.54	13.12	14.34
	6H	16.21	16.71	17.16	17.67	18.89	12.02	12.52	12.97	13.48	14.70
	8H	16.38	16.85	17.33	17.81	19.04	12.15	12.61	13.10	13.57	14.80
	12H	16.48	16.90	17.45	17.87	19.11	12.21	12.63	13.18	13.61	14.84
8H	4H	15.66	16.13	16.62	17.09	18.32	11.89	12.35	12.84	13.31	14.54
	6H	16.23	16.61	17.21	17.61	18.84	12.40	12.78	13.38	13.78	15.01
	8H	16.44	16.78	17.43	17.77	19.02	12.59	12.93	13.57	13.91	15.16
	12H	16.58	16.88	17.57	17.86	19.16	12.70	13.00	13.69	13.98	15.28
12H	4H	15.62	16.04	16.59	17.02	18.25	11.89	12.31	12.87	13.29	14.52
	6H	16.20	16.54	17.19	17.53	18.78	12.45	12.79	13.43	13.78	15.02
	8H	16.42	16.72	17.41	17.71	19.00	12.66	12.95	13.65	13.94	15.23