

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925670

Luminaire Tested: DFN2DIP-SQ3F0-100D080US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P925670  
REPORT IS A COMBINATION OF REPORTS P899946 AND P896733  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-100D080US950-RLLFLL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14863.3 lumens  
Efficiency: N/A  
Efficacy: 93.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 158.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9781  
Total Harmonic Distortion (THDi): 0.075  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P925670  
CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P925670

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52	47
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30	27
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24	21
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19	17
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4518	4518	4518
5°	4522	4443	4473
10°	4474	4353	4326
15°	4410	4206	4100
20°	4326	4005	3822
25°	4239	3780	3555
30°	4124	3550	3216
35°	4011	3303	2918
40°	3896	3047	2577
45°	3763	2764	2268
50°	3625	2478	1966
55°	3480	2173	1676
60°	3313	1855	1378
65°	3119	1532	1238
70°	2885	1230	1119
75°	2590	1078	1014
80°	2165	895	875
85°	1468	583	648

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3763 cd/sqm



TEST NUMBER: P925670

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.5	2.5
10°-20°	1014.4	6.8
20°-30°	1424.2	9.6
30°-40°	1552.5	10.4
40°-50°	1426.9	9.6
50°-60°	1120.6	7.5
60°-70°	729.4	4.9
70°-80°	375.5	2.5
80°-90°	102.7	0.7
90°-100°	149.4	1.0
100°-110°	474.6	3.2
110°-120°	812.1	5.5
120°-130°	1068.1	7.2
130°-140°	1198.9	8.1
140°-150°	1175.6	7.9
150°-160°	986.2	6.6
160°-170°	654.0	4.4
170°-180°	228.6	1.5
0°-30°	2808.2	18.9
0°-40°	4360.7	29.3
0°-60°	6908.2	46.5
0°-90°	8115.8	54.6
90°-120°	1436.1	9.7
90°-150°	4878.6	32.8
90°-180°	6747.0	45.4
0°-180°	14863.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3943	3943	3943	3943	3943	
5°	3943	3925	3878	3911	3900	374
15°	3750	3711	3590	3522	3486	1057
25°	3404	3290	3054	2908	2854	1566
35°	2933	2751	2437	2212	2134	1836
45°	2398	2159	1784	1531	1445	1852
55°	1823	1545	1160	946	878	1629
65°	1231	942	621	500	489	1221
75°	656	407	285	260	257	694
85°	153	78	68	68	68	176
90°	2	26	71	67	69	15
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	



TEST NUMBER: P925670

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3942.9	3942.9	3942.9	3942.9	3942.9
2.5°	3960.6	3942.9	3903.5	3939.4	3932.3
5°	3942.9	3925.0	3878.5	3910.7	3900.0
7.5°	3910.7	3889.5	3839.5	3853.5	3835.7
10°	3867.9	3842.9	3771.7	3760.8	3739.6
12.5°	3814.6	3782.3	3685.8	3664.6	3625.2
15°	3750.2	3710.8	3589.6	3521.9	3486.3
17.5°	3675.2	3618.0	3468.2	3389.8	3332.6
20°	3589.6	3518.1	3339.8	3250.9	3172.0
22.5°	3496.9	3414.7	3207.6	3086.6	3033.1
25°	3404.2	3289.9	3054.3	2908.2	2854.5
27.5°	3293.6	3172.0	2911.6	2743.9	2661.8
30°	3175.9	3039.9	2754.5	2572.8	2476.3
32.5°	3061.6	2897.2	2605.0	2390.7	2301.3
35°	2933.2	2751.1	2437.3	2212.4	2133.6
37.5°	2808.3	2611.8	2280.2	2033.7	1944.7
40°	2676.2	2462.3	2115.9	1862.6	1769.9
42.5°	2540.6	2312.3	1952.0	1687.7	1598.7
45°	2397.9	2158.6	1784.3	1530.6	1445.0
47.5°	2262.4	2009.1	1623.7	1370.0	1291.7
50°	2112.4	1859.2	1466.6	1220.2	1145.6
52.5°	1965.9	1698.3	1316.7	1081.2	1013.4
55°	1823.2	1545.0	1159.6	945.7	877.9
57.5°	1677.1	1391.6	1020.7	820.7	763.6
60°	1527.2	1241.7	874.2	692.4	635.3
62.5°	1381.0	1095.6	749.2	578.1	549.7
65°	1231.1	941.9	620.9	499.7	488.7
67.5°	1088.4	799.2	499.7	438.7	428.2
70°	938.4	660.3	413.7	378.2	363.9
72.5°	795.7	531.5	346.0	317.6	310.4
75°	656.4	406.6	285.4	260.4	257.0
77.5°	517.5	288.9	224.9	210.5	203.3
80°	388.8	207.1	171.1	157.1	157.1
82.5°	271.0	139.3	117.7	110.6	110.6
85°	153.3	78.3	67.7	67.7	67.7
87.5°	57.1	28.4	28.4	25.0	25.0
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3



TEST NUMBER: P925670

CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7



TEST NUMBER: P925670  
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D080US950-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	13.64	13.69	14.58	15.78	8.73	9.60	9.65	10.54	11.74
	3H	14.45	15.22	15.38	16.17	17.40	9.92	10.69	10.85	11.64	12.87
	4H	15.05	15.79	16.00	16.74	17.98	10.36	11.10	11.31	12.05	13.29
	6H	15.47	16.15	16.44	17.11	18.36	10.68	11.36	11.64	12.31	13.57
	8H	15.60	16.24	16.57	17.22	18.47	10.77	11.41	11.74	12.39	13.64
	12H	15.66	16.27	16.63	17.24	18.51	10.81	11.42	11.78	12.39	13.66
4H	2H	12.79	13.53	13.75	14.48	15.72	9.33	10.06	10.28	11.01	12.25
	3H	14.62	15.23	15.58	16.21	17.46	10.68	11.29	11.64	12.27	13.52
	4H	15.31	15.87	16.28	16.84	18.12	11.22	11.78	12.19	12.75	14.03
	6H	15.82	16.30	16.81	17.30	18.58	11.63	12.11	12.62	13.11	14.39
	8H	16.00	16.44	16.98	17.43	18.73	11.76	12.21	12.75	13.20	14.49
	12H	16.09	16.49	17.10	17.50	18.80	11.82	12.23	12.83	13.23	14.53
8H	4H	15.28	15.73	16.27	16.72	18.01	11.50	11.95	12.49	12.94	14.23
	6H	15.84	16.21	16.85	17.24	18.53	12.01	12.38	13.02	13.41	14.70
	8H	16.05	16.38	17.08	17.40	18.71	12.20	12.52	13.22	13.54	14.85
	12H	16.19	16.48	17.21	17.49	18.85	12.31	12.60	13.34	13.61	14.97
12H	4H	15.23	15.63	16.24	16.64	17.94	11.51	11.91	12.51	12.92	14.21
	6H	15.82	16.14	16.84	17.16	18.47	12.06	12.38	13.08	13.41	14.71
	8H	16.03	16.32	17.06	17.34	18.69	12.27	12.55	13.29	13.57	14.92