

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920095

Luminaire Tested: DFN2DIP-SQ3F0-070D050US935-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920095
REPORT IS A COMBINATION OF REPORTS P901406 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-070D050US935-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9384.9 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 102.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		86	86	86		73	73	73		60	60	60
1	99	95	91	88		92	89	85	82		76	74	72		65	63	62		54	53	52
2	91	84	78	73		84	78	73	69		67	63	60		57	55	52		48	46	45
3	83	74	67	61		77	69	63	58		60	55	51		51	48	45		43	41	39
4	76	66	58	52		71	62	55	50		54	48	44		46	42	39		39	36	34
5	70	59	51	45		65	55	48	43		48	43	38		42	37	34		35	32	30
6	65	53	45	40		60	50	43	38		44	38	34		38	33	30		32	29	26
7	60	48	40	35		56	45	38	33		40	34	30		35	30	27		30	26	24
8	56	44	36	31		52	41	34	30		36	31	27		32	27	24		27	24	21
9	52	40	33	28		49	38	31	27		34	28	24		29	25	22		25	22	19
10	49	37	30	25		46	35	28	24		31	26	22		27	23	20		24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2854	2854	2854
5°	2857	2807	2826
10°	2827	2750	2733
15°	2786	2657	2590
20°	2733	2530	2415
25°	2678	2388	2246
30°	2606	2243	2032
35°	2534	2086	1843
40°	2461	1925	1628
45°	2377	1746	1433
50°	2290	1565	1242
55°	2198	1373	1059
60°	2093	1172	870
65°	1971	968	782
70°	1823	777	707
75°	1637	681	641
80°	1368	565	553
85°	928	368	410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2377 cd/sqm

TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.5
10°-20°	640.9	6.8
20°-30°	899.8	9.6
30°-40°	980.8	10.5
40°-50°	901.5	9.6
50°-60°	708.0	7.5
60°-70°	460.8	4.9
70°-80°	237.2	2.5
80°-90°	63.1	0.7
90°-100°	47.9	0.5
100°-110°	178.6	1.9
110°-120°	473.7	5.0
120°-130°	785.6	8.4
130°-140°	834.5	8.9
140°-150°	775.6	8.3
150°-160°	623.5	6.6
160°-170°	401.8	4.3
170°-180°	138.3	1.5
0°-30°	1774.1	18.9
0°-40°	2754.9	29.4
0°-60°	4364.3	46.5
0°-90°	5125.5	54.6
90°-120°	700.2	7.5
90°-150°	3095.8	33.0
90°-180°	4259.0	45.4
0°-180°	9384.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	13	21	26	28	9
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0



TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P920095

CATALOG NUMBER: DFN2DIP-SQ3F0-070D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.18	12.05	12.10	12.98	14.19	7.14	8.01	8.06	8.94	10.15
	3H	12.85	13.63	13.79	14.58	15.81	8.32	9.10	9.26	10.05	11.28
	4H	13.46	14.20	14.41	15.15	16.39	8.77	9.51	9.72	10.46	11.70
	6H	13.88	14.56	14.84	15.51	16.77	9.09	9.76	10.05	10.72	11.97
	8H	14.01	14.65	14.97	15.62	16.87	9.18	9.82	10.14	10.79	12.04
	12H	14.07	14.68	15.04	15.65	16.92	9.22	9.83	10.19	10.80	12.07
4H	2H	11.20	11.93	12.15	12.88	14.12	7.74	8.47	8.69	9.42	10.66
	3H	13.03	13.64	13.99	14.62	15.87	9.08	9.69	10.05	10.67	11.93
	4H	13.72	14.27	14.69	15.25	16.53	9.63	10.18	10.60	11.16	12.44
	6H	14.23	14.71	15.22	15.71	16.98	10.04	10.52	11.03	11.52	12.80
	8H	14.40	14.85	15.39	15.84	17.13	10.17	10.61	11.16	11.61	12.90
	12H	14.50	14.90	15.50	15.91	17.20	10.23	10.63	11.24	11.64	12.94
8H	4H	13.69	14.13	14.67	15.12	16.41	9.91	10.35	10.89	11.35	12.64
	6H	14.25	14.62	15.26	15.65	16.94	10.42	10.79	11.43	11.82	13.11
	8H	14.46	14.79	15.48	15.81	17.11	10.60	10.93	11.63	11.95	13.26
	12H	14.60	14.88	15.62	15.90	17.25	10.72	11.01	11.74	12.02	13.37
12H	4H	13.64	14.04	14.65	15.05	16.35	9.91	10.32	10.92	11.32	12.62
	6H	14.22	14.55	15.24	15.57	16.88	10.47	10.79	11.49	11.81	13.12
	8H	14.44	14.73	15.46	15.74	17.10	10.67	10.96	11.70	11.97	13.33

END OF REPORT