

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925726

Luminaire Tested: DFN2DIP-SQ3F0-120D040US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925726
REPORT IS A COMBINATION OF REPORTS P899878 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D040US950-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13107.9 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 156.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925726
CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P925726

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	78	78	78	74
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68	68	68	68	64
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58	58	58	58	55
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50	50	50	50	47
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	44	44	44	41
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39	39	39	39	36
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35	35	35	35	32
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31	31	31	31	29
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28	28	28	28	26
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26	26	26	26	24
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23	23	23	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5421	5421	5421
5°	5427	5332	5368
10°	5369	5224	5191
15°	5292	5047	4920
20°	5191	4806	4587
25°	5087	4536	4266
30°	4949	4260	3859
35°	4814	3963	3501
40°	4675	3656	3092
45°	4515	3316	2721
50°	4350	2974	2359
55°	4176	2608	2011
60°	3975	2226	1653
65°	3744	1838	1486
70°	3463	1476	1342
75°	3109	1294	1217
80°	2598	1074	1050
85°	1762	700	778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4515 cd/sqm



TEST NUMBER: P925726

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.4	3.4
10°-20°	1217.3	9.3
20°-30°	1709.1	13.0
30°-40°	1863.0	14.2
40°-50°	1712.3	13.1
50°-60°	1344.7	10.3
60°-70°	875.3	6.7
70°-80°	450.6	3.4
80°-90°	118.5	0.9
90°-100°	74.7	0.6
100°-110°	237.3	1.8
110°-120°	406.1	3.1
120°-130°	534.0	4.1
130°-140°	599.4	4.6
140°-150°	587.8	4.5
150°-160°	493.1	3.8
160°-170°	327.0	2.5
170°-180°	114.3	0.9
0°-30°	3369.8	25.7
0°-40°	5232.8	39.9
0°-60°	8289.9	63.2
0°-90°	9734.2	74.3
90°-120°	718.0	5.5
90°-150°	2439.3	18.6
90°-180°	3374.0	25.7
0°-180°	13107.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4732	4732	4732	4732	4732	
5°	4732	4710	4654	4693	4680	449
15°	4500	4453	4308	4226	4184	1268
25°	4085	3948	3665	3490	3425	1879
35°	3520	3301	2925	2655	2560	2203
45°	2878	2590	2141	1837	1734	2222
55°	2188	1854	1392	1135	1054	1955
65°	1477	1130	745	600	586	1465
75°	788	488	343	312	308	833
85°	184	94	81	81	81	211
90°	1	13	36	34	34	13
95°	53	63	65	65	63	59
105°	219	222	224	226	226	231
115°	408	413	412	410	408	403
125°	593	602	599	596	594	530
135°	767	778	780	779	776	593
145°	931	938	944	945	941	582
155°	1064	1067	1070	1076	1072	490
165°	1158	1157	1157	1164	1159	327
175°	1205	1202	1200	1207	1201	114
180°	1207	1207	1207	1207	1207	



TEST NUMBER: P925726

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4731.5	4731.5	4731.5	4731.5	4731.5
2.5°	4752.8	4731.5	4684.2	4727.4	4718.7
5°	4731.5	4710.1	4654.2	4692.8	4680.1
7.5°	4692.8	4667.3	4607.4	4624.2	4602.9
10°	4641.5	4611.5	4526.1	4512.9	4487.5
12.5°	4577.4	4538.8	4422.9	4397.6	4350.3
15°	4500.2	4453.0	4307.6	4226.2	4183.6
17.5°	4410.2	4341.7	4161.7	4067.8	3999.2
20°	4307.6	4221.7	4007.8	3901.0	3806.5
22.5°	4196.3	4097.7	3849.2	3703.8	3639.8
25°	4085.0	3947.7	3665.2	3489.8	3425.3
27.5°	3952.3	3806.5	3493.9	3292.7	3194.1
30°	3811.0	3648.0	3305.4	3087.3	2971.5
32.5°	3673.9	3476.7	3126.0	2868.9	2761.6
35°	3519.9	3301.3	2924.7	2654.9	2560.3
37.5°	3369.9	3134.2	2736.2	2440.4	2333.7
40°	3211.4	2954.7	2539.1	2235.1	2123.8
42.5°	3048.7	2774.8	2342.4	2025.2	1918.5
45°	2877.5	2590.4	2141.1	1836.7	1734.0
47.5°	2714.8	2410.9	1948.4	1644.1	1550.1
50°	2535.0	2231.0	1759.9	1464.2	1374.7
52.5°	2359.1	2037.9	1580.0	1297.4	1216.2
55°	2187.9	1854.0	1391.5	1134.8	1053.5
57.5°	2012.5	1670.0	1224.7	984.9	916.3
60°	1832.6	1490.1	1048.9	830.9	762.3
62.5°	1657.3	1314.7	899.0	693.7	659.6
65°	1477.4	1130.3	745.1	599.7	586.5
67.5°	1306.1	959.0	599.7	526.5	513.8
70°	1126.2	792.3	496.6	453.8	436.6
72.5°	955.0	637.8	415.2	381.1	372.5
75°	787.7	487.9	342.6	312.5	308.4
77.5°	621.1	346.6	269.9	252.6	243.9
80°	466.6	248.5	205.3	188.5	188.5
82.5°	325.3	167.1	141.3	132.6	132.6
85°	184.0	94.1	81.3	81.3	81.3
87.5°	68.6	34.1	34.1	30.0	30.0
90°	1.0	13.1	35.7	33.5	34.5
92.5°	22.5	30.5	31.7	32.7	32.7
95°	53.1	63.3	65.2	65.2	63.3
97.5°	88.4	97.9	101.9	101.9	101.9
100°	129.2	137.6	140.4	140.4	139.4
102.5°	172.1	178.3	182.3	183.4	182.3
105°	219.0	221.9	224.1	225.9	225.9
107.5°	265.6	270.0	270.0	270.6	265.6
110°	310.7	316.5	316.5	316.5	313.7



TEST NUMBER: P925726

CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.5	365.7	364.5	361.7	359.5
115°	407.5	413.4	411.5	410.4	407.5
117.5°	455.2	463.2	458.1	455.2	452.3
120°	503.2	511.2	503.2	503.2	499.9
122.5°	546.8	557.0	552.0	549.0	546.8
125°	592.7	601.8	598.9	595.6	594.5
127.5°	637.5	648.7	644.7	640.3	637.5
130°	679.2	692.4	690.6	688.4	684.4
132.5°	726.2	736.4	737.2	732.0	729.1
135°	766.6	777.9	780.1	778.9	776.1
137.5°	811.8	820.8	822.6	821.9	817.6
140°	851.3	860.5	865.6	865.6	861.6
142.5°	892.2	901.2	904.1	905.3	901.2
145°	930.7	938.0	943.8	944.9	940.9
147.5°	965.3	974.3	978.7	980.5	976.5
150°	1000.9	1007.1	1011.1	1014.4	1011.1
152.5°	1032.6	1038.7	1043.9	1047.9	1043.9
155°	1064.2	1067.1	1070.4	1075.5	1072.2
157.5°	1091.6	1093.7	1095.5	1102.8	1097.7
160°	1115.9	1118.1	1119.1	1125.3	1121.0
162.5°	1138.4	1138.4	1139.6	1146.4	1141.4
165°	1157.8	1156.6	1156.6	1163.9	1158.8
167.5°	1175.2	1171.9	1171.9	1179.2	1174.1
170°	1188.3	1185.3	1184.3	1191.5	1185.3
172.5°	1197.4	1194.5	1193.4	1200.7	1194.5
175°	1204.7	1201.8	1199.6	1206.8	1200.7
177.5°	1208.7	1205.8	1203.6	1209.8	1203.6
180°	1206.8	1206.8	1206.8	1206.8	1206.8



TEST NUMBER: P925726
 CATALOG NUMBER: DFN2DIP-SQ3F0-120D040US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.01	16.08	15.73	16.82	17.70	10.97	12.04	11.69	12.78	13.66
	3H	16.70	17.66	17.44	18.41	19.32	12.17	13.13	12.90	13.88	14.79
	4H	17.31	18.22	18.07	18.98	19.90	12.62	13.53	13.38	14.29	15.21
	6H	17.74	18.58	18.51	19.35	20.29	12.95	13.79	13.72	14.56	15.49
	8H	17.88	18.67	18.65	19.46	20.40	13.05	13.84	13.82	14.63	15.57
	12H	17.94	18.70	18.73	19.48	20.45	13.09	13.85	13.88	14.63	15.60
4H	2H	15.05	15.96	15.81	16.72	17.64	11.59	12.50	12.35	13.26	14.18
	3H	16.90	17.65	17.67	18.45	19.39	12.95	13.71	13.73	14.50	15.44
	4H	17.60	18.28	18.38	19.07	20.04	13.51	14.19	14.29	14.98	15.95
	6H	18.12	18.71	18.92	19.53	20.51	13.93	14.52	14.74	15.34	16.32
	8H	18.30	18.85	19.10	19.66	20.65	14.06	14.61	14.87	15.43	16.42
	12H	18.40	18.90	19.23	19.73	20.73	14.13	14.63	14.96	15.47	16.46
8H	4H	17.58	18.13	18.39	18.95	19.93	13.80	14.35	14.61	15.17	16.16
	6H	18.15	18.61	18.99	19.46	20.45	14.32	14.78	15.16	15.63	16.62
	8H	18.36	18.77	19.21	19.62	20.63	14.51	14.91	15.35	15.77	16.77
	12H	18.51	18.87	19.36	19.71	20.77	14.63	14.99	15.48	15.83	16.90
12H	4H	17.54	18.04	18.37	18.87	19.87	13.82	14.31	14.64	15.15	16.14
	6H	18.12	18.53	18.97	19.39	20.39	14.37	14.77	15.22	15.63	16.63
	8H	18.35	18.71	19.20	19.55	20.62	14.58	14.94	15.43	15.79	16.85