

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920172

Luminaire Tested: DFN2DIP-SQ3F0-090D070US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920172
REPORT IS A COMBINATION OF REPORTS P899925 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-090D070US935-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13005.4 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 140.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920172
CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P920172
 CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50			50
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	50	48	46	42			42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	42	39	35			35
4	76	65	57	51	71	61	54	48	53	48	43	46	42	38	40	36	34	30			30
5	70	58	50	44	65	54	47	41	48	42	37	42	37	33	36	32	29	26			26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	33	29	26	23			23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	21			21
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18			18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17			17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15			15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3455	3455	3455
5°	3458	3404	3428
10°	3428	3356	3381
15°	3375	3299	3307
20°	3305	3220	3232
25°	3235	3126	3145
30°	3148	3038	3035
35°	3065	2935	2918
40°	2963	2830	2807
45°	2862	2726	2694
50°	2751	2616	2562
55°	2635	2489	2441
60°	2503	2338	2302
65°	2359	2182	2138
70°	2175	1991	1962
75°	1922	1763	1797
80°	1615	1470	1485
85°	1137	974	972

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2862 cd/sqm



TEST NUMBER: P920172

CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.8	2.2
10°-20°	798.5	6.1
20°-30°	1173.4	9.0
30°-40°	1362.9	10.5
40°-50°	1361.2	10.5
50°-60°	1186.9	9.1
60°-70°	877.4	6.7
70°-80°	496.4	3.8
80°-90°	136.4	1.0
90°-100°	117.9	0.9
100°-110°	374.8	2.9
110°-120°	641.3	4.9
120°-130°	843.5	6.5
130°-140°	946.7	7.3
140°-150°	928.4	7.1
150°-160°	778.8	6.0
160°-170°	516.5	4.0
170°-180°	180.5	1.4
0°-30°	2255.7	17.3
0°-40°	3618.6	27.8
0°-60°	6166.7	47.4
0°-90°	7676.9	59.0
90°-120°	1134.1	8.7
90°-150°	3852.7	29.6
90°-180°	5328.0	41.0
0°-180°	13005.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3015	3015	3015	3015	3015	
5°	3015	3004	2972	2995	2989	286
15°	2870	2853	2815	2827	2812	808
25°	2598	2575	2526	2531	2526	1195
35°	2241	2212	2166	2148	2134	1400
45°	1824	1804	1760	1728	1716	1408
55°	1380	1363	1328	1293	1279	1234
65°	931	913	884	858	844	920
75°	487	481	467	449	455	520
85°	119	116	113	104	102	132
90°	2	21	56	53	55	13
95°	84	100	103	103	100	93
105°	346	350	354	357	357	365
115°	644	653	650	648	644	637
125°	936	950	946	941	939	837
135°	1211	1229	1232	1230	1226	936
145°	1470	1481	1491	1492	1486	918
155°	1681	1685	1691	1699	1694	774
165°	1828	1827	1827	1838	1830	516
175°	1903	1898	1895	1906	1896	181
180°	1906	1906	1906	1906	1906	



TEST NUMBER: P920172

CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3015.1	3015.1	3015.1	3015.1	3015.1
2.5°	3032.7	3018.2	2986.3	3015.1	3009.6
5°	3015.1	3003.8	2971.8	2994.9	2989.3
7.5°	2994.9	2977.7	2945.6	2969.1	2963.2
10°	2963.2	2942.9	2908.1	2931.2	2922.6
12.5°	2919.5	2902.3	2867.6	2881.9	2876.2
15°	2870.3	2853.1	2815.2	2826.9	2812.4
17.5°	2809.3	2792.1	2754.3	2768.8	2754.3
20°	2742.6	2725.4	2684.8	2693.4	2682.0
22.5°	2676.2	2650.1	2612.2	2612.2	2606.3
25°	2597.7	2574.6	2525.5	2531.0	2525.5
27.5°	2510.7	2490.4	2452.9	2444.3	2429.8
30°	2424.0	2400.5	2357.2	2348.5	2336.9
32.5°	2331.1	2313.8	2267.4	2249.9	2238.2
35°	2241.3	2212.3	2165.8	2148.4	2133.9
37.5°	2139.8	2113.6	2067.1	2046.9	2032.4
40°	2035.4	2012.1	1965.6	1939.7	1928.1
42.5°	1933.9	1910.6	1864.4	1835.2	1818.0
45°	1823.8	1803.5	1759.8	1728.1	1716.5
47.5°	1716.5	1696.2	1649.7	1617.7	1600.5
50°	1603.3	1588.8	1548.2	1507.6	1493.1
52.5°	1493.1	1472.8	1435.3	1403.3	1383.0
55°	1380.3	1362.7	1327.9	1293.2	1278.8
57.5°	1267.0	1252.6	1214.8	1180.0	1168.3
60°	1153.8	1142.5	1101.8	1069.9	1061.3
62.5°	1043.7	1023.4	994.5	965.6	953.9
65°	930.8	913.3	884.3	858.2	843.8
67.5°	814.8	800.1	774.2	754.0	742.3
70°	707.5	695.8	669.7	649.4	638.0
72.5°	597.4	585.7	571.2	551.0	542.3
75°	487.0	481.4	466.7	449.4	455.3
77.5°	388.5	376.9	371.0	362.4	353.8
80°	290.1	287.0	281.1	272.5	266.7
82.5°	197.2	197.2	194.4	182.7	182.7
85°	118.7	116.0	113.2	104.3	101.5
87.5°	52.3	46.4	40.6	32.0	28.9
90°	1.7	20.7	56.3	52.9	54.6
92.5°	35.6	48.3	50.0	51.7	51.7
95°	83.9	100.0	102.9	102.9	100.0
97.5°	139.7	154.5	160.9	160.9	160.9
100°	204.0	217.2	221.8	221.8	220.1
102.5°	271.8	281.5	287.9	289.6	287.9
105°	345.9	350.5	354.0	356.9	356.9
107.5°	419.5	426.4	426.4	427.6	419.5
110°	490.8	500.0	500.0	500.0	495.3



TEST NUMBER: P920172

CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	567.7	577.6	575.8	571.2	567.7
115°	643.6	652.8	650.0	648.2	643.6
117.5°	718.8	731.5	723.5	718.8	714.3
120°	794.7	807.4	794.7	794.7	789.5
122.5°	863.7	879.8	871.8	867.1	863.7
125°	936.1	950.5	945.9	940.7	939.0
127.5°	1006.8	1024.6	1018.3	1011.4	1006.8
130°	1072.9	1093.6	1090.7	1087.3	1080.9
132.5°	1147.0	1163.1	1164.2	1156.2	1151.6
135°	1210.8	1228.6	1232.1	1230.3	1225.7
137.5°	1282.0	1296.4	1299.2	1298.1	1291.2
140°	1344.7	1359.1	1367.1	1367.1	1360.8
142.5°	1409.0	1423.4	1428.0	1429.7	1423.4
145°	1470.0	1481.4	1490.6	1492.4	1486.1
147.5°	1524.6	1538.9	1545.8	1548.7	1542.4
150°	1580.9	1590.6	1597.0	1602.1	1597.0
152.5°	1630.8	1640.6	1648.6	1655.0	1648.6
155°	1680.8	1685.4	1690.7	1698.7	1693.5
157.5°	1724.0	1727.4	1730.3	1741.8	1733.7
160°	1762.5	1765.9	1767.6	1777.4	1770.5
162.5°	1798.1	1798.1	1799.8	1810.7	1802.7
165°	1828.5	1826.8	1826.8	1838.3	1830.2
167.5°	1856.1	1851.0	1851.0	1862.4	1854.4
170°	1876.8	1872.2	1870.5	1882.0	1872.2
172.5°	1891.2	1886.5	1884.8	1896.3	1886.5
175°	1902.6	1898.1	1894.6	1906.1	1896.3
177.5°	1909.0	1904.4	1900.9	1910.7	1900.9
180°	1906.1	1906.1	1906.1	1906.1	1906.1



TEST NUMBER: P920172
 CATALOG NUMBER: DFN2DIP-SQ3F0-090D070US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.34	13.29	13.21	14.18	15.32	11.89	12.84	12.77	13.74	14.88
	3H	14.00	14.85	14.89	15.76	16.92	13.51	14.36	14.40	15.27	16.43
	4H	14.59	15.39	15.49	16.31	17.48	14.10	14.90	15.00	15.81	16.98
	6H	14.99	15.73	15.91	16.65	17.84	14.49	15.23	15.41	16.15	17.34
	8H	15.10	15.80	16.02	16.74	17.92	14.59	15.30	15.52	16.24	17.42
	12H	15.15	15.82	16.07	16.75	17.96	14.64	15.31	15.56	16.24	17.45
4H	2H	12.81	13.61	13.71	14.52	15.69	12.45	13.26	13.36	14.17	15.34
	3H	14.67	15.35	15.59	16.29	17.48	14.27	14.94	15.19	15.88	17.07
	4H	15.39	16.00	16.32	16.94	18.15	14.96	15.58	15.89	16.52	17.73
	6H	15.90	16.43	16.85	17.40	18.61	15.47	16.00	16.42	16.96	18.18
	8H	16.05	16.55	17.00	17.50	18.73	15.62	16.11	16.56	17.07	18.29
	12H	16.13	16.57	17.09	17.55	18.78	15.68	16.13	16.64	17.10	18.33
8H	4H	15.59	16.08	16.53	17.04	18.26	15.21	15.71	16.16	16.66	17.89
	6H	16.22	16.63	17.19	17.62	18.85	15.83	16.24	16.80	17.24	18.46
	8H	16.43	16.80	17.42	17.78	19.03	16.04	16.40	17.02	17.39	18.63
	12H	16.57	16.89	17.55	17.87	19.16	16.16	16.48	17.14	17.46	18.75
12H	4H	15.58	16.02	16.54	17.00	18.23	15.21	15.65	16.17	16.63	17.86
	6H	16.25	16.61	17.23	17.59	18.84	15.87	16.24	16.85	17.22	18.46
	8H	16.49	16.81	17.47	17.79	19.08	16.11	16.43	17.09	17.41	18.70