

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920179

Luminaire Tested: DFN2DIP-SQ3F0-090D080US935-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P920179  
REPORT IS A COMBINATION OF REPORTS P901464 AND P898289  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ3F0-090D080US935-RLLONL  
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13405.7 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 148.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.996  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P920179  
CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P920179

CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41	36				36
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3670	3670	3670
5°	3673	3609	3633
10°	3635	3536	3514
15°	3582	3417	3330
20°	3514	3253	3105
25°	3443	3071	2887
30°	3350	2883	2612
35°	3258	2682	2370
40°	3165	2475	2093
45°	3056	2245	1842
50°	2944	2013	1597
55°	2827	1765	1361
60°	2690	1507	1119
65°	2534	1244	1006
70°	2344	999	909
75°	2104	876	824
80°	1758	727	710
85°	1192	473	527

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3056 cd/sqm



TEST NUMBER: P920179

CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	300.2	2.2
10°-20°	824.0	6.1
20°-30°	1156.9	8.6
30°-40°	1261.0	9.4
40°-50°	1159.0	8.6
50°-60°	910.3	6.8
60°-70°	592.5	4.4
70°-80°	305.0	2.3
80°-90°	81.9	0.6
90°-100°	76.7	0.6
100°-110°	285.7	2.1
110°-120°	757.9	5.7
120°-130°	1256.9	9.4
130°-140°	1335.2	10.0
140°-150°	1240.9	9.3
150°-160°	997.6	7.4
160°-170°	642.8	4.8
170°-180°	221.3	1.7
0°-30°	2281.0	17.0
0°-40°	3542.0	26.4
0°-60°	5611.3	41.9
0°-90°	6590.7	49.2
90°-120°	1120.2	8.4
90°-150°	4953.3	36.9
90°-180°	6815.0	50.8
0°-180°	13405.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3203	3203	3203	3203	3203	
5°	3203	3188	3150	3176	3168	304
15°	3046	3014	2916	2861	2832	858
25°	2765	2672	2481	2362	2319	1272
35°	2383	2235	1980	1797	1733	1491
45°	1948	1753	1449	1243	1174	1504
55°	1481	1255	942	768	713	1323
65°	1000	765	504	406	397	991
75°	533	330	232	212	209	564
85°	124	64	55	55	55	143
90°	2	20	34	42	45	13
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2161	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	



TEST NUMBER: P920179

CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3202.7	3202.7	3202.7	3202.7	3202.7
2.5°	3217.1	3202.7	3170.6	3199.9	3194.0
5°	3202.7	3188.2	3150.4	3176.5	3167.9
7.5°	3176.5	3159.3	3118.7	3130.1	3115.6
10°	3141.8	3121.5	3063.7	3054.7	3037.5
12.5°	3098.4	3072.3	2993.9	2976.6	2944.6
15°	3046.1	3014.2	2915.8	2860.7	2831.8
17.5°	2985.3	2938.8	2817.0	2753.4	2707.0
20°	2915.8	2857.7	2712.7	2640.5	2576.5
22.5°	2840.4	2773.7	2605.5	2507.1	2463.7
25°	2765.1	2672.2	2481.0	2362.2	2318.6
27.5°	2675.3	2576.5	2365.0	2228.8	2162.1
30°	2579.6	2469.3	2237.4	2089.8	2011.4
32.5°	2486.7	2353.3	2115.9	1941.9	1869.3
35°	2382.6	2234.6	1979.7	1797.1	1733.1
37.5°	2281.0	2121.5	1852.1	1651.9	1579.7
40°	2173.8	2000.0	1718.6	1512.9	1437.6
42.5°	2063.6	1878.3	1585.4	1370.9	1298.6
45°	1947.7	1753.4	1449.2	1243.2	1173.7
47.5°	1837.6	1631.9	1318.9	1112.8	1049.2
50°	1715.9	1510.1	1191.3	991.1	930.5
52.5°	1596.9	1379.5	1069.5	878.2	823.2
55°	1480.9	1254.9	941.8	768.2	713.1
57.5°	1362.3	1130.4	829.1	666.7	620.3
60°	1240.4	1008.6	710.1	562.4	516.0
62.5°	1121.8	889.9	608.6	469.6	446.5
65°	1000.0	765.1	504.3	405.9	397.0
67.5°	884.1	649.1	405.9	356.4	347.8
70°	762.3	536.3	336.1	307.2	295.5
72.5°	646.4	431.7	281.0	258.0	252.2
75°	533.2	330.3	231.9	211.5	208.8
77.5°	420.3	234.6	182.6	171.0	165.1
80°	315.8	168.2	139.0	127.6	127.6
82.5°	220.2	113.1	95.7	89.8	89.8
85°	124.5	63.6	55.0	55.0	55.0
87.5°	46.4	23.1	23.1	20.3	20.3
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9



TEST NUMBER: P920179

CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.3	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.1
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.6	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.4	2146.5	2166.6	2176.6	2163.3
157.5°	2196.7	2183.4	2198.6	2210.4	2196.7
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6



TEST NUMBER: P920179  
 CATALOG NUMBER: DFN2DIP-SQ3F0-090D080US935-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.55	12.37	12.52	13.36	14.64	7.51	8.34	8.48	9.32	10.60
	3H	13.22	13.96	14.21	14.95	16.26	8.69	9.43	9.68	10.42	11.73
	4H	13.83	14.53	14.82	15.52	16.83	9.14	9.84	10.13	10.83	12.14
	6H	14.25	14.89	15.25	15.89	17.21	9.45	10.09	10.46	11.09	12.42
	8H	14.37	14.98	15.38	15.99	17.32	9.54	10.15	10.55	11.17	12.49
	12H	14.43	15.01	15.45	16.02	17.37	9.58	10.16	10.60	11.17	12.52
4H	2H	11.57	12.26	12.57	13.26	14.57	8.10	8.80	9.11	9.79	11.11
	3H	13.39	13.97	14.40	14.99	16.32	9.45	10.02	10.46	11.05	12.38
	4H	14.08	14.61	15.10	15.62	16.97	9.99	10.52	11.01	11.53	12.89
	6H	14.59	15.04	15.62	16.08	17.43	10.40	10.85	11.43	11.89	13.24
	8H	14.76	15.18	15.79	16.22	17.58	10.53	10.95	11.56	11.98	13.34
	12H	14.85	15.24	15.90	16.28	17.65	10.59	10.97	11.63	12.02	13.38
8H	4H	14.04	14.47	15.07	15.50	16.86	10.27	10.69	11.30	11.72	13.08
	6H	14.60	14.95	15.66	16.03	17.39	10.77	11.12	11.83	12.20	13.56
	8H	14.82	15.13	15.88	16.18	17.56	10.96	11.27	12.02	12.33	13.71
	12H	14.95	15.22	16.02	16.28	17.70	11.07	11.35	12.14	12.40	13.82
12H	4H	14.00	14.38	15.04	15.42	16.79	10.27	10.65	11.32	11.70	13.07
	6H	14.58	14.89	15.64	15.95	17.33	10.82	11.13	11.88	12.19	13.57
	8H	14.80	15.07	15.86	16.12	17.54	11.03	11.30	12.09	12.35	13.77