

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P903965

Luminaire Tested: DFN2DIP-SQ4F0-060D140US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P903965
REPORT IS A COMBINATION OF REPORTS P901705 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-060D140US830-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18662.3 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 155.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	85	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	77	68	61	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	60	53	47	63	54	48	43	43	39	35	33	30	27	23	21	20
5	65	54	46	40	58	48	42	37	39	34	30	29	26	23	21	19	17
6	60	48	40	35	53	43	37	32	35	30	26	27	23	20	19	17	15
7	55	43	35	30	49	39	32	28	31	26	23	24	21	18	17	15	13
8	51	39	32	26	46	35	29	24	28	24	20	22	19	16	16	14	12
9	47	36	28	23	42	32	26	22	26	21	18	20	17	14	15	12	11
10	44	32	26	21	40	30	23	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1544	1544	1544
5°	1546	1523	1533
10°	1534	1503	1513
15°	1511	1478	1481
20°	1481	1444	1448
25°	1450	1403	1410
30°	1413	1365	1362
35°	1377	1321	1311
40°	1332	1275	1262
45°	1288	1230	1212
50°	1240	1183	1154
55°	1189	1127	1101
60°	1132	1062	1041
65°	1069	995	969
70°	990	912	893
75°	879	813	822
80°	747	688	687
85°	540	471	462

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2388 cd/sqm

TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.1	1.1
10°-20°	582.7	3.1
20°-30°	856.4	4.6
30°-40°	994.6	5.3
40°-50°	993.4	5.3
50°-60°	866.2	4.6
60°-70°	640.3	3.4
70°-80°	362.3	1.9
80°-90°	103.5	0.6
90°-100°	146.9	0.8
100°-110°	547.4	2.9
110°-120°	1451.8	7.8
120°-130°	2408.0	12.9
130°-140°	2557.8	13.7
140°-150°	2377.2	12.7
150°-160°	1911.2	10.2
160°-170°	1231.5	6.6
170°-180°	423.9	2.3
0°-30°	1646.2	8.8
0°-40°	2640.9	14.2
0°-60°	4500.5	24.1
0°-90°	5606.5	30.0
90°-120°	2146.1	11.5
90°-150°	9489.1	50.8
90°-180°	13056.0	70.0
0°-180°	18662.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2200	2200	2200	2200	2200	
5°	2200	2192	2169	2186	2182	209
15°	2095	2082	2055	2063	2053	590
25°	1896	1879	1843	1847	1843	872
35°	1636	1615	1581	1568	1557	1021
45°	1331	1316	1284	1261	1253	1027
55°	1007	994	969	944	933	901
65°	679	667	646	626	616	672
75°	355	351	340	328	332	379
85°	87	85	83	76	74	97
90°	3	39	64	81	87	17
95°	209	103	126	142	139	248
105°	980	1076	197	232	245	1047
115°	1853	1908	1988	496	264	1824
125°	2620	2662	2723	2746	2755	2336
135°	3242	3294	3322	3355	3348	2504
145°	3761	3757	3812	3835	3818	2352
155°	4141	4112	4151	4170	4144	1908
165°	4363	4344	4354	4376	4354	1233
175°	4463	4440	4447	4469	4437	425
180°	4453	4453	4453	4453	4453	

TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2200.5	2200.5	2200.5	2200.5	2200.5
2.5°	2213.3	2202.7	2179.3	2200.5	2196.4
5°	2200.5	2192.2	2168.8	2185.7	2181.6
7.5°	2185.7	2173.1	2149.8	2166.8	2162.6
10°	2162.6	2147.8	2122.3	2139.2	2132.9
12.5°	2130.7	2118.1	2092.7	2103.3	2099.0
15°	2094.7	2082.2	2054.6	2063.1	2052.6
17.5°	2050.3	2037.8	2010.2	2020.6	2010.2
20°	2001.6	1989.0	1959.4	1965.7	1957.4
22.5°	1953.1	1934.0	1906.4	1906.4	1902.1
25°	1895.8	1879.1	1843.0	1847.1	1843.0
27.5°	1832.3	1817.5	1790.1	1783.9	1773.3
30°	1769.1	1751.9	1720.3	1714.0	1705.4
32.5°	1701.2	1688.7	1654.7	1641.9	1633.4
35°	1635.7	1614.6	1580.6	1567.8	1557.3
37.5°	1561.6	1542.5	1508.6	1493.7	1483.2
40°	1485.4	1468.4	1434.5	1415.7	1407.1
42.5°	1411.4	1394.3	1360.7	1339.4	1326.7
45°	1331.1	1316.2	1284.3	1261.2	1252.6
47.5°	1252.6	1237.8	1204.0	1180.6	1168.0
50°	1170.1	1159.5	1129.9	1100.2	1089.7
52.5°	1089.7	1074.9	1047.4	1024.2	1009.4
55°	1007.3	994.5	969.1	943.8	933.2
57.5°	924.7	914.2	886.6	861.2	852.6
60°	842.1	833.8	804.2	780.8	774.5
62.5°	761.7	746.9	725.8	704.6	696.2
65°	679.3	666.6	645.5	626.3	615.8
67.5°	594.6	583.9	565.1	550.3	541.7
70°	516.3	507.8	488.7	473.9	465.6
72.5°	435.9	427.4	416.9	402.1	395.8
75°	355.3	351.4	340.5	328.0	332.2
77.5°	283.5	275.0	270.7	264.5	258.2
80°	211.7	209.4	205.2	198.9	194.6
82.5°	143.9	143.9	141.9	133.4	133.4
85°	86.6	84.6	82.6	76.1	74.1
87.5°	38.2	33.9	29.6	23.4	21.1
90°	3.0	38.6	64.3	80.8	86.9
92.5°	80.8	67.8	77.3	83.8	86.9
95°	209.3	102.9	125.5	141.9	138.6
97.5°	376.9	112.9	164.2	174.1	177.2
100°	570.5	128.9	183.7	209.3	215.8
102.5°	782.9	776.7	190.2	225.4	235.4
105°	979.6	1076.4	196.7	231.9	244.9
107.5°	1208.4	1288.7	203.2	238.4	251.4
110°	1427.7	1495.1	564.0	241.9	254.5

TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1633.9	1691.7	1637.0	248.0	257.9
115°	1852.8	1907.5	1988.3	496.3	264.4
117.5°	2043.0	2107.2	2162.4	1701.3	857.1
120°	2255.8	2304.0	2362.1	2400.7	1965.7
122.5°	2436.0	2487.7	2552.3	2571.4	2574.9
125°	2619.7	2661.7	2723.0	2745.5	2755.1
127.5°	2787.3	2832.4	2881.0	2913.1	2916.2
130°	2945.3	2997.0	3032.2	3067.8	3064.7
132.5°	3106.4	3148.5	3183.7	3212.7	3209.7
135°	3241.9	3293.5	3322.2	3354.7	3348.2
137.5°	3383.4	3422.1	3454.6	3486.7	3477.2
140°	3522.0	3548.0	3583.2	3612.3	3596.2
142.5°	3638.3	3660.8	3702.6	3728.2	3712.1
145°	3760.7	3757.3	3812.0	3834.6	3818.5
147.5°	3866.8	3857.2	3911.9	3928.0	3915.3
150°	3970.1	3947.5	3999.1	4018.2	4002.2
152.5°	4056.9	4031.3	4079.5	4099.0	4076.4
155°	4140.7	4112.0	4150.7	4169.8	4144.2
157.5°	4208.5	4182.8	4211.9	4234.5	4208.5
160°	4266.6	4247.1	4266.6	4285.7	4263.2
162.5°	4317.9	4298.7	4314.9	4337.4	4308.4
165°	4363.0	4343.9	4353.5	4376.0	4353.5
167.5°	4398.7	4379.1	4389.0	4411.7	4382.5
170°	4427.7	4408.2	4414.7	4437.3	4408.2
172.5°	4446.8	4427.7	4434.2	4456.8	4427.7
175°	4462.9	4440.3	4446.8	4469.4	4437.3
177.5°	4469.4	4446.8	4450.3	4472.8	4443.8
180°	4453.3	4453.3	4453.3	4453.3	4453.3

TEST NUMBER: P903965

CATALOG NUMBER: DFN2DIP-SQ4F0-060D140US830-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.59	7.29	7.70	8.40	9.93	6.14	6.85	7.25	7.95	9.49
	3H	8.24	8.87	9.36	9.99	11.53	7.75	8.38	8.87	9.50	11.04
	4H	8.82	9.42	9.95	10.54	12.09	8.33	8.93	9.46	10.04	11.60
	6H	9.22	9.77	10.36	10.89	12.45	8.72	9.27	9.86	10.39	11.95
	8H	9.32	9.85	10.46	10.98	12.54	8.82	9.34	9.96	10.48	12.03
	12H	9.36	9.86	10.51	10.99	12.57	8.85	9.35	10.00	10.48	12.06
4H	2H	7.03	7.63	8.17	8.75	10.30	6.67	7.27	7.81	8.39	9.94
	3H	8.88	9.39	10.03	10.53	12.09	8.48	8.98	9.62	10.12	11.69
	4H	9.60	10.06	10.74	11.19	12.77	9.17	9.63	10.32	10.76	12.35
	6H	10.11	10.50	11.26	11.66	13.23	9.67	10.07	10.83	11.22	12.80
	8H	10.25	10.62	11.41	11.77	13.36	9.82	10.19	10.97	11.33	12.92
	12H	10.32	10.66	11.49	11.81	13.41	9.87	10.21	11.04	11.36	12.96
8H	4H	9.78	10.15	10.93	11.29	12.89	9.40	9.77	10.56	10.92	12.51
	6H	10.41	10.71	11.58	11.90	13.49	10.03	10.33	11.20	11.52	13.11
	8H	10.63	10.90	11.81	12.06	13.67	10.24	10.51	11.42	11.67	13.28
	12H	10.76	10.99	11.94	12.16	13.80	10.35	10.58	11.53	11.75	13.39
12H	4H	9.76	10.09	10.93	11.25	12.85	9.39	9.73	10.56	10.88	12.48
	6H	10.44	10.70	11.62	11.87	13.48	10.07	10.33	11.24	11.50	13.11
	8H	10.68	10.91	11.86	12.07	13.72	10.30	10.53	11.48	11.69	13.34

END OF REPORT