

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920232

Luminaire Tested: DFN2DIP-SQ3F0-110D040US935-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920232
REPORT IS A COMBINATION OF REPORTS P899875 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D040US935-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12424.2 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 142.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920232
CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P920232

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	80	80	80	80	80	80	75
1	104	99	95	91	98	94	91	88	86	83	80	78	76	74	70	69	67	70	69	67	64
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	62	59	57	53
3	86	76	68	62	82	73	66	60	66	61	56	60	56	52	55	51	48	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	49	45	42	39
5	73	60	52	46	69	58	50	44	53	46	42	48	43	39	44	40	36	44	40	36	34
6	67	54	46	40	63	52	44	39	48	41	36	44	38	34	40	36	32	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	34	30	37	32	29	37	32	29	26
8	58	45	37	31	55	43	36	30	40	33	29	37	31	27	34	29	26	34	29	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	31	27	23	21
10	50	38	30	25	48	36	29	25	34	28	23	31	26	22	29	24	21	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4223	4223	4223
5°	4227	4161	4190
10°	4190	4102	4132
15°	4125	4032	4042
20°	4039	3935	3950
25°	3954	3820	3844
30°	3847	3713	3709
35°	3746	3587	3567
40°	3622	3459	3431
45°	3498	3332	3292
50°	3362	3197	3131
55°	3220	3042	2983
60°	3059	2858	2813
65°	2883	2667	2613
70°	2659	2434	2397
75°	2349	2154	2196
80°	1974	1797	1815
85°	1390	1191	1188

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3498 cd/sqm



TEST NUMBER: P920232

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.9	2.8
10°-20°	975.9	7.9
20°-30°	1434.2	11.5
30°-40°	1665.7	13.4
40°-50°	1663.7	13.4
50°-60°	1450.7	11.7
60°-70°	1072.4	8.6
70°-80°	606.7	4.9
80°-90°	163.2	1.3
90°-100°	67.4	0.5
100°-110°	214.2	1.7
110°-120°	366.5	2.9
120°-130°	482.0	3.9
130°-140°	541.0	4.4
140°-150°	530.5	4.3
150°-160°	445.0	3.6
160°-170°	295.1	2.4
170°-180°	103.2	0.8
0°-30°	2757.0	22.2
0°-40°	4422.7	35.6
0°-60°	7537.0	60.7
0°-90°	9379.4	75.5
90°-120°	648.0	5.2
90°-150°	2201.5	17.7
90°-180°	3045.0	24.5
0°-180°	12424.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3671	3632	3660	3654	350
15°	3508	3487	3441	3455	3437	988
25°	3175	3147	3087	3094	3087	1461
35°	2739	2704	2647	2626	2608	1711
45°	2229	2204	2151	2112	2098	1720
55°	1687	1666	1623	1580	1563	1508
65°	1138	1116	1081	1049	1031	1125
75°	595	588	570	549	556	635
85°	145	142	138	127	124	162
90°	1	12	32	30	31	12
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	



TEST NUMBER: P920232

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.2	3685.2	3685.2	3685.2	3685.2
2.5°	3706.6	3688.9	3649.9	3685.2	3678.4
5°	3685.2	3671.3	3632.2	3660.4	3653.6
7.5°	3660.4	3639.4	3600.3	3628.8	3621.7
10°	3621.7	3596.8	3554.4	3582.5	3572.0
12.5°	3568.3	3547.2	3504.8	3522.4	3515.3
15°	3508.1	3487.0	3440.8	3455.1	3437.4
17.5°	3433.7	3412.7	3366.4	3384.1	3366.4
20°	3352.1	3331.0	3281.4	3291.9	3278.1
22.5°	3270.9	3238.9	3192.7	3192.7	3185.5
25°	3175.0	3146.9	3086.7	3093.5	3086.7
27.5°	3068.6	3043.8	2997.9	2987.4	2969.8
30°	2962.6	2934.0	2881.0	2870.5	2856.2
32.5°	2849.0	2828.0	2771.2	2749.8	2735.5
35°	2739.3	2704.0	2647.1	2625.7	2608.0
37.5°	2615.2	2583.3	2526.5	2501.6	2484.0
40°	2487.8	2459.2	2402.4	2370.8	2356.6
42.5°	2363.7	2335.1	2278.7	2243.0	2222.0
45°	2229.1	2204.2	2150.9	2112.2	2097.9
47.5°	2097.9	2073.1	2016.3	1977.2	1956.1
50°	1959.5	1941.9	1892.2	1842.6	1825.0
52.5°	1825.0	1800.1	1754.3	1715.1	1690.3
55°	1687.0	1665.5	1623.1	1580.5	1562.9
57.5°	1548.6	1530.9	1484.7	1442.2	1427.9
60°	1410.2	1396.4	1346.7	1307.6	1297.1
62.5°	1275.7	1250.9	1215.5	1180.2	1165.9
65°	1137.6	1116.2	1080.9	1049.0	1031.3
67.5°	995.9	977.9	946.3	921.5	907.2
70°	864.7	850.4	818.5	793.7	779.7
72.5°	730.1	715.8	698.2	673.4	662.8
75°	595.1	588.4	570.3	549.3	556.5
77.5°	474.8	460.5	453.4	442.9	432.4
80°	354.6	350.8	343.6	333.1	326.0
82.5°	241.0	241.0	237.6	223.3	223.3
85°	145.2	141.7	138.4	127.4	124.1
87.5°	63.9	56.7	49.6	39.1	35.3
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1



TEST NUMBER: P920232

CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2



TEST NUMBER: P920232
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D040US935-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.32	15.47	15.03	16.20	17.05	13.88	15.03	14.58	15.75	16.60
	3H	16.00	17.03	16.72	17.77	18.65	15.51	16.54	16.23	17.28	18.16
	4H	16.60	17.57	17.33	18.32	19.21	16.10	17.08	16.84	17.82	18.72
	6H	17.01	17.91	17.76	18.66	19.57	16.51	17.41	17.26	18.16	19.07
	8H	17.12	17.98	17.88	18.75	19.66	16.62	17.48	17.38	18.25	19.16
	12H	17.18	18.00	17.94	18.76	19.70	16.67	17.49	17.43	18.25	19.19
4H	2H	14.82	15.79	15.55	16.53	17.43	14.46	15.44	15.20	16.18	17.08
	3H	16.70	17.52	17.45	18.29	19.21	16.29	17.11	17.04	17.89	18.80
	4H	17.42	18.16	18.19	18.94	19.89	17.00	17.74	17.77	18.52	19.46
	6H	17.95	18.59	18.73	19.40	20.35	17.52	18.16	18.30	18.96	19.92
	8H	18.10	18.70	18.89	19.50	20.47	17.67	18.27	18.46	19.07	20.03
	12H	18.19	18.73	19.00	19.55	20.52	17.74	18.28	18.55	19.10	20.07
8H	4H	17.64	18.24	18.43	19.04	20.00	17.26	17.86	18.05	18.66	19.63
	6H	18.28	18.77	19.09	19.61	20.58	17.89	18.39	18.71	19.23	20.20
	8H	18.50	18.94	19.33	19.78	20.76	18.10	18.55	18.93	19.39	20.37
	12H	18.64	19.03	19.47	19.86	20.90	18.23	18.62	19.06	19.45	20.49
12H	4H	17.64	18.18	18.45	19.00	19.97	17.27	17.81	18.08	18.63	19.60
	6H	18.31	18.75	19.14	19.59	20.57	17.93	18.38	18.76	19.22	20.20
	8H	18.56	18.95	19.39	19.78	20.82	18.18	18.57	19.01	19.40	20.44