

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904041

Luminaire Tested: DFN2DIP-SQ4F0-080D160US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904041
REPORT IS A COMBINATION OF REPORTS P901727 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D160US830-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22394.8 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2059	2059	2059
5°	2062	2030	2044
10°	2045	2003	2017
15°	2015	1971	1975
20°	1974	1925	1931
25°	1934	1871	1880
30°	1883	1821	1816
35°	1835	1761	1747
40°	1776	1700	1682
45°	1717	1640	1616
50°	1653	1577	1539
55°	1585	1503	1469
60°	1509	1416	1388
65°	1426	1326	1292
70°	1320	1216	1190
75°	1173	1085	1097
80°	996	918	916
85°	720	628	616

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2726 cd/sqm

TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	1.2
10°-20°	777.0	3.5
20°-30°	1141.8	5.1
30°-40°	1326.2	5.9
40°-50°	1324.5	5.9
50°-60°	1155.0	5.2
60°-70°	853.8	3.8
70°-80°	483.0	2.2
80°-90°	136.5	0.6
90°-100°	167.8	0.7
100°-110°	625.6	2.8
110°-120°	1659.3	7.4
120°-130°	2752.0	12.3
130°-140°	2923.2	13.1
140°-150°	2716.8	12.1
150°-160°	2184.3	9.8
160°-170°	1407.5	6.3
170°-180°	484.4	2.2
0°-30°	2195.0	9.8
0°-40°	3521.1	15.7
0°-60°	6000.6	26.8
0°-90°	7473.9	33.4
90°-120°	2452.7	11.0
90°-150°	10844.8	48.4
90°-180°	14921.0	66.6
0°-180°	22394.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	4	44	73	92	99	21
95°	239	118	144	162	158	283
105°	1120	1230	225	265	280	1196
115°	2118	2180	2272	567	302	2085
125°	2994	3042	3112	3138	3149	2670
135°	3705	3764	3797	3834	3826	2862
145°	4298	4294	4357	4382	4364	2688
155°	4732	4699	4744	4766	4736	2181
165°	4986	4964	4975	5001	4975	1409
175°	5100	5075	5082	5108	5071	485
180°	5090	5090	5090	5090	5090	

TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	3.5	44.2	73.4	92.3	99.2
92.5°	92.3	77.4	88.3	95.8	99.2
95°	239.2	117.6	143.5	162.2	158.3
97.5°	430.7	129.0	187.6	199.0	202.5
100°	652.1	147.4	209.9	239.2	246.7
102.5°	894.8	887.8	217.4	257.6	268.9
105°	1119.6	1230.2	224.8	265.0	279.8
107.5°	1381.0	1472.9	232.2	272.5	287.3
110°	1631.6	1708.6	644.6	276.4	290.8

TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1867.4	1933.4	1870.9	283.4	294.7
115°	2117.5	2180.0	2272.3	567.2	302.2
117.5°	2334.9	2408.3	2471.3	1944.4	979.6
120°	2578.0	2633.1	2699.5	2743.7	2246.5
122.5°	2784.0	2843.0	2916.9	2938.8	2942.7
125°	2993.9	3042.0	3112.0	3137.8	3148.8
127.5°	3185.4	3237.1	3292.6	3329.3	3332.8
130°	3366.1	3425.1	3465.4	3506.0	3502.5
132.5°	3550.2	3598.2	3638.5	3671.8	3668.3
135°	3704.9	3764.0	3796.8	3834.0	3826.5
137.5°	3866.8	3911.0	3948.1	3984.9	3973.9
140°	4025.1	4054.8	4095.1	4128.3	4110.0
142.5°	4158.0	4183.9	4231.5	4260.9	4242.5
145°	4298.0	4294.0	4356.6	4382.4	4364.1
147.5°	4419.1	4408.2	4470.8	4489.1	4474.6
150°	4537.2	4511.4	4570.5	4592.3	4574.0
152.5°	4636.5	4607.1	4662.3	4684.6	4658.8
155°	4732.2	4699.4	4743.6	4765.5	4736.2
157.5°	4809.7	4780.4	4813.6	4839.4	4809.7
160°	4876.1	4853.8	4876.1	4898.0	4872.2
162.5°	4934.8	4912.9	4931.2	4957.0	4923.8
165°	4986.3	4964.5	4975.4	5001.2	4975.4
167.5°	5027.0	5004.7	5016.1	5041.8	5008.7
170°	5060.2	5038.0	5045.3	5071.2	5038.0
172.5°	5082.1	5060.2	5067.7	5093.5	5060.2
175°	5100.5	5074.6	5082.1	5107.9	5071.2
177.5°	5107.9	5082.1	5086.1	5111.9	5078.6
180°	5089.5	5089.5	5089.5	5089.5	5089.5

TEST NUMBER: P904041

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.02	8.75	9.11	9.84	11.33	7.58	8.31	8.66	9.39	10.88
	3H	9.68	10.33	10.77	11.42	12.93	9.18	9.84	10.28	10.93	12.44
	4H	10.26	10.88	11.37	11.98	13.49	9.77	10.39	10.87	11.48	13.00
	6H	10.66	11.23	11.77	12.33	13.85	10.16	10.73	11.27	11.83	13.35
	8H	10.76	11.30	11.88	12.42	13.94	10.26	10.80	11.38	11.91	13.43
	12H	10.80	11.32	11.93	12.43	13.97	10.29	10.81	11.42	11.92	13.46
4H	2H	8.47	9.09	9.58	10.18	11.70	8.11	8.73	9.23	9.83	11.34
	3H	10.32	10.84	11.44	11.96	13.49	9.92	10.43	11.04	11.56	13.08
	4H	11.04	11.51	12.16	12.62	14.17	10.61	11.09	11.74	12.20	13.75
	6H	11.55	11.96	12.68	13.09	14.63	11.12	11.52	12.25	12.66	14.20
	8H	11.70	12.08	12.83	13.20	14.76	11.26	11.64	12.39	12.77	14.32
	12H	11.77	12.11	12.91	13.25	14.81	11.32	11.66	12.46	12.80	14.36
8H	4H	11.22	11.60	12.35	12.73	14.29	10.85	11.23	11.98	12.35	13.91
	6H	11.85	12.17	13.01	13.34	14.89	11.47	11.78	12.62	12.95	14.50
	8H	12.08	12.35	13.23	13.50	15.07	11.68	11.96	12.84	13.11	14.68
	12H	12.20	12.45	13.37	13.59	15.20	11.79	12.03	12.96	13.18	14.79
12H	4H	11.20	11.55	12.35	12.69	14.25	10.83	11.18	11.98	12.32	13.88
	6H	11.88	12.16	13.04	13.31	14.88	11.51	11.79	12.67	12.93	14.51
	8H	12.12	12.36	13.28	13.51	15.12	11.74	11.98	12.90	13.13	14.73

END OF REPORT