

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904075

Luminaire Tested: DFN2DIP-SQ4F0-090D140US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904075
REPORT IS A COMBINATION OF REPORTS P901712 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US830-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20274.1 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	28	25	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	61	50	42	37	56	46	39	34	37	32	29	30	26	24	23	20	19
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	17
8	53	41	34	28	48	38	31	26	31	26	23	25	21	19	19	17	15
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2460	2460	2460
5°	2464	2422	2437
10°	2440	2374	2359
15°	2406	2296	2237
20°	2361	2189	2087
25°	2316	2068	1942
30°	2255	1944	1758
35°	2195	1811	1597
40°	2134	1673	1411
45°	2063	1519	1243
50°	1990	1365	1079
55°	1913	1199	921
60°	1825	1027	759
65°	1723	851	684
70°	1600	687	620
75°	1445	606	566
80°	1220	510	493
85°	849	343	375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2388 cd/sqm

TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	1.6
10°-20°	902.0	4.4
20°-30°	1266.4	6.2
30°-40°	1380.5	6.8
40°-50°	1268.8	6.3
50°-60°	996.5	4.9
60°-70°	648.6	3.2
70°-80°	333.9	1.6
80°-90°	93.1	0.5
90°-100°	146.9	0.7
100°-110°	547.4	2.7
110°-120°	1451.8	7.2
120°-130°	2408.0	11.9
130°-140°	2557.8	12.6
140°-150°	2377.2	11.7
150°-160°	1911.2	9.4
160°-170°	1231.5	6.1
170°-180°	423.9	2.1
0°-30°	2497.0	12.3
0°-40°	3877.5	19.1
0°-60°	6142.8	30.3
0°-90°	7218.3	35.6
90°-120°	2146.1	10.6
90°-150°	9489.1	46.8
90°-180°	13056.0	64.4
0°-180°	20274.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3335	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1920	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	3	39	64	81	87	19
95°	209	103	126	142	139	248
105°	980	1076	197	232	245	1047
115°	1853	1908	1988	496	264	1824
125°	2620	2662	2723	2746	2755	2336
135°	3242	3294	3322	3355	3348	2504
145°	3761	3757	3812	3835	3818	2352
155°	4141	4112	4151	4170	4144	1908
165°	4363	4344	4354	4376	4354	1233
175°	4463	4440	4447	4469	4437	425
180°	4453	4453	4453	4453	4453	

TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3506.0	3506.0	3506.0	3506.0	3506.0
2.5°	3521.8	3506.0	3470.9	3503.0	3496.5
5°	3506.0	3490.1	3448.8	3477.3	3467.9
7.5°	3477.3	3458.5	3414.1	3426.5	3410.7
10°	3439.3	3417.1	3353.8	3344.0	3325.2
12.5°	3391.8	3363.3	3277.4	3258.6	3223.5
15°	3334.6	3299.7	3191.9	3131.6	3100.0
17.5°	3268.0	3217.2	3083.8	3014.2	2963.4
20°	3191.9	3128.3	2969.7	2890.6	2820.6
22.5°	3109.4	3036.4	2852.2	2744.5	2697.1
25°	3027.0	2925.3	2715.9	2586.0	2538.2
27.5°	2928.7	2820.6	2589.0	2439.9	2366.8
30°	2824.0	2703.1	2449.3	2287.7	2201.9
32.5°	2722.3	2576.2	2316.3	2125.8	2046.4
35°	2608.2	2446.3	2167.2	1967.3	1897.2
37.5°	2497.1	2322.4	2027.5	1808.4	1729.3
40°	2379.6	2189.4	1881.4	1656.2	1573.8
42.5°	2259.1	2056.2	1735.6	1500.7	1421.5
45°	2132.2	1919.5	1586.5	1360.9	1284.9
47.5°	2011.7	1786.5	1443.8	1218.2	1148.6
50°	1878.4	1653.1	1304.1	1085.0	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.2
55°	1621.2	1373.8	1031.0	840.9	780.6
57.5°	1491.3	1237.5	907.6	729.8	679.0
60°	1357.9	1104.1	777.3	615.7	564.9
62.5°	1228.0	974.2	666.2	514.1	488.8
65°	1094.7	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.6	472.6	307.6	282.4	276.1
75°	583.7	361.6	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.9	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	3.0	38.6	64.3	80.8	86.9
92.5°	80.8	67.8	77.3	83.8	86.9
95°	209.3	102.9	125.5	141.9	138.6
97.5°	376.9	112.9	164.2	174.1	177.2
100°	570.5	128.9	183.7	209.3	215.8
102.5°	782.9	776.7	190.2	225.4	235.4
105°	979.6	1076.4	196.7	231.9	244.9
107.5°	1208.4	1288.7	203.2	238.4	251.4
110°	1427.7	1495.1	564.0	241.9	254.5

TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1633.9	1691.7	1637.0	248.0	257.9
115°	1852.8	1907.5	1988.3	496.3	264.4
117.5°	2043.0	2107.2	2162.4	1701.3	857.1
120°	2255.8	2304.0	2362.1	2400.7	1965.7
122.5°	2436.0	2487.7	2552.3	2571.4	2574.9
125°	2619.7	2661.7	2723.0	2745.5	2755.1
127.5°	2787.3	2832.4	2881.0	2913.1	2916.2
130°	2945.3	2997.0	3032.2	3067.8	3064.7
132.5°	3106.4	3148.5	3183.7	3212.7	3209.7
135°	3241.9	3293.5	3322.2	3354.7	3348.2
137.5°	3383.4	3422.1	3454.6	3486.7	3477.2
140°	3522.0	3548.0	3583.2	3612.3	3596.2
142.5°	3638.3	3660.8	3702.6	3728.2	3712.1
145°	3760.7	3757.3	3812.0	3834.6	3818.5
147.5°	3866.8	3857.2	3911.9	3928.0	3915.3
150°	3970.1	3947.5	3999.1	4018.2	4002.2
152.5°	4056.9	4031.3	4079.5	4099.0	4076.4
155°	4140.7	4112.0	4150.7	4169.8	4144.2
157.5°	4208.5	4182.8	4211.9	4234.5	4208.5
160°	4266.6	4247.1	4266.6	4285.7	4263.2
162.5°	4317.9	4298.7	4314.9	4337.4	4308.4
165°	4363.0	4343.9	4353.5	4376.0	4353.5
167.5°	4398.7	4379.1	4389.0	4411.7	4382.5
170°	4427.7	4408.2	4414.7	4437.3	4408.2
172.5°	4446.8	4427.7	4434.2	4456.8	4427.7
175°	4462.9	4440.3	4446.8	4469.4	4437.3
177.5°	4469.4	4446.8	4450.3	4472.8	4443.8
180°	4453.3	4453.3	4453.3	4453.3	4453.3

TEST NUMBER: P904075

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.77	9.50	9.85	10.57	12.04	4.73	5.46	5.81	6.53	8.00
	3H	10.45	11.09	11.53	12.18	13.66	5.91	6.56	7.00	7.65	9.13
	4H	11.05	11.67	12.15	12.75	14.24	6.36	6.97	7.46	8.06	9.55
	6H	11.47	12.04	12.58	13.13	14.63	6.68	7.24	7.78	8.33	9.83
	8H	11.60	12.14	12.71	13.24	14.73	6.76	7.30	7.87	8.41	9.90
	12H	11.66	12.17	12.77	13.27	14.78	6.81	7.32	7.92	8.41	9.93
4H	2H	8.78	9.39	9.88	10.48	11.97	5.32	5.93	6.42	7.02	8.51
	3H	10.60	11.11	11.71	12.22	13.73	6.66	7.17	7.77	8.28	9.78
	4H	11.29	11.76	12.41	12.86	14.39	7.20	7.67	8.32	8.77	10.30
	6H	11.81	12.21	12.93	13.33	14.85	7.62	8.02	8.74	9.14	10.66
	8H	11.98	12.36	13.10	13.47	15.00	7.75	8.12	8.87	9.24	10.77
	12H	12.08	12.42	13.21	13.54	15.08	7.81	8.15	8.94	9.27	10.81
8H	4H	11.25	11.63	12.38	12.74	14.28	7.48	7.85	8.60	8.97	10.50
	6H	11.82	12.13	12.96	13.29	14.82	8.00	8.30	9.14	9.46	10.99
	8H	12.04	12.31	13.19	13.45	15.00	8.19	8.46	9.34	9.60	11.14
	12H	12.18	12.41	13.33	13.55	15.13	8.30	8.54	9.45	9.67	11.26
12H	4H	11.20	11.54	12.34	12.67	14.20	7.48	7.82	8.62	8.95	10.48
	6H	11.80	12.07	12.94	13.20	14.75	8.05	8.32	9.19	9.45	11.00
	8H	12.02	12.25	13.17	13.39	14.97	8.25	8.49	9.40	9.62	11.21