

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904110

Luminaire Tested: DFN2DIP-SQ4F0-100D140US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904110
REPORT IS A COMBINATION OF REPORTS P900194 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D140US830-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19689.7 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 198.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2733	2733	2733
5°	2738	2691	2708
10°	2711	2638	2621
15°	2673	2552	2485
20°	2624	2432	2319
25°	2573	2298	2158
30°	2505	2160	1954
35°	2439	2012	1774
40°	2371	1859	1568
45°	2292	1688	1381
50°	2211	1516	1199
55°	2126	1333	1024
60°	2028	1141	843
65°	1915	945	760
70°	1778	763	689
75°	1605	674	628
80°	1356	567	548
85°	944	381	417

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3284 cd/sqm

TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	1.9
10°-20°	1002.2	5.1
20°-30°	1407.1	7.1
30°-40°	1533.9	7.8
40°-50°	1409.8	7.2
50°-60°	1107.2	5.6
60°-70°	720.7	3.7
70°-80°	371.0	1.9
80°-90°	106.6	0.5
90°-100°	258.2	1.3
100°-110°	820.5	4.2
110°-120°	1404.2	7.1
120°-130°	1846.7	9.4
130°-140°	2072.8	10.5
140°-150°	2032.6	10.3
150°-160°	1705.1	8.7
160°-170°	1130.8	5.7
170°-180°	395.2	2.0
0°-30°	2774.5	14.1
0°-40°	4308.3	21.9
0°-60°	6825.3	34.7
0°-90°	8023.4	40.7
90°-120°	2483.0	12.6
90°-150°	8435.1	42.8
90°-180°	11666.0	59.2
0°-180°	19689.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3896	3896	3896	3896	3896	
5°	3896	3878	3832	3864	3853	369
15°	3705	3666	3546	3480	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1830
55°	1801	1526	1146	934	867	1610
65°	1216	931	613	494	483	1206
75°	649	402	282	257	254	686
85°	152	77	67	67	67	174
90°	4	45	123	116	120	19
95°	184	219	225	225	219	204
105°	757	768	775	781	781	799
115°	1409	1429	1423	1419	1409	1394
125°	2050	2081	2071	2060	2056	1831
135°	2651	2690	2698	2694	2684	2049
145°	3218	3244	3264	3267	3254	2011
155°	3680	3690	3702	3719	3708	1694
165°	4003	4000	4000	4025	4007	1129
175°	4166	4156	4148	4173	4152	396
180°	4173	4173	4173	4173	4173	

TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.5	3895.5	3895.5	3895.5	3895.5
2.5°	3913.1	3895.5	3856.6	3892.1	3885.1
5°	3895.5	3877.9	3831.9	3863.8	3853.2
7.5°	3863.8	3842.7	3793.4	3807.2	3789.7
10°	3821.4	3796.7	3726.4	3715.6	3694.7
12.5°	3768.8	3736.9	3641.5	3620.6	3581.7
15°	3705.1	3666.2	3546.5	3479.6	3444.4
17.5°	3631.0	3574.6	3426.5	3349.0	3292.6
20°	3546.5	3475.8	3299.7	3211.8	3134.0
22.5°	3454.9	3373.7	3169.1	3049.5	2996.7
25°	3363.3	3250.4	3017.6	2873.2	2820.2
27.5°	3254.0	3134.0	2876.6	2710.9	2629.8
30°	3137.7	3003.4	2721.4	2541.9	2446.6
32.5°	3024.8	2862.4	2573.7	2362.0	2273.7
35°	2897.9	2718.1	2408.0	2185.8	2108.0
37.5°	2774.6	2580.4	2252.8	2009.3	1921.4
40°	2644.0	2432.7	2090.5	1840.2	1748.6
42.5°	2510.1	2284.5	1928.5	1667.5	1579.5
45°	2369.1	2132.7	1762.8	1512.2	1427.7
47.5°	2235.2	1985.0	1604.2	1353.6	1276.2
50°	2087.1	1836.8	1449.0	1205.5	1131.8
52.5°	1942.3	1677.9	1300.9	1068.2	1001.3
55°	1801.3	1526.4	1145.7	934.3	867.3
57.5°	1657.0	1374.9	1008.4	810.9	754.4
60°	1508.8	1226.8	863.7	684.1	627.6
62.5°	1364.4	1082.4	740.2	571.2	543.1
65°	1216.4	930.6	613.4	493.7	482.9
67.5°	1075.3	789.6	493.7	433.5	423.0
70°	927.2	652.3	408.8	373.6	359.5
72.5°	786.2	525.1	341.9	313.8	306.7
75°	648.6	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.2	207.9	200.9
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	3.8	45.3	123.3	115.7	119.5
92.5°	78.0	105.7	109.4	113.2	113.2
95°	183.7	219.0	225.2	225.2	219.0
97.5°	305.8	338.5	352.3	352.3	352.3
100°	446.7	475.6	485.6	485.6	481.8
102.5°	595.1	616.5	630.4	634.1	630.4
105°	757.4	767.5	775.1	781.3	781.3
107.5°	918.4	933.6	933.6	936.0	918.4
110°	1074.5	1094.6	1094.6	1094.6	1084.5

TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1243.0	1264.4	1260.7	1250.6	1243.0
115°	1409.1	1429.3	1423.0	1419.2	1409.1
117.5°	1574.0	1601.7	1584.0	1574.0	1563.9
120°	1740.0	1767.7	1740.0	1740.0	1728.7
122.5°	1891.0	1926.2	1908.6	1898.6	1891.0
125°	2049.6	2080.9	2070.9	2059.5	2055.8
127.5°	2204.2	2243.3	2229.4	2214.3	2204.2
130°	2348.9	2394.2	2387.9	2380.4	2366.5
132.5°	2511.2	2546.5	2549.0	2531.4	2521.3
135°	2650.9	2689.9	2697.5	2693.7	2683.6
137.5°	2806.9	2838.4	2844.7	2842.1	2827.1
140°	2944.0	2975.5	2993.1	2993.1	2979.3
142.5°	3084.9	3116.4	3126.5	3130.3	3116.4
145°	3218.3	3243.5	3263.6	3267.4	3253.6
147.5°	3337.8	3369.3	3384.4	3390.7	3376.8
150°	3461.1	3482.5	3496.4	3507.7	3496.4
152.5°	3570.6	3592.0	3609.7	3623.4	3609.7
155°	3680.1	3690.1	3701.5	3719.1	3707.8
157.5°	3774.4	3782.0	3788.3	3813.4	3795.8
160°	3858.8	3866.3	3870.1	3891.5	3876.3
162.5°	3936.7	3936.7	3940.5	3964.4	3946.8
165°	4003.4	3999.7	3999.7	4024.8	4007.2
167.5°	4063.8	4052.5	4052.5	4077.6	4060.0
170°	4109.1	4099.0	4095.3	4120.4	4099.0
172.5°	4140.6	4130.5	4126.7	4151.9	4130.5
175°	4165.8	4155.7	4148.1	4173.3	4151.9
177.5°	4179.5	4169.5	4162.0	4183.3	4162.0
180°	4173.3	4173.3	4173.3	4173.3	4173.3

TEST NUMBER: P904110

CATALOG NUMBER: DFN2DIP-SQ4F0-100D140US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.72	10.48	10.76	11.52	12.92	5.68	6.44	6.72	7.48	8.88
	3H	11.40	12.08	12.45	13.13	14.55	6.87	7.55	7.91	8.60	10.01
	4H	12.01	12.65	13.07	13.70	15.13	7.31	7.96	8.37	9.01	10.44
	6H	12.43	13.02	13.50	14.08	15.51	7.63	8.22	8.70	9.28	10.72
	8H	12.55	13.12	13.63	14.19	15.62	7.72	8.28	8.79	9.36	10.79
	12H	12.62	13.15	13.69	14.22	15.67	7.76	8.30	8.84	9.36	10.82
4H	2H	9.73	10.37	10.80	11.43	12.85	6.27	6.92	7.34	7.97	9.39
	3H	11.56	12.09	12.63	13.17	14.61	7.62	8.15	8.69	9.23	10.67
	4H	12.25	12.74	13.33	13.81	15.27	8.16	8.65	9.24	9.72	11.18
	6H	12.77	13.19	13.86	14.28	15.74	8.58	9.00	9.67	10.09	11.55
	8H	12.94	13.34	14.03	14.42	15.89	8.71	9.10	9.79	10.18	11.65
	12H	13.04	13.39	14.14	14.49	15.97	8.77	9.12	9.87	10.22	11.70
8H	4H	12.21	12.61	13.30	13.69	15.16	8.44	8.83	9.53	9.92	11.39
	6H	12.78	13.11	13.89	14.23	15.70	8.96	9.28	10.07	10.41	11.88
	8H	13.00	13.29	14.12	14.40	15.88	9.15	9.43	10.27	10.54	12.03
	12H	13.14	13.39	14.26	14.50	16.02	9.26	9.51	10.39	10.62	12.15
12H	4H	12.16	12.52	13.27	13.62	15.09	8.44	8.80	9.55	9.90	11.37
	6H	12.76	13.04	13.87	14.15	15.64	9.01	9.29	10.12	10.40	11.89
	8H	12.98	13.23	14.10	14.33	15.86	9.22	9.46	10.34	10.57	12.10

END OF REPORT