

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904115

Luminaire Tested: DFN2DIP-SQ4F0-100D160US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904115
REPORT IS A COMBINATION OF REPORTS P901732 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US830-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22941.5 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2733	2733	2733
5°	2738	2691	2708
10°	2711	2638	2621
15°	2673	2552	2485
20°	2624	2432	2319
25°	2573	2298	2158
30°	2505	2160	1954
35°	2439	2012	1774
40°	2371	1859	1568
45°	2292	1688	1381
50°	2211	1516	1199
55°	2126	1333	1024
60°	2028	1141	843
65°	1915	945	760
70°	1778	763	689
75°	1605	674	628
80°	1356	567	548
85°	944	381	417

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2726 cd/sqm

TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	1.6
10°-20°	1002.2	4.4
20°-30°	1407.1	6.1
30°-40°	1533.9	6.7
40°-50°	1409.8	6.1
50°-60°	1107.2	4.8
60°-70°	720.7	3.1
70°-80°	371.0	1.6
80°-90°	103.7	0.5
90°-100°	167.8	0.7
100°-110°	625.6	2.7
110°-120°	1659.3	7.2
120°-130°	2752.0	12.0
130°-140°	2923.2	12.7
140°-150°	2716.8	11.8
150°-160°	2184.3	9.5
160°-170°	1407.5	6.1
170°-180°	484.4	2.1
0°-30°	2774.5	12.1
0°-40°	4308.3	18.8
0°-60°	6825.3	29.8
0°-90°	8020.5	35.0
90°-120°	2452.7	10.7
90°-150°	10844.8	47.3
90°-180°	14921.0	65.0
0°-180°	22941.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3896	3896	3896	3896	3896	
5°	3896	3878	3832	3864	3853	369
15°	3705	3666	3546	3480	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1830
55°	1801	1526	1146	934	867	1610
65°	1216	931	613	494	483	1206
75°	649	402	282	257	254	686
85°	152	77	67	67	67	174
90°	4	44	73	92	99	21
95°	239	118	144	162	158	283
105°	1120	1230	225	265	280	1196
115°	2118	2180	2272	567	302	2085
125°	2994	3042	3112	3138	3149	2670
135°	3705	3764	3797	3834	3826	2862
145°	4298	4294	4357	4382	4364	2688
155°	4732	4699	4744	4766	4736	2181
165°	4986	4964	4975	5001	4975	1409
175°	5100	5075	5082	5108	5071	485
180°	5090	5090	5090	5090	5090	

TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.5	3895.5	3895.5	3895.5	3895.5
2.5°	3913.1	3895.5	3856.6	3892.1	3885.1
5°	3895.5	3877.9	3831.9	3863.8	3853.2
7.5°	3863.8	3842.7	3793.4	3807.2	3789.7
10°	3821.4	3796.7	3726.4	3715.6	3694.7
12.5°	3768.8	3736.9	3641.5	3620.6	3581.7
15°	3705.1	3666.2	3546.5	3479.6	3444.4
17.5°	3631.0	3574.6	3426.5	3349.0	3292.6
20°	3546.5	3475.8	3299.7	3211.8	3134.0
22.5°	3454.9	3373.7	3169.1	3049.5	2996.7
25°	3363.3	3250.4	3017.6	2873.2	2820.2
27.5°	3254.0	3134.0	2876.6	2710.9	2629.8
30°	3137.7	3003.4	2721.4	2541.9	2446.6
32.5°	3024.8	2862.4	2573.7	2362.0	2273.7
35°	2897.9	2718.1	2408.0	2185.8	2108.0
37.5°	2774.6	2580.4	2252.8	2009.3	1921.4
40°	2644.0	2432.7	2090.5	1840.2	1748.6
42.5°	2510.1	2284.5	1928.5	1667.5	1579.5
45°	2369.1	2132.7	1762.8	1512.2	1427.7
47.5°	2235.2	1985.0	1604.2	1353.6	1276.2
50°	2087.1	1836.8	1449.0	1205.5	1131.8
52.5°	1942.3	1677.9	1300.9	1068.2	1001.3
55°	1801.3	1526.4	1145.7	934.3	867.3
57.5°	1657.0	1374.9	1008.4	810.9	754.4
60°	1508.8	1226.8	863.7	684.1	627.6
62.5°	1364.4	1082.4	740.2	571.2	543.1
65°	1216.4	930.6	613.4	493.7	482.9
67.5°	1075.3	789.6	493.7	433.5	423.0
70°	927.2	652.3	408.8	373.6	359.5
72.5°	786.2	525.1	341.9	313.8	306.7
75°	648.6	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.2	207.9	200.9
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	3.5	44.2	73.4	92.3	99.2
92.5°	92.3	77.4	88.3	95.8	99.2
95°	239.2	117.6	143.5	162.2	158.3
97.5°	430.7	129.0	187.6	199.0	202.5
100°	652.1	147.4	209.9	239.2	246.7
102.5°	894.8	887.8	217.4	257.6	268.9
105°	1119.6	1230.2	224.8	265.0	279.8
107.5°	1381.0	1472.9	232.2	272.5	287.3
110°	1631.6	1708.6	644.6	276.4	290.8

TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1867.4	1933.4	1870.9	283.4	294.7
115°	2117.5	2180.0	2272.3	567.2	302.2
117.5°	2334.9	2408.3	2471.3	1944.4	979.6
120°	2578.0	2633.1	2699.5	2743.7	2246.5
122.5°	2784.0	2843.0	2916.9	2938.8	2942.7
125°	2993.9	3042.0	3112.0	3137.8	3148.8
127.5°	3185.4	3237.1	3292.6	3329.3	3332.8
130°	3366.1	3425.1	3465.4	3506.0	3502.5
132.5°	3550.2	3598.2	3638.5	3671.8	3668.3
135°	3704.9	3764.0	3796.8	3834.0	3826.5
137.5°	3866.8	3911.0	3948.1	3984.9	3973.9
140°	4025.1	4054.8	4095.1	4128.3	4110.0
142.5°	4158.0	4183.9	4231.5	4260.9	4242.5
145°	4298.0	4294.0	4356.6	4382.4	4364.1
147.5°	4419.1	4408.2	4470.8	4489.1	4474.6
150°	4537.2	4511.4	4570.5	4592.3	4574.0
152.5°	4636.5	4607.1	4662.3	4684.6	4658.8
155°	4732.2	4699.4	4743.6	4765.5	4736.2
157.5°	4809.7	4780.4	4813.6	4839.4	4809.7
160°	4876.1	4853.8	4876.1	4898.0	4872.2
162.5°	4934.8	4912.9	4931.2	4957.0	4923.8
165°	4986.3	4964.5	4975.4	5001.2	4975.4
167.5°	5027.0	5004.7	5016.1	5041.8	5008.7
170°	5060.2	5038.0	5045.3	5071.2	5038.0
172.5°	5082.1	5060.2	5067.7	5093.5	5060.2
175°	5100.5	5074.6	5082.1	5107.9	5071.2
177.5°	5107.9	5082.1	5086.1	5111.9	5078.6
180°	5089.5	5089.5	5089.5	5089.5	5089.5

TEST NUMBER: P904115

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.06	9.78	10.14	10.86	12.33	5.02	5.74	6.10	6.82	8.29
	3H	10.73	11.38	11.83	12.47	13.96	6.20	6.85	7.29	7.93	9.42
	4H	11.34	11.95	12.44	13.04	14.54	6.65	7.26	7.75	8.35	9.84
	6H	11.76	12.32	12.87	13.41	14.92	6.96	7.53	8.07	8.62	10.13
	8H	11.89	12.42	13.00	13.53	15.03	7.05	7.59	8.17	8.69	10.20
	12H	11.95	12.45	13.06	13.55	15.08	7.09	7.60	8.21	8.70	10.23
4H	2H	9.07	9.68	10.17	10.76	12.26	5.61	6.22	6.71	7.31	8.80
	3H	10.89	11.40	12.00	12.51	14.02	6.95	7.46	8.06	8.57	10.08
	4H	11.58	12.05	12.70	13.15	14.68	7.49	7.96	8.61	9.06	10.59
	6H	12.09	12.49	13.22	13.62	15.14	7.91	8.31	9.03	9.43	10.96
	8H	12.27	12.64	13.40	13.76	15.30	8.03	8.41	9.16	9.53	11.06
	12H	12.36	12.70	13.50	13.83	15.37	8.09	8.43	9.24	9.56	11.11
8H	4H	11.54	11.91	12.67	13.03	14.57	7.77	8.14	8.89	9.26	10.80
	6H	12.11	12.42	13.25	13.58	15.11	8.28	8.59	9.43	9.75	11.29
	8H	12.33	12.60	13.48	13.74	15.29	8.47	8.74	9.63	9.88	11.44
	12H	12.46	12.70	13.62	13.84	15.43	8.59	8.82	9.74	9.96	11.55
12H	4H	11.49	11.83	12.63	12.96	14.50	7.77	8.10	8.91	9.24	10.78
	6H	12.08	12.35	13.24	13.49	15.05	8.33	8.60	9.48	9.74	11.30
	8H	12.30	12.54	13.46	13.68	15.27	8.54	8.77	9.69	9.91	11.50

END OF REPORT