

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922776

Luminaire Tested: DFN2DIP-SQ3F0-050D120US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922776
REPORT IS A COMBINATION OF REPORTS P900007 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-050D120US940-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13883.9 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 136.3
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922776
CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P922776

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	39	39	39	39
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	41	39	31	29	28	31	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1988	1988	1988
5°	1990	1959	1973
10°	1972	1931	1945
15°	1942	1898	1903
20°	1902	1853	1860
25°	1861	1798	1809
30°	1811	1748	1746
35°	1763	1689	1679
40°	1705	1629	1615
45°	1647	1568	1550
50°	1583	1505	1474
55°	1516	1432	1404
60°	1440	1345	1324
65°	1357	1255	1230
70°	1252	1146	1129
75°	1106	1014	1034
80°	929	846	855
85°	654	560	559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 3403 cd/sqm



TEST NUMBER: P922776

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	1.2
10°-20°	459.4	3.3
20°-30°	675.2	4.9
30°-40°	784.2	5.6
40°-50°	783.2	5.6
50°-60°	682.9	4.9
60°-70°	504.8	3.6
70°-80°	285.6	2.1
80°-90°	85.0	0.6
90°-100°	209.4	1.5
100°-110°	665.4	4.8
110°-120°	1138.7	8.2
120°-130°	1497.5	10.8
130°-140°	1680.9	12.1
140°-150°	1648.3	11.9
150°-160°	1382.7	10.0
160°-170°	917.0	6.6
170°-180°	320.5	2.3
0°-30°	1297.9	9.3
0°-40°	2082.0	15.0
0°-60°	3548.1	25.6
0°-90°	4423.6	31.9
90°-120°	2013.4	14.5
90°-150°	6840.1	49.3
90°-180°	9460.0	68.1
0°-180°	13883.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	3	37	100	94	97	14
95°	149	178	183	183	178	166
105°	614	622	628	634	634	648
115°	1143	1159	1154	1151	1143	1130
125°	1662	1688	1679	1670	1667	1485
135°	2150	2181	2188	2184	2176	1662
145°	2610	2630	2646	2650	2638	1631
155°	2984	2992	3002	3016	3007	1374
165°	3246	3243	3243	3264	3250	916
175°	3378	3370	3364	3384	3367	321
180°	3384	3384	3384	3384	3384	



TEST NUMBER: P922776

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	3.0	36.7	100.0	93.9	96.9
92.5°	63.2	85.7	88.7	91.8	91.8
95°	148.9	177.5	182.6	182.6	177.5
97.5°	247.9	274.5	285.7	285.7	285.7
100°	362.2	385.7	393.8	393.8	390.7
102.5°	482.6	499.9	511.1	514.2	511.1
105°	614.2	622.3	628.5	633.6	633.6
107.5°	744.8	757.1	757.1	759.0	744.8
110°	871.3	887.6	887.6	887.6	879.5



TEST NUMBER: P922776

CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1008.0	1025.4	1022.3	1014.1	1008.0
115°	1142.6	1159.0	1153.9	1150.8	1142.6
117.5°	1276.3	1298.8	1284.5	1276.3	1268.2
120°	1411.0	1433.4	1411.0	1411.0	1401.9
122.5°	1533.5	1562.0	1547.7	1539.5	1533.5
125°	1662.0	1687.5	1679.4	1670.2	1667.1
127.5°	1787.5	1819.1	1807.9	1795.6	1787.5
130°	1904.8	1941.5	1936.4	1930.3	1919.0
132.5°	2036.4	2065.0	2067.0	2052.7	2044.6
135°	2149.6	2181.3	2187.5	2184.3	2176.2
137.5°	2276.2	2301.7	2306.8	2304.7	2292.5
140°	2387.4	2412.9	2427.1	2427.1	2415.9
142.5°	2501.7	2527.2	2535.3	2538.3	2527.2
145°	2609.8	2630.2	2646.5	2649.6	2638.4
147.5°	2706.7	2732.2	2744.5	2749.6	2738.4
150°	2806.7	2824.0	2835.3	2844.5	2835.3
152.5°	2895.5	2912.8	2927.1	2938.4	2927.1
155°	2984.2	2992.4	3001.6	3015.9	3006.7
157.5°	3060.8	3066.9	3071.9	3092.4	3078.1
160°	3129.1	3135.3	3138.3	3155.7	3143.4
162.5°	3192.3	3192.3	3195.4	3214.8	3200.5
165°	3246.4	3243.4	3243.4	3263.7	3249.5
167.5°	3295.4	3286.2	3286.2	3306.6	3292.4
170°	3332.1	3323.9	3320.9	3341.3	3323.9
172.5°	3357.6	3349.4	3346.4	3366.8	3349.4
175°	3378.1	3369.9	3363.8	3384.1	3366.8
177.5°	3389.3	3381.1	3374.9	3392.3	3374.9
180°	3384.1	3384.1	3384.1	3384.1	3384.1



TEST NUMBER: P922776
 CATALOG NUMBER: DFN2DIP-SQ3F0-050D120US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.66	8.37	8.75	9.47	10.98	7.21	7.93	8.31	9.03	10.53
	3H	9.30	9.95	10.41	11.05	12.58	8.81	9.45	9.92	10.56	12.08
	4H	9.88	10.49	11.00	11.60	13.13	9.38	10.00	10.50	11.10	12.63
	6H	10.27	10.83	11.39	11.94	13.48	9.77	10.33	10.89	11.44	12.98
	8H	10.37	10.90	11.50	12.03	13.56	9.86	10.40	10.99	11.52	13.06
	12H	10.41	10.92	11.54	12.03	13.59	9.90	10.41	11.03	11.52	13.08
4H	2H	8.10	8.71	9.22	9.81	11.34	7.74	8.35	8.87	9.46	10.99
	3H	9.94	10.45	11.07	11.59	13.13	9.53	10.04	10.67	11.18	12.72
	4H	10.65	11.12	11.78	12.24	13.80	10.22	10.69	11.36	11.81	13.38
	6H	11.15	11.55	12.29	12.70	14.25	10.72	11.12	11.86	12.26	13.82
	8H	11.29	11.67	12.43	12.81	14.38	10.86	11.23	12.00	12.37	13.94
	12H	11.36	11.70	12.51	12.85	14.42	10.91	11.25	12.07	12.40	13.97
8H	4H	10.83	11.20	11.97	12.34	13.91	10.45	10.83	11.59	11.96	13.53
	6H	11.45	11.76	12.61	12.94	14.50	11.06	11.37	12.22	12.55	14.12
	8H	11.66	11.93	12.83	13.09	14.68	11.27	11.54	12.44	12.70	14.29
	12H	11.78	12.02	12.96	13.18	14.80	11.37	11.61	12.55	12.77	14.39
12H	4H	10.81	11.15	11.96	12.29	13.87	10.44	10.78	11.59	11.93	13.50
	6H	11.47	11.75	12.64	12.90	14.49	11.10	11.37	12.27	12.53	14.12
	8H	11.71	11.94	12.88	13.10	14.72	11.32	11.56	12.50	12.72	14.34