

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904126

Luminaire Tested: DFN2DIP-SQ4F0-110D080US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904126
REPORT IS A COMBINATION OF REPORTS P900106 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D080US830-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15486.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	79	74	69	68	65	61	59	56	54	50	48	46
3	84	75	67	62	78	70	64	58	61	56	52	53	49	46	45	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	34	30	27
7	61	49	41	35	57	46	39	34	40	35	31	35	31	28	31	27	25
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20
10	49	37	30	26	46	35	29	24	32	26	22	28	24	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3007	3007	3007
5°	3012	2960	2979
10°	2982	2902	2883
15°	2941	2807	2734
20°	2886	2675	2550
25°	2831	2527	2374
30°	2756	2376	2149
35°	2683	2213	1951
40°	2608	2044	1725
45°	2522	1857	1520
50°	2432	1668	1319
55°	2339	1466	1126
60°	2231	1255	928
65°	2106	1040	836
70°	1955	839	758
75°	1766	741	692
80°	1491	624	603
85°	1038	419	459

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2522 cd/sqm

TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	401.6	2.6
10°-20°	1102.5	7.1
20°-30°	1547.8	10.0
30°-40°	1687.2	10.9
40°-50°	1550.8	10.0
50°-60°	1217.9	7.9
60°-70°	792.7	5.1
70°-80°	408.1	2.6
80°-90°	110.9	0.7
90°-100°	147.6	1.0
100°-110°	468.9	3.0
110°-120°	802.4	5.2
120°-130°	1055.3	6.8
130°-140°	1184.5	7.6
140°-150°	1161.5	7.5
150°-160°	974.4	6.3
160°-170°	646.2	4.2
170°-180°	225.9	1.5
0°-30°	3051.9	19.7
0°-40°	4739.1	30.6
0°-60°	7507.8	48.5
0°-90°	8819.5	57.0
90°-120°	1418.8	9.2
90°-150°	4820.1	31.1
90°-180°	6666.0	43.0
0°-180°	15486.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4285	4285	4285	4285	4285	
5°	4285	4266	4215	4250	4239	406
15°	4076	4033	3901	3828	3789	1148
25°	3700	3575	3319	3161	3102	1701
35°	3188	2990	2649	2404	2319	1995
45°	2606	2346	1939	1663	1570	2013
55°	1981	1679	1260	1028	954	1771
65°	1338	1024	675	543	531	1326
75°	713	442	310	283	279	755
85°	167	85	74	74	74	191
90°	2	26	70	66	68	15
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4285.1	4285.1	4285.1	4285.1	4285.1
2.5°	4304.4	4285.1	4242.3	4281.4	4273.6
5°	4285.1	4265.8	4215.1	4250.1	4238.6
7.5°	4250.1	4227.0	4172.7	4188.0	4168.6
10°	4203.6	4176.4	4099.1	4087.1	4064.1
12.5°	4145.6	4110.6	4005.7	3982.6	3939.8
15°	4075.6	4032.9	3901.2	3827.6	3788.8
17.5°	3994.2	3932.1	3769.1	3683.9	3621.8
20°	3901.2	3823.4	3629.6	3532.9	3447.3
22.5°	3800.4	3711.1	3486.1	3354.4	3296.4
25°	3699.6	3575.3	3319.4	3160.6	3102.2
27.5°	3579.5	3447.3	3164.3	2982.0	2892.8
30°	3451.5	3303.8	2993.6	2796.1	2691.1
32.5°	3327.3	3148.7	2831.0	2598.2	2501.1
35°	3187.8	2989.8	2648.8	2404.4	2318.8
37.5°	3052.0	2838.5	2478.0	2210.2	2113.6
40°	2908.4	2676.0	2299.5	2024.2	1923.4
42.5°	2761.1	2513.0	2121.4	1834.2	1737.5
45°	2606.0	2346.0	1939.1	1663.4	1570.5
47.5°	2458.7	2183.5	1764.6	1488.9	1403.8
50°	2295.8	2020.5	1593.9	1326.1	1245.0
52.5°	2136.6	1845.7	1431.0	1175.1	1101.4
55°	1981.4	1679.0	1260.2	1027.7	954.1
57.5°	1822.7	1512.4	1109.2	892.0	829.8
60°	1659.7	1349.5	950.0	752.5	690.4
62.5°	1500.9	1190.7	814.3	628.3	597.4
65°	1337.9	1023.6	674.8	543.1	531.1
67.5°	1182.9	868.6	543.1	476.8	465.3
70°	1019.9	717.6	449.7	411.0	395.4
72.5°	864.8	577.7	376.1	345.2	337.3
75°	713.4	441.9	310.2	283.0	279.4
77.5°	562.4	314.0	244.4	228.8	220.9
80°	422.5	225.1	186.0	170.8	170.8
82.5°	294.5	151.4	128.0	120.2	120.2
85°	166.6	85.2	73.6	73.6	73.6
87.5°	62.1	30.8	30.8	27.1	27.1
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7

TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7

TEST NUMBER: P904126

CATALOG NUMBER: DFN2DIP-SQ4F0-110D080US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.61	12.50	12.51	13.42	14.59	7.57	8.46	8.47	9.38	10.55
	3H	13.30	14.09	14.21	15.02	16.21	8.76	9.56	9.68	10.49	11.68
	4H	13.91	14.66	14.84	15.59	16.80	9.22	9.97	10.15	10.90	12.11
	6H	14.34	15.03	15.28	15.97	17.19	9.54	10.23	10.48	11.17	12.39
	8H	14.47	15.13	15.42	16.08	17.30	9.63	10.29	10.58	11.25	12.46
	12H	14.53	15.16	15.49	16.11	17.35	9.68	10.31	10.63	11.25	12.50
4H	2H	11.63	12.39	12.57	13.32	14.52	8.17	8.93	9.11	9.86	11.06
	3H	13.47	14.10	14.42	15.06	16.28	9.53	10.16	10.48	11.12	12.34
	4H	14.17	14.74	15.13	15.70	16.94	10.08	10.65	11.04	11.61	12.85
	6H	14.69	15.18	15.66	16.16	17.41	10.51	11.00	11.47	11.98	13.22
	8H	14.87	15.33	15.84	16.30	17.56	10.64	11.09	11.61	12.07	13.33
	12H	14.97	15.39	15.96	16.38	17.64	10.70	11.12	11.69	12.11	13.37
8H	4H	14.14	14.60	15.11	15.58	16.83	10.37	10.83	11.34	11.80	13.06
	6H	14.72	15.10	15.71	16.11	17.37	10.89	11.27	11.89	12.29	13.54
	8H	14.94	15.27	15.94	16.27	17.55	11.08	11.42	12.09	12.42	13.70
	12H	15.08	15.37	16.09	16.37	17.69	11.21	11.50	12.21	12.50	13.82
12H	4H	14.10	14.51	15.09	15.50	16.77	10.38	10.79	11.37	11.78	13.04
	6H	14.69	15.03	15.70	16.03	17.31	10.94	11.28	11.95	12.28	13.55
	8H	14.92	15.21	15.92	16.21	17.53	11.16	11.45	12.16	12.45	13.77