

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904144

Luminaire Tested: DFN2DIP-SQ4F0-110D140US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904144
REPORT IS A COMBINATION OF REPORTS P900195 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D140US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21942.4 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2831	2831	2831
5°	2835	2792	2811
10°	2812	2755	2774
15°	2771	2710	2715
20°	2715	2648	2655
25°	2659	2573	2585
30°	2590	2503	2497
35°	2524	2421	2403
40°	2442	2338	2313
45°	2361	2255	2222
50°	2272	2168	2116
55°	2180	2067	2019
60°	2075	1947	1908
65°	1960	1823	1777
70°	1815	1672	1636
75°	1613	1492	1508
80°	1370	1262	1259
85°	990	863	846

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3284 cd/sqm

TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	1.7
10°-20°	1068.3	4.9
20°-30°	1570.0	7.2
30°-40°	1823.5	8.3
40°-50°	1821.2	8.3
50°-60°	1588.0	7.2
60°-70°	1173.9	5.4
70°-80°	664.2	3.0
80°-90°	187.1	0.9
90°-100°	258.2	1.2
100°-110°	820.5	3.7
110°-120°	1404.2	6.4
120°-130°	1846.7	8.4
130°-140°	2072.8	9.4
140°-150°	2032.6	9.3
150°-160°	1705.1	7.8
160°-170°	1130.8	5.2
170°-180°	395.2	1.8
0°-30°	3018.1	13.8
0°-40°	4841.6	22.1
0°-60°	8250.9	37.6
0°-90°	10276.1	46.8
90°-120°	2483.0	11.3
90°-150°	8435.1	38.4
90°-180°	11666.0	53.2
0°-180°	21942.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3767	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1873
45°	2440	2413	2355	2312	2297	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	696
85°	159	155	152	140	136	177
90°	4	45	123	116	120	21
95°	184	219	225	225	219	204
105°	757	768	775	781	781	799
115°	1409	1429	1423	1419	1409	1394
125°	2050	2081	2071	2060	2056	1831
135°	2651	2690	2698	2694	2684	2049
145°	3218	3244	3264	3267	3254	2011
155°	3680	3690	3702	3719	3708	1694
165°	4003	4000	4000	4025	4007	1129
175°	4166	4156	4148	4173	4152	396
180°	4173	4173	4173	4173	4173	

TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.3	4034.3	4034.3	4034.3	4034.3
2.5°	4057.6	4038.3	3995.5	4034.3	4026.8
5°	4034.3	4019.0	3976.2	4007.0	3999.7
7.5°	4007.0	3984.0	3941.2	3972.5	3964.7
10°	3964.7	3937.5	3891.0	3921.8	3910.3
12.5°	3906.3	3883.2	3836.7	3856.0	3848.2
15°	3840.4	3817.3	3766.7	3782.3	3763.0
17.5°	3758.9	3735.9	3685.2	3704.6	3685.2
20°	3669.6	3646.5	3592.2	3603.7	3588.5
22.5°	3580.7	3545.7	3495.0	3495.0	3487.2
25°	3475.7	3444.9	3379.0	3386.5	3379.0
27.5°	3359.2	3332.1	3281.8	3270.3	3251.0
30°	3243.2	3211.9	3153.8	3142.3	3126.7
32.5°	3118.9	3095.9	3033.7	3010.2	2994.6
35°	2998.7	2960.1	2897.8	2874.4	2855.1
37.5°	2862.9	2827.9	2765.8	2738.6	2719.2
40°	2723.4	2692.1	2630.0	2595.4	2579.7
42.5°	2587.6	2556.3	2494.5	2455.4	2432.4
45°	2440.2	2413.0	2354.6	2312.2	2296.6
47.5°	2296.6	2269.5	2207.2	2164.5	2141.4
50°	2145.1	2125.8	2071.4	2017.1	1997.8
52.5°	1997.8	1970.6	1920.4	1877.5	1850.4
55°	1846.7	1823.3	1776.8	1730.2	1710.9
57.5°	1695.3	1675.9	1625.3	1578.8	1563.1
60°	1543.8	1528.6	1474.2	1431.4	1419.9
62.5°	1396.5	1369.3	1330.6	1291.9	1276.3
65°	1245.4	1221.9	1183.3	1148.3	1129.0
67.5°	1090.2	1070.5	1035.9	1008.8	993.2
70°	946.6	930.9	896.0	868.8	853.6
72.5°	799.3	783.6	764.3	737.2	725.6
75°	651.5	644.1	624.3	601.3	609.2
77.5°	519.8	504.2	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	3.8	45.3	123.3	115.7	119.5
92.5°	78.0	105.7	109.4	113.2	113.2
95°	183.7	219.0	225.2	225.2	219.0
97.5°	305.8	338.5	352.3	352.3	352.3
100°	446.7	475.6	485.6	485.6	481.8
102.5°	595.1	616.5	630.4	634.1	630.4
105°	757.4	767.5	775.1	781.3	781.3
107.5°	918.4	933.6	933.6	936.0	918.4
110°	1074.5	1094.6	1094.6	1094.6	1084.5

TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1243.0	1264.4	1260.7	1250.6	1243.0
115°	1409.1	1429.3	1423.0	1419.2	1409.1
117.5°	1574.0	1601.7	1584.0	1574.0	1563.9
120°	1740.0	1767.7	1740.0	1740.0	1728.7
122.5°	1891.0	1926.2	1908.6	1898.6	1891.0
125°	2049.6	2080.9	2070.9	2059.5	2055.8
127.5°	2204.2	2243.3	2229.4	2214.3	2204.2
130°	2348.9	2394.2	2387.9	2380.4	2366.5
132.5°	2511.2	2546.5	2549.0	2531.4	2521.3
135°	2650.9	2689.9	2697.5	2693.7	2683.6
137.5°	2806.9	2838.4	2844.7	2842.1	2827.1
140°	2944.0	2975.5	2993.1	2993.1	2979.3
142.5°	3084.9	3116.4	3126.5	3130.3	3116.4
145°	3218.3	3243.5	3263.6	3267.4	3253.6
147.5°	3337.8	3369.3	3384.4	3390.7	3376.8
150°	3461.1	3482.5	3496.4	3507.7	3496.4
152.5°	3570.6	3592.0	3609.7	3623.4	3609.7
155°	3680.1	3690.1	3701.5	3719.1	3707.8
157.5°	3774.4	3782.0	3788.3	3813.4	3795.8
160°	3858.8	3866.3	3870.1	3891.5	3876.3
162.5°	3936.7	3936.7	3940.5	3964.4	3946.8
165°	4003.4	3999.7	3999.7	4024.8	4007.2
167.5°	4063.8	4052.5	4052.5	4077.6	4060.0
170°	4109.1	4099.0	4095.3	4120.4	4099.0
172.5°	4140.6	4130.5	4126.7	4151.9	4130.5
175°	4165.8	4155.7	4148.1	4173.3	4151.9
177.5°	4179.5	4169.5	4162.0	4183.3	4162.0
180°	4173.3	4173.3	4173.3	4173.3	4173.3

TEST NUMBER: P904144

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.60	11.43	11.58	12.43	13.74	10.15	10.99	11.14	11.98	13.30
	3H	12.26	13.01	13.25	14.01	15.35	11.77	12.52	12.76	13.52	14.86
	4H	12.85	13.56	13.86	14.57	15.91	12.36	13.06	13.36	14.07	15.42
	6H	13.25	13.90	14.27	14.92	16.27	12.75	13.40	13.77	14.42	15.77
	8H	13.36	13.98	14.38	15.01	16.36	12.86	13.48	13.88	14.51	15.86
	12H	13.41	14.00	14.44	15.02	16.40	12.90	13.49	13.93	14.51	15.89
4H	2H	11.06	11.76	12.07	12.77	14.12	10.70	11.41	11.71	12.42	13.76
	3H	12.92	13.51	13.95	14.55	15.91	12.52	13.11	13.54	14.14	15.50
	4H	13.64	14.18	14.67	15.21	16.59	13.22	13.76	14.25	14.79	16.17
	6H	14.16	14.62	15.20	15.68	17.05	13.73	14.19	14.77	15.24	16.62
	8H	14.31	14.74	15.35	15.79	17.18	13.87	14.31	14.91	15.35	16.75
	12H	14.38	14.78	15.44	15.84	17.23	13.93	14.33	14.99	15.39	16.79
8H	4H	13.83	14.27	14.88	15.32	16.71	13.46	13.89	14.50	14.94	16.33
	6H	14.47	14.83	15.54	15.92	17.31	14.09	14.45	15.15	15.53	16.92
	8H	14.69	15.01	15.77	16.08	17.49	14.30	14.62	15.37	15.69	17.10
	12H	14.83	15.10	15.90	16.17	17.62	14.42	14.69	15.49	15.76	17.21
12H	4H	13.82	14.21	14.88	15.27	16.67	13.45	13.84	14.51	14.91	16.30
	6H	14.50	14.82	15.57	15.89	17.30	14.13	14.44	15.20	15.52	16.93
	8H	14.74	15.02	15.82	16.09	17.54	14.36	14.64	15.44	15.71	17.16

END OF REPORT