

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904167

Luminaire Tested: DFN2DIP-SQ4F0-120D090US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904167
REPORT IS A COMBINATION OF REPORTS P901646 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D090US830-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18011.9 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3280	3280	3280
5°	3285	3229	3250
10°	3253	3166	3145
15°	3208	3062	2982
20°	3149	2918	2782
25°	3088	2757	2589
30°	3006	2592	2344
35°	2927	2414	2129
40°	2845	2230	1882
45°	2751	2026	1658
50°	2653	1820	1439
55°	2551	1599	1228
60°	2433	1369	1012
65°	2298	1134	912
70°	2133	916	827
75°	1926	809	754
80°	1627	680	657
85°	1133	458	500

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2751 cd/sqm

TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.4
10°-20°	1202.7	6.7
20°-30°	1688.5	9.4
30°-40°	1840.6	10.2
40°-50°	1691.7	9.4
50°-60°	1328.6	7.4
60°-70°	864.8	4.8
70°-80°	445.2	2.5
80°-90°	118.7	0.7
90°-100°	94.4	0.5
100°-110°	351.9	2.0
110°-120°	933.3	5.2
120°-130°	1548.0	8.6
130°-140°	1644.3	9.1
140°-150°	1528.2	8.5
150°-160°	1228.6	6.8
160°-170°	791.7	4.4
170°-180°	272.5	1.5
0°-30°	3329.4	18.5
0°-40°	5170.0	28.7
0°-60°	8190.3	45.5
0°-90°	9618.9	53.4
90°-120°	1379.6	7.7
90°-150°	6100.2	33.9
90°-180°	8393.0	46.6
0°-180°	18011.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4675	4675	4675	4675	4675	
5°	4675	4654	4598	4636	4624	443
15°	4446	4400	4256	4176	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3478	3262	2890	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1932
65°	1460	1117	736	592	580	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	2	25	41	52	56	17
95°	135	66	81	91	89	159
105°	630	692	126	149	157	673
115°	1191	1226	1278	319	170	1173
125°	1684	1711	1750	1765	1771	1502
135°	2084	2117	2136	2157	2152	1610
145°	2418	2415	2451	2465	2455	1512
155°	2662	2644	2668	2681	2664	1227
165°	2805	2792	2799	2813	2799	792
175°	2869	2854	2859	2873	2852	273
180°	2863	2863	2863	2863	2863	

TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.6	4674.6	4674.6	4674.6	4674.6
2.5°	4695.7	4674.6	4628.0	4670.6	4662.0
5°	4674.6	4653.5	4598.3	4636.5	4623.9
7.5°	4636.5	4611.3	4552.1	4568.7	4547.6
10°	4585.8	4556.2	4471.7	4458.7	4433.6
12.5°	4522.4	4484.3	4369.8	4344.7	4298.1
15°	4446.2	4399.5	4255.9	4175.5	4133.3
17.5°	4357.3	4289.5	4111.7	4018.9	3951.1
20°	4255.9	4171.0	3959.6	3854.1	3760.7
22.5°	4145.9	4048.5	3803.0	3659.3	3596.1
25°	4036.0	3900.3	3621.2	3447.9	3384.2
27.5°	3904.9	3760.7	3452.0	3253.2	3155.7
30°	3765.3	3604.2	3265.7	3050.3	2935.8
32.5°	3629.7	3434.9	3088.4	2834.4	2728.5
35°	3477.6	3261.7	2889.6	2623.0	2529.6
37.5°	3329.4	3096.5	2703.3	2411.1	2305.6
40°	3172.8	2919.2	2508.6	2208.3	2098.3
42.5°	3012.1	2741.5	2314.2	2000.9	1895.5
45°	2842.9	2559.3	2115.3	1814.7	1713.2
47.5°	2682.2	2382.0	1925.0	1624.4	1531.4
50°	2504.5	2204.2	1738.8	1446.6	1358.2
52.5°	2330.8	2013.5	1561.0	1281.9	1201.6
55°	2161.6	1831.7	1374.8	1121.2	1040.8
57.5°	1988.3	1649.9	1210.0	973.1	905.3
60°	1810.6	1472.2	1036.3	821.0	753.2
62.5°	1637.4	1298.9	888.3	685.4	651.7
65°	1459.6	1116.7	736.1	592.5	579.5
67.5°	1290.4	947.4	592.5	520.2	507.7
70°	1112.7	782.8	490.6	448.4	431.3
72.5°	943.5	630.2	410.2	376.5	368.1
75°	778.3	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	2.0	24.9	41.3	51.9	55.8
92.5°	51.9	43.5	49.7	53.9	55.8
95°	134.6	66.2	80.7	91.2	89.1
97.5°	242.3	72.6	105.6	111.9	113.9
100°	366.7	82.9	118.1	134.6	138.7
102.5°	503.3	499.4	122.2	144.9	151.3
105°	629.7	692.0	126.4	149.1	157.4
107.5°	776.8	828.5	130.6	153.3	161.6
110°	917.8	961.1	362.6	155.4	163.6

TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1050.4	1087.5	1052.3	159.4	165.8
115°	1191.1	1226.2	1278.2	319.1	169.9
117.5°	1313.3	1354.7	1390.1	1093.7	551.0
120°	1450.1	1481.1	1518.5	1543.3	1263.7
122.5°	1566.0	1599.2	1640.8	1653.0	1655.3
125°	1684.0	1711.1	1750.5	1765.0	1771.1
127.5°	1791.8	1820.8	1852.1	1872.7	1874.7
130°	1893.4	1926.7	1949.3	1972.1	1970.2
132.5°	1997.0	2024.0	2046.6	2065.4	2063.4
135°	2084.1	2117.2	2135.7	2156.6	2152.5
137.5°	2175.1	2199.9	2220.8	2241.5	2235.3
140°	2264.1	2280.9	2303.5	2322.1	2311.9
142.5°	2338.9	2353.4	2380.2	2396.7	2386.4
145°	2417.6	2415.4	2450.6	2465.1	2454.8
147.5°	2485.8	2479.6	2514.8	2525.2	2517.0
150°	2552.2	2537.7	2570.9	2583.1	2572.9
152.5°	2608.0	2591.5	2622.5	2635.1	2620.6
155°	2661.9	2643.5	2668.2	2680.6	2664.1
157.5°	2705.5	2689.0	2707.6	2722.2	2705.5
160°	2742.8	2730.3	2742.8	2755.1	2740.6
162.5°	2775.8	2763.4	2773.8	2788.3	2769.7
165°	2804.8	2792.5	2798.7	2813.2	2798.7
167.5°	2827.7	2815.2	2821.5	2836.0	2817.4
170°	2846.4	2833.8	2838.0	2852.5	2833.8
172.5°	2858.7	2846.4	2850.5	2865.0	2846.4
175°	2869.0	2854.5	2858.7	2873.2	2852.5
177.5°	2873.2	2858.7	2860.9	2875.4	2856.8
180°	2862.9	2862.9	2862.9	2862.9	2862.9

TEST NUMBER: P904167

CATALOG NUMBER: DFN2DIP-SQ4F0-120D090US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.60	12.46	12.53	13.40	14.63	7.56	8.42	8.49	9.37	10.59
	3H	13.28	14.05	14.23	15.01	16.26	8.75	9.52	9.70	10.48	11.72
	4H	13.90	14.62	14.86	15.58	16.84	9.20	9.93	10.16	10.89	12.15
	6H	14.32	14.99	15.29	15.96	17.23	9.53	10.19	10.50	11.16	12.43
	8H	14.45	15.09	15.43	16.07	17.34	9.62	10.25	10.60	11.24	12.50
	12H	14.52	15.12	15.50	16.10	17.39	9.66	10.27	10.65	11.24	12.53
4H	2H	11.62	12.35	12.59	13.31	14.56	8.16	8.89	9.13	9.85	11.10
	3H	13.46	14.06	14.43	15.05	16.32	9.52	10.12	10.49	11.11	12.38
	4H	14.15	14.70	15.14	15.69	16.98	10.07	10.62	11.05	11.60	12.89
	6H	14.68	15.15	15.67	16.16	17.45	10.49	10.96	11.48	11.97	13.26
	8H	14.85	15.30	15.85	16.30	17.60	10.62	11.06	11.61	12.06	13.37
	12H	14.95	15.35	15.97	16.37	17.68	10.68	11.08	11.70	12.10	13.41
8H	4H	14.12	14.57	15.12	15.57	16.87	10.35	10.79	11.35	11.79	13.10
	6H	14.70	15.06	15.72	16.10	17.41	10.87	11.23	11.89	12.28	13.58
	8H	14.92	15.24	15.95	16.27	17.59	11.06	11.38	12.09	12.41	13.74
	12H	15.06	15.34	16.09	16.36	17.73	11.18	11.47	12.22	12.49	13.86
12H	4H	14.08	14.48	15.09	15.49	16.81	10.36	10.75	11.37	11.77	13.08
	6H	14.67	14.99	15.70	16.02	17.35	10.92	11.24	11.95	12.27	13.60
	8H	14.90	15.18	15.93	16.20	17.57	11.13	11.42	12.17	12.44	13.81

END OF REPORT