

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904192

Luminaire Tested: DFN2DIP-SQ4F0-140D070US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904192
REPORT IS A COMBINATION OF REPORTS P900091 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D070US830-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18902.7 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 196
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3603	3603	3603
5°	3608	3553	3578
10°	3579	3506	3530
15°	3526	3449	3455
20°	3455	3370	3379
25°	3385	3274	3290
30°	3296	3186	3177
35°	3212	3081	3058
40°	3108	2976	2944
45°	3005	2870	2828
50°	2892	2759	2694
55°	2774	2631	2570
60°	2641	2478	2429
65°	2495	2321	2262
70°	2310	2128	2083
75°	2052	1899	1919
80°	1744	1606	1603
85°	1260	1098	1078

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3005 cd/sqm

TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.3	2.6
10°-20°	1359.7	7.2
20°-30°	1998.2	10.6
30°-40°	2320.8	12.3
40°-50°	2318.0	12.3
50°-60°	2021.2	10.7
60°-70°	1494.1	7.9
70°-80°	845.3	4.5
80°-90°	229.0	1.2
90°-100°	129.1	0.7
100°-110°	410.3	2.2
110°-120°	702.1	3.7
120°-130°	923.3	4.9
130°-140°	1036.4	5.5
140°-150°	1016.3	5.4
150°-160°	852.6	4.5
160°-170°	565.4	3.0
170°-180°	197.6	1.0
0°-30°	3841.2	20.3
0°-40°	6162.0	32.6
0°-60°	10501.1	55.6
0°-90°	13069.6	69.1
90°-120°	1241.5	6.6
90°-150°	4217.6	22.3
90°-180°	5833.0	30.9
0°-180°	18902.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5134	5134	5134	5134	5134	
5°	5134	5115	5061	5100	5090	487
15°	4888	4858	4794	4814	4789	1377
25°	4424	4384	4300	4310	4300	2036
35°	3816	3767	3688	3658	3634	2383
45°	3106	3071	2997	2943	2923	2397
55°	2350	2320	2261	2202	2178	2101
65°	1585	1555	1506	1461	1437	1567
75°	829	820	795	765	775	885
85°	202	198	193	178	173	226
90°	2	23	62	58	60	18
95°	92	109	113	113	109	102
105°	379	384	388	391	391	400
115°	705	715	712	710	705	697
125°	1025	1040	1036	1030	1028	916
135°	1326	1345	1349	1347	1342	1025
145°	1609	1622	1632	1634	1627	1005
155°	1840	1845	1851	1860	1854	847
165°	2002	2000	2000	2012	2004	565
175°	2083	2078	2074	2087	2076	198
180°	2087	2087	2087	2087	2087	

TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5134.5	5134.5	5134.5	5134.5	5134.5
2.5°	5164.3	5139.7	5085.2	5134.5	5125.1
5°	5134.5	5115.1	5060.6	5099.9	5090.5
7.5°	5099.9	5070.6	5016.1	5055.9	5045.9
10°	5045.9	5011.4	4952.2	4991.5	4976.8
12.5°	4971.5	4942.2	4883.0	4907.6	4897.7
15°	4887.7	4858.4	4794.0	4813.9	4789.2
17.5°	4784.1	4754.7	4690.3	4714.9	4690.3
20°	4670.4	4641.1	4571.9	4586.6	4567.2
22.5°	4557.2	4512.7	4448.2	4448.2	4438.3
25°	4423.6	4384.3	4300.5	4310.0	4300.5
27.5°	4275.4	4240.9	4177.0	4162.3	4137.7
30°	4127.7	4087.9	4014.0	3999.4	3979.4
32.5°	3969.5	3940.2	3861.0	3831.2	3811.3
35°	3816.5	3767.3	3688.2	3658.4	3633.7
37.5°	3643.7	3599.2	3520.0	3485.5	3460.8
40°	3466.1	3426.3	3347.2	3303.2	3283.3
42.5°	3293.2	3253.5	3174.9	3125.1	3095.8
45°	3105.7	3071.2	2996.8	2942.8	2922.9
47.5°	2922.9	2888.3	2809.2	2754.8	2725.5
50°	2730.2	2705.6	2636.4	2567.2	2542.6
52.5°	2542.6	2508.0	2444.1	2389.6	2355.1
55°	2350.4	2320.5	2261.3	2202.2	2177.6
57.5°	2157.6	2133.0	2068.6	2009.4	1989.4
60°	1964.8	1945.5	1876.3	1821.8	1807.1
62.5°	1777.4	1742.8	1693.5	1644.3	1624.4
65°	1585.1	1555.2	1506.0	1461.4	1436.8
67.5°	1387.6	1362.4	1318.4	1283.8	1263.9
70°	1204.8	1184.9	1140.4	1105.8	1086.4
72.5°	1017.3	997.3	972.7	938.2	923.5
75°	829.2	819.8	794.7	765.3	775.2
77.5°	661.6	641.7	631.7	617.1	602.4
80°	494.0	488.7	478.8	464.1	454.1
82.5°	335.7	335.7	331.0	311.1	311.1
85°	202.2	197.5	192.7	177.6	172.9
87.5°	89.1	79.1	69.2	54.5	49.2
90°	1.9	22.6	61.6	57.9	59.8
92.5°	39.0	52.9	54.8	56.6	56.6
95°	91.8	109.4	112.6	112.6	109.4
97.5°	152.9	169.2	176.2	176.2	176.2
100°	223.3	237.8	242.8	242.8	240.9
102.5°	297.6	308.2	315.2	317.1	315.2
105°	378.7	383.7	387.5	390.7	390.7
107.5°	459.2	466.7	466.7	468.1	459.2
110°	537.2	547.3	547.3	547.3	542.2

TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	621.5	632.3	630.4	625.3	621.5
115°	704.6	714.6	711.5	709.6	704.6
117.5°	786.9	800.8	792.0	786.9	781.9
120°	870.0	883.8	870.0	870.0	864.3
122.5°	945.5	963.1	954.3	949.2	945.5
125°	1024.7	1040.5	1035.5	1029.8	1027.9
127.5°	1102.1	1121.6	1114.7	1107.2	1102.1
130°	1174.5	1197.1	1194.0	1190.2	1183.3
132.5°	1255.7	1273.3	1274.5	1265.7	1260.7
135°	1325.5	1344.9	1348.8	1346.8	1341.8
137.5°	1403.4	1419.2	1422.3	1421.1	1413.5
140°	1472.1	1487.8	1496.6	1496.6	1489.7
142.5°	1542.5	1558.2	1563.2	1565.1	1558.2
145°	1609.2	1621.7	1631.8	1633.7	1626.8
147.5°	1669.0	1684.7	1692.2	1695.4	1688.5
150°	1730.6	1741.3	1748.2	1753.9	1748.2
152.5°	1785.3	1796.0	1804.8	1811.8	1804.8
155°	1840.0	1845.0	1850.8	1859.5	1853.9
157.5°	1887.3	1891.0	1894.1	1906.8	1897.9
160°	1929.4	1933.2	1935.0	1945.7	1938.1
162.5°	1968.4	1968.4	1970.3	1982.2	1973.4
165°	2001.7	1999.8	1999.8	2012.4	2003.6
167.5°	2031.9	2026.3	2026.3	2038.8	2030.0
170°	2054.6	2049.6	2047.7	2060.2	2049.6
172.5°	2070.3	2065.2	2063.3	2075.9	2065.2
175°	2082.8	2077.8	2074.1	2086.6	2075.9
177.5°	2089.8	2084.7	2080.9	2091.7	2080.9
180°	2086.6	2086.6	2086.6	2086.6	2086.6

TEST NUMBER: P904192

CATALOG NUMBER: DFN2DIP-SQ4F0-140D070US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.34	14.40	14.11	15.20	16.17	12.90	13.96	13.67	14.76	15.72
	3H	15.02	15.98	15.81	16.78	17.78	14.53	15.49	15.32	16.29	17.29
	4H	15.62	16.52	16.42	17.34	18.35	15.13	16.03	15.93	16.84	17.85
	6H	16.03	16.87	16.85	17.69	18.71	15.53	16.37	16.35	17.19	18.21
	8H	16.15	16.94	16.97	17.78	18.80	15.64	16.44	16.47	17.28	18.30
	12H	16.20	16.96	17.03	17.79	18.85	15.69	16.45	16.52	17.28	18.34
4H	2H	13.83	14.73	14.63	15.54	16.55	13.47	14.37	14.28	15.19	16.20
	3H	15.71	16.47	16.53	17.32	18.34	15.31	16.06	16.13	16.91	17.93
	4H	16.44	17.13	17.27	17.97	19.03	16.02	16.70	16.85	17.55	18.60
	6H	16.97	17.57	17.82	18.44	19.49	16.54	17.13	17.39	18.00	19.06
	8H	17.13	17.68	17.98	18.55	19.62	16.69	17.25	17.54	18.11	19.18
	12H	17.21	17.71	18.09	18.60	19.68	16.76	17.26	17.64	18.15	19.23
8H	4H	16.65	17.21	17.51	18.07	19.15	16.28	16.83	17.13	17.70	18.77
	6H	17.30	17.76	18.18	18.67	19.74	16.91	17.37	17.80	18.28	19.35
	8H	17.52	17.93	18.42	18.83	19.92	17.13	17.54	18.02	18.44	19.53
	12H	17.67	18.03	18.56	18.92	20.06	17.26	17.62	18.15	18.51	19.65
12H	4H	16.65	17.15	17.52	18.04	19.11	16.28	16.78	17.16	17.67	18.74
	6H	17.33	17.74	18.22	18.64	19.73	16.96	17.37	17.85	18.27	19.36
	8H	17.59	17.94	18.48	18.84	19.98	17.20	17.56	18.10	18.46	19.60