

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904205

Luminaire Tested: DFN2DIP-SQ4F0-140D100US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904205
REPORT IS A COMBINATION OF REPORTS P901665 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D100US830-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22394.8 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 218.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	64	60	58	55	53	50	47	45
3	83	73	66	60	77	69	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	50	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	29	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	26	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3603	3603	3603
5°	3608	3553	3578
10°	3579	3506	3530
15°	3526	3449	3455
20°	3455	3370	3379
25°	3385	3274	3290
30°	3296	3186	3177
35°	3212	3081	3058
40°	3108	2976	2944
45°	3005	2870	2828
50°	2892	2759	2694
55°	2774	2631	2570
60°	2641	2478	2429
65°	2495	2321	2262
70°	2310	2128	2083
75°	2052	1899	1919
80°	1744	1606	1603
85°	1260	1098	1078

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3005 cd/sqm

TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	483.3	2.2
10°-20°	1359.7	6.1
20°-30°	1998.2	8.9
30°-40°	2320.8	10.4
40°-50°	2318.0	10.4
50°-60°	2021.2	9.0
60°-70°	1494.1	6.7
70°-80°	845.3	3.8
80°-90°	228.7	1.0
90°-100°	104.9	0.5
100°-110°	391.0	1.7
110°-120°	1037.0	4.6
120°-130°	1720.0	7.7
130°-140°	1827.0	8.2
140°-150°	1698.0	7.6
150°-160°	1365.2	6.1
160°-170°	879.7	3.9
170°-180°	302.8	1.4
0°-30°	3841.2	17.2
0°-40°	6162.0	27.5
0°-60°	10501.1	46.9
0°-90°	13069.2	58.4
90°-120°	1532.9	6.8
90°-150°	6778.0	30.3
90°-180°	9326.0	41.6
0°-180°	22394.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5134	5134	5134	5134	5134	
5°	5134	5115	5061	5100	5090	487
15°	4888	4858	4794	4814	4789	1377
25°	4424	4384	4300	4310	4300	2036
35°	3816	3767	3688	3658	3634	2383
45°	3106	3071	2997	2943	2923	2397
55°	2350	2320	2261	2202	2178	2101
65°	1585	1555	1506	1461	1437	1567
75°	829	820	795	765	775	885
85°	202	198	193	178	173	226
90°	2	28	46	58	62	21
95°	150	74	90	101	99	177
105°	700	769	140	166	175	748
115°	1323	1362	1420	354	189	1303
125°	1871	1901	1945	1961	1968	1669
135°	2316	2352	2373	2396	2392	1789
145°	2686	2684	2723	2739	2728	1680
155°	2958	2937	2965	2978	2960	1363
165°	3116	3103	3110	3126	3110	880
175°	3188	3172	3176	3192	3170	303
180°	3181	3181	3181	3181	3181	

TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5134.5	5134.5	5134.5	5134.5	5134.5
2.5°	5164.3	5139.7	5085.2	5134.5	5125.1
5°	5134.5	5115.1	5060.6	5099.9	5090.5
7.5°	5099.9	5070.6	5016.1	5055.9	5045.9
10°	5045.9	5011.4	4952.2	4991.5	4976.8
12.5°	4971.5	4942.2	4883.0	4907.6	4897.7
15°	4887.7	4858.4	4794.0	4813.9	4789.2
17.5°	4784.1	4754.7	4690.3	4714.9	4690.3
20°	4670.4	4641.1	4571.9	4586.6	4567.2
22.5°	4557.2	4512.7	4448.2	4448.2	4438.3
25°	4423.6	4384.3	4300.5	4310.0	4300.5
27.5°	4275.4	4240.9	4177.0	4162.3	4137.7
30°	4127.7	4087.9	4014.0	3999.4	3979.4
32.5°	3969.5	3940.2	3861.0	3831.2	3811.3
35°	3816.5	3767.3	3688.2	3658.4	3633.7
37.5°	3643.7	3599.2	3520.0	3485.5	3460.8
40°	3466.1	3426.3	3347.2	3303.2	3283.3
42.5°	3293.2	3253.5	3174.9	3125.1	3095.8
45°	3105.7	3071.2	2996.8	2942.8	2922.9
47.5°	2922.9	2888.3	2809.2	2754.8	2725.5
50°	2730.2	2705.6	2636.4	2567.2	2542.6
52.5°	2542.6	2508.0	2444.1	2389.6	2355.1
55°	2350.4	2320.5	2261.3	2202.2	2177.6
57.5°	2157.6	2133.0	2068.6	2009.4	1989.4
60°	1964.8	1945.5	1876.3	1821.8	1807.1
62.5°	1777.4	1742.8	1693.5	1644.3	1624.4
65°	1585.1	1555.2	1506.0	1461.4	1436.8
67.5°	1387.6	1362.4	1318.4	1283.8	1263.9
70°	1204.8	1184.9	1140.4	1105.8	1086.4
72.5°	1017.3	997.3	972.7	938.2	923.5
75°	829.2	819.8	794.7	765.3	775.2
77.5°	661.6	641.7	631.7	617.1	602.4
80°	494.0	488.7	478.8	464.1	454.1
82.5°	335.7	335.7	331.0	311.1	311.1
85°	202.2	197.5	192.7	177.6	172.9
87.5°	89.1	79.1	69.2	54.5	49.2
90°	2.2	27.6	45.9	57.7	62.0
92.5°	57.7	48.4	55.2	59.9	62.0
95°	149.5	73.5	89.6	101.4	99.0
97.5°	269.2	80.6	117.3	124.3	126.6
100°	407.6	92.1	131.2	149.5	154.2
102.5°	559.2	554.9	135.8	161.0	168.1
105°	699.7	768.8	140.5	165.6	174.9
107.5°	863.2	920.6	145.2	170.3	179.6
110°	1019.7	1067.9	402.8	172.8	181.7

TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1167.1	1208.3	1169.3	177.1	184.3
115°	1323.4	1362.5	1420.2	354.5	188.9
117.5°	1459.2	1505.2	1544.5	1215.2	612.3
120°	1611.3	1645.7	1687.2	1714.9	1404.1
122.5°	1740.0	1776.9	1823.1	1836.7	1839.2
125°	1871.2	1901.3	1945.0	1961.1	1967.9
127.5°	1990.9	2023.2	2057.9	2080.9	2083.0
130°	2103.8	2140.7	2165.9	2191.2	2189.1
132.5°	2218.8	2248.9	2274.1	2294.8	2292.6
135°	2315.6	2352.5	2373.0	2396.2	2391.6
137.5°	2416.8	2444.4	2467.6	2490.6	2483.7
140°	2515.6	2534.3	2559.4	2580.2	2568.7
142.5°	2598.8	2614.9	2644.7	2663.0	2651.6
145°	2686.2	2683.8	2722.9	2739.0	2727.5
147.5°	2761.9	2755.1	2794.2	2805.7	2796.7
150°	2835.7	2819.6	2856.6	2870.2	2858.7
152.5°	2897.8	2879.5	2914.0	2927.8	2911.7
155°	2957.7	2937.2	2964.8	2978.4	2960.1
157.5°	3006.1	2987.8	3008.5	3024.6	3006.1
160°	3047.6	3033.7	3047.6	3061.3	3045.2
162.5°	3084.2	3070.5	3082.0	3098.1	3077.4
165°	3116.4	3102.8	3109.6	3125.8	3109.6
167.5°	3141.9	3127.9	3135.1	3151.2	3130.4
170°	3162.6	3148.8	3153.4	3169.5	3148.8
172.5°	3176.3	3162.6	3167.3	3183.4	3162.6
175°	3187.8	3171.7	3176.3	3192.5	3169.5
177.5°	3192.5	3176.3	3178.8	3194.9	3174.1
180°	3181.0	3181.0	3181.0	3181.0	3181.0

TEST NUMBER: P904205

CATALOG NUMBER: DFN2DIP-SQ4F0-140D100US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.48	13.42	13.36	14.32	15.47	12.03	12.97	12.91	13.88	15.02
	3H	14.15	14.99	15.04	15.90	17.08	13.66	14.50	14.55	15.41	16.58
	4H	14.74	15.54	15.65	16.46	17.64	14.25	15.04	15.16	15.96	17.14
	6H	15.15	15.88	16.07	16.81	18.00	14.65	15.38	15.57	16.31	17.50
	8H	15.26	15.96	16.19	16.90	18.09	14.75	15.46	15.68	16.40	17.59
	12H	15.31	15.98	16.24	16.91	18.13	14.80	15.47	15.73	16.40	17.62
4H	2H	12.95	13.75	13.86	14.66	15.84	12.59	13.39	13.51	14.31	15.49
	3H	14.82	15.49	15.75	16.44	17.64	14.42	15.08	15.34	16.03	17.23
	4H	15.55	16.15	16.48	17.10	18.32	15.12	15.73	16.06	16.67	17.90
	6H	16.07	16.59	17.02	17.56	18.78	15.64	16.16	16.59	17.13	18.35
	8H	16.22	16.71	17.17	17.68	18.91	15.79	16.28	16.74	17.24	18.47
	12H	16.30	16.75	17.27	17.72	18.97	15.85	16.30	16.82	17.27	18.52
8H	4H	15.75	16.24	16.70	17.20	18.44	15.37	15.86	16.32	16.82	18.06
	6H	16.39	16.79	17.37	17.80	19.03	16.00	16.41	16.98	17.41	18.65
	8H	16.61	16.97	17.60	17.96	19.22	16.22	16.58	17.21	17.57	18.82
	12H	16.75	17.07	17.74	18.05	19.35	16.34	16.66	17.33	17.64	18.94
12H	4H	15.74	16.18	16.71	17.16	18.40	15.37	15.81	16.34	16.79	18.03
	6H	16.42	16.78	17.41	17.77	19.02	16.05	16.41	17.03	17.40	18.65
	8H	16.67	16.98	17.66	17.97	19.27	16.29	16.60	17.28	17.59	18.89