

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922890

Luminaire Tested: DFN2DIP-SQ3F0-090D040US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922890
REPORT IS A COMBINATION OF REPORTS P899872 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-090D040US940-RLLFLL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9978.3 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 118.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922890
CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLFL

Luminous Intensity Polar Plot





TEST NUMBER: P922890

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68				68
1	103	98	95	91	97	93	90	87	83	81	78	74	72	70	66	64	63	59				59
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	50				50
3	86	77	70	64	81	73	67	61	66	61	56	59	55	51	52	49	47	44				44
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41	38				38
5	73	62	53	48	69	59	51	46	53	47	43	48	43	39	43	39	36	33				33
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32	30				30
7	63	51	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29	27				27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24				24
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24	22				22
10	51	39	32	27	48	37	31	26	34	29	25	32	27	23	29	25	22	20				20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3801	3801	3801
5°	3804	3738	3763
10°	3764	3662	3639
15°	3710	3538	3449
20°	3639	3369	3215
25°	3566	3180	2990
30°	3469	2986	2705
35°	3374	2778	2455
40°	3278	2563	2168
45°	3165	2325	1908
50°	3049	2085	1654
55°	2927	1828	1410
60°	2787	1561	1159
65°	2624	1289	1042
70°	2427	1035	941
75°	2179	907	853
80°	1821	753	736
85°	1234	491	546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3165 cd/sqm



TEST NUMBER: P922890

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	3.1
10°-20°	853.4	8.6
20°-30°	1198.1	12.0
30°-40°	1306.0	13.1
40°-50°	1200.4	12.0
50°-60°	942.7	9.4
60°-70°	613.6	6.1
70°-80°	315.9	3.2
80°-90°	83.8	0.8
90°-100°	69.8	0.7
100°-110°	221.8	2.2
110°-120°	379.5	3.8
120°-130°	499.2	5.0
130°-140°	560.3	5.6
140°-150°	549.4	5.5
150°-160°	460.9	4.6
160°-170°	305.7	3.1
170°-180°	106.8	1.1
0°-30°	2362.4	23.7
0°-40°	3668.4	36.8
0°-60°	5811.5	58.2
0°-90°	6824.8	68.4
90°-120°	671.2	6.7
90°-150°	2280.1	22.9
90°-180°	3153.0	31.6
0°-180°	9978.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	1	12	33	31	32	10
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P922890

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2



TEST NUMBER: P922890

CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0



TEST NUMBER: P922890
 CATALOG NUMBER: DFN2DIP-SQ3F0-090D040US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.32	14.33	14.11	15.13	16.12	9.28	10.29	10.07	11.09	12.08
	3H	15.00	15.91	15.81	16.72	17.74	10.47	11.38	11.28	12.19	13.21
	4H	15.62	16.47	16.44	17.29	18.32	10.93	11.78	11.75	12.60	13.63
	6H	16.04	16.83	16.88	17.66	18.70	11.25	12.03	12.08	12.87	13.91
	8H	16.17	16.92	17.02	17.77	18.81	11.35	12.09	12.19	12.94	13.98
	12H	16.24	16.95	17.09	17.79	18.86	11.39	12.10	12.24	12.94	14.01
4H	2H	13.36	14.21	14.18	15.03	16.05	9.89	10.74	10.72	11.57	12.59
	3H	15.20	15.90	16.03	16.76	17.80	11.25	11.96	12.09	12.81	13.86
	4H	15.89	16.53	16.74	17.39	18.46	11.80	12.44	12.65	13.30	14.37
	6H	16.41	16.96	17.28	17.84	18.92	12.22	12.78	13.09	13.66	14.73
	8H	16.59	17.10	17.45	17.98	19.06	12.35	12.87	13.22	13.74	14.83
	12H	16.69	17.15	17.57	18.05	19.14	12.42	12.89	13.31	13.78	14.87
8H	4H	15.87	16.39	16.74	17.26	18.35	12.09	12.61	12.96	13.48	14.57
	6H	16.44	16.86	17.33	17.78	18.87	12.61	13.03	13.50	13.95	15.04
	8H	16.65	17.03	17.56	17.94	19.04	12.79	13.17	13.70	14.08	15.19
	12H	16.79	17.13	17.70	18.03	19.18	12.92	13.25	13.82	14.15	15.31
12H	4H	15.83	16.29	16.72	17.19	18.28	12.10	12.57	12.99	13.46	14.55
	6H	16.41	16.79	17.32	17.70	18.80	12.66	13.03	13.56	13.95	15.05
	8H	16.64	16.97	17.54	17.87	19.03	12.87	13.20	13.78	14.10	15.26