

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904247

Luminaire Tested: DFN2DIP-SQ4F0-160D110US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904247
REPORT IS A COMBINATION OF REPORTS P901686 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D110US830-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23082.8 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	100	95	92	88	92	89	86	83	77	74	72	65	64	62	55	54	53
2	91	84	78	73	84	78	73	69	68	64	61	58	55	53	49	47	45
3	83	74	67	62	77	69	63	58	60	56	52	52	48	45	44	41	39
4	77	66	58	53	71	62	55	50	54	49	44	47	43	39	40	37	34
5	71	59	51	45	65	56	48	43	49	43	39	42	38	34	36	33	30
6	65	53	45	40	61	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	46	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	42	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4373	4373	4373
5°	4380	4305	4333
10°	4337	4221	4193
15°	4277	4083	3976
20°	4198	3891	3710
25°	4117	3676	3452
30°	4009	3456	3126
35°	3902	3219	2838
40°	3794	2974	2509
45°	3668	2701	2210
50°	3538	2426	1918
55°	3402	2133	1638
60°	3244	1825	1350
65°	3064	1512	1216
70°	2844	1221	1103
75°	2569	1078	1006
80°	2169	907	877
85°	1510	611	668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3668 cd/sqm

TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	584.1	2.5
10°-20°	1603.6	6.9
20°-30°	2251.4	9.8
30°-40°	2454.2	10.6
40°-50°	2255.7	9.8
50°-60°	1771.5	7.7
60°-70°	1153.0	5.0
70°-80°	593.5	2.6
80°-90°	157.7	0.7
90°-100°	115.4	0.5
100°-110°	430.1	1.9
110°-120°	1140.7	4.9
120°-130°	1892.0	8.2
130°-140°	2009.7	8.7
140°-150°	1867.8	8.1
150°-160°	1501.7	6.5
160°-170°	967.6	4.2
170°-180°	333.0	1.4
0°-30°	4439.2	19.2
0°-40°	6893.3	29.9
0°-60°	10920.4	47.3
0°-90°	12824.7	55.6
90°-120°	1686.2	7.3
90°-150°	7455.8	32.3
90°-180°	10258.0	44.4
0°-180°	23082.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6233	6233	6233	6233	6233	
5°	6233	6205	6131	6182	6165	591
15°	5928	5866	5674	5567	5511	1671
25°	5381	5200	4828	4597	4512	2475
35°	4637	4349	3853	3497	3373	2902
45°	3790	3412	2820	2420	2284	2927
55°	2882	2442	1833	1495	1388	2575
65°	1946	1489	982	790	773	1929
75°	1038	643	451	412	406	1098
85°	242	124	107	107	107	278
90°	2	30	50	63	68	22
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2140	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3254	3231	3261	3276	3256	1499
165°	3428	3413	3421	3438	3421	969
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6232.8	6232.8	6232.8	6232.8	6232.8
2.5°	6260.9	6232.8	6170.5	6227.5	6216.1
5°	6232.8	6204.7	6131.0	6181.9	6165.2
7.5°	6181.9	6148.4	6069.4	6091.6	6063.5
10°	6114.4	6074.9	5962.3	5945.0	5911.4
12.5°	6029.9	5979.1	5826.5	5793.0	5730.8
15°	5928.2	5866.0	5674.5	5567.3	5511.0
17.5°	5809.7	5719.3	5482.4	5358.4	5268.2
20°	5674.5	5561.4	5279.5	5138.8	5014.4
22.5°	5527.8	5397.9	5070.6	4879.2	4794.7
25°	5381.3	5200.5	4828.3	4597.3	4512.3
27.5°	5206.5	5014.4	4602.6	4337.6	4207.7
30°	5020.4	4805.6	4354.3	4067.1	3914.5
32.5°	4839.7	4579.9	4117.9	3779.2	3637.9
35°	4636.7	4348.9	3852.8	3497.3	3372.9
37.5°	4439.3	4128.7	3604.5	3214.8	3074.2
40°	4230.4	3892.3	3344.7	2944.3	2797.7
42.5°	4016.2	3655.3	3085.6	2667.9	2527.2
45°	3790.5	3412.4	2820.5	2419.5	2284.3
47.5°	3576.3	3176.0	2566.7	2165.8	2041.9
50°	3339.3	2938.9	2318.4	1928.8	1810.9
52.5°	3107.8	2684.6	2081.4	1709.2	1602.0
55°	2882.1	2442.2	1833.1	1494.9	1387.8
57.5°	2651.1	2199.9	1613.4	1297.4	1207.0
60°	2414.1	1962.9	1381.8	1094.6	1004.2
62.5°	2183.1	1731.9	1184.3	913.8	868.9
65°	1946.2	1488.9	981.5	789.9	772.6
67.5°	1720.5	1263.3	789.9	693.6	676.8
70°	1483.6	1043.7	654.1	597.9	575.1
72.5°	1257.9	840.2	547.0	502.1	490.7
75°	1037.7	642.7	451.2	411.7	406.3
77.5°	818.0	456.6	355.4	332.7	321.4
80°	614.6	327.3	270.5	248.4	248.4
82.5°	428.5	220.3	186.2	174.7	174.7
85°	242.3	123.9	107.2	107.2	107.2
87.5°	90.4	44.9	44.9	39.5	39.5
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.7	845.7	154.6	182.2	192.5
107.5°	949.5	1012.6	159.7	187.3	197.6
110°	1121.7	1174.7	443.2	190.0	199.9



TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.2	1286.2	194.8	202.6
115°	1455.8	1498.7	1562.3	389.9	207.7
117.5°	1605.2	1655.8	1699.0	1336.7	673.4
120°	1772.4	1810.2	1856.0	1886.3	1544.4
122.5°	1914.0	1954.5	2005.4	2020.4	2023.2
125°	2058.3	2091.4	2139.5	2157.2	2164.7
127.5°	2190.0	2225.4	2263.6	2288.9	2291.3
130°	2314.1	2354.8	2382.4	2410.4	2408.0
132.5°	2440.7	2473.8	2501.5	2524.3	2522.0
135°	2547.2	2587.7	2610.3	2635.9	2630.7
137.5°	2658.4	2688.8	2714.3	2739.6	2732.1
140°	2767.3	2787.7	2815.4	2838.2	2825.6
142.5°	2858.6	2876.4	2909.2	2929.3	2916.7
145°	2954.9	2952.1	2995.1	3012.9	3000.3
147.5°	3038.2	3030.7	3073.6	3086.3	3076.4
150°	3119.3	3101.6	3142.2	3157.2	3144.6
152.5°	3187.6	3167.4	3205.3	3220.7	3202.9
155°	3253.5	3230.8	3261.2	3276.3	3256.1
157.5°	3306.6	3286.5	3309.4	3327.1	3306.6
160°	3352.3	3337.0	3352.3	3367.3	3349.6
162.5°	3392.6	3377.6	3390.2	3408.0	3385.1
165°	3428.1	3413.0	3420.6	3438.3	3420.6
167.5°	3456.0	3440.8	3448.6	3466.3	3443.5
170°	3478.9	3463.6	3468.6	3486.5	3463.6
172.5°	3493.9	3478.9	3484.0	3501.7	3478.9
175°	3506.5	3488.8	3493.9	3511.7	3486.5
177.5°	3511.7	3493.9	3496.6	3514.4	3491.6
180°	3499.1	3499.1	3499.1	3499.1	3499.1

TEST NUMBER: P904247

CATALOG NUMBER: DFN2DIP-SQ4F0-160D110US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.79	13.67	13.71	14.60	15.79	8.75	9.63	9.67	10.56	11.75
	3H	14.48	15.26	15.40	16.20	17.42	9.94	10.73	10.87	11.67	12.88
	4H	15.09	15.83	16.03	16.77	18.00	10.40	11.14	11.34	12.08	13.31
	6H	15.52	16.20	16.47	17.15	18.39	10.72	11.40	11.67	12.35	13.59
	8H	15.65	16.30	16.61	17.26	18.50	10.81	11.46	11.77	12.43	13.66
	12H	15.71	16.33	16.68	17.29	18.55	10.86	11.48	11.82	12.44	13.70
4H	2H	12.81	13.56	13.76	14.50	15.73	9.35	10.10	10.30	11.04	12.27
	3H	14.65	15.27	15.61	16.24	17.48	10.71	11.33	11.67	12.30	13.54
	4H	15.35	15.91	16.32	16.88	18.14	11.26	11.82	12.23	12.79	14.06
	6H	15.87	16.36	16.85	17.35	18.61	11.68	12.17	12.66	13.16	14.42
	8H	16.05	16.50	17.03	17.49	18.76	11.81	12.27	12.79	13.25	14.53
	12H	16.15	16.56	17.15	17.56	18.84	11.88	12.29	12.88	13.29	14.57
8H	4H	15.32	15.77	16.30	16.76	18.04	11.55	12.00	12.53	12.98	14.26
	6H	15.89	16.27	16.90	17.29	18.57	12.07	12.44	13.07	13.47	14.74
	8H	16.11	16.44	17.13	17.46	18.75	12.26	12.59	13.27	13.60	14.90
	12H	16.26	16.55	17.27	17.55	18.90	12.38	12.67	13.40	13.68	15.02
12H	4H	15.28	15.68	16.27	16.68	17.97	11.55	11.96	12.55	12.96	14.25
	6H	15.87	16.20	16.88	17.21	18.51	12.12	12.45	13.13	13.46	14.76
	8H	16.10	16.38	17.11	17.39	18.73	12.33	12.62	13.35	13.63	14.97