

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922924

Luminaire Tested: DFN2DIP-SQ3F0-100D040US940-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922924
REPORT IS A COMBINATION OF REPORTS P899873 AND P896733
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D040US940-FLLFLL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11984.6 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 128.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96		87	87	87		78
1	103	99	95	91	98	94	90	87	85	82	80		77	74	72		69
2	94	86	80	74	89	82	76	71	74	70	66		67	64	61		61
3	86	76	68	62	81	72	65	60	66	60	55		59	55	51		54
4	79	67	59	53	74	64	57	51	58	52	47		53	48	44		48
5	72	60	52	45	68	57	50	44	52	46	41		48	42	38		43
6	67	54	46	40	63	52	44	38	47	41	36		43	38	34		39
7	62	49	41	35	58	47	39	34	43	37	32		39	34	30		36
8	57	45	37	31	54	43	35	30	39	33	28		36	31	27		33
9	54	41	33	28	51	39	32	27	36	30	26		33	28	24		31
10	50	38	30	25	48	36	29	24	33	27	23		31	26	22		28

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3976	3976	3976
5°	3979	3918	3945
10°	3945	3862	3891
15°	3884	3796	3806
20°	3803	3705	3719
25°	3723	3597	3619
30°	3622	3496	3492
35°	3527	3377	3358
40°	3410	3257	3230
45°	3293	3137	3100
50°	3166	3010	2948
55°	3032	2864	2809
60°	2880	2691	2649
65°	2714	2511	2460
70°	2503	2291	2257
75°	2212	2028	2068
80°	1859	1692	1709
85°	1308	1122	1118

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3293 cd/sqm

TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.6	2.7
10°-20°	918.8	7.7
20°-30°	1350.3	11.3
30°-40°	1568.3	13.1
40°-50°	1566.4	13.1
50°-60°	1365.8	11.4
60°-70°	1009.7	8.4
70°-80°	571.3	4.8
80°-90°	154.0	1.3
90°-100°	69.8	0.6
100°-110°	221.8	1.9
110°-120°	379.5	3.2
120°-130°	499.2	4.2
130°-140°	560.3	4.7
140°-150°	549.4	4.6
150°-160°	460.9	3.8
160°-170°	305.7	2.6
170°-180°	106.8	0.9
0°-30°	2595.7	21.7
0°-40°	4164.0	34.7
0°-60°	7096.2	59.2
0°-90°	8831.1	73.7
90°-120°	671.2	5.6
90°-150°	2280.1	19.0
90°-180°	3153.0	26.3
0°-180°	11984.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3470	3470	3470	3470	3470	
5°	3470	3457	3420	3446	3440	329
15°	3303	3283	3240	3253	3236	930
25°	2989	2963	2906	2912	2906	1376
35°	2579	2546	2492	2472	2456	1611
45°	2099	2075	2025	1989	1975	1620
55°	1588	1568	1528	1488	1472	1420
65°	1071	1051	1018	988	971	1059
75°	560	554	537	517	524	598
85°	137	134	130	120	117	152
90°	1	12	33	31	32	11
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	

TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3469.7	3469.7	3469.7	3469.7	3469.7
2.5°	3489.9	3473.2	3436.4	3469.7	3463.3
5°	3469.7	3456.6	3419.8	3446.4	3440.0
7.5°	3446.4	3426.5	3389.7	3416.6	3409.9
10°	3409.9	3386.5	3346.5	3373.1	3363.2
12.5°	3359.6	3339.8	3299.8	3316.4	3309.7
15°	3303.0	3283.2	3239.6	3253.0	3236.5
17.5°	3232.9	3213.1	3169.5	3186.2	3169.5
20°	3156.0	3136.2	3089.5	3099.4	3086.3
22.5°	3079.6	3049.6	3006.0	3006.0	2999.3
25°	2989.4	2962.8	2906.2	2912.5	2906.2
27.5°	2889.1	2865.8	2822.6	2812.7	2796.0
30°	2789.4	2762.4	2712.5	2702.6	2689.1
32.5°	2682.4	2662.6	2609.1	2589.0	2575.5
35°	2579.1	2545.8	2492.3	2472.2	2455.5
37.5°	2462.3	2432.1	2378.7	2355.4	2338.7
40°	2342.3	2315.3	2261.9	2232.2	2218.8
42.5°	2225.4	2198.5	2145.5	2111.8	2092.0
45°	2098.7	2075.4	2025.1	1988.6	1975.2
47.5°	1975.2	1951.9	1898.4	1861.5	1841.7
50°	1844.9	1828.3	1781.5	1734.8	1718.2
52.5°	1718.2	1694.9	1651.6	1614.9	1591.5
55°	1588.3	1568.2	1528.1	1488.1	1471.5
57.5°	1458.0	1441.4	1397.8	1357.9	1344.4
60°	1327.8	1314.6	1267.9	1231.1	1221.2
62.5°	1201.0	1177.7	1144.4	1111.2	1097.7
65°	1071.1	1051.0	1017.7	987.6	971.0
67.5°	937.7	920.7	891.0	867.6	854.2
70°	814.1	800.7	770.6	747.3	734.1
72.5°	687.4	674.0	657.4	634.0	624.0
75°	560.4	554.0	537.0	517.2	523.9
77.5°	447.1	433.6	426.9	417.0	407.1
80°	333.8	330.3	323.5	313.6	306.9
82.5°	226.9	226.9	223.7	210.3	210.3
85°	136.6	133.5	130.3	120.0	116.8
87.5°	60.2	53.4	46.7	36.8	33.3
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2

TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0

TEST NUMBER: P922924

CATALOG NUMBER: DFN2DIP-SQ3F0-100D040US940-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.98	15.10	14.70	15.85	16.74	13.54	14.66	14.26	15.40	16.29
	3H	15.66	16.67	16.39	17.42	18.34	15.17	16.18	15.90	16.93	17.85
	4H	16.25	17.21	17.01	17.97	18.90	15.76	16.71	16.51	17.47	18.41
	6H	16.66	17.54	17.43	18.31	19.26	16.16	17.04	16.93	17.81	18.76
	8H	16.77	17.61	17.55	18.40	19.35	16.27	17.11	17.05	17.90	18.85
	12H	16.83	17.63	17.61	18.41	19.39	16.32	17.12	17.10	17.90	18.88
4H	2H	14.47	15.42	15.23	16.19	17.12	14.11	15.07	14.87	15.83	16.76
	3H	16.35	17.15	17.12	17.95	18.90	15.94	16.74	16.72	17.54	18.49
	4H	17.07	17.80	17.86	18.60	19.57	16.65	17.37	17.44	18.17	19.15
	6H	17.60	18.23	18.40	19.05	20.03	17.17	17.79	17.97	18.62	19.60
	8H	17.75	18.34	18.56	19.16	20.15	17.32	17.90	18.12	18.72	19.72
	12H	17.84	18.36	18.66	19.21	20.21	17.39	17.92	18.22	18.76	19.76
8H	4H	17.29	17.87	18.09	18.69	19.69	16.91	17.50	17.72	18.32	19.31
	6H	17.92	18.41	18.76	19.27	20.27	17.54	18.03	18.38	18.89	19.88
	8H	18.14	18.58	18.99	19.43	20.45	17.75	18.18	18.60	19.04	20.05
	12H	18.28	18.66	19.13	19.51	20.58	17.87	18.25	18.72	19.10	20.17
12H	4H	17.28	17.81	18.11	18.65	19.65	16.92	17.44	17.74	18.28	19.29
	6H	17.95	18.39	18.80	19.24	20.26	17.58	18.01	18.43	18.87	19.88
	8H	18.20	18.59	19.05	19.43	20.50	17.82	18.20	18.67	19.05	20.12