

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922947

Luminaire Tested: DFN2DIP-SQ3F0-100D090US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922947
REPORT IS A COMBINATION OF REPORTS P901484 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D090US940-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15524.6 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 167
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922947
CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P922947

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35	31				31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	19	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4223	4223	4223
5°	4227	4153	4181
10°	4182	4069	4044
15°	4122	3931	3832
20°	4043	3744	3573
25°	3962	3533	3323
30°	3855	3318	3006
35°	3749	3087	2727
40°	3642	2848	2408
45°	3517	2583	2120
50°	3388	2316	1837
55°	3253	2031	1566
60°	3096	1734	1288
65°	2916	1432	1157
70°	2697	1150	1046
75°	2422	1008	948
80°	2023	837	818
85°	1372	545	606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3517 cd/sqm



TEST NUMBER: P922947

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.4	2.2
10°-20°	948.2	6.1
20°-30°	1331.2	8.6
30°-40°	1451.1	9.3
40°-50°	1333.8	8.6
50°-60°	1047.4	6.7
60°-70°	681.8	4.4
70°-80°	351.0	2.3
80°-90°	94.4	0.6
90°-100°	89.3	0.6
100°-110°	332.9	2.1
110°-120°	883.0	5.7
120°-130°	1464.5	9.4
130°-140°	1555.6	10.0
140°-150°	1445.8	9.3
150°-160°	1162.4	7.5
160°-170°	749.0	4.8
170°-180°	257.8	1.7
0°-30°	2624.8	16.9
0°-40°	4076.0	26.3
0°-60°	6457.2	41.6
0°-90°	7584.3	48.9
90°-120°	1305.2	8.4
90°-150°	5771.2	37.2
90°-180°	7940.0	51.1
0°-180°	15524.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3685	3685	3685	3685	3685	
5°	3685	3669	3625	3655	3645	349
15°	3505	3468	3355	3292	3259	988
25°	3182	3075	2855	2718	2668	1463
35°	2742	2572	2278	2068	1994	1716
45°	2241	2018	1668	1431	1351	1731
55°	1704	1444	1084	884	821	1523
65°	1151	880	580	467	457	1141
75°	614	380	267	243	240	649
85°	143	73	63	63	63	164
90°	2	24	39	49	53	15
95°	127	63	76	86	84	151
105°	596	655	120	141	149	637
115°	1127	1160	1209	302	161	1109
125°	1593	1619	1656	1670	1676	1421
135°	1972	2003	2020	2040	2036	1523
145°	2287	2285	2318	2332	2322	1431
155°	2518	2501	2524	2536	2520	1161
165°	2654	2642	2648	2662	2648	750
175°	2714	2700	2705	2718	2699	258
180°	2708	2708	2708	2708	2708	



TEST NUMBER: P922947

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3685.4	3685.4	3685.4	3685.4	3685.4
2.5°	3702.0	3685.4	3648.6	3682.2	3675.5
5°	3685.4	3668.8	3625.2	3655.4	3645.4
7.5°	3655.4	3635.5	3588.8	3601.9	3585.3
10°	3615.4	3592.0	3525.5	3515.2	3495.4
12.5°	3565.5	3535.4	3445.1	3425.3	3388.5
15°	3505.3	3468.5	3355.2	3291.9	3258.7
17.5°	3435.2	3381.8	3241.7	3168.4	3115.0
20°	3355.2	3288.4	3121.7	3038.6	2964.9
22.5°	3268.6	3191.8	2998.2	2885.0	2835.1
25°	3181.9	3075.1	2854.9	2718.3	2668.1
27.5°	3078.5	2964.9	2721.5	2564.7	2488.0
30°	2968.5	2841.4	2574.6	2404.9	2314.6
32.5°	2861.7	2708.0	2434.9	2234.6	2151.1
35°	2741.7	2571.5	2278.1	2068.0	1994.3
37.5°	2624.9	2441.2	2131.3	1900.9	1817.8
40°	2501.4	2301.5	1977.7	1741.0	1654.3
42.5°	2374.7	2161.3	1824.5	1577.5	1494.3
45°	2241.3	2017.7	1667.8	1430.7	1350.7
47.5°	2114.7	1877.9	1517.7	1280.6	1207.4
50°	1974.5	1737.8	1370.8	1140.5	1070.8
52.5°	1837.5	1587.4	1230.7	1010.6	947.3
55°	1704.1	1444.1	1083.9	884.0	820.6
57.5°	1567.6	1300.7	954.0	767.1	713.7
60°	1427.4	1160.7	817.1	647.2	593.8
62.5°	1290.8	1024.0	700.3	540.4	513.8
65°	1150.8	880.4	580.3	467.1	456.8
67.5°	1017.4	747.0	467.1	410.1	400.2
70°	877.2	617.2	386.7	353.5	340.1
72.5°	743.8	496.8	323.4	296.9	290.2
75°	613.6	380.0	266.8	243.4	240.2
77.5°	483.8	270.0	210.2	196.7	190.0
80°	363.4	193.6	160.0	146.9	146.9
82.5°	253.3	130.2	110.0	103.3	103.3
85°	143.3	73.2	63.3	63.3	63.3
87.5°	53.4	26.6	26.6	23.4	23.4
90°	1.9	23.5	39.1	49.1	52.8
92.5°	49.1	41.2	47.0	51.0	52.8
95°	127.3	62.6	76.3	86.3	84.3
97.5°	229.3	68.7	99.9	105.8	107.7
100°	347.0	78.5	111.7	127.3	131.3
102.5°	476.2	472.4	115.7	137.1	143.1
105°	595.8	654.7	119.6	141.1	148.9
107.5°	734.9	783.8	123.6	145.0	152.9
110°	868.3	909.3	343.0	147.0	154.8



TEST NUMBER: P922947

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	993.7	1028.9	995.6	150.8	156.9
115°	1126.9	1160.1	1209.2	301.8	160.8
117.5°	1242.5	1281.7	1315.1	1034.7	521.3
120°	1371.9	1401.2	1436.6	1460.1	1195.5
122.5°	1481.6	1513.0	1552.3	1563.9	1566.0
125°	1593.2	1618.8	1656.1	1669.8	1675.6
127.5°	1695.1	1722.6	1752.2	1771.7	1773.6
130°	1791.3	1822.7	1844.1	1865.7	1863.9
132.5°	1889.3	1914.9	1936.3	1954.0	1952.1
135°	1971.7	2003.0	2020.5	2040.3	2036.4
137.5°	2057.8	2081.3	2101.0	2120.6	2114.8
140°	2142.0	2157.8	2179.3	2196.9	2187.2
142.5°	2212.8	2226.5	2251.8	2267.4	2257.7
145°	2287.2	2285.1	2318.4	2332.2	2322.4
147.5°	2351.7	2345.9	2379.2	2389.0	2381.2
150°	2414.6	2400.8	2432.2	2443.8	2434.1
152.5°	2467.4	2451.8	2481.1	2493.0	2479.2
155°	2518.4	2500.9	2524.3	2536.0	2520.4
157.5°	2559.6	2544.0	2561.6	2575.3	2559.6
160°	2594.9	2583.0	2594.9	2606.6	2592.8
162.5°	2626.1	2614.4	2624.2	2637.9	2620.3
165°	2653.6	2641.9	2647.8	2661.5	2647.8
167.5°	2675.2	2663.4	2669.3	2683.1	2665.4
170°	2692.9	2681.0	2684.9	2698.7	2681.0
172.5°	2704.6	2692.9	2696.8	2710.5	2692.9
175°	2714.3	2700.5	2704.6	2718.2	2698.7
177.5°	2718.2	2704.6	2706.6	2720.3	2702.7
180°	2708.5	2708.5	2708.5	2708.5	2708.5



TEST NUMBER: P922947
 CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.01	12.83	12.98	13.81	15.10	7.97	8.79	8.94	9.77	11.06
	3H	13.68	14.42	14.67	15.41	16.72	9.15	9.89	10.14	10.88	12.19
	4H	14.29	14.98	15.29	15.98	17.30	9.60	10.29	10.59	11.29	12.61
	6H	14.70	15.34	15.71	16.34	17.68	9.91	10.55	10.92	11.55	12.88
	8H	14.83	15.44	15.84	16.45	17.78	10.00	10.61	11.01	11.62	12.95
	12H	14.89	15.47	15.91	16.48	17.83	10.04	10.62	11.06	11.63	12.98
4H	2H	12.02	12.72	13.03	13.71	15.03	8.56	9.26	9.57	10.25	11.57
	3H	13.85	14.42	14.86	15.45	16.78	9.90	10.48	10.92	11.51	12.84
	4H	14.54	15.06	15.56	16.08	17.44	10.45	10.97	11.47	11.99	13.35
	6H	15.05	15.50	16.08	16.54	17.89	10.86	11.31	11.89	12.35	13.71
	8H	15.22	15.64	16.25	16.67	18.04	10.98	11.41	12.01	12.44	13.81
	12H	15.31	15.69	16.36	16.74	18.11	11.04	11.42	12.09	12.47	13.85
8H	4H	14.50	14.92	15.53	15.96	17.33	10.72	11.15	11.75	12.18	13.55
	6H	15.06	15.41	16.12	16.49	17.85	11.23	11.58	12.29	12.66	14.02
	8H	15.28	15.58	16.34	16.64	18.03	11.42	11.72	12.48	12.79	14.17
	12H	15.41	15.68	16.48	16.73	18.16	11.53	11.80	12.60	12.86	14.28
12H	4H	14.45	14.83	15.50	15.88	17.26	10.73	11.11	11.78	12.16	13.53
	6H	15.04	15.34	16.10	16.40	17.79	11.28	11.59	12.34	12.65	14.03
	8H	15.25	15.52	16.32	16.58	18.01	11.48	11.75	12.55	12.81	14.24