

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906764

Luminaire Tested: DFN2DIP-SQ4F0-080D140US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906764
REPORT IS A COMBINATION OF REPORTS P900189 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D140US835-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20310.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 177.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39
2	87	79	73	68	79	72	67	63	59	56	52	47	45	42	36	34	33
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	27	26	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	26	31	26	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	18	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2184	2184	2184
5°	2188	2154	2169
10°	2170	2126	2140
15°	2138	2091	2095
20°	2095	2043	2049
25°	2052	1985	1995
30°	1998	1932	1926
35°	1947	1868	1854
40°	1884	1804	1785
45°	1822	1740	1715
50°	1753	1673	1633
55°	1682	1595	1558
60°	1601	1502	1472
65°	1513	1407	1371
70°	1400	1290	1263
75°	1244	1151	1163
80°	1057	974	972
85°	764	666	653

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3485 cd/sqm

TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	1.4
10°-20°	824.3	4.1
20°-30°	1211.5	6.0
30°-40°	1407.0	6.9
40°-50°	1405.3	6.9
50°-60°	1225.4	6.0
60°-70°	905.8	4.5
70°-80°	512.5	2.5
80°-90°	147.9	0.7
90°-100°	274.0	1.3
100°-110°	870.6	4.3
110°-120°	1489.8	7.3
120°-130°	1959.3	9.6
130°-140°	2199.2	10.8
140°-150°	2156.6	10.6
150°-160°	1809.1	8.9
160°-170°	1199.7	5.9
170°-180°	419.3	2.1
0°-30°	2328.8	11.5
0°-40°	3735.8	18.4
0°-60°	6366.4	31.3
0°-90°	7932.6	39.1
90°-120°	2634.3	13.0
90°-150°	8949.3	44.1
90°-180°	12377.0	60.9
0°-180°	20310.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	4	48	131	123	127	20
95°	195	232	239	239	232	217
105°	804	814	822	829	829	848
115°	1495	1516	1510	1506	1495	1479
125°	2174	2208	2197	2185	2181	1943
135°	2812	2854	2862	2858	2847	2174
145°	3414	3441	3463	3467	3452	2133
155°	3904	3915	3927	3946	3934	1797
165°	4248	4244	4244	4270	4252	1198
175°	4420	4409	4401	4428	4405	420
180°	4428	4428	4428	4428	4428	

TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	4.0	48.1	130.8	122.8	126.8
92.5°	82.8	112.1	116.1	120.1	120.1
95°	194.9	232.3	238.9	238.9	232.3
97.5°	324.4	359.1	373.8	373.8	373.8
100°	473.9	504.6	515.2	515.2	511.2
102.5°	631.4	654.1	668.8	672.8	668.8
105°	803.6	814.3	822.3	828.9	828.9
107.5°	974.4	990.5	990.5	993.1	974.4
110°	1140.0	1161.3	1161.3	1161.3	1150.6

TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1318.8	1341.5	1337.5	1326.8	1318.8
115°	1495.0	1516.4	1509.7	1505.7	1495.0
117.5°	1669.9	1699.3	1680.6	1669.9	1659.2
120°	1846.1	1875.5	1846.1	1846.1	1834.1
122.5°	2006.3	2043.6	2025.0	2014.3	2006.3
125°	2174.5	2207.8	2197.1	2185.1	2181.1
127.5°	2338.6	2380.0	2365.3	2349.3	2338.6
130°	2492.1	2540.2	2533.5	2525.5	2510.8
132.5°	2664.3	2701.7	2704.4	2685.7	2675.0
135°	2812.5	2853.9	2861.9	2857.9	2847.2
137.5°	2978.0	3011.4	3018.1	3015.4	2999.4
140°	3123.5	3156.9	3175.6	3175.6	3160.9
142.5°	3273.0	3306.4	3317.1	3321.1	3306.4
145°	3414.5	3441.2	3462.6	3466.6	3451.9
147.5°	3541.3	3574.7	3590.7	3597.4	3582.7
150°	3672.1	3694.8	3709.5	3721.5	3709.5
152.5°	3788.3	3811.0	3829.7	3844.3	3829.7
155°	3904.4	3915.1	3927.1	3945.8	3933.8
157.5°	4004.5	4012.5	4019.2	4045.9	4027.2
160°	4094.0	4102.0	4106.0	4128.7	4112.6
162.5°	4176.7	4176.7	4180.7	4206.1	4187.4
165°	4247.5	4243.5	4243.5	4270.2	4251.5
167.5°	4311.5	4299.5	4299.5	4326.2	4307.5
170°	4359.6	4348.9	4344.9	4371.6	4348.9
172.5°	4393.0	4382.3	4378.3	4405.0	4382.3
175°	4419.7	4409.0	4401.0	4427.7	4405.0
177.5°	4434.3	4423.7	4415.7	4438.3	4415.7
180°	4427.7	4427.7	4427.7	4427.7	4427.7

TEST NUMBER: P906764

CATALOG NUMBER: DFN2DIP-SQ4F0-080D140US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.89	9.66	9.94	10.71	12.13	8.45	9.22	9.49	10.27	11.69
	3H	10.55	11.24	11.61	12.30	13.74	10.06	10.75	11.11	11.81	13.25
	4H	11.14	11.79	12.20	12.85	14.30	10.64	11.30	11.71	12.36	13.80
	6H	11.53	12.14	12.61	13.20	14.66	11.03	11.64	12.11	12.70	14.16
	8H	11.64	12.21	12.72	13.29	14.75	11.14	11.71	12.22	12.79	14.24
	12H	11.69	12.23	12.77	13.31	14.78	11.18	11.72	12.26	12.80	14.27
4H	2H	9.34	10.00	10.42	11.06	12.50	8.99	9.64	10.06	10.70	12.15
	3H	11.20	11.75	12.29	12.84	14.30	10.80	11.34	11.88	12.43	13.89
	4H	11.92	12.42	13.01	13.50	14.98	11.49	12.00	12.58	13.08	14.56
	6H	12.43	12.86	13.53	13.97	15.44	12.00	12.43	13.10	13.53	15.01
	8H	12.58	12.98	13.68	14.08	15.57	12.15	12.55	13.24	13.64	15.13
	12H	12.65	13.02	13.77	14.13	15.62	12.20	12.57	13.32	13.68	15.17
8H	4H	12.11	12.51	13.20	13.61	15.09	11.73	12.13	12.83	13.23	14.72
	6H	12.74	13.07	13.86	14.21	15.70	12.36	12.69	13.47	13.83	15.31
	8H	12.96	13.25	14.09	14.37	15.88	12.57	12.86	13.69	13.98	15.49
	12H	13.09	13.35	14.22	14.46	16.01	12.68	12.94	13.81	14.05	15.60
12H	4H	12.09	12.45	13.20	13.56	15.06	11.72	12.09	12.83	13.19	14.69
	6H	12.77	13.06	13.89	14.18	15.69	12.40	12.69	13.52	13.81	15.31
	8H	13.01	13.27	14.14	14.38	15.92	12.63	12.89	13.76	14.00	15.54

END OF REPORT