

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906841

Luminaire Tested: DFN2DIP-SQ4F0-100D160US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906841
REPORT IS A COMBINATION OF REPORTS P901731 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25740.0 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2730	2730	2730
5°	2735	2693	2711
10°	2712	2657	2675
15°	2672	2614	2619
20°	2618	2554	2561
25°	2565	2481	2494
30°	2498	2414	2408
35°	2434	2335	2317
40°	2356	2255	2231
45°	2277	2175	2143
50°	2192	2091	2041
55°	2102	1994	1948
60°	2001	1878	1841
65°	1891	1759	1714
70°	1750	1613	1578
75°	1555	1439	1454
80°	1321	1217	1215
85°	955	833	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2894 cd/sqm

TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	1.4
10°-20°	1030.4	4.0
20°-30°	1514.3	5.9
30°-40°	1758.8	6.8
40°-50°	1756.6	6.8
50°-60°	1531.7	6.0
60°-70°	1132.3	4.4
70°-80°	640.6	2.5
80°-90°	178.6	0.7
90°-100°	178.0	0.7
100°-110°	663.8	2.6
110°-120°	1760.4	6.8
120°-130°	2919.7	11.3
130°-140°	3101.5	12.0
140°-150°	2882.5	11.2
150°-160°	2317.4	9.0
160°-170°	1493.3	5.8
170°-180°	514.0	2.0
0°-30°	2911.0	11.3
0°-40°	4669.7	18.1
0°-60°	7958.0	30.9
0°-90°	9909.5	38.5
90°-120°	2602.2	10.1
90°-150°	11505.9	44.7
90°-180°	15831.0	61.5
0°-180°	25740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	4	47	78	98	105	24
95°	254	125	152	172	168	301
105°	1188	1305	238	281	297	1269
115°	2247	2313	2411	602	321	2212
125°	3176	3227	3302	3329	3341	2833
135°	3931	3994	4028	4068	4060	3036
145°	4560	4556	4622	4650	4630	2852
155°	5021	4986	5033	5056	5025	2314
165°	5290	5267	5279	5306	5279	1495
175°	5411	5384	5392	5419	5380	515
180°	5400	5400	5400	5400	5400	

TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	3.7	46.9	77.9	97.9	105.3
92.5°	97.9	82.1	93.7	101.6	105.3
95°	253.8	124.8	152.2	172.1	168.0
97.5°	457.0	136.9	199.0	211.1	214.8
100°	691.8	156.4	222.7	253.8	261.7
102.5°	949.3	941.9	230.6	273.3	285.3
105°	1187.8	1305.2	238.5	281.2	296.9
107.5°	1465.2	1562.7	246.4	289.1	304.8
110°	1731.1	1812.8	683.9	293.2	308.5

TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1981.2	2051.3	1984.9	300.7	312.7
115°	2246.6	2312.9	2410.8	601.8	320.6
117.5°	2477.2	2555.1	2622.0	2062.9	1039.3
120°	2735.2	2793.6	2864.1	2911.0	2383.5
122.5°	2953.7	3016.3	3094.7	3117.9	3122.1
125°	3176.4	3227.4	3301.7	3329.1	3340.7
127.5°	3379.6	3434.4	3493.3	3532.3	3536.0
130°	3571.3	3633.9	3676.6	3719.7	3716.0
132.5°	3766.6	3817.6	3860.3	3895.6	3891.9
135°	3930.8	3993.5	4028.3	4067.7	4059.8
137.5°	4102.5	4149.4	4188.8	4227.8	4216.2
140°	4270.5	4302.0	4344.7	4380.0	4360.5
142.5°	4411.5	4438.9	4489.5	4520.6	4501.1
145°	4560.0	4555.8	4622.2	4649.5	4630.1
147.5°	4688.5	4676.9	4743.3	4762.8	4747.4
150°	4813.8	4786.4	4849.1	4872.3	4852.8
152.5°	4919.1	4888.0	4946.5	4970.2	4942.8
155°	5020.7	4985.9	5032.8	5056.0	5024.9
157.5°	5102.9	5071.8	5107.0	5134.4	5102.9
160°	5173.4	5149.7	5173.4	5196.6	5169.2
162.5°	5235.6	5212.4	5231.8	5259.2	5224.0
165°	5290.3	5267.1	5278.7	5306.1	5278.7
167.5°	5333.5	5309.8	5321.9	5349.2	5314.0
170°	5368.7	5345.1	5352.9	5380.3	5345.1
172.5°	5391.9	5368.7	5376.6	5404.0	5368.7
175°	5411.4	5384.0	5391.9	5419.3	5380.3
177.5°	5419.3	5391.9	5396.1	5423.5	5388.2
180°	5399.8	5399.8	5399.8	5399.8	5399.8

TEST NUMBER: P906841

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.61	10.37	10.66	11.43	12.85	9.16	9.93	10.21	10.98	12.41
	3H	11.26	11.95	12.32	13.02	14.46	10.77	11.46	11.83	12.52	13.97
	4H	11.85	12.50	12.92	13.57	15.02	11.36	12.01	12.43	13.07	14.53
	6H	12.25	12.85	13.33	13.92	15.38	11.75	12.35	12.83	13.42	14.88
	8H	12.35	12.92	13.44	14.01	15.47	11.85	12.42	12.94	13.51	14.97
	12H	12.40	12.94	13.49	14.02	15.50	11.89	12.43	12.98	13.51	14.99
4H	2H	10.06	10.71	11.14	11.77	13.23	9.70	10.35	10.78	11.42	12.87
	3H	11.92	12.46	13.00	13.56	15.02	11.51	12.06	12.60	13.15	14.61
	4H	12.63	13.13	13.72	14.21	15.70	12.21	12.71	13.30	13.79	15.28
	6H	13.15	13.58	14.25	14.68	16.16	12.71	13.14	13.81	14.25	15.73
	8H	13.30	13.70	14.40	14.79	16.29	12.86	13.26	13.96	14.36	15.85
	12H	13.37	13.73	14.48	14.84	16.34	12.92	13.28	14.03	14.39	15.89
8H	4H	12.82	13.22	13.92	14.32	15.82	12.45	12.85	13.54	13.94	15.44
	6H	13.45	13.78	14.58	14.93	16.42	13.07	13.40	14.19	14.54	16.03
	8H	13.68	13.97	14.80	15.09	16.60	13.28	13.57	14.41	14.70	16.21
	12H	13.81	14.06	14.94	15.18	16.73	13.40	13.65	14.53	14.77	16.32
12H	4H	12.80	13.17	13.92	14.28	15.78	12.44	12.80	13.55	13.91	15.41
	6H	13.48	13.77	14.61	14.89	16.41	13.11	13.40	14.24	14.52	16.04
	8H	13.72	13.98	14.86	15.10	16.65	13.34	13.60	14.48	14.72	16.27