

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906843

Luminaire Tested: DFN2DIP-SQ4F0-100D160US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906843
REPORT IS A COMBINATION OF REPORTS P901732 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D160US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24340.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 214.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2900	2900	2900
5°	2905	2855	2873
10°	2876	2799	2780
15°	2836	2707	2637
20°	2784	2580	2460
25°	2730	2438	2289
30°	2658	2292	2073
35°	2587	2134	1882
40°	2516	1972	1664
45°	2432	1791	1466
50°	2346	1609	1272
55°	2256	1414	1086
60°	2151	1210	895
65°	2031	1003	806
70°	1886	809	731
75°	1703	715	667
80°	1438	602	581
85°	1002	405	442

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2894 cd/sqm

TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	1.6
10°-20°	1063.3	4.4
20°-30°	1492.9	6.1
30°-40°	1627.4	6.7
40°-50°	1495.7	6.1
50°-60°	1174.7	4.8
60°-70°	764.6	3.1
70°-80°	393.6	1.6
80°-90°	110.0	0.5
90°-100°	178.0	0.7
100°-110°	663.8	2.7
110°-120°	1760.4	7.2
120°-130°	2919.7	12.0
130°-140°	3101.5	12.7
140°-150°	2882.5	11.8
150°-160°	2317.4	9.5
160°-170°	1493.3	6.1
170°-180°	514.0	2.1
0°-30°	2943.6	12.1
0°-40°	4571.0	18.8
0°-60°	7241.3	29.8
0°-90°	8509.5	35.0
90°-120°	2602.2	10.7
90°-150°	11505.9	47.3
90°-180°	15831.0	65.0
0°-180°	24340.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	4	47	78	98	105	23
95°	254	125	152	172	168	301
105°	1188	1305	238	281	297	1269
115°	2247	2313	2411	602	321	2212
125°	3176	3227	3302	3329	3341	2833
135°	3931	3994	4028	4068	4060	3036
145°	4560	4556	4622	4650	4630	2852
155°	5021	4986	5033	5056	5025	2314
165°	5290	5267	5279	5306	5279	1495
175°	5411	5384	5392	5419	5380	515
180°	5400	5400	5400	5400	5400	

TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	3.7	46.9	77.9	97.9	105.3
92.5°	97.9	82.1	93.7	101.6	105.3
95°	253.8	124.8	152.2	172.1	168.0
97.5°	457.0	136.9	199.0	211.1	214.8
100°	691.8	156.4	222.7	253.8	261.7
102.5°	949.3	941.9	230.6	273.3	285.3
105°	1187.8	1305.2	238.5	281.2	296.9
107.5°	1465.2	1562.7	246.4	289.1	304.8
110°	1731.1	1812.8	683.9	293.2	308.5

TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1981.2	2051.3	1984.9	300.7	312.7
115°	2246.6	2312.9	2410.8	601.8	320.6
117.5°	2477.2	2555.1	2622.0	2062.9	1039.3
120°	2735.2	2793.6	2864.1	2911.0	2383.5
122.5°	2953.7	3016.3	3094.7	3117.9	3122.1
125°	3176.4	3227.4	3301.7	3329.1	3340.7
127.5°	3379.6	3434.4	3493.3	3532.3	3536.0
130°	3571.3	3633.9	3676.6	3719.7	3716.0
132.5°	3766.6	3817.6	3860.3	3895.6	3891.9
135°	3930.8	3993.5	4028.3	4067.7	4059.8
137.5°	4102.5	4149.4	4188.8	4227.8	4216.2
140°	4270.5	4302.0	4344.7	4380.0	4360.5
142.5°	4411.5	4438.9	4489.5	4520.6	4501.1
145°	4560.0	4555.8	4622.2	4649.5	4630.1
147.5°	4688.5	4676.9	4743.3	4762.8	4747.4
150°	4813.8	4786.4	4849.1	4872.3	4852.8
152.5°	4919.1	4888.0	4946.5	4970.2	4942.8
155°	5020.7	4985.9	5032.8	5056.0	5024.9
157.5°	5102.9	5071.8	5107.0	5134.4	5102.9
160°	5173.4	5149.7	5173.4	5196.6	5169.2
162.5°	5235.6	5212.4	5231.8	5259.2	5224.0
165°	5290.3	5267.1	5278.7	5306.1	5278.7
167.5°	5333.5	5309.8	5321.9	5349.2	5314.0
170°	5368.7	5345.1	5352.9	5380.3	5345.1
172.5°	5391.9	5368.7	5376.6	5404.0	5368.7
175°	5411.4	5384.0	5391.9	5419.3	5380.3
177.5°	5419.3	5391.9	5396.1	5423.5	5388.2
180°	5399.8	5399.8	5399.8	5399.8	5399.8

TEST NUMBER: P906843

CATALOG NUMBER: DFN2DIP-SQ4F0-100D160US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.27	9.99	10.35	11.07	12.54	5.23	5.95	6.31	7.03	8.50
	3H	10.94	11.58	12.03	12.67	14.16	6.41	7.05	7.50	8.14	9.63
	4H	11.55	12.16	12.65	13.25	14.74	6.85	7.46	7.96	8.55	10.05
	6H	11.97	12.53	13.08	13.62	15.13	7.17	7.73	8.28	8.82	10.33
	8H	12.09	12.63	13.21	13.73	15.24	7.26	7.79	8.37	8.90	10.40
	12H	12.15	12.66	13.27	13.76	15.28	7.30	7.81	8.42	8.91	10.43
4H	2H	9.27	9.88	10.38	10.97	12.47	5.81	6.42	6.92	7.51	9.01
	3H	11.10	11.60	12.21	12.72	14.23	7.15	7.66	8.27	8.78	10.29
	4H	11.79	12.25	12.91	13.36	14.89	7.70	8.16	8.82	9.27	10.80
	6H	12.30	12.70	13.43	13.83	15.35	8.11	8.51	9.24	9.64	11.16
	8H	12.48	12.85	13.60	13.97	15.51	8.24	8.61	9.36	9.73	11.27
	12H	12.57	12.91	13.71	14.04	15.58	8.30	8.64	9.44	9.77	11.31
8H	4H	11.75	12.12	12.87	13.24	14.78	7.97	8.34	9.10	9.46	11.00
	6H	12.31	12.62	13.46	13.78	15.32	8.49	8.79	9.63	9.96	11.49
	8H	12.53	12.80	13.68	13.94	15.50	8.68	8.95	9.83	10.09	11.64
	12H	12.67	12.91	13.83	14.04	15.63	8.79	9.03	9.95	10.17	11.76
12H	4H	11.69	12.03	12.84	13.16	14.71	7.97	8.31	9.11	9.44	10.98
	6H	12.29	12.56	13.44	13.70	15.25	8.54	8.81	9.69	9.95	11.50
	8H	12.51	12.74	13.66	13.88	15.47	8.74	8.98	9.90	10.12	11.71