

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922971

Luminaire Tested: DFN2DIP-SQ3F0-110D060US940-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922971
REPORT IS A COMBINATION OF REPORTS P901432 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D060US940-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13634.2 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 157
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	77	77	77	66	66	66
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	60	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43
4	78	67	59	54	73	63	56	51	56	51	46	49	45	42	43	40	37
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	39	36	33
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29
7	61	49	41	36	58	47	40	35	42	36	32	37	32	29	33	29	26
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4645	4645	4645
5°	4650	4568	4599
10°	4601	4476	4448
15°	4534	4325	4215
20°	4448	4118	3930
25°	4359	3887	3655
30°	4240	3650	3306
35°	4124	3396	3000
40°	4006	3133	2649
45°	3869	2842	2332
50°	3727	2548	2021
55°	3578	2234	1723
60°	3406	1907	1417
65°	3207	1575	1273
70°	2967	1265	1150
75°	2663	1108	1043
80°	2226	920	900
85°	1510	599	666

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3869 cd/sqm

TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.9	2.8
10°-20°	1043.0	7.6
20°-30°	1464.4	10.7
30°-40°	1596.2	11.7
40°-50°	1467.1	10.8
50°-60°	1152.2	8.5
60°-70°	750.0	5.5
70°-80°	386.0	2.8
80°-90°	101.7	0.7
90°-100°	59.5	0.4
100°-110°	222.0	1.6
110°-120°	588.7	4.3
120°-130°	976.3	7.2
130°-140°	1037.1	7.6
140°-150°	963.9	7.1
150°-160°	774.9	5.7
160°-170°	499.3	3.7
170°-180°	171.9	1.3
0°-30°	2887.3	21.2
0°-40°	4483.6	32.9
0°-60°	7102.9	52.1
0°-90°	8340.7	61.2
90°-120°	870.2	6.4
90°-150°	3847.4	28.2
90°-180°	5294.0	38.8
0°-180°	13634.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4054	4054	4054	4054	4054	
5°	4054	4036	3988	4021	4010	384
15°	3856	3815	3691	3621	3584	1087
25°	3500	3382	3140	2990	2935	1610
35°	3016	2829	2506	2275	2194	1888
45°	2466	2220	1834	1574	1486	1904
55°	1875	1588	1192	972	903	1675
65°	1266	968	638	514	502	1255
75°	675	418	294	268	264	714
85°	158	81	70	70	70	181
90°	1	16	26	33	35	13
95°	85	42	51	58	56	101
105°	397	436	80	94	99	424
115°	751	774	806	201	107	740
125°	1062	1079	1104	1113	1117	947
135°	1314	1335	1347	1360	1358	1015
145°	1525	1523	1546	1555	1548	954
155°	1679	1667	1683	1691	1680	774
165°	1769	1761	1765	1774	1765	500
175°	1810	1800	1803	1812	1799	172
180°	1806	1806	1806	1806	1806	

TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4054.0	4054.0	4054.0	4054.0	4054.0
2.5°	4072.3	4054.0	4013.5	4050.5	4043.1
5°	4054.0	4035.7	3987.8	4020.9	4010.0
7.5°	4020.9	3999.1	3947.7	3962.1	3943.8
10°	3976.9	3951.2	3878.0	3866.7	3845.0
12.5°	3922.0	3888.9	3789.7	3767.8	3727.3
15°	3855.8	3815.4	3690.8	3621.1	3584.5
17.5°	3778.8	3720.0	3565.9	3485.2	3426.5
20°	3690.8	3617.2	3433.9	3342.4	3261.4
22.5°	3595.5	3510.9	3298.1	3173.5	3118.6
25°	3500.1	3382.5	3140.4	2990.2	2934.9
27.5°	3386.4	3261.4	2993.7	2821.2	2736.7
30°	3265.4	3125.6	2832.2	2645.3	2546.0
32.5°	3147.8	2978.8	2678.3	2458.1	2366.2
35°	3015.9	2828.6	2506.0	2274.8	2193.8
37.5°	2887.4	2685.4	2344.4	2091.0	1999.6
40°	2751.6	2531.7	2175.5	1915.0	1819.7
42.5°	2612.2	2377.5	2007.0	1735.3	1643.8
45°	2465.5	2219.5	1834.5	1573.7	1485.8
47.5°	2326.1	2065.7	1669.5	1408.6	1328.1
50°	2171.9	1911.6	1508.0	1254.5	1177.9
52.5°	2021.3	1746.1	1353.8	1111.7	1042.0
55°	1874.6	1588.5	1192.2	972.3	902.7
57.5°	1724.4	1430.8	1049.4	843.9	785.1
60°	1570.2	1276.8	898.8	711.9	653.2
62.5°	1420.0	1126.5	770.3	594.4	565.2
65°	1265.8	968.4	638.4	513.8	502.5
67.5°	1119.1	821.7	513.8	451.1	440.2
70°	964.9	678.9	425.4	388.9	374.1
72.5°	818.1	546.5	355.8	326.5	319.1
75°	674.9	418.0	293.5	267.8	264.3
77.5°	532.1	297.0	231.2	216.4	209.0
80°	399.8	212.9	175.9	161.6	161.6
82.5°	278.7	143.2	121.1	113.7	113.7
85°	157.7	80.6	69.6	69.6	69.6
87.5°	58.8	29.2	29.2	25.7	25.7
90°	1.2	15.7	26.0	32.7	35.2
92.5°	32.7	27.5	31.3	34.0	35.2
95°	84.9	41.7	50.9	57.6	56.2
97.5°	152.8	45.7	66.5	70.6	71.9
100°	231.3	52.3	74.5	84.9	87.5
102.5°	317.4	315.0	77.1	91.4	95.4
105°	397.2	436.4	79.7	94.0	99.3
107.5°	490.0	522.5	82.4	96.7	101.9
110°	578.9	606.2	228.7	98.1	103.2



TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	662.5	685.9	663.7	100.5	104.6
115°	751.3	773.5	806.2	201.3	107.2
117.5°	828.3	854.4	876.7	689.8	347.5
120°	914.6	934.2	957.8	973.4	797.0
122.5°	987.7	1008.6	1034.8	1042.6	1044.0
125°	1062.2	1079.2	1104.0	1113.2	1117.0
127.5°	1130.2	1148.4	1168.1	1181.2	1182.4
130°	1194.2	1215.1	1229.4	1243.8	1242.6
132.5°	1259.5	1276.6	1290.8	1302.6	1301.4
135°	1314.5	1335.4	1347.0	1360.2	1357.5
137.5°	1371.8	1387.5	1400.7	1413.7	1409.9
140°	1428.0	1438.6	1452.9	1464.6	1458.1
142.5°	1475.2	1484.3	1501.3	1511.6	1505.1
145°	1524.8	1523.4	1545.6	1554.8	1548.3
147.5°	1567.8	1563.9	1586.1	1592.6	1587.5
150°	1609.7	1600.5	1621.5	1629.2	1622.7
152.5°	1644.9	1634.5	1654.0	1662.0	1652.8
155°	1678.9	1667.2	1682.9	1690.7	1680.2
157.5°	1706.4	1695.9	1707.7	1716.9	1706.4
160°	1729.9	1722.0	1729.9	1737.7	1728.6
162.5°	1750.7	1742.9	1749.4	1758.6	1746.9
165°	1769.1	1761.3	1765.1	1774.3	1765.1
167.5°	1783.4	1775.6	1779.6	1788.8	1776.9
170°	1795.3	1787.3	1790.0	1799.1	1787.3
172.5°	1803.0	1795.3	1797.9	1807.1	1795.3
175°	1809.5	1800.4	1803.0	1812.1	1799.1
177.5°	1812.1	1803.0	1804.4	1813.6	1801.8
180°	1805.6	1805.6	1805.6	1805.6	1805.6

TEST NUMBER: P922971

CATALOG NUMBER: DFN2DIP-SQ3F0-110D060US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	14.36	14.29	15.24	16.35	9.39	10.32	10.26	11.20	12.31
	3H	15.11	15.95	15.99	16.83	17.97	10.58	11.42	11.46	12.30	13.44
	4H	15.72	16.51	16.61	17.40	18.55	11.03	11.82	11.92	12.71	13.86
	6H	16.15	16.87	17.05	17.77	18.93	11.35	12.08	12.26	12.98	14.13
	8H	16.27	16.96	17.18	17.88	19.03	11.44	12.13	12.35	13.05	14.20
	12H	16.34	16.99	17.25	17.90	19.08	11.49	12.14	12.40	13.05	14.23
4H	2H	13.46	14.25	14.36	15.14	16.28	10.00	10.78	10.89	11.68	12.82
	3H	15.29	15.95	16.20	16.87	18.03	11.35	12.00	12.26	12.93	14.09
	4H	15.99	16.58	16.90	17.50	18.68	11.90	12.49	12.81	13.41	14.60
	6H	16.50	17.01	17.43	17.96	19.14	12.32	12.83	13.25	13.77	14.96
	8H	16.68	17.15	17.61	18.09	19.29	12.44	12.92	13.38	13.86	15.06
	12H	16.77	17.20	17.73	18.16	19.36	12.51	12.94	13.46	13.90	15.10
8H	4H	15.96	16.44	16.89	17.38	18.57	12.18	12.66	13.12	13.60	14.80
	6H	16.52	16.92	17.48	17.90	19.10	12.70	13.09	13.66	14.07	15.27
	8H	16.74	17.09	17.71	18.06	19.27	12.88	13.23	13.85	14.20	15.42
	12H	16.88	17.18	17.85	18.15	19.41	13.00	13.31	13.97	14.27	15.53
12H	4H	15.92	16.35	16.87	17.30	18.51	12.19	12.62	13.14	13.58	14.78
	6H	16.50	16.85	17.47	17.82	19.03	12.74	13.09	13.71	14.06	15.28
	8H	16.72	17.03	17.69	17.99	19.26	12.95	13.26	13.92	14.22	15.49