

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906873

Luminaire Tested: DFN2DIP-SQ4F0-110D140US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906873
REPORT IS A COMBINATION OF REPORTS P901715 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D140US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 24750.0 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906873
CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P906873

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20								20								20								20								20							
RC	80								50								30								10								0															
RW	70	50	30	10					70	50	30	10					50	30	10					50	30	10					50	30	10					0										
RCR																																																
0	106	106	106	106					97	97	97	97					80	80	80					65	65	65					51	51	51					44										
1	96	92	88	85					88	84	81	78					70	68	66					57	55	54					45	44	43					37										
2	88	80	74	69					80	74	69	64					61	58	54					50	47	45					39	38	36					31										
3	80	71	63	58					73	65	59	54					54	50	46					44	41	38					35	33	31					26										
4	73	63	55	49					67	58	51	45					48	43	39					39	36	33					31	29	26					23										
5	67	56	48	42					61	51	44	39					43	38	34					35	31	28					28	25	23					20										
6	62	50	42	36					56	46	39	34					39	33	29					32	28	25					25	23	20					17										
7	57	45	37	32					52	42	35	30					35	30	26					29	25	22					23	20	18					15										
8	53	41	33	28					48	38	31	26					32	27	23					27	22	19					21	18	16					14										
9	49	37	30	25					45	35	28	23					29	24	20					24	20	17					20	17	15					12										
10	46	34	27	22					42	32	25	21					27	22	18					23	19	16					18	15	13					11										

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3003	3003	3003
5°	3008	2962	2982
10°	2984	2923	2943
15°	2940	2875	2880
20°	2880	2809	2817
25°	2821	2730	2743
30°	2747	2656	2649
35°	2677	2569	2549
40°	2591	2481	2454
45°	2505	2393	2358
50°	2411	2300	2245
55°	2313	2193	2142
60°	2201	2066	2025
65°	2080	1935	1885
70°	1925	1774	1736
75°	1711	1583	1600
80°	1454	1339	1336
85°	1051	916	898

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2534 cd/sqm



TEST NUMBER: P906873

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.8	1.6
10°-20°	1133.5	4.6
20°-30°	1665.7	6.7
30°-40°	1934.7	7.8
40°-50°	1932.3	7.8
50°-60°	1684.9	6.8
60°-70°	1245.5	5.0
70°-80°	704.7	2.8
80°-90°	194.3	0.8
90°-100°	155.8	0.6
100°-110°	580.8	2.3
110°-120°	1540.3	6.2
120°-130°	2554.8	10.3
130°-140°	2713.8	11.0
140°-150°	2522.1	10.2
150°-160°	2027.7	8.2
160°-170°	1306.6	5.3
170°-180°	449.7	1.8
0°-30°	3202.1	12.9
0°-40°	5136.7	20.8
0°-60°	8753.8	35.4
0°-90°	10898.3	44.0
90°-120°	2276.9	9.2
90°-150°	10067.6	40.7
90°-180°	13852.0	56.0
0°-180°	24750.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4280	4280	4280	4280	4280	
5°	4280	4264	4219	4251	4244	406
15°	4074	4050	3996	4013	3992	1148
25°	3688	3655	3585	3593	3585	1697
35°	3182	3140	3074	3050	3029	1987
45°	2589	2560	2498	2453	2437	1998
55°	1959	1934	1885	1836	1815	1752
65°	1321	1296	1255	1218	1198	1306
75°	691	683	662	638	646	738
85°	169	165	161	148	144	188
90°	3	41	68	86	92	23
95°	222	109	133	151	147	263
105°	1039	1142	209	246	260	1110
115°	1966	2024	2110	527	280	1935
125°	2779	2824	2889	2913	2923	2479
135°	3440	3494	3525	3559	3552	2657
145°	3990	3986	4044	4068	4051	2495
155°	4393	4363	4404	4424	4397	2024
165°	4629	4609	4619	4643	4619	1308
175°	4735	4711	4718	4742	4708	451
180°	4725	4725	4725	4725	4725	



TEST NUMBER: P906873

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4280.2	4280.2	4280.2	4280.2	4280.2
2.5°	4305.0	4284.5	4239.1	4280.2	4272.3
5°	4280.2	4264.0	4218.6	4251.3	4243.5
7.5°	4251.3	4226.9	4181.5	4214.7	4206.4
10°	4206.4	4177.5	4128.2	4160.9	4148.7
12.5°	4144.4	4119.9	4070.6	4091.1	4082.8
15°	4074.5	4050.0	3996.3	4012.9	3992.4
17.5°	3988.0	3963.6	3909.9	3930.4	3909.9
20°	3893.3	3868.8	3811.2	3823.4	3807.3
22.5°	3799.0	3761.8	3708.1	3708.1	3699.8
25°	3687.6	3654.9	3585.0	3592.9	3585.0
27.5°	3564.0	3535.2	3481.9	3469.7	3449.2
30°	3440.9	3407.7	3346.1	3333.9	3317.3
32.5°	3309.0	3284.6	3218.6	3193.7	3177.1
35°	3181.5	3140.5	3074.5	3049.6	3029.1
37.5°	3037.4	3000.3	2934.4	2905.5	2885.0
40°	2889.4	2856.2	2790.3	2753.6	2737.0
42.5°	2745.3	2712.1	2646.6	2605.1	2580.7
45°	2589.0	2560.1	2498.1	2453.2	2436.6
47.5°	2436.6	2407.8	2341.8	2296.4	2271.9
50°	2275.9	2255.4	2197.7	2140.1	2119.6
52.5°	2119.6	2090.7	2037.5	1992.0	1963.2
55°	1959.3	1934.4	1885.1	1835.7	1815.2
57.5°	1798.6	1778.1	1724.4	1675.0	1658.4
60°	1637.9	1621.8	1564.1	1518.7	1506.5
62.5°	1481.6	1452.8	1411.7	1370.7	1354.1
65°	1321.3	1296.4	1255.4	1218.3	1197.8
67.5°	1156.7	1135.8	1099.1	1070.3	1053.7
70°	1004.3	987.7	950.6	921.8	905.6
72.5°	848.0	831.4	810.9	782.1	769.8
75°	691.2	683.4	662.4	638.0	646.3
77.5°	551.5	534.9	526.6	514.4	502.2
80°	411.8	407.4	399.1	386.9	378.6
82.5°	279.9	279.9	276.0	259.4	259.4
85°	168.6	164.6	160.7	148.0	144.1
87.5°	74.2	65.9	57.6	45.4	41.0
90°	3.2	41.0	68.2	85.7	92.2
92.5°	85.7	71.9	82.0	88.9	92.2
95°	222.1	109.2	133.2	150.6	147.0
97.5°	399.9	119.8	174.2	184.7	188.0
100°	605.3	136.8	194.9	222.1	229.0
102.5°	830.6	824.1	201.8	239.1	249.7
105°	1039.3	1142.0	208.7	246.0	259.8
107.5°	1282.1	1367.3	215.6	252.9	266.7
110°	1514.7	1586.2	598.4	256.6	270.0



TEST NUMBER: P906873

CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1733.5	1794.8	1736.8	263.1	273.6
115°	1965.8	2023.8	2109.5	526.6	280.5
117.5°	2167.5	2235.7	2294.2	1805.0	909.4
120°	2393.3	2444.4	2506.1	2547.1	2085.5
122.5°	2584.5	2639.3	2707.9	2728.2	2731.9
125°	2779.4	2824.0	2889.0	2912.9	2923.1
127.5°	2957.2	3005.1	3056.6	3090.7	3094.0
130°	3124.8	3179.7	3217.0	3254.8	3251.5
132.5°	3295.8	3340.4	3377.8	3408.6	3405.4
135°	3439.5	3494.3	3524.7	3559.2	3552.3
137.5°	3589.7	3630.7	3665.2	3699.3	3689.2
140°	3736.7	3764.3	3801.6	3832.5	3815.4
142.5°	3860.1	3884.0	3928.3	3955.5	3938.4
145°	3990.0	3986.3	4044.4	4068.4	4051.3
147.5°	4102.5	4092.3	4150.4	4167.4	4154.0
150°	4212.1	4188.1	4242.9	4263.2	4246.2
152.5°	4304.2	4277.0	4328.2	4348.9	4324.9
155°	4393.1	4362.7	4403.7	4424.0	4396.8
157.5°	4465.0	4437.8	4468.7	4492.6	4465.0
160°	4526.7	4506.0	4526.7	4547.0	4523.1
162.5°	4581.1	4560.8	4577.9	4601.8	4571.0
165°	4629.0	4608.7	4618.9	4642.8	4618.9
167.5°	4666.8	4646.1	4656.6	4680.6	4649.7
170°	4697.6	4676.9	4683.8	4707.8	4676.9
172.5°	4717.9	4697.6	4704.5	4728.5	4697.6
175°	4735.0	4711.0	4717.9	4741.9	4707.8
177.5°	4741.9	4717.9	4721.6	4745.5	4714.7
180°	4724.8	4724.8	4724.8	4724.8	4724.8



TEST NUMBER: P906873
 CATALOG NUMBER: DFN2DIP-SQ4F0-110D140US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.53	11.34	11.53	12.35	13.71	10.08	10.89	11.09	11.91	13.26
	3H	12.19	12.91	13.21	13.94	15.31	11.70	12.42	12.71	13.45	14.82
	4H	12.78	13.46	13.81	14.49	15.87	12.28	12.97	13.31	14.00	15.38
	6H	13.18	13.81	14.22	14.84	16.24	12.68	13.31	13.72	14.34	15.74
	8H	13.28	13.89	14.33	14.93	16.32	12.78	13.38	13.83	14.43	15.82
	12H	13.33	13.90	14.38	14.95	16.36	12.82	13.39	13.87	14.44	15.85
4H	2H	10.98	11.67	12.02	12.70	14.08	10.63	11.32	11.66	12.34	13.73
	3H	12.85	13.42	13.89	14.48	15.87	12.44	13.02	13.49	14.07	15.47
	4H	13.56	14.09	14.62	15.14	16.56	13.14	13.67	14.19	14.71	16.13
	6H	14.08	14.53	15.14	15.60	17.02	13.65	14.10	14.71	15.17	16.58
	8H	14.23	14.65	15.29	15.72	17.15	13.79	14.22	14.86	15.28	16.71
	12H	14.30	14.69	15.38	15.76	17.20	13.85	14.24	14.93	15.32	16.75
8H	4H	13.76	14.18	14.82	15.24	16.67	13.38	13.80	14.44	14.87	16.30
	6H	14.39	14.74	15.48	15.85	17.27	14.01	14.36	15.09	15.46	16.89
	8H	14.61	14.92	15.71	16.01	17.45	14.22	14.53	15.31	15.62	17.06
	12H	14.75	15.02	15.84	16.10	17.59	14.34	14.61	15.43	15.69	17.17
12H	4H	13.74	14.12	14.82	15.20	16.63	13.37	13.75	14.45	14.83	16.27
	6H	14.42	14.73	15.51	15.82	17.26	14.05	14.36	15.14	15.45	16.89
	8H	14.66	14.93	15.76	16.02	17.50	14.28	14.55	15.38	15.64	17.12