

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906879

Luminaire Tested: DFN2DIP-SQ4F0-110D160US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906879
REPORT IS A COMBINATION OF REPORTS P901734 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D160US835-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 25190.0 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 227.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	64	59	56	53	47	45	42	35	34	33
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	29	26	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17
8	53	41	34	29	48	38	31	27	31	26	23	26	22	19	20	17	15
9	49	38	30	26	45	35	28	24	29	24	21	23	20	17	18	16	14
10	46	34	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3190	3190	3190
5°	3195	3140	3160
10°	3163	3079	3058
15°	3120	2978	2900
20°	3062	2838	2706
25°	3003	2681	2518
30°	2924	2521	2280
35°	2846	2348	2070
40°	2767	2169	1830
45°	2675	1970	1612
50°	2580	1770	1399
55°	2481	1555	1195
60°	2367	1331	984
65°	2234	1103	887
70°	2074	890	804
75°	1873	786	734
80°	1582	662	640
85°	1102	445	487

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2894 cd/sqm

TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	426.1	1.7
10°-20°	1169.7	4.6
20°-30°	1642.2	6.5
30°-40°	1790.1	7.1
40°-50°	1645.3	6.5
50°-60°	1292.1	5.1
60°-70°	841.1	3.3
70°-80°	432.9	1.7
80°-90°	120.0	0.5
90°-100°	178.0	0.7
100°-110°	663.8	2.6
110°-120°	1760.4	7.0
120°-130°	2919.7	11.6
130°-140°	3101.5	12.3
140°-150°	2882.5	11.4
150°-160°	2317.4	9.2
160°-170°	1493.3	5.9
170°-180°	514.0	2.0
0°-30°	3238.0	12.9
0°-40°	5028.1	20.0
0°-60°	7965.5	31.6
0°-90°	9359.5	37.2
90°-120°	2602.2	10.3
90°-150°	11505.9	45.7
90°-180°	15831.0	62.8
0°-180°	25190.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4546	4546	4546	4546	4546	
5°	4546	4526	4472	4509	4497	431
15°	4324	4279	4139	4061	4020	1218
25°	3925	3793	3522	3353	3291	1805
35°	3382	3172	2810	2551	2460	2117
45°	2765	2489	2057	1765	1666	2135
55°	2102	1781	1337	1090	1012	1879
65°	1420	1086	716	576	564	1407
75°	757	469	329	300	296	801
85°	177	90	78	78	78	203
90°	4	47	78	98	105	23
95°	254	125	152	172	168	301
105°	1188	1305	238	281	297	1269
115°	2247	2313	2411	602	321	2212
125°	3176	3227	3302	3329	3341	2833
135°	3931	3994	4028	4068	4060	3036
145°	4560	4556	4622	4650	4630	2852
155°	5021	4986	5033	5056	5025	2314
165°	5290	5267	5279	5306	5279	1495
175°	5411	5384	5392	5419	5380	515
180°	5400	5400	5400	5400	5400	

TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4546.3	4546.3	4546.3	4546.3	4546.3
2.5°	4566.8	4546.3	4500.9	4542.4	4534.1
5°	4546.3	4525.8	4472.1	4509.2	4497.0
7.5°	4509.2	4484.7	4427.1	4443.3	4422.7
10°	4459.9	4431.0	4349.0	4336.3	4311.9
12.5°	4398.3	4361.2	4249.9	4225.4	4180.0
15°	4324.1	4278.7	4139.0	4060.9	4019.8
17.5°	4237.7	4171.8	3998.9	3908.5	3842.6
20°	4139.0	4056.5	3850.9	3748.3	3657.5
22.5°	4032.1	3937.3	3698.6	3558.9	3497.3
25°	3925.1	3793.3	3521.8	3353.3	3291.3
27.5°	3797.7	3657.5	3357.2	3163.8	3069.1
30°	3661.9	3505.2	3176.1	2966.5	2855.2
32.5°	3530.1	3340.6	3003.6	2756.6	2653.6
35°	3382.1	3172.1	2810.3	2551.0	2460.2
37.5°	3238.1	3011.5	2629.1	2344.9	2242.4
40°	3085.7	2839.1	2439.7	2147.6	2040.7
42.5°	2929.4	2666.2	2250.7	1946.0	1843.4
45°	2764.9	2489.0	2057.3	1764.8	1666.2
47.5°	2608.6	2316.6	1872.2	1579.7	1489.4
50°	2435.7	2143.7	1691.1	1406.9	1320.9
52.5°	2266.8	1958.2	1518.2	1246.7	1168.5
55°	2102.2	1781.4	1337.0	1090.4	1012.3
57.5°	1933.8	1604.6	1176.8	946.4	880.4
60°	1760.9	1431.8	1007.9	798.4	732.5
62.5°	1592.4	1263.3	863.9	666.6	633.8
65°	1419.5	1086.0	715.9	576.2	563.5
67.5°	1255.0	921.5	576.2	505.9	493.7
70°	1082.1	761.3	477.1	436.1	419.5
72.5°	917.5	612.9	399.0	366.2	357.9
75°	756.9	468.8	329.1	300.3	296.4
77.5°	596.7	333.1	259.3	242.7	234.4
80°	448.3	238.8	197.3	181.2	181.2
82.5°	312.5	160.6	135.8	127.5	127.5
85°	176.8	90.4	78.1	78.1	78.1
87.5°	65.9	32.7	32.7	28.8	28.8
90°	3.7	46.9	77.9	97.9	105.3
92.5°	97.9	82.1	93.7	101.6	105.3
95°	253.8	124.8	152.2	172.1	168.0
97.5°	457.0	136.9	199.0	211.1	214.8
100°	691.8	156.4	222.7	253.8	261.7
102.5°	949.3	941.9	230.6	273.3	285.3
105°	1187.8	1305.2	238.5	281.2	296.9
107.5°	1465.2	1562.7	246.4	289.1	304.8
110°	1731.1	1812.8	683.9	293.2	308.5

TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1981.2	2051.3	1984.9	300.7	312.7
115°	2246.6	2312.9	2410.8	601.8	320.6
117.5°	2477.2	2555.1	2622.0	2062.9	1039.3
120°	2735.2	2793.6	2864.1	2911.0	2383.5
122.5°	2953.7	3016.3	3094.7	3117.9	3122.1
125°	3176.4	3227.4	3301.7	3329.1	3340.7
127.5°	3379.6	3434.4	3493.3	3532.3	3536.0
130°	3571.3	3633.9	3676.6	3719.7	3716.0
132.5°	3766.6	3817.6	3860.3	3895.6	3891.9
135°	3930.8	3993.5	4028.3	4067.7	4059.8
137.5°	4102.5	4149.4	4188.8	4227.8	4216.2
140°	4270.5	4302.0	4344.7	4380.0	4360.5
142.5°	4411.5	4438.9	4489.5	4520.6	4501.1
145°	4560.0	4555.8	4622.2	4649.5	4630.1
147.5°	4688.5	4676.9	4743.3	4762.8	4747.4
150°	4813.8	4786.4	4849.1	4872.3	4852.8
152.5°	4919.1	4888.0	4946.5	4970.2	4942.8
155°	5020.7	4985.9	5032.8	5056.0	5024.9
157.5°	5102.9	5071.8	5107.0	5134.4	5102.9
160°	5173.4	5149.7	5173.4	5196.6	5169.2
162.5°	5235.6	5212.4	5231.8	5259.2	5224.0
165°	5290.3	5267.1	5278.7	5306.1	5278.7
167.5°	5333.5	5309.8	5321.9	5349.2	5314.0
170°	5368.7	5345.1	5352.9	5380.3	5345.1
172.5°	5391.9	5368.7	5376.6	5404.0	5368.7
175°	5411.4	5384.0	5391.9	5419.3	5380.3
177.5°	5419.3	5391.9	5396.1	5423.5	5388.2
180°	5399.8	5399.8	5399.8	5399.8	5399.8

TEST NUMBER: P906879

CATALOG NUMBER: DFN2DIP-SQ4F0-110D160US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.86	10.59	10.92	11.66	13.10	5.82	6.55	6.89	7.62	9.06
	3H	11.53	12.19	12.61	13.26	14.73	7.00	7.66	8.08	8.73	10.20
	4H	12.14	12.76	13.23	13.84	15.31	7.45	8.07	8.53	9.15	10.62
	6H	12.56	13.13	13.66	14.21	15.69	7.76	8.34	8.86	9.42	10.90
	8H	12.69	13.23	13.79	14.33	15.80	7.85	8.40	8.95	9.49	10.97
	12H	12.75	13.26	13.85	14.35	15.85	7.89	8.41	9.00	9.50	11.00
4H	2H	9.86	10.49	10.96	11.56	13.03	6.41	7.03	7.50	8.10	9.57
	3H	11.69	12.21	12.79	13.31	14.79	7.75	8.27	8.85	9.37	10.85
	4H	12.38	12.86	13.49	13.95	15.45	8.29	8.77	9.40	9.86	11.36
	6H	12.90	13.30	14.01	14.42	15.92	8.71	9.11	9.82	10.23	11.73
	8H	13.07	13.45	14.18	14.56	16.07	8.84	9.22	9.95	10.32	11.84
	12H	13.17	13.51	14.29	14.63	16.15	8.90	9.24	10.03	10.36	11.88
8H	4H	12.34	12.72	13.45	13.83	15.34	8.57	8.95	9.68	10.06	11.57
	6H	12.91	13.22	14.04	14.37	15.88	9.08	9.40	10.22	10.55	12.06
	8H	13.13	13.40	14.27	14.53	16.06	9.28	9.55	10.42	10.68	12.21
	12H	13.27	13.51	14.41	14.63	16.20	9.39	9.63	10.53	10.76	12.33
12H	4H	12.29	12.63	13.42	13.75	15.27	8.57	8.91	9.70	10.03	11.55
	6H	12.89	13.16	14.02	14.29	15.82	9.13	9.41	10.27	10.54	12.07
	8H	13.11	13.35	14.25	14.47	16.04	9.34	9.58	10.49	10.71	12.28

END OF REPORT