

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906885

Luminaire Tested: DFN2DIP-SQ4F0-120D070US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906885
REPORT IS A COMBINATION OF REPORTS P901609 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D070US835-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18810.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 169.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91		79	79	79		68
1	101	96	92	89	94	91	87	84	80	77	75		70	68	66		60
2	92	84	78	73	86	79	74	69	70	66	62		61	58	55		53
3	84	74	67	61	78	70	63	58	62	56	52		54	50	47		47
4	77	66	57	51	72	62	55	49	55	49	44		48	44	40		42
5	70	59	50	44	66	55	48	42	49	43	38		43	39	35		38
6	65	53	44	38	61	50	42	37	44	38	34		39	34	30		34
7	60	48	39	34	56	45	38	32	40	34	30		36	31	27		31
8	56	43	35	30	52	41	34	29	37	31	26		33	28	24		29
9	52	40	32	27	49	38	31	26	34	28	24		30	25	22		27
10	49	36	29	24	46	35	28	23	31	25	21		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3276	3276	3276
5°	3282	3231	3253
10°	3255	3188	3210
15°	3207	3137	3142
20°	3142	3064	3073
25°	3078	2978	2992
30°	2997	2897	2890
35°	2921	2802	2781
40°	2827	2706	2678
45°	2733	2610	2572
50°	2630	2509	2449
55°	2523	2392	2337
60°	2401	2254	2209
65°	2269	2110	2057
70°	2100	1935	1894
75°	1867	1726	1745
80°	1586	1460	1458
85°	1146	999	980

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2733 cd/sqm

TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	2.3
10°-20°	1236.5	6.6
20°-30°	1817.2	9.7
30°-40°	2110.5	11.2
40°-50°	2107.9	11.2
50°-60°	1838.0	9.8
60°-70°	1358.7	7.2
70°-80°	768.7	4.1
80°-90°	207.1	1.1
90°-100°	77.9	0.4
100°-110°	290.4	1.5
110°-120°	770.2	4.1
120°-130°	1277.4	6.8
130°-140°	1356.9	7.2
140°-150°	1261.1	6.7
150°-160°	1013.9	5.4
160°-170°	653.3	3.5
170°-180°	224.9	1.2
0°-30°	3493.1	18.6
0°-40°	5603.7	29.8
0°-60°	9549.6	50.8
0°-90°	11884.1	63.2
90°-120°	1138.5	6.1
90°-150°	5033.8	26.8
90°-180°	6926.0	36.8
0°-180°	18810.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4669	4669	4669	4669	4669	
5°	4669	4652	4602	4638	4629	443
15°	4445	4418	4360	4378	4355	1252
25°	4023	3987	3911	3920	3911	1851
35°	3471	3426	3354	3327	3304	2167
45°	2824	2793	2725	2676	2658	2180
55°	2137	2110	2056	2003	1980	1911
65°	1442	1414	1370	1329	1307	1425
75°	754	746	723	696	705	805
85°	184	180	175	162	157	205
90°	2	20	34	43	46	17
95°	111	55	67	75	74	131
105°	520	571	104	123	130	555
115°	983	1012	1055	263	140	968
125°	1390	1412	1444	1456	1462	1239
135°	1720	1747	1762	1780	1776	1328
145°	1995	1993	2022	2034	2026	1248
155°	2197	2181	2202	2212	2198	1012
165°	2314	2304	2309	2321	2309	654
175°	2368	2356	2359	2371	2354	225
180°	2362	2362	2362	2362	2362	

TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4669.3	4669.3	4669.3	4669.3	4669.3
2.5°	4696.4	4674.0	4624.5	4669.3	4660.7
5°	4669.3	4651.6	4602.1	4637.8	4629.2
7.5°	4637.8	4611.1	4561.6	4597.8	4588.8
10°	4588.8	4557.3	4503.5	4539.2	4525.9
12.5°	4521.1	4494.4	4440.6	4463.0	4453.9
15°	4444.9	4418.2	4359.6	4377.7	4355.3
17.5°	4350.6	4323.9	4265.3	4287.7	4265.3
20°	4247.2	4220.5	4157.7	4171.0	4153.4
22.5°	4144.3	4103.8	4045.2	4045.2	4036.2
25°	4022.8	3987.1	3910.9	3919.5	3910.9
27.5°	3888.0	3856.6	3798.5	3785.1	3762.8
30°	3753.7	3717.5	3650.3	3637.0	3618.9
32.5°	3609.8	3583.2	3511.2	3484.1	3466.0
35°	3470.7	3426.0	3354.0	3326.9	3304.5
37.5°	3313.5	3273.1	3201.1	3169.7	3147.3
40°	3152.1	3115.9	3043.9	3003.9	2985.8
42.5°	2994.9	2958.7	2887.2	2842.0	2815.3
45°	2824.3	2792.9	2725.2	2676.2	2658.1
47.5°	2658.1	2626.6	2554.7	2505.2	2478.5
50°	2482.8	2460.4	2397.5	2334.6	2312.2
52.5°	2312.2	2280.8	2222.7	2173.1	2141.7
55°	2137.4	2110.3	2056.4	2002.6	1980.2
57.5°	1962.1	1939.7	1881.1	1827.3	1809.2
60°	1786.8	1769.2	1706.3	1656.8	1643.4
62.5°	1616.3	1584.8	1540.1	1495.3	1477.2
65°	1441.5	1414.3	1369.5	1329.0	1306.7
67.5°	1261.9	1239.0	1199.0	1167.6	1149.5
70°	1095.6	1077.5	1037.0	1005.6	988.0
72.5°	925.1	907.0	884.6	853.2	839.8
75°	754.1	745.5	722.6	696.0	705.0
77.5°	601.6	583.5	574.5	561.1	547.8
80°	449.2	444.4	435.4	422.1	413.0
82.5°	305.3	305.3	301.1	283.0	283.0
85°	183.9	179.6	175.3	161.5	157.2
87.5°	81.0	71.9	62.9	49.5	44.8
90°	1.6	20.5	34.1	42.8	46.1
92.5°	42.8	35.9	41.0	44.5	46.1
95°	111.0	54.6	66.6	75.3	73.5
97.5°	199.9	59.9	87.1	92.4	94.0
100°	302.7	68.4	97.4	111.0	114.5
102.5°	415.3	412.1	100.9	119.6	124.8
105°	519.7	571.0	104.3	123.0	129.9
107.5°	641.0	683.7	107.8	126.5	133.4
110°	757.4	793.1	299.2	128.3	135.0

TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	866.8	897.4	868.4	131.5	136.8
115°	982.9	1011.9	1054.7	263.3	140.3
117.5°	1083.8	1117.9	1147.1	902.5	454.7
120°	1196.6	1222.2	1253.1	1273.6	1042.8
122.5°	1292.2	1319.6	1354.0	1364.1	1365.9
125°	1389.7	1412.0	1444.5	1456.5	1461.5
127.5°	1478.6	1502.5	1528.3	1545.4	1547.0
130°	1562.4	1589.8	1608.5	1627.4	1625.8
132.5°	1647.9	1670.2	1688.9	1704.3	1702.7
135°	1719.7	1747.1	1762.4	1779.6	1776.2
137.5°	1794.8	1815.4	1832.6	1849.7	1844.6
140°	1868.3	1882.1	1900.8	1916.2	1907.7
142.5°	1930.0	1942.0	1964.1	1977.7	1969.2
145°	1995.0	1993.2	2022.2	2034.2	2025.7
147.5°	2051.2	2046.2	2075.2	2083.7	2077.0
150°	2106.0	2094.1	2121.5	2131.6	2123.1
152.5°	2152.1	2138.5	2164.1	2174.4	2162.5
155°	2196.6	2181.3	2201.8	2212.0	2198.4
157.5°	2232.5	2218.9	2234.3	2246.3	2232.5
160°	2263.4	2253.0	2263.4	2273.5	2261.5
162.5°	2290.6	2280.4	2288.9	2300.9	2285.5
165°	2314.5	2304.4	2309.4	2321.4	2309.4
167.5°	2333.4	2323.0	2328.3	2340.3	2324.9
170°	2348.8	2338.5	2341.9	2353.9	2338.5
172.5°	2359.0	2348.8	2352.3	2364.2	2348.8
175°	2367.5	2355.5	2359.0	2370.9	2353.9
177.5°	2370.9	2359.0	2360.8	2372.8	2357.3
180°	2362.4	2362.4	2362.4	2362.4	2362.4

TEST NUMBER: P906885

CATALOG NUMBER: DFN2DIP-SQ4F0-120D070US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.54	13.54	13.38	14.39	15.46	12.10	13.09	12.93	13.95	15.02
	3H	14.22	15.11	15.06	15.98	17.07	13.73	14.62	14.57	15.49	16.58
	4H	14.81	15.66	15.68	16.53	17.64	14.32	15.16	15.18	16.04	17.14
	6H	15.22	16.00	16.10	16.88	18.00	14.72	15.50	15.60	16.38	17.50
	8H	15.33	16.07	16.22	16.97	18.09	14.83	15.57	15.72	16.47	17.59
	12H	15.39	16.09	16.28	16.99	18.13	14.88	15.58	15.77	16.48	17.62
4H	2H	13.02	13.86	13.89	14.74	15.84	12.66	13.51	13.53	14.38	15.49
	3H	14.90	15.61	15.78	16.51	17.63	14.49	15.20	15.37	16.10	17.23
	4H	15.63	16.27	16.52	17.17	18.32	15.20	15.84	16.09	16.75	17.89
	6H	16.15	16.71	17.06	17.63	18.78	15.72	16.27	16.63	17.20	18.35
	8H	16.31	16.83	17.22	17.75	18.91	15.87	16.39	16.78	17.31	18.47
	12H	16.39	16.86	17.32	17.79	18.96	15.94	16.41	16.87	17.35	18.52
8H	4H	15.83	16.35	16.74	17.27	18.44	15.46	15.97	16.37	16.89	18.06
	6H	16.47	16.90	17.41	17.87	19.03	16.09	16.52	17.03	17.48	18.65
	8H	16.70	17.08	17.65	18.03	19.21	16.31	16.69	17.25	17.64	18.82
	12H	16.84	17.17	17.79	18.12	19.35	16.43	16.76	17.38	17.71	18.94
12H	4H	15.82	16.29	16.75	17.23	18.40	15.46	15.92	16.39	16.86	18.03
	6H	16.51	16.89	17.45	17.84	19.02	16.13	16.51	17.08	17.47	18.65
	8H	16.76	17.09	17.71	18.04	19.27	16.38	16.71	17.33	17.66	18.89