

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923025

Luminaire Tested: DFN2DIP-SQ3F0-120D110US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923025
REPORT IS A COMBINATION OF REPORTS P901523 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-120D110US940-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20304.2 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 211.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	87	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41
3	82	72	65	59	75	67	61	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	33	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4771	4771	4771
5°	4775	4701	4734
10°	4734	4635	4669
15°	4661	4555	4567
20°	4564	4446	4463
25°	4467	4316	4343
30°	4347	4195	4191
35°	4232	4052	4030
40°	4092	3909	3876
45°	3952	3764	3719
50°	3799	3612	3538
55°	3638	3437	3370
60°	3456	3229	3178
65°	3257	3013	2953
70°	3004	2749	2709
75°	2654	2433	2481
80°	2231	2031	2051
85°	1570	1345	1343

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3952 cd/sqm

TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.9	1.9
10°-20°	1102.6	5.4
20°-30°	1620.4	8.0
30°-40°	1882.0	9.3
40°-50°	1879.7	9.3
50°-60°	1639.0	8.1
60°-70°	1211.6	6.0
70°-80°	685.5	3.4
80°-90°	186.8	0.9
90°-100°	109.2	0.5
100°-110°	406.9	2.0
110°-120°	1079.2	5.3
120°-130°	1789.9	8.8
130°-140°	1901.3	9.4
140°-150°	1767.1	8.7
150°-160°	1420.7	7.0
160°-170°	915.4	4.5
170°-180°	315.1	1.6
0°-30°	3114.9	15.3
0°-40°	4996.9	24.6
0°-60°	8515.5	41.9
0°-90°	10599.4	52.2
90°-120°	1595.3	7.9
90°-150°	7053.7	34.7
90°-180°	9705.0	47.8
0°-180°	20304.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4164	4164	4164	4164	4164	
5°	4164	4148	4104	4136	4128	395
15°	3964	3940	3888	3904	3884	1116
25°	3587	3555	3487	3495	3487	1651
35°	3095	3055	2991	2967	2947	1933
45°	2518	2490	2430	2386	2370	1944
55°	1906	1882	1834	1786	1766	1704
65°	1285	1261	1221	1185	1165	1271
75°	672	665	644	621	629	718
85°	164	160	156	144	140	183
90°	2	29	48	60	65	19
95°	156	76	93	106	103	184
105°	728	800	146	172	182	778
115°	1377	1418	1478	369	196	1356
125°	1947	1979	2024	2041	2048	1737
135°	2410	2448	2470	2494	2489	1862
145°	2796	2793	2834	2850	2838	1748
155°	3078	3057	3085	3100	3080	1418
165°	3243	3229	3236	3253	3236	916
175°	3317	3301	3306	3322	3298	316
180°	3310	3310	3310	3310	3310	

TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4163.7	4163.7	4163.7	4163.7	4163.7
2.5°	4187.8	4167.9	4123.7	4163.7	4156.0
5°	4163.7	4147.9	4103.7	4135.6	4127.9
7.5°	4135.6	4111.8	4067.6	4099.9	4091.9
10°	4091.9	4063.8	4015.8	4047.7	4035.8
12.5°	4031.5	4007.7	3959.7	3979.7	3971.6
15°	3963.6	3939.8	3887.5	3903.6	3883.7
17.5°	3879.5	3855.7	3803.4	3823.4	3803.4
20°	3787.3	3763.5	3707.5	3719.3	3703.6
22.5°	3695.5	3659.4	3607.1	3607.1	3599.1
25°	3587.2	3555.3	3487.4	3495.1	3487.4
27.5°	3467.0	3439.0	3387.2	3375.2	3355.3
30°	3347.2	3314.9	3255.0	3243.2	3227.0
32.5°	3218.9	3195.2	3131.0	3106.8	3090.7
35°	3094.9	3055.0	2990.8	2966.6	2946.7
37.5°	2954.7	2918.7	2854.5	2826.5	2806.5
40°	2810.8	2778.5	2714.3	2678.6	2662.5
42.5°	2670.6	2638.3	2574.5	2534.2	2510.4
45°	2518.5	2490.5	2430.1	2386.4	2370.3
47.5°	2370.3	2342.2	2278.1	2233.9	2210.1
50°	2213.9	2194.0	2137.9	2081.8	2061.8
52.5°	2061.8	2033.8	1982.0	1937.8	1909.8
55°	1905.9	1881.8	1833.7	1785.7	1765.8
57.5°	1749.6	1729.7	1677.4	1629.4	1613.3
60°	1593.3	1577.6	1521.5	1477.4	1465.4
62.5°	1441.3	1413.2	1373.3	1333.4	1317.2
65°	1285.4	1261.1	1221.2	1185.1	1165.2
67.5°	1125.2	1104.8	1069.2	1041.2	1025.0
70°	977.0	960.8	924.7	896.7	881.0
72.5°	824.9	808.8	788.8	760.8	748.9
75°	672.4	664.8	644.3	620.6	628.7
77.5°	536.5	520.3	512.3	500.3	488.5
80°	400.6	396.3	388.3	376.4	368.3
82.5°	272.2	272.2	268.5	252.4	252.4
85°	164.0	160.2	156.3	144.0	140.2
87.5°	72.2	64.1	56.1	44.1	39.9
90°	2.3	28.7	47.8	60.0	64.6
92.5°	60.0	50.4	57.4	62.3	64.6
95°	155.6	76.5	93.3	105.5	103.0
97.5°	280.2	83.9	122.0	129.4	131.7
100°	424.1	95.9	136.5	155.6	160.4
102.5°	581.9	577.4	141.3	167.6	175.0
105°	728.2	800.1	146.2	172.4	182.1
107.5°	898.3	958.0	151.1	177.2	186.9
110°	1061.2	1111.3	419.3	179.8	189.1

TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1214.6	1257.5	1216.8	184.3	191.7
115°	1377.2	1417.9	1478.0	368.9	196.5
117.5°	1518.7	1566.5	1607.4	1264.6	637.1
120°	1676.8	1712.6	1755.9	1784.6	1461.2
122.5°	1810.8	1849.1	1897.2	1911.5	1914.1
125°	1947.3	1978.6	2024.1	2040.9	2048.0
127.5°	2071.9	2105.4	2141.5	2165.4	2167.7
130°	2189.3	2227.8	2253.9	2280.4	2278.1
132.5°	2309.1	2340.4	2366.6	2388.2	2385.9
135°	2409.8	2448.2	2469.5	2493.8	2488.9
137.5°	2515.1	2543.8	2567.9	2591.8	2584.7
140°	2618.1	2637.3	2663.5	2685.1	2673.2
142.5°	2704.5	2721.2	2752.3	2771.3	2759.4
145°	2795.5	2792.9	2833.6	2850.4	2838.5
147.5°	2874.3	2867.2	2907.9	2919.8	2910.5
150°	2951.1	2934.4	2972.7	2987.0	2975.0
152.5°	3015.7	2996.6	3032.4	3047.0	3030.2
155°	3078.0	3056.6	3085.3	3099.6	3080.5
157.5°	3128.3	3109.2	3130.9	3147.6	3128.3
160°	3171.5	3157.0	3171.5	3185.7	3169.0
162.5°	3209.6	3195.4	3207.4	3224.2	3202.6
165°	3243.2	3229.0	3236.1	3252.9	3236.1
167.5°	3269.6	3255.2	3262.6	3279.4	3257.8
170°	3291.3	3276.8	3281.6	3298.4	3276.8
172.5°	3305.5	3291.3	3296.1	3312.9	3291.3
175°	3317.4	3300.7	3305.5	3322.3	3298.4
177.5°	3322.3	3305.5	3308.1	3324.8	3303.3
180°	3310.4	3310.4	3310.4	3310.4	3310.4

TEST NUMBER: P923025

CATALOG NUMBER: DFN2DIP-SQ3F0-120D110US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.87	13.75	13.81	14.70	15.94	12.42	13.31	13.36	14.26	15.50
	3H	14.53	15.32	15.47	16.28	17.54	14.04	14.83	14.98	15.79	17.05
	4H	15.11	15.86	16.07	16.83	18.10	14.62	15.37	15.58	16.33	17.61
	6H	15.51	16.20	16.48	17.17	18.46	15.01	15.70	15.98	16.67	17.96
	8H	15.61	16.27	16.59	17.26	18.54	15.11	15.77	16.09	16.76	18.04
	12H	15.66	16.28	16.65	17.27	18.58	15.15	15.77	16.14	16.76	18.07
4H	2H	13.33	14.08	14.30	15.04	16.32	12.97	13.72	13.94	14.69	15.96
	3H	15.19	15.81	16.17	16.81	18.10	14.78	15.41	15.76	16.40	17.69
	4H	15.90	16.47	16.89	17.46	18.77	15.48	16.05	16.47	17.04	18.35
	6H	16.41	16.91	17.41	17.92	19.23	15.98	16.47	16.98	17.49	18.80
	8H	16.56	17.02	17.56	18.03	19.35	16.12	16.58	17.13	17.59	18.91
	12H	16.63	17.05	17.65	18.07	19.40	16.18	16.60	17.20	17.62	18.95
8H	4H	16.10	16.56	17.10	17.56	18.89	15.72	16.18	16.72	17.19	18.51
	6H	16.72	17.10	17.75	18.15	19.47	16.34	16.72	17.36	17.77	19.09
	8H	16.94	17.27	17.97	18.31	19.65	16.55	16.88	17.58	17.92	19.26
	12H	17.07	17.36	18.11	18.39	19.78	16.66	16.95	17.70	17.98	19.37
12H	4H	16.08	16.50	17.10	17.52	18.85	15.71	16.13	16.73	17.15	18.48
	6H	16.75	17.09	17.78	18.12	19.46	16.38	16.71	17.41	17.75	19.09
	8H	16.99	17.28	18.03	18.31	19.70	16.61	16.90	17.65	17.93	19.32