

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906910

Luminaire Tested: DFN2DIP-SQ4F0-120D140US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906910
REPORT IS A COMBINATION OF REPORTS P900198 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-120D140US835-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22590.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 223.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29
5	69	57	50	44	63	53	46	41	45	40	36	37	33	30	30	28	25
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3480	3480	3480
5°	3486	3425	3448
10°	3451	3359	3337
15°	3403	3249	3164
20°	3341	3096	2952
25°	3276	2925	2747
30°	3190	2750	2487
35°	3105	2561	2259
40°	3019	2366	1996
45°	2919	2149	1759
50°	2815	1931	1527
55°	2707	1697	1303
60°	2582	1452	1074
65°	2438	1204	968
70°	2263	971	877
75°	2044	858	800
80°	1726	722	697
85°	1202	486	531

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3485 cd/sqm

TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.8	2.1
10°-20°	1276.0	5.6
20°-30°	1791.5	7.9
30°-40°	1952.8	8.6
40°-50°	1794.9	7.9
50°-60°	1409.6	6.2
60°-70°	917.5	4.1
70°-80°	472.3	2.1
80°-90°	133.1	0.6
90°-100°	274.0	1.2
100°-110°	870.6	3.9
110°-120°	1489.8	6.6
120°-130°	1959.3	8.7
130°-140°	2199.2	9.7
140°-150°	2156.6	9.5
150°-160°	1809.1	8.0
160°-170°	1199.7	5.3
170°-180°	419.3	1.9
0°-30°	3532.3	15.6
0°-40°	5485.2	24.3
0°-60°	8689.6	38.5
0°-90°	10212.6	45.2
90°-120°	2634.3	11.7
90°-150°	8949.3	39.6
90°-180°	12377.0	54.8
0°-180°	22590.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4960	4960	4960	4960	4960	
5°	4960	4937	4879	4919	4906	470
15°	4717	4668	4515	4430	4385	1329
25°	4282	4138	3842	3658	3590	1969
35°	3690	3460	3066	2783	2684	2309
45°	3016	2715	2244	1925	1818	2329
55°	2293	1943	1459	1190	1104	2049
65°	1549	1185	781	629	615	1535
75°	826	511	359	328	323	873
85°	193	99	85	85	85	221
90°	4	48	131	123	127	22
95°	195	232	239	239	232	217
105°	804	814	822	829	829	848
115°	1495	1516	1510	1506	1495	1479
125°	2174	2208	2197	2185	2181	1943
135°	2812	2854	2862	2858	2847	2174
145°	3414	3441	3463	3467	3452	2133
155°	3904	3915	3927	3946	3934	1797
165°	4248	4244	4244	4270	4252	1198
175°	4420	4409	4401	4428	4405	420
180°	4428	4428	4428	4428	4428	

TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4959.6	4959.6	4959.6	4959.6	4959.6
2.5°	4982.0	4959.6	4910.1	4955.3	4946.2
5°	4959.6	4937.2	4878.6	4919.1	4905.8
7.5°	4919.1	4892.4	4829.6	4847.2	4824.8
10°	4865.3	4833.9	4744.3	4730.5	4703.9
12.5°	4798.1	4757.7	4636.2	4609.6	4560.1
15°	4717.2	4667.7	4515.3	4430.0	4385.3
17.5°	4622.9	4551.0	4362.4	4263.9	4192.0
20°	4515.3	4425.3	4201.0	4089.1	3990.0
22.5°	4398.6	4295.3	4034.8	3882.4	3815.3
25°	4282.0	4138.1	3841.9	3658.1	3590.5
27.5°	4142.9	3990.0	3662.4	3451.5	3348.1
30°	3994.8	3823.9	3464.8	3236.2	3114.8
32.5°	3851.0	3644.3	3276.7	3007.2	2894.8
35°	3689.6	3460.5	3065.7	2782.9	2683.8
37.5°	3532.4	3285.3	2868.1	2558.1	2446.2
40°	3366.2	3097.2	2661.5	2342.9	2226.2
42.5°	3195.7	2908.6	2455.3	2122.9	2011.0
45°	3016.2	2715.3	2244.3	1925.3	1817.6
47.5°	2845.7	2527.2	2042.4	1723.4	1624.8
50°	2657.2	2338.6	1844.8	1534.8	1441.0
52.5°	2472.9	2136.2	1656.2	1360.0	1274.8
55°	2293.4	1943.4	1458.6	1189.5	1104.3
57.5°	2109.5	1750.5	1283.8	1032.4	960.5
60°	1921.0	1561.9	1099.5	871.0	799.1
62.5°	1737.2	1378.1	942.4	727.2	691.4
65°	1548.6	1184.8	781.0	628.6	614.8
67.5°	1369.1	1005.2	628.6	551.9	538.6
70°	1180.5	830.5	520.5	475.7	457.6
72.5°	1001.0	668.6	435.2	399.5	390.5
75°	825.7	511.4	359.1	327.6	323.3
77.5°	651.0	363.3	282.9	264.8	255.7
80°	489.1	260.5	215.2	197.6	197.6
82.5°	341.0	175.2	148.1	139.0	139.0
85°	192.9	98.6	85.2	85.2	85.2
87.5°	71.9	35.7	35.7	31.4	31.4
90°	4.0	48.1	130.8	122.8	126.8
92.5°	82.8	112.1	116.1	120.1	120.1
95°	194.9	232.3	238.9	238.9	232.3
97.5°	324.4	359.1	373.8	373.8	373.8
100°	473.9	504.6	515.2	515.2	511.2
102.5°	631.4	654.1	668.8	672.8	668.8
105°	803.6	814.3	822.3	828.9	828.9
107.5°	974.4	990.5	990.5	993.1	974.4
110°	1140.0	1161.3	1161.3	1161.3	1150.6

TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1318.8	1341.5	1337.5	1326.8	1318.8
115°	1495.0	1516.4	1509.7	1505.7	1495.0
117.5°	1669.9	1699.3	1680.6	1669.9	1659.2
120°	1846.1	1875.5	1846.1	1846.1	1834.1
122.5°	2006.3	2043.6	2025.0	2014.3	2006.3
125°	2174.5	2207.8	2197.1	2185.1	2181.1
127.5°	2338.6	2380.0	2365.3	2349.3	2338.6
130°	2492.1	2540.2	2533.5	2525.5	2510.8
132.5°	2664.3	2701.7	2704.4	2685.7	2675.0
135°	2812.5	2853.9	2861.9	2857.9	2847.2
137.5°	2978.0	3011.4	3018.1	3015.4	2999.4
140°	3123.5	3156.9	3175.6	3175.6	3160.9
142.5°	3273.0	3306.4	3317.1	3321.1	3306.4
145°	3414.5	3441.2	3462.6	3466.6	3451.9
147.5°	3541.3	3574.7	3590.7	3597.4	3582.7
150°	3672.1	3694.8	3709.5	3721.5	3709.5
152.5°	3788.3	3811.0	3829.7	3844.3	3829.7
155°	3904.4	3915.1	3927.1	3945.8	3933.8
157.5°	4004.5	4012.5	4019.2	4045.9	4027.2
160°	4094.0	4102.0	4106.0	4128.7	4112.6
162.5°	4176.7	4176.7	4180.7	4206.1	4187.4
165°	4247.5	4243.5	4243.5	4270.2	4251.5
167.5°	4311.5	4299.5	4299.5	4326.2	4307.5
170°	4359.6	4348.9	4344.9	4371.6	4348.9
172.5°	4393.0	4382.3	4378.3	4405.0	4382.3
175°	4419.7	4409.0	4401.0	4427.7	4405.0
177.5°	4434.3	4423.7	4415.7	4438.3	4415.7
180°	4427.7	4427.7	4427.7	4427.7	4427.7

TEST NUMBER: P906910

CATALOG NUMBER: DFN2DIP-SQ4F0-120D140US835-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.03	11.82	12.03	12.83	14.17	6.99	7.78	7.99	8.79	10.13
	3H	12.70	13.41	13.72	14.43	15.79	8.17	8.88	9.19	9.90	11.26
	4H	13.31	13.99	14.34	15.01	16.38	8.62	9.29	9.65	10.31	11.68
	6H	13.74	14.35	14.77	15.38	16.76	8.94	9.56	9.98	10.58	11.97
	8H	13.87	14.45	14.91	15.49	16.87	9.03	9.62	10.07	10.66	12.04
	12H	13.93	14.49	14.97	15.52	16.92	9.07	9.63	10.12	10.67	12.07
4H	2H	11.04	11.71	12.07	12.73	14.10	7.58	8.25	8.61	9.27	10.64
	3H	12.87	13.43	13.91	14.48	15.86	8.93	9.48	9.97	10.53	11.92
	4H	13.56	14.07	14.61	15.12	16.52	9.47	9.98	10.52	11.03	12.43
	6H	14.08	14.52	15.14	15.58	16.98	9.89	10.33	10.95	11.40	12.80
	8H	14.26	14.67	15.32	15.72	17.14	10.02	10.43	11.08	11.49	12.90
	12H	14.35	14.72	15.43	15.80	17.22	10.08	10.45	11.16	11.53	12.95
8H	4H	13.53	13.94	14.59	15.00	16.41	9.75	10.16	10.81	11.22	12.64
	6H	14.10	14.44	15.18	15.54	16.95	10.27	10.61	11.35	11.71	13.12
	8H	14.32	14.61	15.41	15.70	17.13	10.46	10.76	11.55	11.84	13.28
	12H	14.46	14.72	15.55	15.80	17.27	10.58	10.84	11.67	11.92	13.39
12H	4H	13.48	13.85	14.55	14.92	16.34	9.76	10.13	10.83	11.20	12.62
	6H	14.07	14.37	15.16	15.45	16.89	10.32	10.62	11.41	11.70	13.13
	8H	14.30	14.56	15.39	15.63	17.11	10.53	10.79	11.62	11.87	13.34