

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P906954

Luminaire Tested: DFN2DIP-SQ4F0-160D060US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P906954
REPORT IS A COMBINATION OF REPORTS P900076 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D060US835-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18910.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 211.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4640	4640	4640
5°	4647	4567	4597
10°	4601	4479	4449
15°	4538	4331	4219
20°	4454	4128	3936
25°	4368	3900	3663
30°	4253	3667	3316
35°	4140	3415	3011
40°	4025	3155	2662
45°	3891	2866	2345
50°	3753	2574	2035
55°	3609	2262	1738
60°	3442	1936	1432
65°	3250	1605	1290
70°	3017	1295	1170
75°	2725	1144	1067
80°	2302	963	930
85°	1602	648	709

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3891 cd/sqm

TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	619.8	3.3
10°-20°	1701.4	9.0
20°-30°	2388.6	12.6
30°-40°	2603.8	13.8
40°-50°	2393.2	12.7
50°-60°	1879.5	9.9
60°-70°	1223.3	6.5
70°-80°	629.7	3.3
80°-90°	166.2	0.9
90°-100°	117.4	0.6
100°-110°	373.1	2.0
110°-120°	638.5	3.4
120°-130°	839.7	4.4
130°-140°	942.5	5.0
140°-150°	924.2	4.9
150°-160°	775.3	4.1
160°-170°	514.2	2.7
170°-180°	179.7	1.0
0°-30°	4709.8	24.9
0°-40°	7313.5	38.7
0°-60°	11586.2	61.3
0°-90°	13605.4	71.9
90°-120°	1129.0	6.0
90°-150°	3835.4	20.3
90°-180°	5305.0	28.1
0°-180°	18910.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6613	6613	6613	6613	6613	
5°	6613	6583	6505	6559	6541	627
15°	6290	6224	6020	5907	5847	1772
25°	5709	5518	5123	4878	4787	2626
35°	4919	4614	4088	3710	3578	3079
45°	4022	3620	2992	2567	2424	3106
55°	3058	2591	1945	1586	1472	2732
65°	2065	1580	1041	838	820	2047
75°	1101	682	479	437	431	1164
85°	257	131	114	114	114	295
90°	2	21	56	53	54	18
95°	84	100	102	102	100	93
105°	344	349	352	355	355	363
115°	641	650	647	645	641	634
125°	932	946	942	936	935	833
135°	1205	1223	1226	1225	1220	932
145°	1463	1475	1484	1486	1479	914
155°	1673	1678	1683	1691	1686	770
165°	1820	1819	1819	1830	1822	514
175°	1894	1890	1886	1898	1888	180
180°	1898	1898	1898	1898	1898	

TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6612.8	6612.8	6612.8	6612.8	6612.8
2.5°	6642.6	6612.8	6546.7	6607.1	6595.0
5°	6612.8	6582.9	6504.8	6558.8	6541.0
7.5°	6558.8	6523.2	6439.4	6462.9	6433.1
10°	6487.1	6445.2	6325.8	6307.4	6271.8
12.5°	6397.5	6343.6	6181.7	6146.1	6080.1
15°	6289.6	6223.6	6020.4	5906.7	5847.0
17.5°	6163.9	6068.0	5816.6	5685.1	5589.3
20°	6020.4	5900.4	5601.3	5452.1	5320.1
22.5°	5864.8	5727.0	5379.7	5176.6	5087.0
25°	5709.3	5517.5	5122.6	4877.5	4787.4
27.5°	5523.9	5320.1	4883.2	4602.0	4464.2
30°	5326.4	5098.5	4619.7	4315.0	4153.1
32.5°	5134.7	4859.1	4368.9	4009.6	3859.7
35°	4919.4	4614.0	4087.7	3710.5	3578.5
37.5°	4709.9	4380.4	3824.2	3410.8	3261.6
40°	4488.3	4129.6	3548.6	3123.8	2968.3
42.5°	4261.0	3878.1	3273.7	2830.5	2681.3
45°	4021.6	3620.4	2992.4	2567.0	2423.5
47.5°	3794.3	3369.6	2723.2	2297.8	2166.4
50°	3542.9	3118.1	2459.7	2046.4	1921.3
52.5°	3297.2	2848.3	2208.3	1813.4	1699.7
55°	3057.8	2591.1	1944.8	1586.0	1472.4
57.5°	2812.7	2334.0	1711.8	1376.5	1280.6
60°	2561.3	2082.6	1466.0	1161.3	1065.4
62.5°	2316.2	1837.5	1256.5	969.5	921.9
65°	2064.8	1579.7	1041.3	838.1	819.7
67.5°	1825.4	1340.3	838.1	735.9	718.1
70°	1574.0	1107.3	694.0	634.3	610.2
72.5°	1334.6	891.4	580.3	532.7	520.6
75°	1101.0	681.9	478.7	436.8	431.1
77.5°	867.9	484.4	377.1	353.0	341.0
80°	652.1	347.3	287.0	263.5	263.5
82.5°	454.6	233.7	197.5	185.4	185.4
85°	257.1	131.4	113.7	113.7	113.7
87.5°	95.9	47.6	47.6	41.9	41.9
90°	1.7	20.6	56.1	52.6	54.3
92.5°	35.5	48.1	49.8	51.5	51.5
95°	83.5	99.5	102.4	102.4	99.5
97.5°	139.0	153.9	160.2	160.2	160.2
100°	203.1	216.2	220.8	220.8	219.1
102.5°	270.6	280.3	286.6	288.3	286.6
105°	344.4	349.0	352.4	355.3	355.3
107.5°	417.6	424.5	424.5	425.6	417.6
110°	488.6	497.7	497.7	497.7	493.1

TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	565.2	574.9	573.2	568.6	565.2
115°	640.7	649.9	647.0	645.3	640.7
117.5°	715.7	728.3	720.2	715.7	711.1
120°	791.2	803.8	791.2	791.2	786.0
122.5°	859.8	875.8	867.8	863.3	859.8
125°	931.9	946.2	941.6	936.5	934.8
127.5°	1002.3	1020.0	1013.7	1006.9	1002.3
130°	1068.1	1088.7	1085.8	1082.4	1076.1
132.5°	1141.9	1157.9	1159.0	1151.0	1146.4
135°	1205.4	1223.1	1226.5	1224.8	1220.2
137.5°	1276.3	1290.6	1293.5	1292.3	1285.5
140°	1338.7	1353.0	1361.0	1361.0	1354.7
142.5°	1402.7	1417.0	1421.6	1423.3	1417.0
145°	1463.4	1474.8	1484.0	1485.7	1479.4
147.5°	1517.7	1532.0	1538.9	1541.7	1535.4
150°	1573.8	1583.5	1589.8	1594.9	1589.8
152.5°	1623.5	1633.3	1641.3	1647.6	1641.3
155°	1673.3	1677.9	1683.0	1691.1	1685.9
157.5°	1716.2	1719.7	1722.5	1734.0	1726.0
160°	1754.6	1758.0	1759.7	1769.4	1762.6
162.5°	1790.0	1790.0	1791.7	1802.6	1794.6
165°	1820.3	1818.6	1818.6	1830.1	1822.1
167.5°	1847.8	1842.7	1842.7	1854.1	1846.1
170°	1868.4	1863.8	1862.1	1873.5	1863.8
172.5°	1882.7	1878.1	1876.4	1887.8	1878.1
175°	1894.1	1889.6	1886.1	1897.6	1887.8
177.5°	1900.4	1895.9	1892.4	1902.1	1892.4
180°	1897.6	1897.6	1897.6	1897.6	1897.6

TEST NUMBER: P906954

CATALOG NUMBER: DFN2DIP-SQ4F0-160D060US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.33	15.38	15.08	16.15	17.07	10.30	11.34	11.05	12.11	13.03
	3H	16.03	16.97	16.80	17.75	18.70	11.50	12.44	12.26	13.22	14.17
	4H	16.65	17.54	17.44	18.32	19.29	11.96	12.85	12.74	13.63	14.60
	6H	17.09	17.91	17.88	18.70	19.68	12.29	13.11	13.09	13.90	14.88
	8H	17.23	18.00	18.03	18.81	19.79	12.39	13.17	13.20	13.98	14.96
	12H	17.30	18.03	18.11	18.84	19.85	12.44	13.18	13.25	13.99	14.99
4H	2H	14.38	15.26	15.16	16.05	17.01	10.92	11.80	11.70	12.59	13.55
	3H	16.23	16.97	17.03	17.79	18.77	12.29	13.02	13.09	13.84	14.83
	4H	16.94	17.60	17.75	18.42	19.43	12.85	13.51	13.66	14.33	15.34
	6H	17.47	18.04	18.30	18.89	19.90	13.28	13.85	14.11	14.70	15.71
	8H	17.65	18.19	18.48	19.03	20.05	13.41	13.95	14.24	14.79	15.82
	12H	17.76	18.24	18.61	19.10	20.13	13.49	13.97	14.34	14.83	15.86
8H	4H	16.92	17.46	17.75	18.30	19.32	13.15	13.68	13.98	14.52	15.55
	6H	17.50	17.94	18.36	18.82	19.85	13.67	14.12	14.53	15.00	16.03
	8H	17.72	18.11	18.59	18.99	20.04	13.87	14.26	14.74	15.14	16.18
	12H	17.87	18.22	18.74	19.09	20.19	14.00	14.34	14.87	15.21	16.31
12H	4H	16.88	17.36	17.73	18.23	19.26	13.16	13.64	14.01	14.50	15.54
	6H	17.48	17.87	18.35	18.75	19.79	13.72	14.12	14.60	15.00	16.04
	8H	17.71	18.06	18.58	18.92	20.02	13.95	14.29	14.82	15.16	16.26