

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909509

Luminaire Tested: DFN2DIP-SQ4F0-090D080US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909509
REPORT IS A COMBINATION OF REPORTS P901621 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D080US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16996.0 lumens
Efficiency: N/A
Efficacy: 119.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 142.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	108	108	108	108		100	100	100	100		85	85	85		71	71	71		59	59	59
1	98	94	90	87		91	87	84	81		75	72	70		63	61	59		52	51	50
2	90	82	76	71		83	76	71	66		65	61	58		55	52	50		46	44	42
3	82	72	65	59		75	67	61	55		58	53	49		49	45	42		41	38	36
4	75	64	56	50		69	60	53	47		51	46	41		43	39	36		36	33	31
5	69	57	49	43		63	53	46	40		46	40	36		39	35	31		33	29	27
6	63	51	43	37		58	48	40	35		41	36	31		35	31	27		30	26	24
7	59	46	38	33		54	43	36	31		37	32	28		32	28	24		27	24	21
8	54	42	34	29		50	39	32	27		34	29	24		29	25	22		25	21	19
9	51	38	31	26		47	36	29	24		31	26	22		27	23	19		23	20	17
10	47	35	28	23		44	33	26	22		29	24	20		25	21	18		21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2481	2481	2481
5°	2485	2447	2464
10°	2465	2415	2431
15°	2429	2376	2380
20°	2380	2321	2327
25°	2331	2255	2266
30°	2270	2194	2189
35°	2212	2122	2106
40°	2141	2050	2028
45°	2070	1977	1948
50°	1992	1900	1855
55°	1911	1812	1770
60°	1819	1707	1673
65°	1719	1598	1558
70°	1591	1466	1435
75°	1414	1308	1322
80°	1201	1106	1104
85°	868	757	742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2070 cd/sqm

TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.9	2.0
10°-20°	936.5	5.5
20°-30°	1376.3	8.1
30°-40°	1598.5	9.4
40°-50°	1596.5	9.4
50°-60°	1392.1	8.2
60°-70°	1029.1	6.1
70°-80°	582.2	3.4
80°-90°	158.5	0.9
90°-100°	89.9	0.5
100°-110°	335.1	2.0
110°-120°	888.9	5.2
120°-130°	1474.3	8.7
130°-140°	1566.0	9.2
140°-150°	1455.4	8.6
150°-160°	1170.1	6.9
160°-170°	754.0	4.4
170°-180°	259.5	1.5
0°-30°	2645.7	15.6
0°-40°	4244.2	25.0
0°-60°	7232.9	42.6
0°-90°	9002.7	53.0
90°-120°	1314.0	7.7
90°-150°	5809.7	34.2
90°-180°	7993.0	47.0
0°-180°	16996.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3536	3536	3536	3536	3536	
5°	3536	3523	3486	3513	3506	336
15°	3367	3346	3302	3316	3299	948
25°	3047	3020	2962	2969	2962	1402
35°	2629	2595	2540	2520	2503	1642
45°	2139	2115	2064	2027	2013	1651
55°	1619	1598	1558	1517	1500	1447
65°	1092	1071	1037	1007	990	1079
75°	571	565	547	527	534	610
85°	139	136	133	122	119	155
90°	2	24	39	49	53	16
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3536.4	3536.4	3536.4	3536.4	3536.4
2.5°	3557.0	3540.1	3502.6	3536.4	3530.0
5°	3536.4	3523.1	3485.7	3512.7	3506.2
7.5°	3512.7	3492.5	3455.0	3482.4	3475.6
10°	3475.6	3451.7	3410.9	3438.0	3427.9
12.5°	3424.3	3404.1	3363.4	3380.2	3373.5
15°	3366.6	3346.4	3302.0	3315.7	3298.7
17.5°	3295.1	3274.9	3230.6	3247.5	3230.6
20°	3216.8	3196.6	3149.0	3159.1	3145.7
22.5°	3138.9	3108.3	3063.8	3063.8	3057.0
25°	3046.9	3019.8	2962.1	2968.6	2962.1
27.5°	2944.8	2920.9	2877.0	2866.9	2849.9
30°	2843.1	2815.6	2764.7	2754.6	2741.0
32.5°	2734.1	2713.9	2659.4	2638.9	2625.1
35°	2628.8	2594.8	2540.3	2519.8	2502.9
37.5°	2509.7	2479.0	2424.5	2400.8	2383.8
40°	2387.3	2360.0	2305.4	2275.1	2261.5
42.5°	2268.3	2240.9	2186.8	2152.5	2132.3
45°	2139.1	2115.4	2064.1	2026.9	2013.3
47.5°	2013.3	1989.4	1934.9	1897.4	1877.2
50°	1880.5	1863.5	1815.8	1768.3	1751.3
52.5°	1751.3	1727.5	1683.4	1646.0	1622.1
55°	1618.9	1598.3	1557.5	1516.8	1499.9
57.5°	1486.1	1469.2	1424.8	1384.0	1370.3
60°	1353.3	1340.0	1292.3	1254.9	1244.8
62.5°	1224.2	1200.3	1166.4	1132.6	1118.8
65°	1091.8	1071.2	1037.2	1006.6	989.7
67.5°	955.7	938.5	908.1	884.3	870.6
70°	829.8	816.1	785.5	761.6	748.3
72.5°	700.6	686.9	669.9	646.2	636.1
75°	571.2	564.6	547.3	527.1	534.0
77.5°	455.7	442.0	435.2	425.1	415.0
80°	340.2	336.6	329.7	319.6	312.9
82.5°	231.3	231.3	228.0	214.3	214.3
85°	139.3	136.0	132.8	122.3	119.1
87.5°	61.3	54.4	47.7	37.6	33.9
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8

TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5

TEST NUMBER: P909509

CATALOG NUMBER: DFN2DIP-SQ4F0-090D080US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.71	11.60	11.64	12.55	13.78	10.27	11.16	11.20	12.11	13.33
	3H	12.38	13.18	13.32	14.13	15.39	11.89	12.69	12.83	13.64	14.90
	4H	12.97	13.73	13.93	14.69	15.95	12.48	13.23	13.43	14.19	15.45
	6H	13.38	14.07	14.34	15.04	16.31	12.88	13.57	13.84	14.54	15.81
	8H	13.48	14.15	14.46	15.13	16.40	12.98	13.64	13.96	14.63	15.90
	12H	13.53	14.16	14.52	15.14	16.44	13.02	13.65	14.01	14.63	15.93
4H	2H	11.18	11.93	12.14	12.89	14.15	10.82	11.58	11.79	12.54	13.80
	3H	13.05	13.68	14.02	14.67	15.95	12.64	13.27	13.62	14.26	15.54
	4H	13.77	14.34	14.75	15.33	16.63	13.35	13.92	14.33	14.91	16.21
	6H	14.29	14.79	15.28	15.80	17.09	13.86	14.35	14.85	15.36	16.66
	8H	14.44	14.91	15.44	15.91	17.22	14.01	14.47	15.00	15.47	16.78
	12H	14.52	14.94	15.53	15.96	17.27	14.07	14.49	15.08	15.51	16.82
8H	4H	13.97	14.43	14.96	15.43	16.75	13.59	14.06	14.59	15.06	16.37
	6H	14.61	14.99	15.63	16.03	17.34	14.22	14.61	15.24	15.65	16.96
	8H	14.83	15.17	15.86	16.20	17.53	14.44	14.78	15.47	15.81	17.13
	12H	14.97	15.26	16.00	16.29	17.66	14.55	14.85	15.59	15.88	17.25
12H	4H	13.96	14.37	14.97	15.39	16.71	13.59	14.01	14.60	15.02	16.34
	6H	14.64	14.97	15.66	16.01	17.33	14.26	14.60	15.29	15.63	16.96
	8H	14.88	15.18	15.92	16.21	17.58	14.50	14.80	15.54	15.83	17.20

END OF REPORT