

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909543

Luminaire Tested: DFN2DIP-SQ4F0-100D070US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909543
REPORT IS A COMBINATION OF REPORTS P901606 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-100D070US840-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15582.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 144.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	92	88	92	89	86	83	76	74	72	65	63	62	55	53	52
2	91	84	78	73	84	78	73	69	68	64	60	58	55	52	49	47	45
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	77	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	39	42	38	34	36	33	30
6	65	53	45	40	60	50	43	38	44	38	34	38	34	30	33	29	27
7	60	48	41	35	56	45	38	33	40	34	30	35	30	27	30	27	24
8	56	44	36	31	52	41	35	30	37	31	27	32	28	24	28	24	22
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	26	22	20
10	49	37	30	25	46	35	29	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2929	2929	2929
5°	2933	2883	2901
10°	2904	2827	2808
15°	2864	2734	2663
20°	2811	2606	2484
25°	2757	2462	2312
30°	2684	2314	2093
35°	2613	2156	1901
40°	2540	1991	1680
45°	2456	1809	1480
50°	2369	1625	1285
55°	2278	1428	1097
60°	2173	1222	904
65°	2051	1013	814
70°	1904	817	738
75°	1720	722	674
80°	1452	608	587
85°	1011	409	447

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2456 cd/sqm

TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.2	2.5
10°-20°	1073.8	6.9
20°-30°	1507.6	9.7
30°-40°	1643.4	10.5
40°-50°	1510.5	9.7
50°-60°	1186.3	7.6
60°-70°	772.1	5.0
70°-80°	397.5	2.6
80°-90°	105.7	0.7
90°-100°	78.7	0.5
100°-110°	293.3	1.9
110°-120°	777.8	5.0
120°-130°	1290.0	8.3
130°-140°	1370.3	8.8
140°-150°	1273.5	8.2
150°-160°	1023.9	6.6
160°-170°	659.7	4.2
170°-180°	227.1	1.5
0°-30°	2972.6	19.1
0°-40°	4616.1	29.6
0°-60°	7312.8	46.9
0°-90°	8588.0	55.1
90°-120°	1149.7	7.4
90°-150°	5083.5	32.6
90°-180°	6994.0	44.9
0°-180°	15582.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4106	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3604	3482	3233	3078	3022	1657
35°	3105	2912	2580	2342	2259	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1636	1228	1001	929	1725
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	2	21	34	43	47	15
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.8	4173.8	4173.8	4173.8	4173.8
2.5°	4192.6	4173.8	4132.1	4170.1	4162.6
5°	4173.8	4154.9	4105.6	4139.7	4128.4
7.5°	4139.7	4117.2	4064.3	4079.1	4060.4
10°	4094.4	4067.9	3992.6	3981.0	3958.6
12.5°	4037.9	4003.8	3901.6	3879.2	3837.5
15°	3969.8	3928.1	3799.8	3728.1	3690.5
17.5°	3890.4	3829.9	3671.3	3588.3	3527.8
20°	3799.8	3724.1	3535.3	3441.2	3357.8
22.5°	3701.7	3614.7	3395.5	3267.3	3210.8
25°	3603.5	3482.5	3233.2	3078.5	3021.6
27.5°	3486.5	3357.8	3082.1	2904.6	2817.6
30°	3361.8	3217.9	2915.8	2723.5	2621.3
32.5°	3240.9	3066.9	2757.5	2530.7	2436.1
35°	3104.9	2912.3	2580.0	2342.0	2258.6
37.5°	2972.7	2764.7	2413.7	2152.8	2058.6
40°	2832.9	2606.5	2239.8	1971.7	1873.5
42.5°	2689.4	2447.7	2066.3	1786.6	1692.3
45°	2538.3	2285.0	1888.8	1620.2	1529.6
47.5°	2394.9	2126.8	1718.8	1450.3	1367.4
50°	2236.1	1968.0	1552.5	1291.6	1212.6
52.5°	2081.0	1797.8	1393.8	1144.5	1072.8
55°	1930.0	1635.5	1227.5	1001.1	929.3
57.5°	1775.3	1473.1	1080.5	868.8	808.3
60°	1616.6	1314.4	925.3	733.0	672.5
62.5°	1461.9	1159.7	793.0	612.0	581.9
65°	1303.2	997.0	657.2	529.0	517.4
67.5°	1152.2	846.0	529.0	464.4	453.2
70°	993.4	698.9	438.0	400.3	385.2
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.9	430.4	302.2	275.7	272.1
77.5°	547.9	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P909543

CATALOG NUMBER: DFN2DIP-SQ4F0-100D070US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.36	12.23	12.28	13.16	14.36	7.32	8.19	8.24	9.12	10.32
	3H	13.04	13.82	13.97	14.77	15.99	8.51	9.29	9.44	10.23	11.46
	4H	13.66	14.39	14.60	15.34	16.57	8.96	9.70	9.91	10.65	11.88
	6H	14.08	14.76	15.04	15.72	16.96	9.29	9.97	10.24	10.92	12.16
	8H	14.21	14.86	15.18	15.83	17.07	9.38	10.03	10.34	11.00	12.24
	12H	14.28	14.89	15.25	15.86	17.12	9.43	10.04	10.39	11.00	12.27
4H	2H	11.38	12.12	12.33	13.07	14.30	7.92	8.66	8.87	9.61	10.84
	3H	13.22	13.83	14.18	14.81	16.06	9.28	9.89	10.24	10.87	12.11
	4H	13.92	14.48	14.89	15.45	16.72	9.83	10.39	10.80	11.36	12.63
	6H	14.44	14.92	15.42	15.91	17.18	10.25	10.73	11.23	11.73	13.00
	8H	14.62	15.07	15.60	16.05	17.34	10.38	10.83	11.36	11.82	13.10
	12H	14.72	15.12	15.72	16.13	17.41	10.45	10.85	11.45	11.86	13.15
8H	4H	13.89	14.34	14.87	15.32	16.61	10.11	10.56	11.10	11.55	12.83
	6H	14.46	14.83	15.47	15.86	17.14	10.63	11.01	11.64	12.04	13.32
	8H	14.68	15.01	15.70	16.02	17.33	10.83	11.15	11.84	12.17	13.47
	12H	14.82	15.11	15.84	16.12	17.47	10.95	11.24	11.97	12.25	13.59
12H	4H	13.84	14.25	14.84	15.25	16.54	10.12	10.53	11.12	11.53	12.82
	6H	14.44	14.76	15.45	15.78	17.08	10.68	11.01	11.70	12.03	13.33
	8H	14.66	14.95	15.68	15.96	17.31	10.90	11.19	11.92	12.20	13.54

END OF REPORT