

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925673

Luminaire Tested: DFN2DIP-SQ3F0-100D090US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925673
REPORT IS A COMBINATION OF REPORTS P901483 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-100D090US950-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17944.7 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 167
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23
7	59	46	38	33	54	43	36	31	37	32	27	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4253	4253	4253
5°	4257	4191	4221
10°	4220	4132	4162
15°	4155	4061	4072
20°	4069	3964	3979
25°	3983	3848	3872
30°	3875	3740	3736
35°	3773	3613	3592
40°	3648	3485	3456
45°	3523	3356	3316
50°	3387	3220	3154
55°	3243	3064	3005
60°	3081	2879	2834
65°	2904	2686	2632
70°	2678	2451	2415
75°	2366	2170	2212
80°	1988	1810	1829
85°	1400	1200	1197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3523 cd/sqm

TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	1.9
10°-20°	983.0	5.5
20°-30°	1444.7	8.1
30°-40°	1677.9	9.4
40°-50°	1675.8	9.3
50°-60°	1461.2	8.1
60°-70°	1080.2	6.0
70°-80°	611.1	3.4
80°-90°	166.4	0.9
90°-100°	95.6	0.5
100°-110°	356.2	2.0
110°-120°	944.7	5.3
120°-130°	1566.8	8.7
130°-140°	1664.3	9.3
140°-150°	1546.8	8.6
150°-160°	1243.6	6.9
160°-170°	801.3	4.5
170°-180°	275.8	1.5
0°-30°	2777.1	15.5
0°-40°	4454.9	24.8
0°-60°	7592.0	42.3
0°-90°	9449.7	52.7
90°-120°	1396.4	7.8
90°-150°	6174.3	34.4
90°-180°	8495.0	47.3
0°-180°	17944.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3712	3712	3712	3712	3712	
5°	3712	3698	3659	3687	3680	352
15°	3534	3512	3466	3480	3462	995
25°	3198	3170	3109	3116	3109	1472
35°	2759	2724	2666	2645	2627	1723
45°	2245	2220	2166	2128	2113	1733
55°	1699	1678	1635	1592	1574	1519
65°	1146	1124	1089	1057	1039	1133
75°	600	593	574	553	560	640
85°	146	143	139	128	125	163
90°	2	25	42	53	56	17
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	

TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3712.1	3712.1	3712.1	3712.1	3712.1
2.5°	3733.7	3715.8	3676.4	3712.1	3705.2
5°	3712.1	3698.1	3658.7	3687.1	3680.2
7.5°	3687.1	3665.8	3626.4	3655.3	3648.1
10°	3648.1	3623.1	3580.3	3608.7	3598.1
12.5°	3594.3	3573.1	3530.3	3548.1	3540.9
15°	3533.7	3512.5	3465.9	3480.3	3462.5
17.5°	3458.7	3437.5	3390.9	3408.7	3390.9
20°	3376.5	3355.3	3305.3	3315.9	3301.9
22.5°	3294.7	3262.6	3215.9	3215.9	3208.8
25°	3198.2	3169.8	3109.2	3116.0	3109.2
27.5°	3091.0	3066.0	3019.8	3009.2	2991.4
30°	2984.2	2955.4	2902.0	2891.4	2877.0
32.5°	2869.8	2848.6	2791.4	2769.8	2755.4
35°	2759.3	2723.7	2666.4	2644.9	2627.0
37.5°	2634.3	2602.0	2544.9	2519.9	2502.1
40°	2505.9	2477.1	2419.9	2388.1	2373.7
42.5°	2380.9	2352.1	2295.3	2259.4	2238.2
45°	2245.3	2220.3	2166.5	2127.5	2113.2
47.5°	2113.2	2088.2	2031.0	1991.6	1970.4
50°	1973.8	1956.0	1906.0	1856.0	1838.3
52.5°	1838.3	1813.3	1767.0	1727.7	1702.7
55°	1699.3	1677.7	1634.9	1592.0	1574.3
57.5°	1559.9	1542.0	1495.5	1452.8	1438.3
60°	1420.5	1406.5	1356.5	1317.1	1306.5
62.5°	1284.9	1259.9	1224.4	1188.8	1174.4
65°	1145.9	1124.4	1088.8	1056.6	1038.8
67.5°	1003.2	985.0	953.2	928.2	913.8
70°	871.0	856.6	824.4	799.5	785.4
72.5°	735.4	721.0	703.3	678.3	667.6
75°	599.5	592.7	574.5	553.3	560.5
77.5°	478.3	463.9	456.7	446.1	435.5
80°	357.1	353.4	346.1	335.5	328.4
82.5°	242.8	242.8	239.4	225.0	225.0
85°	146.2	142.8	139.4	128.4	125.0
87.5°	64.4	57.1	50.0	39.4	35.6
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6

TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7

TEST NUMBER: P925673

CATALOG NUMBER: DFN2DIP-SQ3F0-100D090US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.51	13.40	13.44	14.35	15.58	12.07	12.95	13.00	13.90	15.14
	3H	14.17	14.96	15.11	15.92	17.18	13.68	14.47	14.62	15.43	16.69
	4H	14.75	15.51	15.71	16.47	17.74	14.26	15.01	15.22	15.98	17.24
	6H	15.15	15.84	16.12	16.81	18.09	14.65	15.34	15.62	16.31	17.59
	8H	15.26	15.91	16.23	16.90	18.18	14.75	15.41	15.73	16.40	17.68
	12H	15.30	15.93	16.29	16.91	18.21	14.79	15.42	15.78	16.40	17.70
4H	2H	12.97	13.72	13.94	14.69	15.95	12.62	13.37	13.58	14.33	15.60
	3H	14.83	15.46	15.81	16.46	17.73	14.43	15.05	15.40	16.05	17.33
	4H	15.54	16.12	16.53	17.11	18.41	15.12	15.69	16.11	16.68	17.99
	6H	16.06	16.55	17.05	17.56	18.86	15.62	16.12	16.62	17.13	18.43
	8H	16.21	16.67	17.20	17.67	18.99	15.77	16.23	16.77	17.23	18.55
	12H	16.28	16.69	17.29	17.71	19.04	15.83	16.25	16.84	17.27	18.59
8H	4H	15.74	16.20	16.74	17.21	18.52	15.36	15.82	16.36	16.83	18.14
	6H	16.37	16.75	17.39	17.79	19.11	15.98	16.36	17.00	17.41	18.72
	8H	16.58	16.92	17.61	17.95	19.29	16.19	16.53	17.22	17.56	18.89
	12H	16.71	17.01	17.75	18.04	19.41	16.30	16.60	17.34	17.63	19.00
12H	4H	15.73	16.14	16.74	17.16	18.48	15.36	15.77	16.37	16.79	18.12
	6H	16.39	16.73	17.42	17.76	19.10	16.02	16.36	17.05	17.39	18.72
	8H	16.63	16.93	17.67	17.96	19.33	16.25	16.55	17.29	17.58	18.95