

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925703

Luminaire Tested: DFN2DIP-SQ3F0-110D070US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925703
REPORT IS A COMBINATION OF REPORTS P901450 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D070US950-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15531.1 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925703
CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P925703
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57	57	57	57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	57	55	54	50	48	47	42
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42	42	42	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	40	37	37	37	37
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32	32	32	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28	28	28	28
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	30	28	25	25	25	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22	22	22	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	27	23	20	18	18	18	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17	17	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4970	4970	4970
5°	4974	4887	4920
10°	4922	4788	4759
15°	4851	4627	4510
20°	4758	4406	4205
25°	4663	4158	3910
30°	4537	3905	3537
35°	4412	3633	3210
40°	4286	3352	2834
45°	4139	3040	2494
50°	3987	2726	2162
55°	3828	2390	1843
60°	3644	2040	1516
65°	3431	1685	1362
70°	3174	1353	1230
75°	2850	1186	1116
80°	2381	984	963
85°	1615	641	713

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4139 cd/sqm



TEST NUMBER: P925703

CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.5	2.6
10°-20°	1115.9	7.2
20°-30°	1566.7	10.1
30°-40°	1707.7	11.0
40°-50°	1569.6	10.1
50°-60°	1232.7	7.9
60°-70°	802.4	5.2
70°-80°	413.0	2.7
80°-90°	109.4	0.7
90°-100°	74.3	0.5
100°-110°	277.0	1.8
110°-120°	734.8	4.7
120°-130°	1218.6	7.8
130°-140°	1294.5	8.3
140°-150°	1203.1	7.7
150°-160°	967.2	6.2
160°-170°	623.3	4.0
170°-180°	214.5	1.4
0°-30°	3089.0	19.9
0°-40°	4796.8	30.9
0°-60°	7599.1	48.9
0°-90°	8923.9	57.5
90°-120°	1086.1	7.0
90°-150°	4802.2	30.9
90°-180°	6607.0	42.5
0°-180°	15531.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4337	4337	4337	4337	4337	
5°	4337	4318	4266	4302	4290	411
15°	4125	4082	3949	3874	3835	1162
25°	3744	3619	3360	3199	3140	1722
35°	3226	3026	2681	2434	2347	2019
45°	2638	2374	1963	1684	1590	2037
55°	2006	1700	1276	1040	966	1792
65°	1354	1036	683	550	538	1343
75°	722	447	314	286	283	764
85°	169	86	74	74	74	194
90°	2	20	32	41	44	15
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P925703

CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4337.2	4337.2	4337.2	4337.2	4337.2
2.5°	4356.7	4337.2	4293.9	4333.4	4325.5
5°	4337.2	4317.6	4266.4	4301.8	4290.1
7.5°	4301.8	4278.4	4223.5	4238.9	4219.3
10°	4254.7	4227.2	4148.9	4136.8	4113.6
12.5°	4196.0	4160.6	4054.4	4031.0	3987.7
15°	4125.2	4081.9	3948.6	3874.1	3834.9
17.5°	4042.8	3979.9	3815.0	3728.7	3665.8
20°	3948.6	3869.9	3673.8	3575.9	3489.3
22.5°	3846.6	3756.2	3528.5	3395.2	3336.4
25°	3744.5	3618.8	3359.8	3199.0	3139.9
27.5°	3623.0	3489.3	3202.8	3018.3	2927.9
30°	3493.5	3344.0	3030.0	2830.0	2723.9
32.5°	3367.7	3186.9	2865.4	2629.8	2531.5
35°	3226.5	3026.2	2681.0	2433.7	2347.0
37.5°	3089.1	2873.0	2508.2	2237.0	2139.2
40°	2943.8	2708.5	2327.5	2048.8	1946.8
42.5°	2794.6	2543.6	2147.2	1856.5	1758.6
45°	2637.7	2374.5	1962.7	1683.6	1589.6
47.5°	2488.6	2210.0	1786.1	1507.0	1420.9
50°	2323.7	2045.1	1613.3	1342.2	1260.1
52.5°	2162.5	1868.1	1448.4	1189.4	1114.7
55°	2005.5	1699.5	1275.5	1040.2	965.7
57.5°	1844.8	1530.8	1122.7	902.9	839.9
60°	1679.9	1365.9	961.5	761.7	698.8
62.5°	1519.1	1205.2	824.2	635.9	604.6
65°	1354.2	1036.0	683.0	549.7	537.6
67.5°	1197.3	879.1	549.7	482.6	471.0
70°	1032.3	726.3	455.2	416.0	400.2
72.5°	875.3	584.7	380.6	349.4	341.4
75°	722.1	447.2	314.0	286.5	282.8
77.5°	569.3	317.8	247.4	231.5	223.6
80°	427.7	227.8	188.2	172.9	172.9
82.5°	298.1	153.2	129.6	121.6	121.6
85°	168.7	86.2	74.5	74.5	74.5
87.5°	62.9	31.2	31.2	27.5	27.5
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8



TEST NUMBER: P925703

CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7



TEST NUMBER: P925703
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D070US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.35	14.25	14.25	15.16	16.32	9.31	10.21	10.21	11.12	12.28
	3H	15.03	15.83	15.94	16.75	17.94	10.50	11.30	11.41	12.22	13.41
	4H	15.64	16.40	16.56	17.32	18.52	10.95	11.71	11.87	12.63	13.83
	6H	16.06	16.76	17.00	17.69	18.90	11.27	11.96	12.20	12.90	14.11
	8H	16.19	16.85	17.13	17.80	19.01	11.36	12.02	12.30	12.97	14.18
	12H	16.25	16.88	17.20	17.82	19.06	11.40	12.03	12.35	12.97	14.21
4H	2H	13.38	14.13	14.31	15.06	16.26	9.92	10.67	10.85	11.60	12.80
	3H	15.21	15.84	16.15	16.79	18.01	11.26	11.89	12.20	12.85	14.06
	4H	15.90	16.47	16.85	17.42	18.66	11.81	12.38	12.76	13.33	14.57
	6H	16.41	16.90	17.38	17.88	19.12	12.22	12.72	13.19	13.69	14.93
	8H	16.59	17.05	17.55	18.02	19.27	12.35	12.81	13.32	13.78	15.03
	12H	16.68	17.10	17.66	18.08	19.34	12.42	12.83	13.40	13.82	15.07
8H	4H	15.87	16.33	16.83	17.30	18.55	12.09	12.55	13.06	13.52	14.77
	6H	16.43	16.81	17.42	17.82	19.07	12.60	12.98	13.59	13.99	15.24
	8H	16.65	16.98	17.65	17.98	19.25	12.79	13.12	13.79	14.12	15.39
	12H	16.78	17.08	17.79	18.07	19.39	12.91	13.20	13.91	14.19	15.51
12H	4H	15.82	16.24	16.81	17.22	18.48	12.10	12.51	13.08	13.50	14.75
	6H	16.41	16.74	17.41	17.74	19.01	12.65	12.99	13.65	13.99	15.25
	8H	16.63	16.92	17.63	17.92	19.23	12.86	13.15	13.86	14.15	15.46