

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909573

Luminaire Tested: DFN2DIP-SQ4F0-110D060US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909573
REPORT IS A COMBINATION OF REPORTS P901589 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-110D060US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16996.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 150.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92		80	80	80		70
1	101	97	93	89	95	91	88	84	80	78	75		71	69	67		62
2	92	84	78	73	86	80	74	69	70	66	62		62	59	56		54
3	84	74	67	61	79	70	63	58	62	57	53		55	51	47		48
4	77	66	58	51	72	62	55	49	55	49	45		49	44	41		43
5	71	59	50	44	66	56	48	42	50	43	39		44	39	35		39
6	65	53	44	39	61	50	42	37	45	39	34		40	35	31		35
7	60	48	40	34	57	45	38	33	41	34	30		36	31	27		32
8	56	43	36	30	53	41	34	29	37	31	27		33	28	25		30
9	52	40	32	27	49	38	31	26	34	28	24		31	26	22		27
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3033	3033	3033
5°	3038	2991	3012
10°	3013	2952	2972
15°	2969	2904	2909
20°	2909	2837	2845
25°	2849	2757	2770
30°	2774	2682	2675
35°	2704	2594	2574
40°	2617	2505	2479
45°	2530	2416	2381
50°	2435	2323	2268
55°	2335	2215	2164
60°	2223	2086	2045
65°	2100	1954	1904
70°	1944	1792	1753
75°	1728	1598	1616
80°	1468	1352	1349
85°	1061	925	907

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2530 cd/sqm

TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.8	2.4
10°-20°	1144.7	6.7
20°-30°	1682.2	9.9
30°-40°	1953.7	11.5
40°-50°	1951.3	11.5
50°-60°	1701.5	10.0
60°-70°	1257.8	7.4
70°-80°	711.6	4.2
80°-90°	191.4	1.1
90°-100°	67.4	0.4
100°-110°	251.4	1.5
110°-120°	666.7	3.9
120°-130°	1105.7	6.5
130°-140°	1174.5	6.9
140°-150°	1091.6	6.4
150°-160°	877.6	5.2
160°-170°	565.5	3.3
170°-180°	194.6	1.1
0°-30°	3233.7	19.0
0°-40°	5187.4	30.5
0°-60°	8840.2	52.0
0°-90°	11001.0	64.7
90°-120°	985.5	5.8
90°-150°	4357.2	25.6
90°-180°	5995.0	35.3
0°-180°	16996.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4322	4322	4322	4322	4322	
5°	4322	4306	4260	4293	4285	410
15°	4115	4090	4036	4052	4032	1159
25°	3724	3691	3620	3628	3620	1714
35°	3213	3172	3105	3080	3059	2006
45°	2614	2585	2523	2477	2461	2018
55°	1979	1954	1904	1854	1833	1769
65°	1334	1309	1268	1230	1210	1319
75°	698	690	669	644	653	745
85°	170	166	162	150	146	190
90°	1	18	30	37	40	16
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4322.4	4322.4	4322.4	4322.4	4322.4
2.5°	4347.5	4326.8	4280.9	4322.4	4314.4
5°	4322.4	4306.1	4260.2	4293.2	4285.4
7.5°	4293.2	4268.6	4222.8	4256.3	4247.9
10°	4247.9	4218.7	4168.9	4201.9	4189.6
12.5°	4185.3	4160.5	4110.8	4131.5	4123.1
15°	4114.7	4090.0	4035.7	4052.5	4031.8
17.5°	4027.3	4002.7	3948.5	3969.2	3948.5
20°	3931.7	3907.0	3848.8	3861.1	3844.9
22.5°	3836.5	3798.9	3744.7	3744.7	3736.3
25°	3724.0	3691.0	3620.4	3628.3	3620.4
27.5°	3599.2	3570.1	3516.3	3503.9	3483.2
30°	3474.8	3441.3	3379.1	3366.8	3350.0
32.5°	3341.6	3317.0	3250.4	3225.2	3208.4
35°	3212.9	3171.5	3104.8	3079.7	3059.0
37.5°	3067.4	3029.9	2963.3	2934.2	2913.5
40°	2917.9	2884.4	2817.8	2780.8	2764.0
42.5°	2772.4	2738.9	2672.7	2630.8	2606.2
45°	2614.5	2585.4	2522.7	2477.4	2460.6
47.5°	2460.6	2431.6	2364.9	2319.1	2294.3
50°	2298.4	2277.7	2219.4	2161.2	2140.5
52.5°	2140.5	2111.3	2057.6	2011.7	1982.6
55°	1978.6	1953.5	1903.7	1853.8	1833.1
57.5°	1816.3	1795.6	1741.4	1691.5	1674.8
60°	1654.1	1637.8	1579.5	1533.7	1521.4
62.5°	1496.2	1467.1	1425.6	1384.2	1367.5
65°	1334.3	1309.2	1267.8	1230.3	1209.6
67.5°	1168.1	1147.0	1109.9	1080.9	1064.1
70°	1014.2	997.4	960.0	930.9	914.5
72.5°	856.4	839.6	818.9	789.8	777.4
75°	698.0	690.1	668.9	644.3	652.7
77.5°	556.9	540.2	531.8	519.5	507.2
80°	415.9	411.4	403.0	390.7	382.3
82.5°	282.7	282.7	278.7	262.0	262.0
85°	170.3	166.2	162.3	149.5	145.5
87.5°	74.9	66.6	58.2	45.8	41.4
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9

TEST NUMBER: P909573

CATALOG NUMBER: DFN2DIP-SQ4F0-110D060US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.40	13.41	13.22	14.25	15.30	11.95	12.96	12.77	13.81	14.85
	3H	14.07	14.98	14.91	15.83	16.91	13.58	14.49	14.42	15.34	16.41
	4H	14.67	15.53	15.52	16.39	17.47	14.18	15.03	15.03	15.89	16.98
	6H	15.08	15.87	15.94	16.74	17.84	14.58	15.37	15.44	16.24	17.34
	8H	15.19	15.95	16.06	16.83	17.93	14.69	15.44	15.56	16.33	17.43
	12H	15.25	15.97	16.12	16.84	17.97	14.74	15.46	15.61	16.33	17.46
4H	2H	12.88	13.73	13.73	14.59	15.68	12.52	13.38	13.38	14.24	15.32
	3H	14.76	15.48	15.63	16.37	17.47	14.35	15.07	15.22	15.96	17.06
	4H	15.48	16.14	16.36	17.03	18.15	15.06	15.71	15.94	16.60	17.73
	6H	16.01	16.58	16.91	17.49	18.62	15.58	16.15	16.47	17.06	18.18
	8H	16.17	16.70	17.06	17.60	18.74	15.73	16.26	16.63	17.17	18.31
	12H	16.25	16.73	17.17	17.65	18.80	15.80	16.28	16.72	17.20	18.35
8H	4H	15.69	16.22	16.59	17.13	18.27	15.32	15.84	16.21	16.75	17.89
	6H	16.34	16.77	17.26	17.72	18.86	15.95	16.39	16.88	17.34	18.48
	8H	16.56	16.95	17.49	17.89	19.05	16.17	16.56	17.10	17.50	18.65
	12H	16.70	17.04	17.64	17.98	19.19	16.29	16.63	17.23	17.57	18.77
12H	4H	15.69	16.16	16.60	17.09	18.23	15.32	15.79	16.23	16.72	17.87
	6H	16.37	16.76	17.30	17.70	18.85	16.00	16.38	16.93	17.32	18.48
	8H	16.62	16.96	17.56	17.89	19.10	16.24	16.58	17.18	17.51	18.72