

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925711

Luminaire Tested: DFN2DIP-SQ3F0-110D090US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925711
REPORT IS A COMBINATION OF REPORTS P901486 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D090US950-RLLONL
Description: 3 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17420.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 180.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925711
CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P925711

CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44	44	44	44
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42	38	38	38	38
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37	33	33	33	33
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32	28	28	28	28
5	70	58	51	45	64	54	48	42	47	42	37	40	36	33	34	31	28	25	25	25	25
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25	22	22	22	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20	20	20	20
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20	18	18	18	18
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18	16	16	16	16
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4970	4970	4970
5°	4974	4887	4920
10°	4922	4788	4759
15°	4851	4627	4510
20°	4758	4406	4205
25°	4663	4158	3910
30°	4537	3905	3537
35°	4412	3633	3210
40°	4286	3352	2834
45°	4139	3040	2494
50°	3987	2726	2162
55°	3828	2390	1843
60°	3644	2040	1516
65°	3431	1685	1362
70°	3174	1353	1230
75°	2850	1186	1116
80°	2381	984	963
85°	1615	641	713

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4139 cd/sqm



TEST NUMBER: P925711

CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.5	2.3
10°-20°	1115.9	6.4
20°-30°	1566.7	9.0
30°-40°	1707.7	9.8
40°-50°	1569.6	9.0
50°-60°	1232.7	7.1
60°-70°	802.4	4.6
70°-80°	413.0	2.4
80°-90°	110.5	0.6
90°-100°	95.6	0.5
100°-110°	356.2	2.0
110°-120°	944.7	5.4
120°-130°	1566.8	9.0
130°-140°	1664.3	9.6
140°-150°	1546.8	8.9
150°-160°	1243.6	7.1
160°-170°	801.3	4.6
170°-180°	275.8	1.6
0°-30°	3089.0	17.7
0°-40°	4796.8	27.5
0°-60°	7599.1	43.6
0°-90°	8925.0	51.2
90°-120°	1396.4	8.0
90°-150°	6174.3	35.4
90°-180°	8495.0	48.8
0°-180°	17420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4337	4337	4337	4337	4337	
5°	4337	4318	4266	4302	4290	411
15°	4125	4082	3949	3874	3835	1162
25°	3744	3619	3360	3199	3140	1722
35°	3226	3026	2681	2434	2347	2019
45°	2638	2374	1963	1684	1590	2037
55°	2006	1700	1276	1040	966	1792
65°	1354	1036	683	550	538	1343
75°	722	447	314	286	283	764
85°	169	86	74	74	74	194
90°	2	25	42	53	56	16
95°	136	67	82	92	90	161
105°	637	700	128	151	159	681
115°	1206	1241	1294	323	172	1187
125°	1704	1732	1772	1786	1793	1520
135°	2109	2143	2162	2183	2179	1629
145°	2447	2445	2480	2495	2485	1530
155°	2694	2676	2701	2713	2696	1242
165°	2839	2826	2833	2847	2833	802
175°	2904	2889	2894	2908	2887	276
180°	2898	2898	2898	2898	2898	



TEST NUMBER: P925711

CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4337.2	4337.2	4337.2	4337.2	4337.2
2.5°	4356.7	4337.2	4293.9	4333.4	4325.5
5°	4337.2	4317.6	4266.4	4301.8	4290.1
7.5°	4301.8	4278.4	4223.5	4238.9	4219.3
10°	4254.7	4227.2	4148.9	4136.8	4113.6
12.5°	4196.0	4160.6	4054.4	4031.0	3987.7
15°	4125.2	4081.9	3948.6	3874.1	3834.9
17.5°	4042.8	3979.9	3815.0	3728.7	3665.8
20°	3948.6	3869.9	3673.8	3575.9	3489.3
22.5°	3846.6	3756.2	3528.5	3395.2	3336.4
25°	3744.5	3618.8	3359.8	3199.0	3139.9
27.5°	3623.0	3489.3	3202.8	3018.3	2927.9
30°	3493.5	3344.0	3030.0	2830.0	2723.9
32.5°	3367.7	3186.9	2865.4	2629.8	2531.5
35°	3226.5	3026.2	2681.0	2433.7	2347.0
37.5°	3089.1	2873.0	2508.2	2237.0	2139.2
40°	2943.8	2708.5	2327.5	2048.8	1946.8
42.5°	2794.6	2543.6	2147.2	1856.5	1758.6
45°	2637.7	2374.5	1962.7	1683.6	1589.6
47.5°	2488.6	2210.0	1786.1	1507.0	1420.9
50°	2323.7	2045.1	1613.3	1342.2	1260.1
52.5°	2162.5	1868.1	1448.4	1189.4	1114.7
55°	2005.5	1699.5	1275.5	1040.2	965.7
57.5°	1844.8	1530.8	1122.7	902.9	839.9
60°	1679.9	1365.9	961.5	761.7	698.8
62.5°	1519.1	1205.2	824.2	635.9	604.6
65°	1354.2	1036.0	683.0	549.7	537.6
67.5°	1197.3	879.1	549.7	482.6	471.0
70°	1032.3	726.3	455.2	416.0	400.2
72.5°	875.3	584.7	380.6	349.4	341.4
75°	722.1	447.2	314.0	286.5	282.8
77.5°	569.3	317.8	247.4	231.5	223.6
80°	427.7	227.8	188.2	172.9	172.9
82.5°	298.1	153.2	129.6	121.6	121.6
85°	168.7	86.2	74.5	74.5	74.5
87.5°	62.9	31.2	31.2	27.5	27.5
90°	2.0	25.2	41.8	52.6	56.5
92.5°	52.6	44.1	50.3	54.6	56.5
95°	136.2	67.0	81.7	92.3	90.2
97.5°	245.3	73.5	106.8	113.2	115.2
100°	371.2	84.0	119.5	136.2	140.4
102.5°	509.4	505.4	123.7	146.6	153.1
105°	637.4	700.4	127.9	150.9	159.3
107.5°	786.3	838.6	132.2	155.1	163.6
110°	928.9	972.8	367.0	157.3	165.6



TEST NUMBER: P925711

CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1063.1	1100.7	1065.1	161.3	167.8
115°	1205.6	1241.2	1293.7	322.9	172.0
117.5°	1329.3	1371.2	1407.0	1107.0	557.7
120°	1467.7	1499.1	1537.0	1562.1	1279.0
122.5°	1585.1	1618.7	1660.7	1673.1	1675.4
125°	1704.5	1731.9	1771.8	1786.5	1792.7
127.5°	1813.6	1842.9	1874.6	1895.5	1897.5
130°	1916.4	1950.1	1973.0	1996.1	1994.1
132.5°	2021.2	2048.6	2071.5	2090.5	2088.5
135°	2109.4	2143.0	2161.7	2182.8	2178.6
137.5°	2201.5	2226.6	2247.8	2268.7	2262.5
140°	2291.6	2308.6	2331.5	2350.4	2340.0
142.5°	2367.4	2382.0	2409.1	2425.8	2415.4
145°	2447.0	2444.7	2480.4	2495.1	2484.6
147.5°	2516.0	2509.8	2545.4	2555.9	2547.6
150°	2583.2	2568.5	2602.1	2614.5	2604.1
152.5°	2639.7	2623.0	2654.4	2667.1	2652.4
155°	2694.3	2675.6	2700.7	2713.2	2696.5
157.5°	2738.4	2721.7	2740.6	2755.2	2738.4
160°	2776.1	2763.5	2776.1	2788.6	2773.9
162.5°	2809.5	2797.0	2807.5	2822.2	2803.3
165°	2838.9	2826.4	2832.7	2847.4	2832.7
167.5°	2862.1	2849.4	2855.8	2870.5	2851.6
170°	2881.0	2868.3	2872.5	2887.2	2868.3
172.5°	2893.5	2881.0	2885.2	2899.9	2881.0
175°	2903.9	2889.2	2893.5	2908.1	2887.2
177.5°	2908.1	2893.5	2895.7	2910.4	2891.5
180°	2897.7	2897.7	2897.7	2897.7	2897.7



TEST NUMBER: P925711
 CATALOG NUMBER: DFN2DIP-SQ3F0-110D090US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.80	13.64	13.75	14.60	15.86	8.76	9.60	9.71	10.56	11.82
	3H	14.47	15.22	15.44	16.20	17.48	9.94	10.69	10.91	11.67	12.95
	4H	15.08	15.79	16.06	16.77	18.05	10.39	11.10	11.37	12.08	13.36
	6H	15.50	16.15	16.49	17.13	18.43	10.70	11.36	11.69	12.34	13.64
	8H	15.62	16.24	16.62	17.24	18.54	10.79	11.41	11.79	12.41	13.71
	12H	15.68	16.27	16.68	17.27	18.59	10.83	11.42	11.83	12.42	13.74
4H	2H	12.82	13.53	13.80	14.50	15.79	9.35	10.06	10.34	11.04	12.33
	3H	14.64	15.23	15.63	16.24	17.54	10.70	11.29	11.69	12.29	13.60
	4H	15.33	15.87	16.33	16.87	18.19	11.24	11.78	12.24	12.78	14.10
	6H	15.84	16.30	16.85	17.33	18.65	11.65	12.12	12.67	13.14	14.46
	8H	16.01	16.45	17.03	17.46	18.80	11.78	12.21	12.79	13.23	14.56
	12H	16.11	16.50	17.14	17.53	18.87	11.84	12.23	12.87	13.26	14.60
8H	4H	15.30	15.73	16.31	16.75	18.08	11.52	11.95	12.53	12.97	14.30
	6H	15.86	16.21	16.90	17.27	18.61	12.03	12.39	13.07	13.44	14.78
	8H	16.07	16.39	17.12	17.43	18.78	12.22	12.53	13.26	13.57	14.93
	12H	16.21	16.48	17.26	17.52	18.92	12.33	12.61	13.38	13.64	15.04
12H	4H	15.25	15.64	16.28	16.67	18.01	11.52	11.91	12.56	12.95	14.29
	6H	15.83	16.15	16.88	17.19	18.55	12.08	12.39	13.12	13.44	14.79
	8H	16.05	16.33	17.10	17.37	18.76	12.28	12.56	13.33	13.60	14.99