

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P925721

Luminaire Tested: DFN2DIP-SQ3F0-110D120US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P925721
REPORT IS A COMBINATION OF REPORTS P901539 AND P898289
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ3F0-110D120US950-FLLONL
Description: 3 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21722.6 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.06' x L: 3.06' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 206
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	67	59	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4679	4679	4679
5°	4683	4610	4643
10°	4642	4545	4579
15°	4571	4467	4479
20°	4476	4360	4377
25°	4381	4233	4259
30°	4263	4114	4110
35°	4151	3974	3952
40°	4013	3833	3801
45°	3876	3691	3648
50°	3725	3542	3470
55°	3568	3370	3305
60°	3389	3166	3117
65°	3194	2955	2895
70°	2946	2696	2656
75°	2602	2386	2433
80°	2188	1991	2011
85°	1540	1319	1317

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3876 cd/sqm

TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	384.3	1.8
10°-20°	1081.3	5.0
20°-30°	1589.1	7.3
30°-40°	1845.7	8.5
40°-50°	1843.4	8.5
50°-60°	1607.4	7.4
60°-70°	1188.2	5.5
70°-80°	672.3	3.1
80°-90°	184.2	0.8
90°-100°	127.4	0.6
100°-110°	474.9	2.2
110°-120°	1259.5	5.8
120°-130°	2089.1	9.6
130°-140°	2219.1	10.2
140°-150°	2062.4	9.5
150°-160°	1658.1	7.6
160°-170°	1068.4	4.9
170°-180°	367.7	1.7
0°-30°	3054.8	14.1
0°-40°	4900.4	22.6
0°-60°	8351.2	38.4
0°-90°	10395.9	47.9
90°-120°	1861.9	8.6
90°-150°	8232.4	37.9
90°-180°	11327.0	52.1
0°-180°	21722.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4083	4083	4083	4083	4083	
5°	4083	4068	4024	4056	4048	388
15°	3887	3864	3812	3828	3809	1095
25°	3518	3487	3420	3428	3420	1619
35°	3035	2996	2933	2909	2890	1895
45°	2470	2442	2383	2340	2324	1906
55°	1869	1845	1798	1751	1732	1671
65°	1260	1237	1198	1162	1143	1246
75°	659	652	632	609	617	704
85°	161	157	153	141	138	179
90°	3	34	56	70	75	20
95°	182	89	109	123	120	215
105°	850	934	171	201	212	908
115°	1607	1655	1725	430	229	1582
125°	2273	2309	2362	2382	2390	2027
135°	2812	2857	2882	2910	2905	2173
145°	3263	3260	3307	3327	3313	2041
155°	3592	3567	3601	3618	3595	1655
165°	3785	3769	3777	3796	3777	1069
175°	3872	3852	3858	3878	3850	368
180°	3864	3864	3864	3864	3864	

TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4083.3	4083.3	4083.3	4083.3	4083.3
2.5°	4107.0	4087.4	4044.1	4083.3	4075.8
5°	4083.3	4067.9	4024.5	4055.7	4048.3
7.5°	4055.7	4032.5	3989.2	4020.8	4012.9
10°	4012.9	3985.3	3938.3	3969.5	3957.9
12.5°	3953.8	3930.4	3883.4	3902.9	3895.0
15°	3887.1	3863.7	3812.5	3828.3	3808.7
17.5°	3804.6	3781.3	3730.0	3749.6	3730.0
20°	3714.2	3690.8	3635.9	3647.5	3632.2
22.5°	3624.2	3588.8	3537.5	3537.5	3529.6
25°	3518.0	3486.8	3420.1	3427.6	3420.1
27.5°	3400.1	3372.6	3321.7	3310.1	3290.5
30°	3282.6	3250.9	3192.2	3180.5	3164.7
32.5°	3156.8	3133.5	3070.5	3046.8	3031.0
35°	3035.2	2996.0	2933.1	2909.3	2889.8
37.5°	2897.7	2862.3	2799.4	2771.8	2752.3
40°	2756.5	2724.8	2661.9	2626.9	2611.1
42.5°	2619.0	2587.3	2524.9	2485.3	2462.0
45°	2469.9	2442.3	2383.2	2340.4	2324.5
47.5°	2324.5	2297.0	2234.1	2190.8	2167.4
50°	2171.2	2151.7	2096.6	2041.7	2022.1
52.5°	2022.1	1994.5	1943.8	1900.4	1872.9
55°	1869.2	1845.4	1798.4	1751.3	1731.7
57.5°	1715.9	1696.3	1645.1	1597.9	1582.1
60°	1562.6	1547.2	1492.2	1448.8	1437.2
62.5°	1413.4	1386.0	1346.8	1307.6	1291.8
65°	1260.5	1236.8	1197.7	1162.3	1142.7
67.5°	1103.5	1083.6	1048.5	1021.1	1005.2
70°	958.1	942.3	906.9	879.4	863.9
72.5°	809.0	793.2	773.6	746.1	734.4
75°	659.4	652.0	631.9	608.7	616.6
77.5°	526.1	510.3	502.4	490.7	479.1
80°	392.9	388.7	380.7	369.1	361.2
82.5°	267.0	267.0	263.3	247.5	247.5
85°	160.8	157.0	153.3	141.2	137.5
87.5°	70.8	62.9	55.0	43.3	39.1
90°	2.7	33.5	55.8	70.0	75.4
92.5°	70.0	58.8	67.1	72.7	75.4
95°	181.5	89.3	108.9	123.2	120.2
97.5°	327.0	98.0	142.4	151.0	153.7
100°	494.9	111.9	159.3	181.5	187.3
102.5°	679.2	673.9	164.9	195.6	204.2
105°	849.8	933.9	170.7	201.2	212.5
107.5°	1048.4	1118.1	176.3	206.8	218.1
110°	1238.6	1297.1	489.3	209.8	220.8

TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1417.5	1467.6	1420.2	215.1	223.7
115°	1607.4	1654.9	1724.9	430.5	229.4
117.5°	1772.4	1828.2	1876.0	1475.9	743.6
120°	1957.0	1998.8	2049.3	2082.9	1705.4
122.5°	2113.4	2158.2	2214.3	2230.9	2233.9
125°	2272.7	2309.3	2362.4	2381.9	2390.2
127.5°	2418.1	2457.3	2499.5	2527.3	2530.0
130°	2555.2	2600.0	2630.6	2661.5	2658.8
132.5°	2695.0	2731.5	2762.0	2787.3	2784.6
135°	2812.5	2857.3	2882.2	2910.5	2904.8
137.5°	2935.4	2968.8	2997.1	3024.9	3016.6
140°	3055.6	3078.1	3108.6	3133.9	3120.0
142.5°	3156.4	3176.1	3212.2	3234.4	3220.5
145°	3262.7	3259.7	3307.1	3326.8	3312.8
147.5°	3354.6	3346.3	3393.9	3407.8	3396.8
150°	3444.2	3424.7	3469.5	3486.1	3472.2
152.5°	3519.6	3497.4	3539.2	3556.1	3536.6
155°	3592.3	3567.4	3601.0	3617.6	3595.3
157.5°	3651.1	3628.8	3654.1	3673.7	3651.1
160°	3701.5	3684.6	3701.5	3718.1	3698.6
162.5°	3746.1	3729.5	3743.4	3763.0	3737.8
165°	3785.2	3768.6	3776.9	3796.5	3776.9
167.5°	3816.1	3799.1	3807.8	3827.4	3802.2
170°	3841.3	3824.4	3830.0	3849.6	3824.4
172.5°	3857.9	3841.3	3847.0	3866.6	3841.3
175°	3871.8	3852.3	3857.9	3877.5	3849.6
177.5°	3877.5	3857.9	3860.9	3880.5	3855.3
180°	3863.6	3863.6	3863.6	3863.6	3863.6

TEST NUMBER: P925721

CATALOG NUMBER: DFN2DIP-SQ3F0-110D120US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.40	13.24	13.37	14.23	15.53	11.95	12.79	12.93	13.78	15.09
	3H	14.05	14.81	15.04	15.81	17.13	13.56	14.32	14.55	15.31	16.64
	4H	14.64	15.35	15.63	16.35	17.68	14.14	14.86	15.14	15.86	17.19
	6H	15.03	15.69	16.04	16.70	18.04	14.53	15.19	15.54	16.20	17.54
	8H	15.13	15.76	16.15	16.78	18.12	14.63	15.26	15.65	16.28	17.62
	12H	15.18	15.78	16.20	16.79	18.16	14.67	15.27	15.69	16.28	17.65
4H	2H	12.85	13.57	13.86	14.57	15.90	12.50	13.21	13.50	14.21	15.54
	3H	14.71	15.31	15.73	16.34	17.68	14.30	14.90	15.32	15.93	17.28
	4H	15.42	15.97	16.44	16.99	18.36	15.00	15.54	16.02	16.57	17.93
	6H	15.93	16.40	16.96	17.45	18.81	15.50	15.97	16.53	17.01	18.38
	8H	16.08	16.52	17.11	17.56	18.93	15.64	16.08	16.67	17.12	18.50
	12H	16.15	16.54	17.20	17.60	18.98	15.70	16.10	16.75	17.15	18.53
8H	4H	15.61	16.05	16.65	17.09	18.47	15.23	15.67	16.27	16.71	18.09
	6H	16.24	16.60	17.29	17.68	19.06	15.85	16.22	16.91	17.30	18.67
	8H	16.45	16.77	17.52	17.84	19.23	16.06	16.38	17.13	17.45	18.84
	12H	16.58	16.86	17.65	17.92	19.36	16.17	16.45	17.24	17.51	18.95
12H	4H	15.60	15.99	16.65	17.05	18.43	15.23	15.62	16.28	16.68	18.06
	6H	16.26	16.58	17.33	17.65	19.04	15.89	16.21	16.96	17.28	18.67
	8H	16.50	16.78	17.57	17.84	19.28	16.12	16.40	17.19	17.46	18.90