

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909647

Luminaire Tested: DFN2DIP-SQ4F0-140D060US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909647
REPORT IS A COMBINATION OF REPORTS P901594 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D060US840-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18016.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 189
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4100	4100	4100
5°	4107	4036	4062
10°	4066	3957	3931
15°	4010	3827	3728
20°	3936	3648	3478
25°	3860	3446	3237
30°	3758	3240	2930
35°	3658	3018	2661
40°	3557	2788	2352
45°	3439	2532	2072
50°	3316	2275	1799
55°	3189	1999	1536
60°	3042	1711	1265
65°	2872	1418	1140
70°	2666	1144	1034
75°	2408	1011	943
80°	2034	851	822
85°	1416	572	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3439 cd/sqm

TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.6	3.0
10°-20°	1503.4	8.3
20°-30°	2110.7	11.7
30°-40°	2300.8	12.8
40°-50°	2114.7	11.7
50°-60°	1660.7	9.2
60°-70°	1081.0	6.0
70°-80°	556.5	3.1
80°-90°	145.7	0.8
90°-100°	67.4	0.4
100°-110°	251.4	1.4
110°-120°	666.7	3.7
120°-130°	1105.7	6.1
130°-140°	1174.5	6.5
140°-150°	1091.6	6.1
150°-160°	877.6	4.9
160°-170°	565.5	3.1
170°-180°	194.6	1.1
0°-30°	4161.7	23.1
0°-40°	6462.5	35.9
0°-60°	10237.9	56.8
0°-90°	12021.0	66.7
90°-120°	985.5	5.5
90°-150°	4357.2	24.2
90°-180°	5995.0	33.3
0°-180°	18016.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5843	5843	5843	5843	5843	
5°	5843	5817	5748	5796	5780	554
15°	5558	5499	5320	5219	5167	1566
25°	5045	4875	4526	4310	4230	2320
35°	4347	4077	3612	3279	3162	2721
45°	3554	3199	2644	2268	2142	2744
55°	2702	2290	1718	1402	1301	2414
65°	1824	1396	920	740	724	1809
75°	973	603	423	386	381	1029
85°	227	116	100	100	100	261
90°	1	18	30	37	40	17
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1489	1512	1526	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2004	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2038	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5843.3	5843.3	5843.3	5843.3	5843.3
2.5°	5869.6	5843.3	5784.9	5838.2	5827.5
5°	5843.3	5816.9	5747.9	5795.6	5779.9
7.5°	5795.6	5764.1	5690.1	5710.9	5684.5
10°	5732.2	5695.1	5589.7	5573.3	5541.9
12.5°	5653.0	5605.4	5462.3	5430.9	5372.6
15°	5557.7	5499.3	5319.8	5219.4	5166.7
17.5°	5446.6	5361.9	5139.7	5023.6	4938.8
20°	5319.8	5213.7	4949.6	4817.7	4701.0
22.5°	5182.3	5060.6	4753.7	4574.2	4495.1
25°	5044.9	4875.4	4526.5	4309.9	4230.2
27.5°	4881.1	4701.0	4315.0	4066.4	3944.7
30°	4706.6	4505.2	4082.2	3812.8	3669.8
32.5°	4537.1	4293.6	3860.5	3543.0	3410.6
35°	4347.0	4077.1	3612.0	3278.7	3162.0
37.5°	4161.9	3870.6	3379.1	3013.9	2882.1
40°	3966.0	3649.0	3135.6	2760.4	2622.9
42.5°	3765.2	3426.9	2892.8	2501.1	2369.2
45°	3553.6	3199.1	2644.2	2268.3	2141.5
47.5°	3352.8	2977.5	2406.3	2030.4	1914.3
50°	3130.6	2755.3	2173.4	1808.3	1697.7
52.5°	2913.5	2516.8	1951.3	1602.4	1501.9
55°	2702.0	2289.6	1718.5	1401.5	1301.0
57.5°	2485.4	2062.3	1512.6	1216.4	1131.7
60°	2263.2	1840.2	1295.5	1026.1	941.4
62.5°	2046.7	1623.7	1110.3	856.7	814.7
65°	1824.5	1395.8	920.1	740.5	724.3
67.5°	1613.0	1184.4	740.5	650.3	634.5
70°	1390.8	978.5	613.2	560.5	539.2
72.5°	1179.3	787.7	512.8	470.7	460.1
75°	972.8	602.6	423.0	386.0	380.9
77.5°	767.0	428.1	333.3	311.9	301.2
80°	576.2	306.9	253.6	232.9	232.9
82.5°	401.7	206.4	174.5	163.8	163.8
85°	227.2	116.1	100.4	100.4	100.4
87.5°	84.7	42.1	42.1	37.1	37.1
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	262.0	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.4	103.5	108.1
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.8	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.8	751.6	113.8	118.5
115°	850.8	876.0	913.0	227.9	121.4
117.5°	938.1	967.7	992.9	781.2	393.5
120°	1035.8	1057.9	1084.7	1102.4	902.6
122.5°	1118.5	1142.3	1171.9	1180.7	1182.4
125°	1203.0	1222.2	1250.3	1260.7	1265.1
127.5°	1279.9	1300.6	1322.9	1337.7	1339.1
130°	1352.4	1376.1	1392.3	1408.7	1407.2
132.5°	1426.4	1445.7	1461.9	1475.2	1473.8
135°	1488.6	1512.4	1525.5	1540.4	1537.4
137.5°	1553.6	1571.4	1586.3	1601.0	1596.7
140°	1617.2	1629.2	1645.4	1658.7	1651.3
142.5°	1670.6	1681.0	1700.2	1711.9	1704.6
145°	1726.9	1725.3	1750.4	1760.8	1753.4
147.5°	1775.5	1771.1	1796.2	1803.6	1797.9
150°	1823.0	1812.6	1836.3	1845.1	1837.8
152.5°	1862.9	1851.1	1873.2	1882.2	1871.8
155°	1901.4	1888.1	1905.9	1914.7	1902.9
157.5°	1932.5	1920.7	1934.0	1944.4	1932.5
160°	1959.1	1950.2	1959.1	1967.9	1957.6
162.5°	1982.7	1973.9	1981.3	1991.7	1978.3
165°	2003.5	1994.7	1999.0	2009.4	1999.0
167.5°	2019.7	2010.8	2015.4	2025.8	2012.4
170°	2033.2	2024.2	2027.2	2037.5	2024.2
172.5°	2041.9	2033.2	2036.1	2046.5	2033.2
175°	2049.3	2038.9	2041.9	2052.2	2037.5
177.5°	2052.2	2041.9	2043.5	2053.9	2040.5
180°	2044.9	2044.9	2044.9	2044.9	2044.9

TEST NUMBER: P909647

CATALOG NUMBER: DFN2DIP-SQ4F0-140D060US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.50	14.48	14.30	15.31	16.32	9.46	10.45	10.26	11.27	12.28
	3H	15.19	16.07	16.01	16.91	17.95	10.66	11.54	11.48	12.38	13.42
	4H	15.81	16.64	16.65	17.48	18.54	11.12	11.95	11.95	12.79	13.84
	6H	16.24	17.01	17.09	17.86	18.93	11.45	12.21	12.30	13.06	14.13
	8H	16.38	17.11	17.23	17.97	19.04	11.54	12.27	12.40	13.14	14.21
	12H	16.44	17.14	17.31	18.00	19.09	11.59	12.29	12.45	13.15	14.24
4H	2H	13.53	14.37	14.38	15.21	16.26	10.07	10.91	10.92	11.75	12.80
	3H	15.38	16.07	16.23	16.95	18.02	11.44	12.13	12.29	13.01	14.08
	4H	16.08	16.71	16.95	17.58	18.68	12.00	12.62	12.86	13.50	14.59
	6H	16.61	17.15	17.49	18.05	19.15	12.42	12.97	13.30	13.86	14.96
	8H	16.79	17.30	17.68	18.19	19.30	12.56	13.06	13.44	13.95	15.06
	12H	16.90	17.35	17.80	18.26	19.38	12.63	13.08	13.53	13.99	15.11
8H	4H	16.06	16.57	16.95	17.46	18.57	12.29	12.80	13.17	13.69	14.80
	6H	16.64	17.06	17.55	17.99	19.10	12.81	13.23	13.73	14.17	15.28
	8H	16.86	17.23	17.78	18.16	19.29	13.01	13.38	13.93	14.30	15.43
	12H	17.01	17.34	17.93	18.25	19.43	13.13	13.46	14.06	14.38	15.56
12H	4H	16.02	16.48	16.93	17.39	18.51	12.30	12.76	13.20	13.67	14.78
	6H	16.62	16.99	17.54	17.91	19.04	12.87	13.24	13.79	14.16	15.29
	8H	16.85	17.17	17.77	18.09	19.27	13.08	13.41	14.01	14.33	15.51

END OF REPORT