

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909658

Luminaire Tested: DFN2DIP-SQ4F0-140D090US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909658
REPORT IS A COMBINATION OF REPORTS P900128 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D090US840-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20061.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 210.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	50	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	36
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	31	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	28	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4100	4100	4100
5°	4107	4036	4062
10°	4066	3957	3931
15°	4010	3827	3728
20°	3936	3648	3478
25°	3860	3446	3237
30°	3758	3240	2930
35°	3658	3018	2661
40°	3557	2788	2352
45°	3439	2532	2072
50°	3316	2275	1799
55°	3189	1999	1536
60°	3042	1711	1265
65°	2872	1418	1140
70°	2666	1144	1034
75°	2408	1011	943
80°	2034	851	822
85°	1416	572	626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3439 cd/sqm

TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.6	2.7
10°-20°	1503.4	7.5
20°-30°	2110.7	10.5
30°-40°	2300.8	11.5
40°-50°	2114.7	10.5
50°-60°	1660.7	8.3
60°-70°	1081.0	5.4
70°-80°	556.5	2.8
80°-90°	150.2	0.7
90°-100°	177.9	0.9
100°-110°	565.2	2.8
110°-120°	967.2	4.8
120°-130°	1272.0	6.3
130°-140°	1427.7	7.1
140°-150°	1400.0	7.0
150°-160°	1174.4	5.9
160°-170°	778.9	3.9
170°-180°	272.2	1.4
0°-30°	4161.7	20.7
0°-40°	6462.5	32.2
0°-60°	10237.9	51.0
0°-90°	12025.6	59.9
90°-120°	1710.2	8.5
90°-150°	5809.9	29.0
90°-180°	8035.0	40.1
0°-180°	20061.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5843	5843	5843	5843	5843	
5°	5843	5817	5748	5796	5780	554
15°	5558	5499	5320	5219	5167	1566
25°	5045	4875	4526	4310	4230	2320
35°	4347	4077	3612	3279	3162	2721
45°	3554	3199	2644	2268	2142	2744
55°	2702	2290	1718	1402	1301	2414
65°	1824	1396	920	740	724	1809
75°	973	603	423	386	381	1029
85°	227	116	100	100	100	261
90°	3	31	85	80	82	20
95°	126	151	155	155	151	141
105°	522	529	534	538	538	551
115°	971	984	980	978	971	960
125°	1412	1433	1426	1419	1416	1261
135°	1826	1853	1858	1855	1848	1411
145°	2217	2234	2248	2250	2241	1385
155°	2535	2542	2550	2562	2554	1167
165°	2757	2755	2755	2772	2760	778
175°	2869	2862	2857	2874	2860	273
180°	2874	2874	2874	2874	2874	

TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5843.3	5843.3	5843.3	5843.3	5843.3
2.5°	5869.6	5843.3	5784.9	5838.2	5827.5
5°	5843.3	5816.9	5747.9	5795.6	5779.9
7.5°	5795.6	5764.1	5690.1	5710.9	5684.5
10°	5732.2	5695.1	5589.7	5573.3	5541.9
12.5°	5653.0	5605.4	5462.3	5430.9	5372.6
15°	5557.7	5499.3	5319.8	5219.4	5166.7
17.5°	5446.6	5361.9	5139.7	5023.6	4938.8
20°	5319.8	5213.7	4949.6	4817.7	4701.0
22.5°	5182.3	5060.6	4753.7	4574.2	4495.1
25°	5044.9	4875.4	4526.5	4309.9	4230.2
27.5°	4881.1	4701.0	4315.0	4066.4	3944.7
30°	4706.6	4505.2	4082.2	3812.8	3669.8
32.5°	4537.1	4293.6	3860.5	3543.0	3410.6
35°	4347.0	4077.1	3612.0	3278.7	3162.0
37.5°	4161.9	3870.6	3379.1	3013.9	2882.1
40°	3966.0	3649.0	3135.6	2760.4	2622.9
42.5°	3765.2	3426.9	2892.8	2501.1	2369.2
45°	3553.6	3199.1	2644.2	2268.3	2141.5
47.5°	3352.8	2977.5	2406.3	2030.4	1914.3
50°	3130.6	2755.3	2173.4	1808.3	1697.7
52.5°	2913.5	2516.8	1951.3	1602.4	1501.9
55°	2702.0	2289.6	1718.5	1401.5	1301.0
57.5°	2485.4	2062.3	1512.6	1216.4	1131.7
60°	2263.2	1840.2	1295.5	1026.1	941.4
62.5°	2046.7	1623.7	1110.3	856.7	814.7
65°	1824.5	1395.8	920.1	740.5	724.3
67.5°	1613.0	1184.4	740.5	650.3	634.5
70°	1390.8	978.5	613.2	560.5	539.2
72.5°	1179.3	787.7	512.8	470.7	460.1
75°	972.8	602.6	423.0	386.0	380.9
77.5°	767.0	428.1	333.3	311.9	301.2
80°	576.2	306.9	253.6	232.9	232.9
82.5°	401.7	206.4	174.5	163.8	163.8
85°	227.2	116.1	100.4	100.4	100.4
87.5°	84.7	42.1	42.1	37.1	37.1
90°	2.6	31.2	84.9	79.7	82.3
92.5°	53.7	72.8	75.4	78.0	78.0
95°	126.5	150.8	155.1	155.1	150.8
97.5°	210.6	233.1	242.7	242.7	242.7
100°	307.6	327.6	334.5	334.5	331.9
102.5°	409.9	424.6	434.1	436.8	434.1
105°	521.7	528.6	533.8	538.2	538.2
107.5°	632.6	643.0	643.0	644.7	632.6
110°	740.0	754.0	754.0	754.0	747.0

TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	856.2	870.9	868.3	861.4	856.2
115°	970.6	984.4	980.1	977.5	970.6
117.5°	1084.1	1103.2	1091.1	1084.1	1077.1
120°	1198.5	1217.5	1198.5	1198.5	1190.6
122.5°	1302.4	1326.8	1314.6	1307.7	1302.4
125°	1411.7	1433.3	1426.4	1418.6	1416.0
127.5°	1518.2	1545.1	1535.6	1525.2	1518.2
130°	1617.9	1649.1	1644.8	1639.5	1630.0
132.5°	1729.7	1753.9	1755.7	1743.5	1736.7
135°	1825.8	1852.7	1858.0	1855.3	1848.5
137.5°	1933.3	1955.0	1959.3	1957.6	1947.2
140°	2027.8	2049.4	2061.5	2061.5	2052.0
142.5°	2124.9	2146.5	2153.4	2156.1	2146.5
145°	2216.8	2234.0	2247.9	2250.5	2241.0
147.5°	2299.1	2320.7	2331.1	2335.4	2325.9
150°	2384.0	2398.7	2408.2	2416.0	2408.2
152.5°	2459.3	2474.1	2486.2	2495.8	2486.2
155°	2534.8	2541.6	2549.5	2561.6	2553.8
157.5°	2599.7	2604.9	2609.3	2626.6	2614.4
160°	2657.8	2663.0	2665.6	2680.3	2669.9
162.5°	2711.5	2711.5	2714.1	2730.6	2718.5
165°	2757.4	2754.8	2754.8	2772.2	2760.1
167.5°	2799.0	2791.3	2791.3	2808.5	2796.4
170°	2830.2	2823.3	2820.8	2838.0	2823.3
172.5°	2851.9	2845.0	2842.4	2859.7	2845.0
175°	2869.2	2862.3	2857.1	2874.5	2859.7
177.5°	2878.7	2871.9	2866.6	2881.3	2866.6
180°	2874.5	2874.5	2874.5	2874.5	2874.5

TEST NUMBER: P909658

CATALOG NUMBER: DFN2DIP-SQ4F0-140D090US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.94	13.86	13.82	14.75	15.87	8.90	9.82	9.78	10.71	11.84
	3H	14.63	15.45	15.52	16.35	17.50	10.10	10.92	10.99	11.82	12.97
	4H	15.25	16.02	16.15	16.93	18.09	10.55	11.33	11.46	12.23	13.40
	6H	15.68	16.39	16.59	17.30	18.48	10.88	11.59	11.79	12.51	13.68
	8H	15.81	16.49	16.73	17.42	18.59	10.97	11.65	11.89	12.58	13.75
	12H	15.87	16.52	16.80	17.44	18.64	11.02	11.67	11.95	12.59	13.79
4H	2H	12.97	13.75	13.88	14.65	15.81	9.51	10.29	10.42	11.19	12.35
	3H	14.81	15.46	15.73	16.39	17.57	10.87	11.51	11.79	12.45	13.63
	4H	15.51	16.10	16.44	17.03	18.23	11.42	12.01	12.35	12.94	14.14
	6H	16.04	16.54	16.98	17.50	18.70	11.85	12.35	12.79	13.31	14.51
	8H	16.22	16.69	17.16	17.64	18.85	11.98	12.45	12.92	13.40	14.61
	12H	16.32	16.74	17.28	17.71	18.93	12.05	12.47	13.01	13.44	14.66
8H	4H	15.49	15.96	16.43	16.91	18.12	11.71	12.18	12.66	13.13	14.35
	6H	16.06	16.45	17.03	17.44	18.66	12.23	12.62	13.20	13.62	14.83
	8H	16.28	16.62	17.26	17.61	18.84	12.43	12.77	13.41	13.75	14.98
	12H	16.43	16.73	17.41	17.70	18.98	12.55	12.85	13.53	13.83	15.11
12H	4H	15.44	15.87	16.41	16.83	18.05	11.72	12.15	12.68	13.11	14.33
	6H	16.04	16.38	17.02	17.36	18.59	12.29	12.63	13.26	13.61	14.84
	8H	16.26	16.57	17.25	17.54	18.82	12.50	12.80	13.48	13.78	15.06