

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909672

Luminaire Tested: DFN2DIP-SQ4F0-140D140US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909672
REPORT IS A COMBINATION OF REPORTS P900199 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D140US840-FLLFLL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 26509.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 249.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3860	3860	3860
5°	3866	3807	3833
10°	3835	3757	3782
15°	3778	3695	3702
20°	3702	3610	3620
25°	3626	3508	3525
30°	3531	3413	3404
35°	3441	3301	3276
40°	3330	3188	3155
45°	3220	3075	3030
50°	3099	2956	2886
55°	2972	2819	2754
60°	2829	2655	2602
65°	2673	2487	2423
70°	2475	2280	2231
75°	2199	2034	2056
80°	1868	1721	1718
85°	1350	1177	1154

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3520 cd/sqm

TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.8	2.0
10°-20°	1456.8	5.5
20°-30°	2141.0	8.1
30°-40°	2486.6	9.4
40°-50°	2483.5	9.4
50°-60°	2165.5	8.2
60°-70°	1600.8	6.0
70°-80°	905.7	3.4
80°-90°	251.8	0.9
90°-100°	276.7	1.0
100°-110°	879.1	3.3
110°-120°	1504.5	5.7
120°-130°	1978.6	7.5
130°-140°	2220.9	8.4
140°-150°	2177.8	8.2
150°-160°	1826.9	6.9
160°-170°	1211.6	4.6
170°-180°	423.5	1.6
0°-30°	4115.6	15.5
0°-40°	6602.1	24.9
0°-60°	11251.2	42.4
0°-90°	14009.4	52.8
90°-120°	2660.3	10.0
90°-150°	9037.6	34.1
90°-180°	12500.0	47.2
0°-180°	26509.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5501	5501	5501	5501	5501	
5°	5501	5480	5422	5464	5454	522
15°	5237	5206	5136	5158	5131	1475
25°	4740	4698	4608	4618	4608	2181
35°	4089	4036	3952	3920	3893	2554
45°	3328	3290	3211	3153	3132	2568
55°	2518	2486	2423	2359	2333	2251
65°	1698	1666	1614	1566	1539	1679
75°	888	878	851	820	831	948
85°	217	212	206	190	185	242
90°	4	49	132	124	128	26
95°	197	235	241	241	235	219
105°	812	822	830	837	837	856
115°	1510	1531	1525	1521	1510	1493
125°	2196	2230	2219	2207	2203	1962
135°	2840	2882	2890	2886	2875	2195
145°	3448	3475	3497	3501	3486	2154
155°	3943	3954	3966	3985	3973	1815
165°	4289	4285	4285	4312	4293	1210
175°	4463	4452	4444	4471	4448	424
180°	4471	4471	4471	4471	4471	

TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5501.2	5501.2	5501.2	5501.2	5501.2
2.5°	5533.2	5506.8	5448.4	5501.2	5491.1
5°	5501.2	5480.4	5422.1	5464.2	5454.1
7.5°	5464.2	5432.8	5374.4	5417.0	5406.3
10°	5406.3	5369.4	5305.9	5348.0	5332.3
12.5°	5326.6	5295.2	5231.8	5258.2	5247.6
15°	5236.9	5205.5	5136.4	5157.8	5131.3
17.5°	5125.8	5094.4	5025.3	5051.7	5025.3
20°	5004.0	4972.6	4898.5	4914.2	4893.4
22.5°	4882.7	4835.0	4766.0	4766.0	4755.4
25°	4739.6	4697.5	4607.7	4617.8	4607.7
27.5°	4580.8	4543.8	4475.3	4459.6	4433.2
30°	4422.5	4379.9	4300.7	4285.1	4263.7
32.5°	4253.0	4221.6	4136.8	4104.9	4083.5
35°	4089.1	4036.4	3951.6	3919.7	3893.2
37.5°	3903.9	3856.3	3771.4	3734.5	3708.0
40°	3713.7	3671.1	3586.2	3539.2	3517.8
42.5°	3528.5	3485.9	3401.6	3348.3	3316.9
45°	3327.5	3290.5	3210.9	3153.0	3131.7
47.5°	3131.7	3094.6	3009.9	2951.5	2920.1
50°	2925.2	2898.8	2824.7	2750.6	2724.2
52.5°	2724.2	2687.2	2618.7	2560.3	2523.4
55°	2518.3	2486.3	2422.9	2359.4	2333.1
57.5°	2311.7	2285.3	2216.4	2152.9	2131.5
60°	2105.2	2084.5	2010.3	1952.0	1936.2
62.5°	1904.3	1867.2	1814.4	1761.7	1740.4
65°	1698.3	1666.3	1613.6	1565.8	1539.4
67.5°	1486.7	1459.8	1412.6	1375.5	1354.2
70°	1290.8	1269.5	1221.8	1184.8	1164.0
72.5°	1089.9	1068.5	1042.2	1005.2	989.5
75°	888.5	878.4	851.4	820.0	830.6
77.5°	708.8	687.5	676.8	661.2	645.4
80°	529.3	523.6	513.0	497.3	486.6
82.5°	359.7	359.7	354.7	333.4	333.4
85°	216.6	211.6	206.5	190.3	185.2
87.5°	95.4	84.7	74.1	58.4	52.7
90°	4.0	48.6	132.1	124.0	128.1
92.5°	83.6	113.2	117.2	121.3	121.3
95°	196.8	234.6	241.3	241.3	234.6
97.5°	327.6	362.6	377.5	377.5	377.5
100°	478.6	509.6	520.3	520.3	516.2
102.5°	637.6	660.6	675.4	679.4	675.4
105°	811.5	822.3	830.4	837.1	837.1
107.5°	984.0	1000.3	1000.3	1002.9	984.0
110°	1151.2	1172.8	1172.8	1172.8	1162.0



TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1331.8	1354.7	1350.7	1339.9	1331.8
115°	1509.7	1531.4	1524.6	1520.6	1509.7
117.5°	1686.4	1716.1	1697.2	1686.4	1675.6
120°	1864.3	1894.0	1864.3	1864.3	1852.2
122.5°	2026.1	2063.8	2045.0	2034.2	2026.1
125°	2196.0	2229.6	2218.8	2206.7	2202.6
127.5°	2361.7	2403.5	2388.6	2372.5	2361.7
130°	2516.7	2565.3	2558.5	2550.4	2535.6
132.5°	2690.6	2728.4	2731.1	2712.2	2701.4
135°	2840.2	2882.1	2890.1	2886.1	2875.3
137.5°	3007.4	3041.1	3047.9	3045.1	3029.0
140°	3154.3	3188.0	3206.9	3206.9	3192.1
142.5°	3305.3	3339.0	3349.8	3353.9	3339.0
145°	3448.2	3475.1	3496.8	3500.8	3486.0
147.5°	3576.2	3610.0	3626.1	3632.9	3618.0
150°	3708.3	3731.3	3746.1	3758.2	3746.1
152.5°	3825.7	3848.6	3867.5	3882.2	3867.5
155°	3942.9	3953.7	3965.8	3984.7	3972.6
157.5°	4044.0	4052.1	4058.9	4085.8	4066.9
160°	4134.4	4142.5	4146.5	4169.4	4153.2
162.5°	4217.9	4217.9	4221.9	4247.6	4228.7
165°	4289.4	4285.4	4285.4	4312.3	4293.4
167.5°	4354.0	4341.9	4341.9	4368.9	4350.0
170°	4402.6	4391.8	4387.8	4414.7	4391.8
172.5°	4436.3	4425.5	4421.5	4448.5	4425.5
175°	4463.3	4452.5	4444.4	4471.4	4448.5
177.5°	4478.0	4467.3	4459.3	4482.1	4459.3
180°	4471.4	4471.4	4471.4	4471.4	4471.4

TEST NUMBER: P909672

CATALOG NUMBER: DFN2DIP-SQ4F0-140D140US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.24	13.12	13.17	14.07	15.30	11.79	12.68	12.72	13.63	14.86
	3H	13.90	14.70	14.85	15.66	16.91	13.41	14.21	14.36	15.17	16.42
	4H	14.49	15.25	15.45	16.21	17.47	14.00	14.75	14.96	15.72	16.98
	6H	14.90	15.59	15.87	16.56	17.84	14.40	15.09	15.37	16.06	17.34
	8H	15.01	15.67	15.98	16.65	17.93	14.50	15.17	15.48	16.15	17.42
	12H	15.06	15.69	16.04	16.67	17.96	14.55	15.18	15.53	16.16	17.45
4H	2H	12.70	13.45	13.66	14.42	15.68	12.35	13.10	13.31	14.06	15.32
	3H	14.57	15.20	15.55	16.20	17.47	14.17	14.79	15.14	15.79	17.06
	4H	15.29	15.87	16.27	16.85	18.15	14.87	15.44	15.85	16.43	17.73
	6H	15.81	16.31	16.81	17.32	18.62	15.38	15.88	16.38	16.89	18.18
	8H	15.97	16.43	16.96	17.43	18.74	15.53	15.99	16.52	16.99	18.31
	12H	16.04	16.46	17.06	17.48	18.80	15.59	16.01	16.61	17.03	18.35
8H	4H	15.49	15.95	16.49	16.96	18.27	15.11	15.58	16.11	16.58	17.89
	6H	16.13	16.51	17.15	17.56	18.87	15.74	16.13	16.77	17.17	18.48
	8H	16.35	16.69	17.38	17.72	19.05	15.96	16.30	16.99	17.33	18.66
	12H	16.49	16.79	17.52	17.81	19.19	16.08	16.37	17.11	17.40	18.77
12H	4H	15.48	15.90	16.49	16.92	18.23	15.11	15.53	16.13	16.55	17.87
	6H	16.16	16.50	17.19	17.53	18.86	15.79	16.13	16.82	17.16	18.49
	8H	16.41	16.70	17.44	17.73	19.10	16.03	16.32	17.06	17.35	18.72