

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904000

Luminaire Tested: DFN2DIP-SQ4F0-070D140US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904000
REPORT IS A COMBINATION OF REPORTS P900187 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-070D140US830-FLLFL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18210.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 167.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1801	1801	1801
5°	1804	1777	1789
10°	1790	1753	1765
15°	1763	1725	1728
20°	1728	1685	1689
25°	1692	1637	1645
30°	1648	1593	1589
35°	1606	1541	1529
40°	1554	1488	1472
45°	1503	1435	1414
50°	1446	1379	1347
55°	1387	1315	1285
60°	1320	1239	1214
65°	1248	1160	1131
70°	1155	1064	1041
75°	1026	949	960
80°	871	803	802
85°	630	549	538

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3284 cd/sqm

TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.6	1.3
10°-20°	679.9	3.7
20°-30°	999.1	5.5
30°-40°	1160.4	6.4
40°-50°	1159.0	6.4
50°-60°	1010.6	5.5
60°-70°	747.1	4.1
70°-80°	422.7	2.3
80°-90°	123.4	0.7
90°-100°	258.2	1.4
100°-110°	820.5	4.5
110°-120°	1404.2	7.7
120°-130°	1846.7	10.1
130°-140°	2072.8	11.4
140°-150°	2032.6	11.2
150°-160°	1705.1	9.4
160°-170°	1130.8	6.2
170°-180°	395.2	2.2
0°-30°	1920.6	10.5
0°-40°	3081.0	16.9
0°-60°	5250.6	28.8
0°-90°	6543.7	35.9
90°-120°	2483.0	13.6
90°-150°	8435.1	46.3
90°-180°	11666.0	64.1
0°-180°	18210.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2567	2567	2567	2567	2567	
5°	2567	2558	2530	2550	2545	244
15°	2444	2429	2397	2407	2395	688
25°	2212	2192	2150	2155	2150	1018
35°	1908	1884	1844	1829	1817	1192
45°	1553	1536	1498	1471	1461	1198
55°	1175	1160	1131	1101	1089	1051
65°	793	778	753	731	718	784
75°	415	410	397	383	388	443
85°	101	99	96	89	86	113
90°	4	45	123	116	120	18
95°	184	219	225	225	219	204
105°	757	768	775	781	781	799
115°	1409	1429	1423	1419	1409	1394
125°	2050	2081	2071	2060	2056	1831
135°	2651	2690	2698	2694	2684	2049
145°	3218	3244	3264	3267	3254	2011
155°	3680	3690	3702	3719	3708	1694
165°	4003	4000	4000	4025	4007	1129
175°	4166	4156	4148	4173	4152	396
180°	4173	4173	4173	4173	4173	

TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2567.2	2567.2	2567.2	2567.2	2567.2
2.5°	2582.2	2569.8	2542.6	2567.2	2562.5
5°	2567.2	2557.6	2530.3	2550.0	2545.2
7.5°	2550.0	2535.3	2508.0	2528.0	2523.0
10°	2523.0	2505.7	2476.1	2495.8	2488.4
12.5°	2485.8	2471.2	2441.6	2453.8	2448.8
15°	2443.9	2429.2	2397.0	2407.0	2394.6
17.5°	2392.0	2377.4	2345.1	2357.5	2345.1
20°	2335.1	2320.5	2285.9	2293.3	2283.6
22.5°	2278.6	2256.4	2224.1	2224.1	2219.1
25°	2211.9	2192.2	2150.3	2155.0	2150.3
27.5°	2137.7	2120.4	2088.5	2081.1	2068.8
30°	2063.9	2043.9	2007.0	1999.7	1989.7
32.5°	1984.7	1970.1	1930.5	1915.6	1905.6
35°	1908.3	1883.7	1844.1	1829.2	1816.8
37.5°	1821.8	1799.6	1760.0	1742.8	1730.4
40°	1733.1	1713.2	1673.6	1651.6	1641.6
42.5°	1646.6	1626.7	1587.4	1562.5	1547.8
45°	1552.8	1535.6	1498.4	1471.4	1461.4
47.5°	1461.4	1444.2	1404.6	1377.3	1362.7
50°	1365.1	1352.7	1318.1	1283.6	1271.3
52.5°	1271.3	1254.1	1222.1	1194.9	1177.5
55°	1175.2	1160.3	1130.7	1101.1	1088.7
57.5°	1078.8	1066.5	1034.3	1004.7	994.8
60°	982.4	972.7	938.2	911.0	903.6
62.5°	888.6	871.4	846.8	822.2	812.2
65°	792.6	777.6	753.0	730.8	718.4
67.5°	693.8	681.3	659.2	642.0	632.0
70°	602.4	592.5	570.1	552.9	543.2
72.5°	508.6	498.7	486.4	469.1	461.8
75°	414.6	409.9	397.3	382.7	387.7
77.5°	330.8	320.8	315.8	308.5	301.2
80°	246.9	244.4	239.4	232.1	227.1
82.5°	167.9	167.9	165.5	155.6	155.6
85°	101.1	98.8	96.4	88.8	86.4
87.5°	44.5	39.6	34.6	27.2	24.6
90°	3.8	45.3	123.3	115.7	119.5
92.5°	78.0	105.7	109.4	113.2	113.2
95°	183.7	219.0	225.2	225.2	219.0
97.5°	305.8	338.5	352.3	352.3	352.3
100°	446.7	475.6	485.6	485.6	481.8
102.5°	595.1	616.5	630.4	634.1	630.4
105°	757.4	767.5	775.1	781.3	781.3
107.5°	918.4	933.6	933.6	936.0	918.4
110°	1074.5	1094.6	1094.6	1094.6	1084.5

TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1243.0	1264.4	1260.7	1250.6	1243.0
115°	1409.1	1429.3	1423.0	1419.2	1409.1
117.5°	1574.0	1601.7	1584.0	1574.0	1563.9
120°	1740.0	1767.7	1740.0	1740.0	1728.7
122.5°	1891.0	1926.2	1908.6	1898.6	1891.0
125°	2049.6	2080.9	2070.9	2059.5	2055.8
127.5°	2204.2	2243.3	2229.4	2214.3	2204.2
130°	2348.9	2394.2	2387.9	2380.4	2366.5
132.5°	2511.2	2546.5	2549.0	2531.4	2521.3
135°	2650.9	2689.9	2697.5	2693.7	2683.6
137.5°	2806.9	2838.4	2844.7	2842.1	2827.1
140°	2944.0	2975.5	2993.1	2993.1	2979.3
142.5°	3084.9	3116.4	3126.5	3130.3	3116.4
145°	3218.3	3243.5	3263.6	3267.4	3253.6
147.5°	3337.8	3369.3	3384.4	3390.7	3376.8
150°	3461.1	3482.5	3496.4	3507.7	3496.4
152.5°	3570.6	3592.0	3609.7	3623.4	3609.7
155°	3680.1	3690.1	3701.5	3719.1	3707.8
157.5°	3774.4	3782.0	3788.3	3813.4	3795.8
160°	3858.8	3866.3	3870.1	3891.5	3876.3
162.5°	3936.7	3936.7	3940.5	3964.4	3946.8
165°	4003.4	3999.7	3999.7	4024.8	4007.2
167.5°	4063.8	4052.5	4052.5	4077.6	4060.0
170°	4109.1	4099.0	4095.3	4120.4	4099.0
172.5°	4140.6	4130.5	4126.7	4151.9	4130.5
175°	4165.8	4155.7	4148.1	4173.3	4151.9
177.5°	4179.5	4169.5	4162.0	4183.3	4162.0
180°	4173.3	4173.3	4173.3	4173.3	4173.3



TEST NUMBER: P904000

CATALOG NUMBER: DFN2DIP-SQ4F0-070D140US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.86	8.61	8.93	9.68	11.14	7.42	8.17	8.49	9.24	10.70
	3H	9.52	10.19	10.60	11.27	12.75	9.03	9.70	10.11	10.78	12.26
	4H	10.11	10.74	11.20	11.82	13.31	9.61	10.25	10.70	11.33	12.81
	6H	10.50	11.09	11.60	12.17	13.67	10.00	10.59	11.10	11.67	13.17
	8H	10.61	11.16	11.71	12.26	13.75	10.11	10.66	11.21	11.76	13.25
	12H	10.65	11.18	11.76	12.28	13.79	10.14	10.67	11.25	11.77	13.28
4H	2H	8.31	8.95	9.41	10.03	11.51	7.96	8.59	9.05	9.67	11.16
	3H	10.17	10.70	11.28	11.81	13.31	9.77	10.30	10.87	11.40	12.90
	4H	10.89	11.37	11.99	12.47	13.99	10.46	10.95	11.57	12.05	13.56
	6H	11.40	11.82	12.51	12.94	14.45	10.97	11.38	12.08	12.51	14.01
	8H	11.55	11.94	12.66	13.05	14.58	11.11	11.50	12.23	12.61	14.14
	12H	11.62	11.97	12.75	13.10	14.63	11.17	11.52	12.30	12.65	14.18
8H	4H	11.07	11.46	12.19	12.58	14.10	10.70	11.09	11.81	12.20	13.73
	6H	11.70	12.03	12.84	13.18	14.70	11.32	11.64	12.46	12.80	14.32
	8H	11.93	12.21	13.07	13.34	14.89	11.53	11.82	12.68	12.95	14.49
	12H	12.06	12.30	13.20	13.44	15.02	11.65	11.89	12.79	13.03	14.60
12H	4H	11.05	11.41	12.19	12.53	14.06	10.69	11.04	11.82	12.17	13.70
	6H	11.73	12.02	12.88	13.15	14.69	11.36	11.64	12.51	12.78	14.32
	8H	11.97	12.22	13.12	13.35	14.93	11.59	11.84	12.74	12.97	14.55

END OF REPORT