

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909677

Luminaire Tested: DFN2DIP-SQ4F0-140D160US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909677
REPORT IS A COMBINATION OF REPORTS P901737 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-140D160US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 29993.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 265.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	56	47	46	45			39
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	39	38			33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32			28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28			24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	27	24			21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	25	27	24	21			18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19			16
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17			15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15			13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3860	3860	3860
5°	3866	3807	3833
10°	3835	3757	3782
15°	3778	3695	3702
20°	3702	3610	3620
25°	3626	3508	3525
30°	3531	3413	3404
35°	3441	3301	3276
40°	3330	3188	3155
45°	3220	3075	3030
50°	3099	2956	2886
55°	2972	2819	2754
60°	2829	2655	2602
65°	2673	2487	2423
70°	2475	2280	2231
75°	2199	2034	2056
80°	1868	1721	1718
85°	1350	1177	1154

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3220 cd/sqm

TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.8	1.7
10°-20°	1456.8	4.9
20°-30°	2141.0	7.1
30°-40°	2486.6	8.3
40°-50°	2483.5	8.3
50°-60°	2165.5	7.2
60°-70°	1600.8	5.3
70°-80°	905.7	3.0
80°-90°	248.6	0.8
90°-100°	179.8	0.6
100°-110°	670.3	2.2
110°-120°	1777.8	5.9
120°-130°	2948.5	9.8
130°-140°	3132.1	10.4
140°-150°	2910.9	9.7
150°-160°	2340.3	7.8
160°-170°	1508.0	5.0
170°-180°	519.0	1.7
0°-30°	4115.6	13.7
0°-40°	6602.1	22.0
0°-60°	11251.2	37.5
0°-90°	14006.3	46.7
90°-120°	2627.9	8.8
90°-150°	11619.4	38.7
90°-180°	15987.0	53.3
0°-180°	29993.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5501	5501	5501	5501	5501	
5°	5501	5480	5422	5464	5454	522
15°	5237	5206	5136	5158	5131	1475
25°	4740	4698	4608	4618	4608	2181
35°	4089	4036	3952	3920	3893	2554
45°	3328	3290	3211	3153	3132	2568
55°	2518	2486	2423	2359	2333	2251
65°	1698	1666	1614	1566	1539	1679
75°	888	878	851	820	831	948
85°	217	212	206	190	185	242
90°	4	47	79	99	106	28
95°	256	126	154	174	170	304
105°	1200	1318	241	284	300	1282
115°	2269	2336	2435	608	324	2234
125°	3208	3259	3334	3362	3374	2861
135°	3970	4033	4068	4108	4100	3066
145°	4605	4601	4668	4695	4676	2880
155°	5070	5035	5082	5106	5074	2336
165°	5342	5319	5331	5358	5331	1509
175°	5465	5437	5445	5473	5433	520
180°	5453	5453	5453	5453	5453	

TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5501.2	5501.2	5501.2	5501.2	5501.2
2.5°	5533.2	5506.8	5448.4	5501.2	5491.1
5°	5501.2	5480.4	5422.1	5464.2	5454.1
7.5°	5464.2	5432.8	5374.4	5417.0	5406.3
10°	5406.3	5369.4	5305.9	5348.0	5332.3
12.5°	5326.6	5295.2	5231.8	5258.2	5247.6
15°	5236.9	5205.5	5136.4	5157.8	5131.3
17.5°	5125.8	5094.4	5025.3	5051.7	5025.3
20°	5004.0	4972.6	4898.5	4914.2	4893.4
22.5°	4882.7	4835.0	4766.0	4766.0	4755.4
25°	4739.6	4697.5	4607.7	4617.8	4607.7
27.5°	4580.8	4543.8	4475.3	4459.6	4433.2
30°	4422.5	4379.9	4300.7	4285.1	4263.7
32.5°	4253.0	4221.6	4136.8	4104.9	4083.5
35°	4089.1	4036.4	3951.6	3919.7	3893.2
37.5°	3903.9	3856.3	3771.4	3734.5	3708.0
40°	3713.7	3671.1	3586.2	3539.2	3517.8
42.5°	3528.5	3485.9	3401.6	3348.3	3316.9
45°	3327.5	3290.5	3210.9	3153.0	3131.7
47.5°	3131.7	3094.6	3009.9	2951.5	2920.1
50°	2925.2	2898.8	2824.7	2750.6	2724.2
52.5°	2724.2	2687.2	2618.7	2560.3	2523.4
55°	2518.3	2486.3	2422.9	2359.4	2333.1
57.5°	2311.7	2285.3	2216.4	2152.9	2131.5
60°	2105.2	2084.5	2010.3	1952.0	1936.2
62.5°	1904.3	1867.2	1814.4	1761.7	1740.4
65°	1698.3	1666.3	1613.6	1565.8	1539.4
67.5°	1486.7	1459.8	1412.6	1375.5	1354.2
70°	1290.8	1269.5	1221.8	1184.8	1164.0
72.5°	1089.9	1068.5	1042.2	1005.2	989.5
75°	888.5	878.4	851.4	820.0	830.6
77.5°	708.8	687.5	676.8	661.2	645.4
80°	529.3	523.6	513.0	497.3	486.6
82.5°	359.7	359.7	354.7	333.4	333.4
85°	216.6	211.6	206.5	190.3	185.2
87.5°	95.4	84.7	74.1	58.4	52.7
90°	3.7	47.4	78.7	98.9	106.3
92.5°	98.9	82.9	94.6	102.6	106.3
95°	256.3	126.0	153.7	173.8	169.7
97.5°	461.5	138.3	201.0	213.2	216.9
100°	698.6	157.9	224.9	256.3	264.3
102.5°	958.7	951.2	232.9	276.0	288.1
105°	1199.5	1318.1	240.9	284.0	299.8
107.5°	1479.7	1578.1	248.8	292.0	307.8
110°	1748.2	1830.7	690.6	296.1	311.5

TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	2000.7	2071.5	2004.5	303.7	315.8
115°	2268.8	2335.7	2434.6	607.7	323.8
117.5°	2501.6	2580.3	2647.9	2083.3	1049.6
120°	2762.2	2821.2	2892.4	2939.7	2407.0
122.5°	2982.8	3046.1	3125.2	3148.7	3152.9
125°	3207.7	3259.2	3334.3	3361.9	3373.7
127.5°	3412.9	3468.3	3527.8	3567.1	3570.9
130°	3606.5	3669.8	3712.9	3756.4	3752.7
132.5°	3803.8	3855.3	3898.4	3934.0	3930.3
135°	3969.6	4032.9	4068.0	4107.8	4099.9
137.5°	4143.0	4190.3	4230.1	4269.5	4257.8
140°	4312.6	4344.4	4387.6	4423.2	4403.5
142.5°	4455.0	4482.7	4533.8	4565.2	4545.5
145°	4605.0	4600.7	4667.8	4695.4	4675.8
147.5°	4734.8	4723.0	4790.1	4809.8	4794.2
150°	4861.3	4833.6	4896.9	4920.4	4900.7
152.5°	4967.6	4936.2	4995.3	5019.2	4991.6
155°	5070.2	5035.1	5082.5	5105.9	5074.5
157.5°	5153.2	5121.8	5157.4	5185.1	5153.2
160°	5224.4	5200.5	5224.4	5247.9	5220.2
162.5°	5287.3	5263.8	5283.4	5311.1	5275.5
165°	5342.5	5319.1	5330.8	5358.4	5330.8
167.5°	5386.1	5362.2	5374.4	5402.0	5366.4
170°	5421.7	5397.8	5405.7	5433.4	5397.8
172.5°	5445.1	5421.7	5429.6	5457.3	5421.7
175°	5464.8	5437.1	5445.1	5472.8	5433.4
177.5°	5472.8	5445.1	5449.3	5477.0	5441.4
180°	5453.1	5453.1	5453.1	5453.1	5453.1

TEST NUMBER: P909677

CATALOG NUMBER: DFN2DIP-SQ4F0-140D160US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.66	12.50	12.65	13.49	14.81	11.22	12.05	12.20	13.05	14.37
	3H	13.33	14.07	14.32	15.08	16.42	12.84	13.58	13.83	14.59	15.93
	4H	13.92	14.62	14.92	15.63	16.98	13.42	14.13	14.43	15.14	16.48
	6H	14.32	14.97	15.34	15.98	17.34	13.82	14.47	14.84	15.48	16.84
	8H	14.42	15.04	15.45	16.07	17.43	13.92	14.54	14.95	15.57	16.93
	12H	14.47	15.06	15.50	16.09	17.47	13.96	14.55	14.99	15.58	16.96
4H	2H	12.12	12.83	13.14	13.84	15.19	11.77	12.47	12.78	13.48	14.83
	3H	13.99	14.58	15.01	15.62	16.98	13.58	14.17	14.61	15.21	16.57
	4H	14.71	15.25	15.74	16.28	17.66	14.28	14.82	15.31	15.85	17.24
	6H	15.22	15.69	16.27	16.74	18.12	14.79	15.26	15.83	16.31	17.69
	8H	15.38	15.81	16.42	16.86	18.25	14.94	15.37	15.98	16.42	17.81
	12H	15.45	15.84	16.51	16.90	18.30	15.00	15.39	16.06	16.45	17.85
8H	4H	14.90	15.33	15.94	16.38	17.78	14.52	14.96	15.57	16.01	17.40
	6H	15.54	15.89	16.60	16.98	18.38	15.15	15.51	16.22	16.60	17.99
	8H	15.76	16.07	16.83	17.15	18.56	15.37	15.68	16.44	16.76	18.17
	12H	15.89	16.17	16.97	17.24	18.69	15.48	15.76	16.56	16.83	18.28
12H	4H	14.89	15.28	15.95	16.34	17.74	14.52	14.91	15.58	15.97	17.37
	6H	15.57	15.88	16.64	16.95	18.37	15.19	15.51	16.27	16.58	17.99
	8H	15.81	16.09	16.89	17.16	18.61	15.43	15.71	16.51	16.78	18.23