

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909689

Luminaire Tested: DFN2DIP-SQ4F0-160D080US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909689
REPORT IS A COMBINATION OF REPORTS P901631 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D080US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 23994.4 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 226.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71	71	71	67
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63	62	60	56
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49	46	43	40
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44	40	37	34
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4412	4412	4412
5°	4418	4351	4381
10°	4383	4293	4323
15°	4318	4223	4231
20°	4231	4126	4137
25°	4144	4009	4029
30°	4036	3901	3891
35°	3933	3773	3744
40°	3806	3644	3605
45°	3680	3514	3463
50°	3542	3379	3298
55°	3397	3221	3147
60°	3233	3034	2974
65°	3055	2842	2770
70°	2828	2606	2550
75°	2513	2325	2350
80°	2135	1966	1963
85°	1543	1345	1319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3680 cd/sqm

TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.7	2.5
10°-20°	1664.9	6.9
20°-30°	2446.8	10.2
30°-40°	2841.8	11.8
40°-50°	2838.3	11.8
50°-60°	2474.9	10.3
60°-70°	1829.5	7.6
70°-80°	1035.1	4.3
80°-90°	278.0	1.2
90°-100°	89.9	0.4
100°-110°	335.1	1.4
110°-120°	888.9	3.7
120°-130°	1474.3	6.1
130°-140°	1566.0	6.5
140°-150°	1455.4	6.1
150°-160°	1170.1	4.9
160°-170°	754.0	3.1
170°-180°	259.5	1.1
0°-30°	4703.5	19.6
0°-40°	7545.3	31.4
0°-60°	12858.5	53.6
0°-90°	16001.0	66.7
90°-120°	1314.0	5.5
90°-150°	5809.7	24.2
90°-180°	7993.0	33.3
0°-180°	23994.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6287	6287	6287	6287	6287	
5°	6287	6263	6197	6245	6233	597
15°	5985	5949	5870	5895	5864	1686
25°	5417	5369	5266	5278	5266	2492
35°	4673	4613	4516	4480	4450	2918
45°	3803	3760	3670	3603	3579	2935
55°	2878	2842	2769	2696	2666	2573
65°	1941	1904	1844	1790	1759	1919
75°	1015	1004	973	937	949	1084
85°	248	242	236	217	212	276
90°	2	24	39	49	53	22
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6287.1	6287.1	6287.1	6287.1	6287.1
2.5°	6323.7	6293.5	6226.8	6287.1	6275.5
5°	6287.1	6263.4	6196.6	6244.8	6233.2
7.5°	6244.8	6208.9	6142.1	6190.9	6178.7
10°	6178.7	6136.3	6063.9	6112.0	6094.0
12.5°	6087.7	6051.7	5979.2	6009.4	5997.2
15°	5985.0	5949.1	5870.1	5894.6	5864.4
17.5°	5858.0	5822.1	5743.2	5773.3	5743.2
20°	5718.8	5682.9	5598.2	5616.2	5592.4
22.5°	5580.3	5525.8	5446.8	5446.8	5434.7
25°	5416.7	5368.6	5265.9	5277.6	5265.9
27.5°	5235.1	5192.8	5114.6	5096.7	5066.5
30°	5054.3	5005.6	4915.1	4897.1	4872.8
32.5°	4860.6	4824.7	4727.8	4691.2	4666.9
35°	4673.4	4613.1	4516.1	4479.6	4449.5
37.5°	4461.7	4407.2	4310.3	4267.9	4237.8
40°	4244.2	4195.5	4098.6	4044.7	4020.4
42.5°	4032.6	3983.8	3887.6	3826.7	3790.7
45°	3803.0	3760.5	3669.5	3603.4	3579.1
47.5°	3579.1	3536.8	3439.9	3373.2	3337.3
50°	3343.1	3312.9	3228.2	3143.5	3113.4
52.5°	3113.4	3071.1	2992.8	2926.1	2883.8
55°	2878.0	2841.5	2769.0	2696.4	2666.3
57.5°	2642.0	2611.8	2532.9	2460.4	2436.1
60°	2405.9	2382.2	2297.5	2230.8	2212.8
62.5°	2176.3	2133.9	2073.7	2013.4	1989.0
65°	1940.9	1904.3	1844.0	1789.6	1759.4
67.5°	1699.1	1668.3	1614.5	1572.1	1547.7
70°	1475.2	1450.9	1396.3	1354.0	1330.3
72.5°	1245.6	1221.2	1191.1	1148.7	1130.8
75°	1015.3	1003.8	973.0	937.1	949.3
77.5°	810.1	785.8	773.6	755.6	737.6
80°	604.8	598.4	586.2	568.3	556.1
82.5°	411.1	411.1	405.4	381.0	381.0
85°	247.6	241.8	236.0	217.4	211.7
87.5°	109.1	96.8	84.6	66.8	60.3
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8

TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5

TEST NUMBER: P909689

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.85	14.89	14.65	15.71	16.72	13.41	14.44	14.21	15.27	16.28
	3H	15.53	16.46	16.34	17.29	18.33	15.04	15.97	15.85	16.80	17.84
	4H	16.13	17.01	16.96	17.85	18.90	15.64	16.51	16.46	17.35	18.40
	6H	16.54	17.35	17.38	18.20	19.26	16.04	16.85	16.88	17.70	18.76
	8H	16.65	17.42	17.50	18.29	19.36	16.15	16.92	17.00	17.79	18.85
	12H	16.71	17.44	17.57	18.30	19.40	16.20	16.93	17.06	17.79	18.89
4H	2H	14.34	15.21	15.17	16.05	17.10	13.98	14.86	14.82	15.70	16.75
	3H	16.22	16.95	17.07	17.83	18.89	15.81	16.55	16.66	17.42	18.49
	4H	16.95	17.61	17.81	18.48	19.58	16.52	17.19	17.38	18.06	19.15
	6H	17.48	18.05	18.35	18.95	20.04	17.04	17.62	17.92	18.52	19.61
	8H	17.63	18.17	18.51	19.06	20.17	17.19	17.73	18.07	18.62	19.73
	12H	17.72	18.20	18.61	19.11	20.23	17.27	17.75	18.16	18.66	19.78
8H	4H	17.16	17.70	18.04	18.59	19.70	16.78	17.32	17.66	18.21	19.32
	6H	17.80	18.25	18.71	19.18	20.29	17.42	17.86	18.32	18.80	19.91
	8H	18.03	18.42	18.94	19.35	20.47	17.63	18.03	18.55	18.95	20.08
	12H	18.17	18.52	19.09	19.43	20.61	17.76	18.11	18.68	19.02	20.20
12H	4H	17.15	17.64	18.05	18.55	19.66	16.78	17.27	17.68	18.18	19.29
	6H	17.83	18.23	18.75	19.15	20.28	17.46	17.86	18.38	18.78	19.91
	8H	18.09	18.44	19.00	19.35	20.53	17.71	18.06	18.62	18.97	20.15