

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909691

Luminaire Tested: DFN2DIP-SQ4F0-160D080US840-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909691
REPORT IS A COMBINATION OF REPORTS P901632 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D080US840-RLLONL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 21732.3 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 226.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4686	4686	4686
5°	4693	4612	4642
10°	4647	4523	4493
15°	4583	4374	4260
20°	4498	4169	3975
25°	4411	3939	3699
30°	4295	3703	3349
35°	4181	3449	3041
40°	4065	3186	2688
45°	3930	2894	2368
50°	3790	2600	2056
55°	3645	2285	1755
60°	3476	1955	1446
65°	3282	1621	1303
70°	3047	1308	1181
75°	2752	1155	1078
80°	2324	972	939
85°	1618	654	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3930 cd/sqm

TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	625.9	2.9
10°-20°	1718.2	7.9
20°-30°	2412.2	11.1
30°-40°	2629.5	12.1
40°-50°	2416.8	11.1
50°-60°	1898.0	8.7
60°-70°	1235.4	5.7
70°-80°	635.9	2.9
80°-90°	167.2	0.8
90°-100°	89.9	0.4
100°-110°	335.1	1.5
110°-120°	888.9	4.1
120°-130°	1474.3	6.8
130°-140°	1566.0	7.2
140°-150°	1455.4	6.7
150°-160°	1170.1	5.4
160°-170°	754.0	3.5
170°-180°	259.5	1.2
0°-30°	4756.2	21.9
0°-40°	7385.7	34.0
0°-60°	11700.5	53.8
0°-90°	13739.0	63.2
90°-120°	1314.0	6.0
90°-150°	5809.7	26.7
90°-180°	7993.0	36.8
0°-180°	21732.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6678	6678	6678	6678	6678	
5°	6678	6648	6569	6624	6606	633
15°	6352	6285	6080	5965	5905	1790
25°	5766	5572	5173	4926	4835	2652
35°	4968	4660	4128	3747	3614	3109
45°	4061	3656	3022	2592	2447	3136
55°	3088	2617	1964	1602	1487	2759
65°	2085	1595	1052	846	828	2067
75°	1112	689	483	441	435	1176
85°	260	133	115	115	115	298
90°	2	24	39	49	53	21
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2518	2541	2553	2537	1168
165°	2671	2660	2665	2679	2665	755
175°	2732	2719	2723	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6678.0	6678.0	6678.0	6678.0	6678.0
2.5°	6708.1	6678.0	6611.3	6672.3	6660.1
5°	6678.0	6647.8	6569.0	6623.5	6605.5
7.5°	6623.5	6587.6	6502.9	6526.7	6496.6
10°	6551.1	6508.8	6388.2	6369.6	6333.7
12.5°	6460.6	6406.2	6242.7	6206.7	6140.1
15°	6351.7	6285.0	6079.8	5965.0	5904.7
17.5°	6224.7	6127.9	5874.0	5741.2	5644.4
20°	6079.8	5958.6	5656.6	5505.9	5372.6
22.5°	5922.7	5783.5	5432.8	5227.7	5137.2
25°	5765.6	5571.9	5173.1	4925.6	4834.6
27.5°	5578.4	5372.6	4931.4	4647.4	4508.2
30°	5378.9	5148.8	4665.3	4357.6	4194.1
32.5°	5185.4	4907.0	4412.0	4049.2	3897.8
35°	4967.9	4659.5	4128.0	3747.1	3613.8
37.5°	4756.4	4423.6	3861.9	3444.4	3293.8
40°	4532.6	4170.3	3583.6	3154.6	2997.6
42.5°	4303.0	3916.4	3306.0	2858.4	2707.8
45°	4061.3	3656.1	3021.9	2592.3	2447.4
47.5°	3831.7	3402.8	2750.1	2320.5	2187.8
50°	3577.9	3148.9	2484.0	2066.6	1940.3
52.5°	3329.7	2876.4	2230.1	1831.3	1716.5
55°	3088.0	2616.7	1964.0	1601.6	1486.9
57.5°	2840.4	2357.0	1728.7	1390.1	1293.2
60°	2586.6	2103.1	1480.5	1172.8	1075.9
62.5°	2339.1	1855.6	1268.9	979.1	931.0
65°	2085.2	1595.3	1051.6	846.4	827.8
67.5°	1843.4	1353.5	846.4	743.2	725.2
70°	1589.5	1118.2	700.8	640.6	616.2
72.5°	1347.8	900.2	586.0	538.0	525.7
75°	1111.9	688.6	483.4	441.1	435.4
77.5°	876.5	489.2	380.8	356.5	344.4
80°	658.5	350.7	289.8	266.1	266.1
82.5°	459.1	236.0	199.4	187.2	187.2
85°	259.6	132.7	114.8	114.8	114.8
87.5°	96.8	48.1	48.1	42.3	42.3
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.2	63.0	76.9	86.9	84.8
97.5°	230.8	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.2	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.8	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8



TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.4	1035.7	1002.3	151.8	157.9
115°	1134.4	1167.9	1217.3	303.9	161.9
117.5°	1250.8	1290.2	1323.9	1041.6	524.8
120°	1381.1	1410.6	1446.2	1469.9	1203.5
122.5°	1491.4	1523.1	1562.7	1574.4	1576.5
125°	1603.9	1629.6	1667.1	1680.9	1686.8
127.5°	1706.5	1734.1	1763.9	1783.5	1785.4
130°	1803.2	1834.8	1856.4	1878.2	1876.3
132.5°	1901.9	1927.6	1949.2	1967.0	1965.1
135°	1984.8	2016.4	2034.0	2054.0	2049.9
137.5°	2071.5	2095.2	2115.1	2134.8	2128.9
140°	2156.3	2172.2	2193.8	2211.6	2201.7
142.5°	2227.6	2241.3	2266.8	2282.6	2272.7
145°	2302.5	2300.4	2333.9	2347.7	2337.8
147.5°	2367.4	2361.6	2395.0	2404.9	2397.1
150°	2430.6	2416.8	2448.4	2460.1	2450.3
152.5°	2483.9	2468.1	2497.6	2509.6	2495.8
155°	2535.2	2517.6	2541.2	2552.9	2537.3
157.5°	2576.6	2560.9	2578.7	2592.5	2576.6
160°	2612.2	2600.3	2612.2	2623.9	2610.1
162.5°	2643.6	2631.9	2641.7	2655.5	2637.8
165°	2671.3	2659.6	2665.4	2679.2	2665.4
167.5°	2693.0	2681.1	2687.2	2701.0	2683.2
170°	2710.9	2698.9	2702.9	2716.7	2698.9
172.5°	2722.6	2710.9	2714.8	2728.7	2710.9
175°	2732.4	2718.6	2722.6	2736.3	2716.7
177.5°	2736.3	2722.6	2724.6	2738.5	2720.7
180°	2726.5	2726.5	2726.5	2726.5	2726.5

TEST NUMBER: P909691

CATALOG NUMBER: DFN2DIP-SQ4F0-160D080US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.68	14.63	14.52	15.49	16.56	9.64	10.59	10.48	11.45	12.52
	3H	15.37	16.22	16.22	17.09	18.19	10.84	11.69	11.69	12.56	13.66
	4H	15.99	16.79	16.86	17.66	18.77	11.29	12.10	12.17	12.97	14.08
	6H	16.42	17.16	17.30	18.04	19.16	11.62	12.36	12.50	13.24	14.37
	8H	16.55	17.25	17.44	18.15	19.27	11.72	12.42	12.61	13.32	14.44
	12H	16.62	17.29	17.51	18.18	19.33	11.76	12.43	12.66	13.33	14.47
4H	2H	13.71	14.51	14.59	15.39	16.50	10.25	11.05	11.13	11.93	13.04
	3H	15.56	16.22	16.44	17.13	18.25	11.61	12.28	12.50	13.19	14.31
	4H	16.26	16.86	17.15	17.77	18.92	12.17	12.77	13.07	13.68	14.83
	6H	16.78	17.30	17.70	18.23	19.39	12.59	13.12	13.51	14.04	15.20
	8H	16.96	17.45	17.88	18.37	19.54	12.73	13.21	13.64	14.14	15.30
	12H	17.07	17.50	18.00	18.44	19.62	12.80	13.24	13.73	14.18	15.35
8H	4H	16.23	16.72	17.15	17.64	18.81	12.46	12.95	13.37	13.87	15.03
	6H	16.81	17.21	17.75	18.18	19.34	12.98	13.39	13.92	14.35	15.52
	8H	17.03	17.38	17.98	18.34	19.52	13.18	13.53	14.13	14.49	15.67
	12H	17.18	17.49	18.13	18.44	19.67	13.30	13.61	14.25	14.56	15.79
12H	4H	16.19	16.63	17.13	17.57	18.74	12.47	12.91	13.40	13.85	15.02
	6H	16.78	17.14	17.74	18.10	19.28	13.03	13.39	13.98	14.35	15.53
	8H	17.01	17.33	17.97	18.27	19.51	13.25	13.56	14.20	14.51	15.75

END OF REPORT