

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904025

Luminaire Tested: DFN2DIP-SQ4F0-080D100US830-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P904025  
REPORT IS A COMBINATION OF REPORTS P901655 AND P898471  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-SQ4F0-080D100US830-FLLONL  
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16796.1 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 146.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9954  
Total Harmonic Distortion (THDi): 0.076  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P904025  
CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P904025

CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	37				37
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31				31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27				27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27	23				23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23	20				20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17				17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	12				12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2059	2059	2059
5°	2062	2030	2044
10°	2045	2003	2017
15°	2015	1971	1975
20°	1974	1925	1931
25°	1934	1871	1880
30°	1883	1821	1816
35°	1835	1761	1747
40°	1776	1700	1682
45°	1717	1640	1616
50°	1653	1577	1539
55°	1585	1503	1469
60°	1509	1416	1388
65°	1426	1326	1292
70°	1320	1216	1190
75°	1173	1085	1097
80°	996	918	916
85°	720	628	616

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1717 cd/sqm



TEST NUMBER: P904025

CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.1	1.6
10°-20°	777.0	4.6
20°-30°	1141.8	6.8
30°-40°	1326.2	7.9
40°-50°	1324.5	7.9
50°-60°	1155.0	6.9
60°-70°	853.8	5.1
70°-80°	483.0	2.9
80°-90°	133.1	0.8
90°-100°	104.9	0.6
100°-110°	391.0	2.3
110°-120°	1037.0	6.2
120°-130°	1720.0	10.2
130°-140°	1827.0	10.9
140°-150°	1698.0	10.1
150°-160°	1365.2	8.1
160°-170°	879.7	5.2
170°-180°	302.8	1.8
0°-30°	2195.0	13.1
0°-40°	3521.1	21.0
0°-60°	6000.6	35.7
0°-90°	7470.5	44.5
90°-120°	1532.9	9.1
90°-150°	6778.0	40.4
90°-180°	9326.0	55.5
0°-180°	16796.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	279
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2458	2463	2458	1163
35°	2181	2153	2108	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	896
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	2	28	46	58	62	15
95°	150	74	90	101	99	177
105°	700	769	140	166	175	748
115°	1323	1362	1420	354	189	1303
125°	1871	1901	1945	1961	1968	1669
135°	2316	2352	2373	2396	2392	1789
145°	2686	2684	2723	2739	2728	1680
155°	2958	2937	2965	2978	2960	1363
165°	3116	3103	3110	3126	3110	880
175°	3188	3172	3176	3192	3170	303
180°	3181	3181	3181	3181	3181	



TEST NUMBER: P904025

CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2933.9	2933.9	2933.9	2933.9	2933.9
2.5°	2951.0	2937.0	2905.9	2933.9	2928.6
5°	2933.9	2922.9	2891.8	2914.2	2908.9
7.5°	2914.2	2897.5	2866.4	2889.1	2883.4
10°	2883.4	2863.6	2829.8	2852.2	2843.9
12.5°	2840.9	2824.1	2790.3	2804.3	2798.7
15°	2793.0	2776.3	2739.4	2750.8	2736.8
17.5°	2733.7	2717.0	2680.1	2694.3	2680.1
20°	2668.8	2652.0	2612.5	2620.9	2609.8
22.5°	2604.2	2578.7	2541.8	2541.8	2536.2
25°	2527.8	2505.4	2457.5	2462.9	2457.5
27.5°	2443.1	2423.4	2386.8	2378.4	2364.4
30°	2358.7	2335.9	2293.8	2285.4	2274.0
32.5°	2268.3	2251.5	2206.3	2189.2	2177.9
35°	2180.9	2152.8	2107.5	2090.5	2076.4
37.5°	2082.1	2056.6	2011.5	1991.7	1977.6
40°	1980.7	1957.8	1912.7	1887.5	1876.1
42.5°	1881.9	1859.1	1814.2	1785.7	1769.1
45°	1774.7	1754.9	1712.4	1681.6	1670.3
47.5°	1670.3	1650.5	1605.2	1574.1	1557.4
50°	1560.1	1546.1	1506.5	1467.0	1452.9
52.5°	1452.9	1433.1	1396.7	1365.6	1345.8
55°	1343.0	1326.0	1292.2	1258.4	1244.3
57.5°	1232.9	1218.9	1182.0	1148.2	1136.8
60°	1122.8	1111.7	1072.1	1041.0	1032.6
62.5°	1015.6	995.9	967.7	939.6	928.2
65°	905.8	888.7	860.5	835.1	821.0
67.5°	792.9	778.5	753.4	733.7	722.3
70°	688.4	677.0	651.7	631.9	620.8
72.5°	581.3	570.0	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.1	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	2.2	27.6	45.9	57.7	62.0
92.5°	57.7	48.4	55.2	59.9	62.0
95°	149.5	73.5	89.6	101.4	99.0
97.5°	269.2	80.6	117.3	124.3	126.6
100°	407.6	92.1	131.2	149.5	154.2
102.5°	559.2	554.9	135.8	161.0	168.1
105°	699.7	768.8	140.5	165.6	174.9
107.5°	863.2	920.6	145.2	170.3	179.6
110°	1019.7	1067.9	402.8	172.8	181.7



TEST NUMBER: P904025

CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1167.1	1208.3	1169.3	177.1	184.3
115°	1323.4	1362.5	1420.2	354.5	188.9
117.5°	1459.2	1505.2	1544.5	1215.2	612.3
120°	1611.3	1645.7	1687.2	1714.9	1404.1
122.5°	1740.0	1776.9	1823.1	1836.7	1839.2
125°	1871.2	1901.3	1945.0	1961.1	1967.9
127.5°	1990.9	2023.2	2057.9	2080.9	2083.0
130°	2103.8	2140.7	2165.9	2191.2	2189.1
132.5°	2218.8	2248.9	2274.1	2294.8	2292.6
135°	2315.6	2352.5	2373.0	2396.2	2391.6
137.5°	2416.8	2444.4	2467.6	2490.6	2483.7
140°	2515.6	2534.3	2559.4	2580.2	2568.7
142.5°	2598.8	2614.9	2644.7	2663.0	2651.6
145°	2686.2	2683.8	2722.9	2739.0	2727.5
147.5°	2761.9	2755.1	2794.2	2805.7	2796.7
150°	2835.7	2819.6	2856.6	2870.2	2858.7
152.5°	2897.8	2879.5	2914.0	2927.8	2911.7
155°	2957.7	2937.2	2964.8	2978.4	2960.1
157.5°	3006.1	2987.8	3008.5	3024.6	3006.1
160°	3047.6	3033.7	3047.6	3061.3	3045.2
162.5°	3084.2	3070.5	3082.0	3098.1	3077.4
165°	3116.4	3102.8	3109.6	3125.8	3109.6
167.5°	3141.9	3127.9	3135.1	3151.2	3130.4
170°	3162.6	3148.8	3153.4	3169.5	3148.8
172.5°	3176.3	3162.6	3167.3	3183.4	3162.6
175°	3187.8	3171.7	3176.3	3192.5	3169.5
177.5°	3192.5	3176.3	3178.8	3194.9	3174.1
180°	3181.0	3181.0	3181.0	3181.0	3181.0



TEST NUMBER: P904025  
 CATALOG NUMBER: DFN2DIP-SQ4F0-080D100US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.26	10.07	10.26	11.09	12.44	8.82	9.63	9.82	10.64	11.99
	3H	10.92	11.65	11.93	12.67	14.04	10.43	11.16	11.44	12.18	13.55
	4H	11.51	12.20	12.54	13.23	14.60	11.02	11.71	12.04	12.73	14.11
	6H	11.91	12.55	12.95	13.58	14.97	11.41	12.05	12.45	13.08	14.47
	8H	12.02	12.62	13.06	13.67	15.05	11.51	12.12	12.56	13.17	14.55
	12H	12.06	12.64	13.11	13.68	15.09	11.55	12.13	12.60	13.17	14.58
4H	2H	9.72	10.41	10.75	11.43	12.81	9.36	10.05	10.39	11.08	12.45
	3H	11.58	12.16	12.62	13.21	14.60	11.17	11.75	12.22	12.81	14.19
	4H	12.30	12.83	13.35	13.87	15.28	11.87	12.40	12.92	13.45	14.86
	6H	12.81	13.27	13.87	14.34	15.74	12.38	12.84	13.44	13.91	15.31
	8H	12.97	13.39	14.02	14.45	15.87	12.53	12.95	13.59	14.01	15.44
	12H	13.04	13.42	14.11	14.50	15.93	12.59	12.97	13.67	14.05	15.48
8H	4H	12.49	12.92	13.55	13.98	15.40	12.11	12.54	13.17	13.60	15.02
	6H	13.13	13.48	14.21	14.58	16.00	12.74	13.09	13.82	14.20	15.62
	8H	13.35	13.66	14.44	14.74	16.18	12.96	13.26	14.04	14.35	15.79
	12H	13.48	13.75	14.57	14.83	16.31	13.07	13.34	14.16	14.42	15.90
12H	4H	12.47	12.86	13.55	13.93	15.36	12.11	12.49	13.18	13.57	14.99
	6H	13.16	13.46	14.24	14.55	15.99	12.78	13.09	13.87	14.18	15.62
	8H	13.40	13.67	14.49	14.75	16.23	13.02	13.29	14.11	14.37	15.85