

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909693

Luminaire Tested: DFN2DIP-SQ4F0-160D090US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909693
REPORT IS A COMBINATION OF REPORTS P901649 AND P898471
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-160D090US840-FLLONL
Description: 4 foot, Square Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 24994.1 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 233.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	80	80	80	69	69	69
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	61	60	58
2	92	84	78	73	86	79	74	69	70	66	62	62	58	55	54	51	49
3	84	74	67	61	78	70	63	58	62	57	52	55	50	47	48	45	42
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	31
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28
7	60	48	40	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4412	4412	4412
5°	4418	4351	4381
10°	4383	4293	4323
15°	4318	4223	4231
20°	4231	4126	4137
25°	4144	4009	4029
30°	4036	3901	3891
35°	3933	3773	3744
40°	3806	3644	3605
45°	3680	3514	3463
50°	3542	3379	3298
55°	3397	3221	3147
60°	3233	3034	2974
65°	3055	2842	2770
70°	2828	2606	2550
75°	2513	2325	2350
80°	2135	1966	1963
85°	1543	1345	1319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3680 cd/sqm

TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	591.7	2.4
10°-20°	1664.9	6.7
20°-30°	2446.8	9.8
30°-40°	2841.8	11.4
40°-50°	2838.3	11.4
50°-60°	2474.9	9.9
60°-70°	1829.5	7.3
70°-80°	1035.1	4.1
80°-90°	278.6	1.1
90°-100°	101.2	0.4
100°-110°	377.0	1.5
110°-120°	1000.0	4.0
120°-130°	1658.6	6.6
130°-140°	1761.8	7.0
140°-150°	1637.4	6.6
150°-160°	1316.4	5.3
160°-170°	848.2	3.4
170°-180°	292.0	1.2
0°-30°	4703.5	18.8
0°-40°	7545.3	30.2
0°-60°	12858.5	51.4
0°-90°	16001.6	64.0
90°-120°	1478.2	5.9
90°-150°	6535.9	26.1
90°-180°	8992.0	36.0
0°-180°	24994.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6287	6287	6287	6287	6287	
5°	6287	6263	6197	6245	6233	597
15°	5985	5949	5870	5895	5864	1686
25°	5417	5369	5266	5278	5266	2492
35°	4673	4613	4516	4480	4450	2918
45°	3803	3760	3670	3603	3579	2935
55°	2878	2842	2769	2696	2666	2573
65°	1941	1904	1844	1790	1759	1919
75°	1015	1004	973	937	949	1084
85°	248	242	236	217	212	276
90°	2	27	44	56	60	23
95°	144	71	86	98	95	171
105°	675	741	135	160	169	721
115°	1276	1314	1370	342	182	1256
125°	1804	1833	1876	1891	1898	1609
135°	2233	2268	2288	2311	2306	1725
145°	2590	2588	2626	2641	2630	1620
155°	2852	2832	2859	2872	2854	1314
165°	3005	2992	2999	3014	2999	849
175°	3074	3058	3063	3078	3056	293
180°	3067	3067	3067	3067	3067	

TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6287.1	6287.1	6287.1	6287.1	6287.1
2.5°	6323.7	6293.5	6226.8	6287.1	6275.5
5°	6287.1	6263.4	6196.6	6244.8	6233.2
7.5°	6244.8	6208.9	6142.1	6190.9	6178.7
10°	6178.7	6136.3	6063.9	6112.0	6094.0
12.5°	6087.7	6051.7	5979.2	6009.4	5997.2
15°	5985.0	5949.1	5870.1	5894.6	5864.4
17.5°	5858.0	5822.1	5743.2	5773.3	5743.2
20°	5718.8	5682.9	5598.2	5616.2	5592.4
22.5°	5580.3	5525.8	5446.8	5446.8	5434.7
25°	5416.7	5368.6	5265.9	5277.6	5265.9
27.5°	5235.1	5192.8	5114.6	5096.7	5066.5
30°	5054.3	5005.6	4915.1	4897.1	4872.8
32.5°	4860.6	4824.7	4727.8	4691.2	4666.9
35°	4673.4	4613.1	4516.1	4479.6	4449.5
37.5°	4461.7	4407.2	4310.3	4267.9	4237.8
40°	4244.2	4195.5	4098.6	4044.7	4020.4
42.5°	4032.6	3983.8	3887.6	3826.7	3790.7
45°	3803.0	3760.5	3669.5	3603.4	3579.1
47.5°	3579.1	3536.8	3439.9	3373.2	3337.3
50°	3343.1	3312.9	3228.2	3143.5	3113.4
52.5°	3113.4	3071.1	2992.8	2926.1	2883.8
55°	2878.0	2841.5	2769.0	2696.4	2666.3
57.5°	2642.0	2611.8	2532.9	2460.4	2436.1
60°	2405.9	2382.2	2297.5	2230.8	2212.8
62.5°	2176.3	2133.9	2073.7	2013.4	1989.0
65°	1940.9	1904.3	1844.0	1789.6	1759.4
67.5°	1699.1	1668.3	1614.5	1572.1	1547.7
70°	1475.2	1450.9	1396.3	1354.0	1330.3
72.5°	1245.6	1221.2	1191.1	1148.7	1130.8
75°	1015.3	1003.8	973.0	937.1	949.3
77.5°	810.1	785.8	773.6	755.6	737.6
80°	604.8	598.4	586.2	568.3	556.1
82.5°	411.1	411.1	405.4	381.0	381.0
85°	247.6	241.8	236.0	217.4	211.7
87.5°	109.1	96.8	84.6	66.8	60.3
90°	2.1	26.7	44.2	55.6	59.8
92.5°	55.6	46.7	53.2	57.8	59.8
95°	144.2	70.9	86.4	97.8	95.4
97.5°	259.6	77.8	113.1	119.9	122.0
100°	392.9	88.9	126.5	144.2	148.7
102.5°	539.3	535.0	131.0	155.2	162.1
105°	674.7	741.4	135.4	159.8	168.6
107.5°	832.3	887.7	140.0	164.2	173.2
110°	983.3	1029.8	388.5	166.5	175.3

TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1125.4	1165.2	1127.5	170.8	177.6
115°	1276.2	1313.8	1369.5	341.8	182.1
117.5°	1407.1	1451.5	1489.3	1171.8	590.4
120°	1553.7	1586.9	1627.0	1653.6	1353.9
122.5°	1677.9	1713.4	1758.0	1771.1	1773.5
125°	1804.3	1833.3	1875.5	1891.1	1897.6
127.5°	1919.8	1950.9	1984.4	2006.5	2008.6
130°	2028.6	2064.3	2088.5	2112.9	2110.9
132.5°	2139.6	2168.6	2192.8	2212.9	2210.8
135°	2232.9	2268.5	2288.3	2310.7	2306.2
137.5°	2330.5	2357.0	2379.4	2401.6	2395.0
140°	2425.8	2443.8	2468.0	2488.0	2477.0
142.5°	2506.0	2521.5	2550.2	2567.9	2556.9
145°	2590.3	2587.9	2625.7	2641.2	2630.1
147.5°	2663.3	2656.8	2694.4	2705.5	2696.7
150°	2734.5	2719.0	2754.5	2767.6	2756.6
152.5°	2794.3	2776.6	2809.8	2823.3	2807.7
155°	2852.1	2832.3	2858.8	2872.1	2854.4
157.5°	2898.7	2881.0	2901.0	2916.6	2898.7
160°	2938.7	2925.3	2938.7	2951.9	2936.4
162.5°	2974.1	2960.8	2971.9	2987.5	2967.5
165°	3005.2	2991.9	2998.6	3014.1	2998.6
167.5°	3029.7	3016.3	3023.0	3038.6	3018.6
170°	3049.7	3036.3	3040.7	3056.3	3036.3
172.5°	3062.9	3049.7	3054.1	3069.7	3049.7
175°	3073.9	3058.4	3062.9	3078.4	3056.3
177.5°	3078.4	3062.9	3065.2	3080.8	3060.8
180°	3067.4	3067.4	3067.4	3067.4	3067.4

TEST NUMBER: P909693

CATALOG NUMBER: DFN2DIP-SQ4F0-160D090US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.64	14.65	14.47	15.50	16.55	13.20	14.20	14.03	15.05	16.11
	3H	15.32	16.22	16.16	17.08	18.16	14.83	15.73	15.67	16.59	17.67
	4H	15.92	16.77	16.77	17.63	18.73	15.42	16.27	16.28	17.14	18.23
	6H	16.33	17.11	17.19	17.98	19.09	15.83	16.61	16.69	17.48	18.59
	8H	16.44	17.18	17.31	18.08	19.18	15.93	16.68	16.81	17.57	18.68
	12H	16.49	17.20	17.37	18.09	19.22	15.98	16.69	16.86	17.58	18.71
4H	2H	14.12	14.97	14.98	15.84	16.93	13.77	14.62	14.63	15.48	16.58
	3H	16.01	16.72	16.88	17.61	18.72	15.60	16.31	16.47	17.21	18.32
	4H	16.73	17.38	17.61	18.27	19.41	16.30	16.95	17.19	17.85	18.98
	6H	17.26	17.82	18.16	18.73	19.87	16.82	17.38	17.72	18.30	19.44
	8H	17.41	17.93	18.31	18.85	20.00	16.97	17.50	17.88	18.41	19.56
	12H	17.49	17.96	18.42	18.90	20.05	17.04	17.52	17.97	18.45	19.60
8H	4H	16.94	17.46	17.84	18.37	19.52	16.56	17.08	17.46	18.00	19.15
	6H	17.58	18.01	18.51	18.97	20.12	17.20	17.63	18.12	18.58	19.73
	8H	17.80	18.19	18.74	19.13	20.30	17.41	17.80	18.35	18.74	19.91
	12H	17.95	18.28	18.89	19.22	20.44	17.53	17.87	18.48	18.81	20.03
12H	4H	16.93	17.40	17.85	18.33	19.49	16.56	17.03	17.48	17.97	19.12
	6H	17.61	17.99	18.55	18.94	20.11	17.24	17.62	18.18	18.57	19.74
	8H	17.86	18.20	18.80	19.14	20.36	17.48	17.82	18.42	18.76	19.98