

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904042

Luminaire Tested: DFN2DIP-SQ4F0-080D160US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904042
REPORT IS A COMBINATION OF REPORTS P900208 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-080D160US830-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19756.6 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 193.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	31	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	15	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2187	2187	2187
5°	2190	2152	2166
10°	2168	2111	2097
15°	2139	2041	1988
20°	2099	1946	1855
25°	2059	1838	1726
30°	2004	1728	1563
35°	1951	1609	1419
40°	1897	1487	1254
45°	1834	1351	1105
50°	1769	1213	959
55°	1701	1066	819
60°	1622	913	675
65°	1532	756	608
70°	1422	611	551
75°	1284	539	503
80°	1085	454	438
85°	755	305	333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3754 cd/sqm

TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	1.5
10°-20°	801.8	4.1
20°-30°	1125.7	5.7
30°-40°	1227.1	6.2
40°-50°	1127.8	5.7
50°-60°	885.7	4.5
60°-70°	576.5	2.9
70°-80°	296.8	1.5
80°-90°	89.3	0.5
90°-100°	295.1	1.5
100°-110°	937.8	4.7
110°-120°	1604.9	8.1
120°-130°	2110.7	10.7
130°-140°	2369.1	12.0
140°-150°	2323.2	11.8
150°-160°	1948.8	9.9
160°-170°	1292.4	6.5
170°-180°	451.7	2.3
0°-30°	2219.6	11.2
0°-40°	3446.7	17.4
0°-60°	5460.2	27.6
0°-90°	6422.9	32.5
90°-120°	2837.8	14.4
90°-150°	9640.8	48.8
90°-180°	13334.0	67.5
0°-180°	19756.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	4	52	141	132	137	20
95°	210	250	257	257	250	234
105°	866	877	886	893	893	914
115°	1610	1634	1626	1622	1610	1593
125°	2342	2378	2367	2354	2350	2093
135°	3030	3074	3083	3079	3067	2342
145°	3678	3707	3730	3734	3719	2298
155°	4206	4218	4230	4251	4238	1936
165°	4576	4571	4571	4600	4580	1291
175°	4761	4750	4741	4770	4745	452
180°	4770	4770	4770	4770	4770	

TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	4.3	51.7	140.9	132.3	136.6
92.5°	89.2	120.8	125.1	129.4	129.4
95°	209.9	250.2	257.4	257.4	250.2
97.5°	349.4	386.8	402.7	402.7	402.7
100°	510.5	543.6	555.1	555.1	550.7
102.5°	680.1	704.6	720.4	724.7	720.4
105°	865.6	877.1	885.8	893.0	893.0
107.5°	1049.7	1067.0	1067.0	1069.9	1049.7
110°	1228.0	1251.0	1251.0	1251.0	1239.5

TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1420.7	1445.2	1440.9	1429.4	1420.7
115°	1610.5	1633.5	1626.4	1622.0	1610.5
117.5°	1798.9	1830.5	1810.4	1798.9	1787.4
120°	1988.8	2020.3	1988.8	1988.8	1975.8
122.5°	2161.2	2201.6	2181.4	2169.9	2161.2
125°	2342.5	2378.4	2366.9	2354.0	2349.7
127.5°	2519.3	2563.9	2548.1	2530.8	2519.3
130°	2684.7	2736.5	2729.3	2720.6	2704.8
132.5°	2870.2	2910.5	2913.3	2893.2	2881.7
135°	3029.8	3074.4	3083.1	3078.7	3067.2
137.5°	3208.1	3244.0	3251.3	3248.4	3231.1
140°	3364.9	3400.8	3421.0	3421.0	3405.1
142.5°	3526.0	3561.9	3573.4	3577.7	3561.9
145°	3678.4	3707.1	3730.1	3734.4	3718.6
147.5°	3814.9	3850.9	3868.2	3875.4	3859.5
150°	3955.8	3980.4	3996.2	4009.1	3996.2
152.5°	4081.0	4105.4	4125.6	4141.3	4125.6
155°	4206.1	4217.6	4230.5	4250.7	4237.8
157.5°	4313.9	4322.6	4329.8	4358.5	4338.4
160°	4410.2	4418.9	4423.3	4447.7	4430.4
162.5°	4499.4	4499.4	4503.7	4531.1	4510.9
165°	4575.7	4571.3	4571.3	4600.1	4580.0
167.5°	4644.7	4631.7	4631.7	4660.5	4640.3
170°	4696.4	4684.9	4680.7	4709.4	4684.9
172.5°	4732.4	4720.9	4716.6	4745.3	4720.9
175°	4761.2	4749.7	4741.0	4769.8	4745.3
177.5°	4777.0	4765.5	4756.8	4781.3	4756.8
180°	4769.8	4769.8	4769.8	4769.8	4769.8

TEST NUMBER: P904042

CATALOG NUMBER: DFN2DIP-SQ4F0-080D160US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.98	8.68	9.08	9.77	11.28	3.94	4.64	5.04	5.74	7.24
	3H	9.65	10.28	10.76	11.38	12.90	5.12	5.75	6.23	6.85	8.37
	4H	10.25	10.85	11.37	11.96	13.48	5.56	6.16	6.68	7.26	8.79
	6H	10.67	11.22	11.80	12.33	13.87	5.88	6.43	7.00	7.53	9.07
	8H	10.80	11.32	11.93	12.44	13.97	5.96	6.49	7.09	7.61	9.14
	12H	10.86	11.35	11.99	12.47	14.02	6.00	6.50	7.14	7.62	9.17
4H	2H	7.98	8.58	9.10	9.68	11.21	4.52	5.12	5.65	6.22	7.75
	3H	9.80	10.30	10.93	11.43	12.97	5.86	6.36	6.99	7.49	9.02
	4H	10.49	10.95	11.63	12.07	13.63	6.40	6.86	7.54	7.98	9.54
	6H	11.00	11.40	12.15	12.54	14.09	6.82	7.21	7.96	8.35	9.90
	8H	11.18	11.55	12.32	12.68	14.24	6.94	7.31	8.08	8.44	10.01
	12H	11.27	11.60	12.43	12.75	14.32	7.00	7.33	8.16	8.48	10.05
8H	4H	10.45	10.82	11.59	11.95	13.52	6.68	7.04	7.82	8.17	9.74
	6H	11.02	11.32	12.18	12.49	14.06	7.19	7.49	8.35	8.67	10.23
	8H	11.24	11.50	12.40	12.65	14.24	7.38	7.65	8.55	8.80	10.38
	12H	11.37	11.60	12.54	12.75	14.37	7.50	7.73	8.67	8.88	10.50
12H	4H	10.40	10.73	11.55	11.87	13.44	6.68	7.01	7.83	8.15	9.72
	6H	10.99	11.26	12.16	12.41	13.99	7.24	7.50	8.41	8.66	10.24
	8H	11.21	11.44	12.38	12.59	14.21	7.45	7.68	8.62	8.83	10.45