

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904074

Luminaire Tested: DFN2DIP-SQ4F0-090D140US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904074
REPORT IS A COMBINATION OF REPORTS P900192 AND P896915
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ4F0-090D140US830-RLLFLL
Description: 4 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18888.6 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.92' x L: 3.92' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 188.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.983
Total Harmonic Distortion (THDi): 0.073
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	50	66	57	51	46	47	43	39	38	35	32	29	27	25
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	46	38	33	52	42	35	30	35	30	26	28	25	22	22	20	18
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2460	2460	2460
5°	2464	2422	2437
10°	2440	2374	2359
15°	2406	2296	2237
20°	2361	2189	2087
25°	2316	2068	1942
30°	2255	1944	1758
35°	2195	1811	1597
40°	2134	1673	1411
45°	2063	1519	1243
50°	1990	1365	1079
55°	1913	1199	921
60°	1825	1027	759
65°	1723	851	684
70°	1600	687	620
75°	1445	606	566
80°	1220	510	493
85°	849	343	375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3284 cd/sqm

TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	1.7
10°-20°	902.0	4.8
20°-30°	1266.4	6.7
30°-40°	1380.5	7.3
40°-50°	1268.8	6.7
50°-60°	996.5	5.3
60°-70°	648.6	3.4
70°-80°	333.9	1.8
80°-90°	97.1	0.5
90°-100°	258.2	1.4
100°-110°	820.5	4.3
110°-120°	1404.2	7.4
120°-130°	1846.7	9.8
130°-140°	2072.8	11.0
140°-150°	2032.6	10.8
150°-160°	1705.1	9.0
160°-170°	1130.8	6.0
170°-180°	395.2	2.1
0°-30°	2497.0	13.2
0°-40°	3877.5	20.5
0°-60°	6142.8	32.5
0°-90°	7222.3	38.2
90°-120°	2483.0	13.1
90°-150°	8435.1	44.7
90°-180°	11666.0	61.8
0°-180°	18888.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3335	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1920	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	4	45	123	116	120	19
95°	184	219	225	225	219	204
105°	757	768	775	781	781	799
115°	1409	1429	1423	1419	1409	1394
125°	2050	2081	2071	2060	2056	1831
135°	2651	2690	2698	2694	2684	2049
145°	3218	3244	3264	3267	3254	2011
155°	3680	3690	3702	3719	3708	1694
165°	4003	4000	4000	4025	4007	1129
175°	4166	4156	4148	4173	4152	396
180°	4173	4173	4173	4173	4173	

TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3506.0	3506.0	3506.0	3506.0	3506.0
2.5°	3521.8	3506.0	3470.9	3503.0	3496.5
5°	3506.0	3490.1	3448.8	3477.3	3467.9
7.5°	3477.3	3458.5	3414.1	3426.5	3410.7
10°	3439.3	3417.1	3353.8	3344.0	3325.2
12.5°	3391.8	3363.3	3277.4	3258.6	3223.5
15°	3334.6	3299.7	3191.9	3131.6	3100.0
17.5°	3268.0	3217.2	3083.8	3014.2	2963.4
20°	3191.9	3128.3	2969.7	2890.6	2820.6
22.5°	3109.4	3036.4	2852.2	2744.5	2697.1
25°	3027.0	2925.3	2715.9	2586.0	2538.2
27.5°	2928.7	2820.6	2589.0	2439.9	2366.8
30°	2824.0	2703.1	2449.3	2287.7	2201.9
32.5°	2722.3	2576.2	2316.3	2125.8	2046.4
35°	2608.2	2446.3	2167.2	1967.3	1897.2
37.5°	2497.1	2322.4	2027.5	1808.4	1729.3
40°	2379.6	2189.4	1881.4	1656.2	1573.8
42.5°	2259.1	2056.2	1735.6	1500.7	1421.5
45°	2132.2	1919.5	1586.5	1360.9	1284.9
47.5°	2011.7	1786.5	1443.8	1218.2	1148.6
50°	1878.4	1653.1	1304.1	1085.0	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.2
55°	1621.2	1373.8	1031.0	840.9	780.6
57.5°	1491.3	1237.5	907.6	729.8	679.0
60°	1357.9	1104.1	777.3	615.7	564.9
62.5°	1228.0	974.2	666.2	514.1	488.8
65°	1094.7	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.6	472.6	307.6	282.4	276.1
75°	583.7	361.6	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.9	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	3.8	45.3	123.3	115.7	119.5
92.5°	78.0	105.7	109.4	113.2	113.2
95°	183.7	219.0	225.2	225.2	219.0
97.5°	305.8	338.5	352.3	352.3	352.3
100°	446.7	475.6	485.6	485.6	481.8
102.5°	595.1	616.5	630.4	634.1	630.4
105°	757.4	767.5	775.1	781.3	781.3
107.5°	918.4	933.6	933.6	936.0	918.4
110°	1074.5	1094.6	1094.6	1094.6	1084.5

TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1243.0	1264.4	1260.7	1250.6	1243.0
115°	1409.1	1429.3	1423.0	1419.2	1409.1
117.5°	1574.0	1601.7	1584.0	1574.0	1563.9
120°	1740.0	1767.7	1740.0	1740.0	1728.7
122.5°	1891.0	1926.2	1908.6	1898.6	1891.0
125°	2049.6	2080.9	2070.9	2059.5	2055.8
127.5°	2204.2	2243.3	2229.4	2214.3	2204.2
130°	2348.9	2394.2	2387.9	2380.4	2366.5
132.5°	2511.2	2546.5	2549.0	2531.4	2521.3
135°	2650.9	2689.9	2697.5	2693.7	2683.6
137.5°	2806.9	2838.4	2844.7	2842.1	2827.1
140°	2944.0	2975.5	2993.1	2993.1	2979.3
142.5°	3084.9	3116.4	3126.5	3130.3	3116.4
145°	3218.3	3243.5	3263.6	3267.4	3253.6
147.5°	3337.8	3369.3	3384.4	3390.7	3376.8
150°	3461.1	3482.5	3496.4	3507.7	3496.4
152.5°	3570.6	3592.0	3609.7	3623.4	3609.7
155°	3680.1	3690.1	3701.5	3719.1	3707.8
157.5°	3774.4	3782.0	3788.3	3813.4	3795.8
160°	3858.8	3866.3	3870.1	3891.5	3876.3
162.5°	3936.7	3936.7	3940.5	3964.4	3946.8
165°	4003.4	3999.7	3999.7	4024.8	4007.2
167.5°	4063.8	4052.5	4052.5	4077.6	4060.0
170°	4109.1	4099.0	4095.3	4120.4	4099.0
172.5°	4140.6	4130.5	4126.7	4151.9	4130.5
175°	4165.8	4155.7	4148.1	4173.3	4151.9
177.5°	4179.5	4169.5	4162.0	4183.3	4162.0
180°	4173.3	4173.3	4173.3	4173.3	4173.3



TEST NUMBER: P904074

CATALOG NUMBER: DFN2DIP-SQ4F0-090D140US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.08	9.82	10.14	10.88	12.31	5.04	5.78	6.10	6.84	8.27
	3H	10.75	11.42	11.82	12.48	13.93	6.22	6.88	7.29	7.95	9.40
	4H	11.36	11.99	12.44	13.06	14.51	6.67	7.30	7.75	8.36	9.82
	6H	11.78	12.36	12.87	13.43	14.90	6.98	7.56	8.07	8.63	10.10
	8H	11.91	12.46	13.00	13.54	15.01	7.07	7.62	8.16	8.71	10.17
	12H	11.97	12.49	13.06	13.57	15.06	7.11	7.64	8.21	8.72	10.20
4H	2H	9.08	9.71	10.17	10.78	12.24	5.62	6.25	6.71	7.32	8.78
	3H	10.91	11.43	12.00	12.53	14.00	6.97	7.49	8.06	8.59	10.06
	4H	11.60	12.08	12.70	13.17	14.66	7.51	7.99	8.61	9.08	10.57
	6H	12.12	12.53	13.22	13.64	15.12	7.93	8.34	9.03	9.45	10.93
	8H	12.29	12.68	13.40	13.78	15.28	8.06	8.44	9.16	9.54	11.04
	12H	12.39	12.73	13.51	13.85	15.35	8.12	8.46	9.24	9.58	11.08
8H	4H	11.56	11.95	12.67	13.05	14.55	7.79	8.17	8.89	9.27	10.77
	6H	12.13	12.45	13.26	13.59	15.09	8.31	8.62	9.43	9.77	11.26
	8H	12.35	12.63	13.48	13.75	15.27	8.50	8.77	9.63	9.90	11.42
	12H	12.49	12.73	13.62	13.85	15.41	8.61	8.86	9.75	9.98	11.53
12H	4H	11.51	11.86	12.63	12.97	14.48	7.79	8.14	8.91	9.25	10.76
	6H	12.11	12.38	13.24	13.51	15.03	8.36	8.63	9.49	9.76	11.27
	8H	12.33	12.57	13.46	13.69	15.24	8.56	8.81	9.70	9.93	11.48